

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI> 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LEDbulbs

Versions



LEDclassic 60W A60 E27 CL
WGD90 SRT4 1





LEDclassic 60W G93 E27 CL
WGD90 1PF 4 1



LEDclassic 60W ST64 E27 CL
WGD90 SRT4 1

Dimensional drawing




Product	D	C
LEDclassic 60W A60 2700K E27 D CL AU	60 mm	104 mm

Product	D	C
LEDclassic 60W ST64 2700K E27 D CL AU	64 mm	140 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LEDclassic 60W G93 2700K E27 D CL AU	95 mm	137 mm

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	15,000 hour(s)
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	90
Color Code	927
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	806 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	60 W
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Consumption kWh/1000 h	6 kWh

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929003010379	LEDclassic 60W A60 2700K E27 D CL AU	A60
929003010979	LEDclassic 60W G93 2700K E27 D CL AU	G93
929003010779	LEDclassic 60W ST64 2700K E27 D CL AU	ST64

Classic filament LEDbulbs

