



Create a vintage look while saving money with LED technology

Classic filament LEDbulbs

Philips LED vintage-style lamps allow you to maintain a warm, classic light effect while providing longer life and energy savings.

Benefits

- Greater than 80% energy savings when compared to conventional equivalents
- 5 times the lifetime when compared to conventional equivalents (15,000 hrs)
- Light distribution and color which replicates the effect of standard, vintage-style incandescent lamps
- Provides a warm, cozy light effect even at maximum brightness
- Some products feature an amber finish to increase the decorative effect when in use and also when turned off

Features

- A variety of aesthetically pleasing, classic lamp shapes
- Integrates a compact driver design to achieve the decorative look and feel
- Instant on
- Certain models feature smooth (and deeper) dimming
- Select models are UL wet rated for outdoor usage

Classic filament LEDbulbs

Application


- Use inside with clear pendants, table or floor lamps for a classic interior design
- UL wet rated models can be used outside on string lights over a patio or pergola, in a marquee, or install them in outdoor fixtures with a medium base

Versions



Single Contact Medium Screw A19
(A19) Frosted

Dimensional drawing



Product	D	C
5A19/PER/927-22/FR/G/WGX 4/2FB T20	2-3/8 in	4-1/4 in



Classic filament LEDbulbs

