

Classic LEDbulbs lamps for decorative lighting

Classic filament LEDbulbs

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI > 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels





Classic filament LEDbulbs

Versions



Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LEDClassic 40W Diamond E27 2700K CL D	112 mm	142 mm


Product	D	C
LEDClassic 4-35W A60 E27 825 CL _G NDAPR	60 mm	106 mm

Product	D	C
LED CLA giant 25W E27 G200 pink DIM	200 mm	283 mm
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm


Product	D	C
LED classic 25W G93 E27 pink D 1PF/4	95 mm	140 mm
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm

Classic filament LEDbulbs


Dimensional drawing




Product	D	C
LED classic 25W ST64 E27 pink D SRT4	64 mm	140 mm



Product	D	C
LEDClassic 6W G120 E27 830 CLND1PF/6	125 mm	178 mm







Product	D	C
LED giant 20W E27 A160 1800K smoky D	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm



Product	D	C
LED giant crystal 26W E27 smoky DIM	103 mm	366 mm

Classic filament LEDbulbs

Dimensional drawing



Product	D	C
LED giant 20W E27 T65 1800K smoky D	66 mm	273 mm
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm

Product	D	C
LED double layers 20W E27 smoky DIM	202 mm	293 mm

Product	D	C
LEDClassic 40W Mushroom E27 1800K GOLD D	202 mm	188 mm

Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm

Classic filament LEDbulbs

Operating and electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
General information	
Cap-Base	E27
Light technical	
Colour Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001935701	LEDClassic 40W Diamond E27 2700K CL D	5 kWh
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	- kWh
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	- kWh
929002453701	LED classic 25W ST64 E27 pink D SRT4	5 kWh
929002453801	LED classic 25W G93 E27 pink D 1PF/4	5 kWh
929002453901	LED CLA giant 25W E27 G200 pink DIM	5 kWh
929002982301	LED double layers 20W E27 smoky DIM	7 kWh
929002982401	LED giant crystal 26W E27 smoky DIM	7 kWh
929002982501	LED giant 20W E27 A160 1800K smoky D	7 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002982601	LED giant 20W E27 G200 1800K smoky D	7 kWh
929002982701	LED giant 20W E27 T65 1800K smoky D	7 kWh
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	4 kWh
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	4 kWh
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	7 kWh
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	7 kWh
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	7 kWh
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	6 kWh

Controls and dimming

Order Code	Full Product Name	Dimmable
929001935701	LEDClassic 40W Diamond E27 2700K CL D	Only with specific dimmers
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	No
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	No
929002453701	LED classic 25W ST64 E27 pink D SRT4	Yes
929002453801	LED classic 25W G93 E27 pink D 1PF/4	Yes
929002453901	LED CLA giant 25W E27 G200 pink DIM	Yes
929002982301	LED double layers 20W E27 smoky DIM	Yes
929002982401	LED giant crystal 26W E27 smoky DIM	Yes
929002982501	LED giant 20W E27 A160 1800K smoky D	Yes

Order Code	Full Product Name	Dimmable
929002982601	LED giant 20W E27 G200 1800K smoky D	Yes
929002982701	LED giant 20W E27 T65 1800K smoky D	Yes
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	Only with specific dimmers
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	Yes
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Yes
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Yes
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Yes
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	No

Operating and electrical

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Nom)
929001935701	LEDClassic 40W Diamond E27 2700K CL D	220-240 V	40 W	5 W
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	100-240 V	35 W	4 W
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	220-240 V	50 W	6 W
929002453701	LED classic 25W ST64 E27 pink D SRT4	220-240 V	25 W	4.5 W

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Nom)
929002453801	LED classic 25W G93 E27 pink D 1PF/4	220-240 V	25 W	4.5 W
929002453901	LED CLA giant 25W E27 G200 pink DIM	220-240 V	25 W	4.5 W
929002982301	LED double layers 20W E27 smoky DIM	220-240 V	20 W	6.5 W
929002982401	LED giant crystal 26W E27 smoky DIM	220-240 V	26 W	7 W

Classic filament LEDbulbs

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Nom)
929002982501	LED giant 20W E27 A160 1800K smoky D	220-240 V	20 W	6.5 W
929002982601	LED giant 20W E27 G200 1800K smoky D	220-240 V	20 W	6.5 W
929002982701	LED giant 20W E27 T65 1800K smoky D	220-240 V	20 W	6.5 W
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	220-240 V	25 W	4 W
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	220-240 V	25 W	4 W

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Nom)
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	220-240 V	40 W	7 W
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	220-240 V	40 W	7 W
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	220-240 V	40 W	7 W
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	220-240 V	40 W	5.5 W

General information

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
929001935701	LEDClassic 40W Diamond E27 2700K CL D	15000 h	20,000X
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	15000 h	20000
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	10000 h	20000
929002453701	LED classic 25W ST64 E27 pink D SRT4	15000 h	20,000X
929002453801	LED classic 25W G93 E27 pink D 1PF/4	15000 h	20,000X
929002453901	LED CLA giant 25W E27 G200 pink DIM	15000 h	20,000X
929002982301	LED double layers 20W E27 smoky DIM	15000 h	20,000X
929002982401	LED giant crystal 26W E27 smoky DIM	15000 h	20,000X
929002982501	LED giant 20W E27 A160 1800K smoky D	15000 h	20,000X

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
929002982601	LED giant 20W E27 G200 1800K smoky D	15000 h	20,000X
929002982701	LED giant 20W E27 T65 1800K smoky D	15000 h	20,000X
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	15000 h	20000
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	15000 h	20,000X
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	15000 h	20,000X
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	15000 h	20,000X
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	15000 h	20,000X
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	15000 h	20,000X

Light technical

Order Code	Full Product Name	Beam Angle	Colour Code	Correlated Colour Temperature (Nom)	Luminous Flux (Nom)
		(Nom)			
929001935701	LEDClassic 40W Diamond E27 2700K CL D	-	827	2700 K	500 lm
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	-	825	2500 K	400 lm
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	270 °	830	3000 K	570 lm
929002453701	LED classic 25W ST64 E27 pink D SRT4	-	818	1800 K	250 lm

Order Code	Full Product Name	Beam Angle	Colour Code	Correlated Colour Temperature (Nom)	Luminous Flux (Nom)
		(Nom)			
929002453801	LED classic 25W G93 E27 pink D 1PF/4	-	818	1800 K	250 lm
929002453901	LED CLA giant 25W E27 G200 pink DIM	-	818	1800 K	270 lm
929002982301	LED double layers 20W E27 smoky DIM	-	818	1800 K	200 lm
929002982401	LED giant crystal 26W E27 smoky DIM	-	818	1800 K	270 lm
929002982501	LED giant 20W E27 A160 1800K smoky D	-	818	1800 K	200 lm

Classic filament LEDbulbs

Order Code	Full Product Name	Beam	Colour Code	Correlated	Luminous Flux (Nom)
		Angle (Nom)		Colour Temperature (Nom)	
929002982601	LED giant 20W E27 G200 1800K smoky D	-	818	1800 K	200 lm
929002982701	LED giant 20W E27 T65 1800K smoky D	-	818	1800 K	200 lm
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	-	818	1800 K	250 lm
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	-	818	1800 K	250 lm
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	-	818	1800 K	470 lm

Order Code	Full Product Name	Beam	Colour Code	Correlated	Luminous Flux (Nom)
		Angle (Nom)		Colour Temperature (Nom)	
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	-	818	1800 K	470 lm
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	-	818	1800 K	470 lm
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	-	818	1800 K	470 lm

Mechanical and housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001935701	LEDClassic 40W Diamond E27 2700K CL D	Clear	Others
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	Transparent Amber	A60
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	Clear	G120
929002453701	LED classic 25W ST64 E27 pink D SRT4	Pink	ST19
929002453801	LED classic 25W G93 E27 pink D 1PF/4	Pink	G93
929002453901	LED CLA giant 25W E27 G200 pink DIM	Pink	G200
929002982301	LED double layers 20W E27 smoky DIM	smoky	Double layers
929002982401	LED giant crystal 26W E27 smoky DIM	smoky	Crystal
929002982501	LED giant 20W E27 A160 1800K smoky D	smoky	A160
929002982601	LED giant 20W E27 G200 1800K smoky D	smoky	G200

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002982701	LED giant 20W E27 T65 1800K smoky D	smoky	T65
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	Amber	ST64
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	Amber	G93
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	Amber	A160
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	Amber	G200
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	Amber	T65
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	Amber	Others










Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001935701	LEDClassic 40W Diamond E27 2700K CL D	35 °C
929001941508	LEDClassic 4-35W A60 E27 825 CL _G NDAPR	52 °C
929001975142	LEDClassic 6W G120 E27 830 CLND1PF/6	40 °C
929002453701	LED classic 25W ST64 E27 pink D SRT4	40 °C
929002453801	LED classic 25W G93 E27 pink D 1PF/4	40 °C
929002453901	LED CLA giant 25W E27 G200 pink DIM	40 °C
929002982301	LED double layers 20W E27 smoky DIM	30 °C
929002982401	LED giant crystal 26W E27 smoky DIM	35 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929002982501	LED giant 20W E27 A160 1800K smoky D	45 °C
929002982601	LED giant 20W E27 G200 1800K smoky D	45 °C
929002982701	LED giant 20W E27 T65 1800K smoky D	45 °C
929002982901	LED classic 25W ST64 E27GOLD SP D RFSRT4	35 °C
929002983001	LED classic 25W G93 E27 GOLD SP D SRT4	35 °C
929002983501	LED classic-giant 40W E27 A160 GOLD DIM	45 °C
929002983601	LED classic-giant 40W E27 G200 GOLD DIM	45 °C
929002983701	LED classic-giant 40W E27 T65 GOLD DIM	45 °C

Classic filament LEDbulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
929002984001	LEDClassic 40W Mushroom E27 1800K GOLD D	35 °C



Classic filament LEDbulbs

