

Lămpi cu becuri LEDbulbs clasice pentru iluminat decorativ

Becuri LEDbulbs clasice cu filament

Disponând de un design clasic tradițional, becurile LEDbulbs clasice cu filament combină formele familiare ale becurilor clasice cu incandescență cu avantajele tehnologiei LED cu durată mare de viață. Acestea oferă lumină albă caldă atrăgătoare, decorativă, în același timp reducând consumul de energie cu aproximativ 90% în comparație cu becurile tradiționale.

Beneficii

- Reducere a consumului de energie cu aproximativ 90%
- Durată de viață foarte lungă, care reduce necesitatea înlocuirii
- Înlocuire ușoară a lămpilor clasice convenționale

Caracteristici

- Designul tradițional cu formă clasică
- Cu un design atrăgător, arată bine indiferent dacă sunt stinse sau aprinse
- Potrivire perfectă și finisaj de înaltă calitate
- Redare superioară a culorii (CRI > 80) pentru culori vii
- Ecologice: nu conțin mercur sau alte substanțe periculoase

Cerere

- Perfecte pentru instalații decorative
- Aplicații casnice
- Industria hotelieră: restaurante și hoteluri

Becuri LEDbulbs clasice cu filament

Versions



LEDclassic G93 G95 E27 POS2



CLA LEDbulb 60W E27 827 CL G93




LEDclassic A60 E27 smoky POS2



LEDclassic T32 E27 smoky POS2



Bulb G95 230V 5W-25W 250lm
2000K E27 D



LEDbulb classic-giant 40W E27
G200 GOLD DIM



LEDclassic giant 28W E27 G200
GOLD ND



25W E27 G200

Becuri LEDbulbs clasice cu filament

Versions



LEDbulb classic-giant 40W E27
T65 GOLD DIM




LEDclassic ST64 E27 smoky POS2



LEDbulb classic-giant 40W E27
A160 GOLD DIM




LEDclassic giant 28W E27 A160
GOLD ND



LEDbulb G93 E27 smoky







25W E27 T65



25W E27 A160

Becuri LEDbulbs clasice cu filament

Cote



Product	D	C
LEDclassic 11W A60 E27 smoky ND RFSRT4	60 mm	106 mm





Product	D	C
LED classic 60W G93 E27 WW CL ND 1PF	95 mm	140 mm

Product	D	C
LED classic-giant 28W E27 A160 GOLD ND	162 mm	293 mm
LED classic-giant 40W E27 A160 GOLD DIM	162 mm	293 mm
LED giant 20W E27 A160 1800K smoky D	162 mm	293 mm

Product	D	C
LED classic-giant 28W E27 G200 GOLD ND	202 mm	286 mm
LED classic-giant 40W E27 G200 GOLD DIM	202 mm	286 mm
LED giant 20W E27 G200 1800K smoky D	202 mm	286 mm

Becuri LEDbulbs clasice cu filament

Cote



Product	D	C
LED classic 120W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 120W A67 E27 CW FR NDRF1SRT4	70 mm	121 mm
LED classic 120W A67 E27 WW FR NDRFSRT4	70 mm	121 mm
LED classic 150W A67 E27 CDL FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 CW FR ND 1SRT4	70 mm	121 mm
LED classic 150W A67 E27 WW FR NDRFSRT4	70 mm	121 mm





Product	D	C
LED classic-giant 40W E27 T65 GOLD DIM	66 mm	273 mm
LED giant 20W E27 T65 1800K smoky D	66 mm	273 mm

Product	D	C
LED classic 25W G93 E27 GOLD SP D SRT4	96 mm	143 mm
LED classic 60W G93 E27 WW FR ND RFSRT4	95 mm	140 mm

Product	D	C
LED classic 100W A60 CW FR ND 1CT/10	60 mm	104 mm
LED classic 100W A60 WW FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 CW A60 FR ND 1CT/10	60 mm	104 mm
LED classic 75W E27 WW A60 FR ND 1CT10	60 mm	104 mm

Becuri LEDbulbs clasice cu filament

Cote



Product	D	C
LED classic 200W A95 E27 CDL FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 CW FR ND 1PF/4	95 mm	165 mm
LED classic 200W A95 E27 WW FR ND 1PF	95 mm	165 mm


Product	D	C
LED classic 11W G93 E27 smoky ND RF 1PF	95 mm	142 mm

Product	D	C
LED cla 120W G120 E27 WW FR ND RFSRT4	124 mm	177 mm
LED classic 75W G120 E27 WW FR ND SRT4	125 mm	177 mm

Product	D	C
LEDclassic 11W ST64 E27 smoky ND RFSRT4	64 mm	143 mm

Becuri LEDbulbs clasice cu filament

Cote



Product	D	C
LED classic 11W T32 E27 smoky ND RFSRT4	32 mm	140 mm

Informații generale

Baza elementului de fixare	E27
Durată de viață nominală (ore)	15.000 ore
Ciclu de comutare	20.000
Durată de viață nominală	15.000 ore

Date tehnice lumină

Indice de redare a culorilor (IRC)	80
Factorul de menținere a fluxului luminos al lămpii la sfârșitul duratei de viață nominale (nom.)	70 %

Funcționare și sistem electric

Frecvență de intrare	De la 50 până la 60 Hz
Frecvență linie	50 to 60 Hz
Timp de pornire (nom.)	0,5 s

Date tehnice lumină

Order Code	Full Product Name	Unghi de distribuție luminoasă (nom.)	Temperatură de culoare corelată (nom.)	Cod culoare	Flux luminos
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	6500 K	865	2.000 lm
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	-	2700 K	827	2.452 lm
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	-	4000 K	840	2.452 lm
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	6500 K	865	2.452 lm
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	-	2700 K	827	806 lm
74245700	LED classic 60W G93 E27 WW CL ND 1PF	-	2700 K	827	806 lm
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	-	2700 K	827	1.055 lm
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-	4000 K	840	1.055 lm
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	330 °	1800 K	818	250 lm
31378100	LED classic-giant 40W E27 G200 GOLD DIM	330 °	1800 K	818	470 lm
31384200	LED classic-giant 28W E27 G200 GOLD ND	330 °	1800 K	818	300 lm
76463000	LED classic 200W A95 E27 WW FR ND 1PF	-	2700 K	827	3.452 lm
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	-	4000 K	840	3.452 lm
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	6500 K	865	3.452 lm

Becuri LEDbulbs clasice cu filament

Order Code	Full Product Name	Unghi de distribuție luminoasă (nom.)	Temperatură de culoare corelată (nom.)	Cod culoare	Flux luminos
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	-	2700 K	827	2.000 lm
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	-	4000 K	840	2.000 lm
70416200	LED classic 100W A60 WW FR ND 1CT/10	-	2700 K	827	1.521 lm
70414800	LED classic 100W A60 CW FR ND 1CT/10	-	4000 K	840	1.521 lm
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	2700 K	827	1.055 lm
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-	2700 K	827	2.000 lm
31539600	LED giant 20W E27 G200 1800K smoky D	300 °	1800 K	818	200 lm
31380400	LED classic-giant 40W E27 T65 GOLD DIM	330 °	1800 K	818	470 lm
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	-	1800 K	818	100 lm
31376700	LED classic-giant 40W E27 A160 GOLD DIM	330 °	1800 K	818	470 lm
31382800	LED classic-giant 28W E27 A160 GOLD ND	330 °	1800 K	818	300 lm
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	-	1800 K	818	100 lm
31541900	LED giant 20W E27 T65 1800K smoky D	300 °	1800 K	818	200 lm
31537200	LED giant 20W E27 A160 1800K smoky D	-	1800 K	818	200 lm

Funcționare și sistem electric

Order Code	Full Product Name	Consum de curent	Echivalent putere	Order Code	Full Product Name	Consum de curent	Echivalent putere
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	13 W	120 W	75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	2,3 W	11 W
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	17,5 W	150 W	75967400	LED classic 11W T32 E27 smoky ND RFSRT4	2,3 W	11 W
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	17,5 W	150 W	31547100	LED classic 25W G93 E27 GOLD SP D SRT4	4 W	25 W
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	17,5 W	150 W	31378100	LED classic-giant 40W E27 G200 GOLD DIM	7 W	40 W
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	7 W	60 W	31384200	LED classic-giant 28W E27 G200 GOLD ND	4,5 W	28 W
74245700	LED classic 60W G93 E27 WW CL ND 1PF	7 W	60 W	76463000	LED classic 200W A95 E27 WW FR ND 1PF	23 W	200 W
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	8,5 W	75 W	76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	23 W	200 W
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	8,5 W	75 W	76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	23 W	200 W

Becuri LEDbulbs clasice cu filament

Order Code	Full Product Name	Consum de curent	Echivalent putere
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	13 W	120 W
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	13 W	120 W
70416200	LED classic 100W A60 WW FR ND 1CT/10	10,5 W	100 W
70414800	LED classic 100W A60 CW FR ND 1CT/10	10,5 W	100 W
76475300	LED classic 75W G120 E27 WW FR ND SRT4	8,5 W	75 W
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 W	120 W
31539600	LED giant 20W E27 G200 1800K smoky D	6,5 W	20 W

Order Code	Full Product Name	Consum de curent	Echivalent putere
31380400	LED classic-giant 40W E27 T65 GOLD DIM	7 W	40 W
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	2,3 W	11 W
31376700	LED classic-giant 40W E27 A160 GOLD DIM	7 W	40 W
31382800	LED classic-giant 28W E27 A160 GOLD ND	4,5 W	28 W
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	2 W	11 W
31541900	LED giant 20W E27 T65 1800K smoky D	6,5 W	20 W
31537200	LED giant 20W E27 A160 1800K smoky D	6,5 W	20 W

Temperatură

Order Code	Full Product Name	Interval temperatură ambientală	Maximum T-case (nom.)
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	-	60 °C
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	-	60 °C
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	-	60 °C
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	-	60 °C
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	-	45 °C
74245700	LED classic 60W G93 E27 WW CL ND 1PF	-	45 °C
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	-	50 °C
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	-	50 °C
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	De la -20 până la +40 °C	40 °C
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	De la -20 până la +40 °C	40 °C
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	De la -20 până la +45 °C	35 °C
31378100	LED classic-giant 40W E27 G200 GOLD DIM	De la -20 până la +45 °C	45 °C
31384200	LED classic-giant 28W E27 G200 GOLD ND	De la -20 până la +45 °C	45 °C
76463000	LED classic 200W A95 E27 WW FR ND 1PF	-	55 °C
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	-	55 °C

Order Code	Full Product Name	Interval temperatură ambientală	Maximum T-case (nom.)
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	-	55 °C
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	-	60 °C
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	-	60 °C
70416200	LED classic 100W A60 WW FR ND 1CT/10	-	55 °C
70414800	LED classic 100W A60 CW FR ND 1CT/10	-	55 °C
76475300	LED classic 75W G120 E27 WW FR ND SRT4	-	50 °C
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	-	55 °C
31539600	LED giant 20W E27 G200 1800K smoky D	De la -20 până la +45 °C	45 °C
31380400	LED classic-giant 40W E27 T65 GOLD DIM	De la -20 până la +45 °C	45 °C
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	De la -20 până la +40 °C	40 °C
31376700	LED classic-giant 40W E27 A160 GOLD DIM	De la -20 până la +45 °C	45 °C
31382800	LED classic-giant 28W E27 A160 GOLD ND	De la -20 până la +45 °C	45 °C
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	De la -20 până la +40 °C	40 °C
31541900	LED giant 20W E27 T65 1800K smoky D	De la -20 până la +45 °C	45 °C
31537200	LED giant 20W E27 A160 1800K smoky D	De la -20 până la +45 °C	45 °C

Sisteme de comandă și reglarea intensității luminoase

Becuri LEDbulbs clasice cu filament

Order Code	Full Product Name	Cu reglarea intensității luminoase
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	Nu
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	Nu
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	Nu
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	Nu
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	Nu
74245700	LED classic 60W G93 E27 WW CL ND 1PF	Nu
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	Nu
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	Nu
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	Nu
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	Nu
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Numai cu anumite variatoare
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Numai cu anumite variatoare
31384200	LED classic-giant 28W E27 G200 GOLD ND	Nu
76463000	LED classic 200W A95 E27 WW FR ND 1PF	Nu
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	Nu
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	Nu
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	Nu

Order Code	Full Product Name	Cu reglarea intensității luminoase
76453100	LED classic 120W A67 E27 CW FR NDRF1SRT4	Nu
70416200	LED classic 100W A60 WW FR ND 1CT/10	Nu
70414800	LED classic 100W A60 CW FR ND 1CT/10	Nu
76475300	LED classic 75W G120 E27 WW FR ND SRT4	Nu
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	Nu
31539600	LED giant 20W E27 G200 1800K smoky D	Numai cu anumite variatoare
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Numai cu anumite variatoare
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	Nu
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Numai cu anumite variatoare
31382800	LED classic-giant 28W E27 A160 GOLD ND	Nu
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	Nu
31541900	LED giant 20W E27 T65 1800K smoky D	Numai cu anumite variatoare
31537200	LED giant 20W E27 A160 1800K smoky D	Numai cu anumite variatoare

Sistem mecanic și carcasă

Order Code	Full Product Name	Finisaj bec	Formă bec
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	Mat	A67
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	Mat	A67
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	Mat	A67
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	Mat	A67
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	Mat	G93
74245700	LED classic 60W G93 E27 WW CL ND 1PF	Transparent	G93
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	Mat	A60
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	Mat	A60
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	fumuriu	A60
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	fumuriu	T32
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	Chihlimbar	G93
31378100	LED classic-giant 40W E27 G200 GOLD DIM	Chihlimbar	G200
31384200	LED classic-giant 28W E27 G200 GOLD ND	Chihlimbar	G200
76463000	LED classic 200W A95 E27 WW FR ND 1PF	Mat	A95
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	Mat	A95

Order Code	Full Product Name	Finisaj bec	Formă bec
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	Mat	A95
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	Mat	A67
76453100	LED classic 120W A67 E27 CW FR NDRF1SRT4	Mat	A67
70416200	LED classic 100W A60 WW FR ND 1CT/10	Mat	A60
70414800	LED classic 100W A60 CW FR ND 1CT/10	Mat	A60
76475300	LED classic 75W G120 E27 WW FR ND SRT4	Mat	G120
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	Mat	G120
31539600	LED giant 20W E27 G200 1800K smoky D	fumuriu	G200
31380400	LED classic-giant 40W E27 T65 GOLD DIM	Chihlimbar	T65
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	fumuriu	ST64
31376700	LED classic-giant 40W E27 A160 GOLD DIM	Chihlimbar	A160
31382800	LED classic-giant 28W E27 A160 GOLD ND	Chihlimbar	A160
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	fumuriu	G93
31541900	LED giant 20W E27 T65 1800K smoky D	fumuriu	T65
31537200	LED giant 20W E27 A160 1800K smoky D	fumuriu	A160









Aprobare și aplicație

Order Code	Full Product Name	Consum de energie kWh/1000 h
76455500	LED classic 120W A67 E27 CDL FR ND 1SRT4	13 kWh
76457900	LED classic 150W A67 E27 WW FR NDRFSRT4	18 kWh
76459300	LED classic 150W A67 E27 CW FR ND 1SRT4	18 kWh
76461600	LED classic 150W A67 E27 CDL FR ND 1SRT4	18 kWh
76469200	LED classic 60W G93 E27 WW FR ND RFSRT4	7 kWh
74245700	LED classic 60W G93 E27 WW CL ND 1PF	7 kWh
70555100	LED classic 75W E27 WW A60 FR ND 1CT10	9 kWh











Order Code	Full Product Name	Consum de energie kWh/1000 h
70561200	LED classic 75W E27 CW A60 FR ND 1CT/10	9 kWh
75963600	LEDclassic 11W A60 E27 smoky ND RFSRT4	3 kWh
75967400	LED classic 11W T32 E27 smoky ND RFSRT4	3 kWh
31547100	LED classic 25W G93 E27 GOLD SP D SRT4	4 kWh
31378100	LED classic-giant 40W E27 G200 GOLD DIM	7 kWh
31384200	LED classic-giant 28W E27 G200 GOLD ND	5 kWh
76463000	LED classic 200W A95 E27 WW FR ND 1PF	23 kWh

Becuri LEDbulbs clasice cu filament

Order Code	Full Product Name	Consum de energie kWh/ 1000 h
76465400	LED classic 200W A95 E27 CW FR ND 1PF/4	23 kWh
76467800	LED classic 200W A95 E27 CDL FR ND 1PF/4	23 kWh
76451700	LED classic 120W A67 E27 WW FR NDRFSRT4	13 kWh
76453100	LED classic 120W A67 E27 CW FR NDRFISRT4	13 kWh
70416200	LED classic 100W A60 WW FR FR ND 1CT/10	11 kWh
70414800	LED classic 100W A60 CW FR ND 1CT/10	11 kWh
76475300	LED classic 75W G120 E27 WW FR ND SRT4	9 kWh
76481400	LED cla 120W G120 E27 WW FR ND RFSRT4	13 kWh
31539600	LED giant 20W E27 G200 1800K smoky D	7 kWh
31380400	LED classic-giant 40W E27 T65 GOLD DIM	7 kWh
75965000	LEDclassic 11W ST64 E27 smoky ND RFSRT4	3 kWh
31376700	LED classic-giant 40W E27 A160 GOLD DIM	7 kWh
31382800	LED classic-giant 28W E27 A160 GOLD ND	5 kWh
75969800	LED classic 11W G93 E27 smoky ND RF 1PF	2 kWh
31541900	LED giant 20W E27 T65 1800K smoky D	7 kWh
31537200	LED giant 20W E27 A160 1800K smoky D	7 kWh



Becuri LEDbulbs clasice cu filament



Becuri LEDbulbs clasice cu filament

