



Philips TrueLine suspended: True line of light

TrueLine, suspended

Architects need a lighting solution that matches the interior architecture of the space they are enhancing. They want a light line with elegant proportions and high light levels that offers maximum design freedom. Philips TrueLine is a flexible linear luminaire for indoor office applications that offers excellent quality with the promise of future-proof upgrades. Specifiers need luminaires that save energy, at the same time as providing the right level of light. TrueLine recessed meets both these sets of requirements. Not only is it compliant with the WELL Building Standard for Light, TrueLine surface is rated UGR<19, which is compliant with all office norms (OC). TrueLine also comes in surface and recess-mounted versions. All the luminaires in the family are available in different lengths, shapes, colors and light outputs. This offers the ultimate design flexibility and unlimited possibilities. TrueLine luminaires are also a sustainable, future-proof choice with high efficiency up to 140 lm/W and the option to upgrade to wireless connectivity and control.

Benefits

- Extremely high efficacy for a line luminaire
- Office compliant lighting
- Future-ready, scalable smart office capabilities
- Compatible with the Interact connected lighting system
- Supports sustainable building design and energy-saving subsidy criteria

TrueLine, suspended

Features

- Highly-uniform lighting with excellent glare control ($UGR < 19$, $L65 < 3000 \text{cd/m}^2$)
- Best-in-class efficacy up to 140 lm/W
- 3000K, 4000K, and Tunable White versions, all CRI > 90
- Long lifetime L90@50,000 hours
- Integrated sensors/wireless drivers for data collection, occupancy, daylight regulation and wayfinding
- Environmental Product Declaration (EPD)
- Recessed, suspended and surface mounted options, including all accessories

Application

- Offices
- Education
- Retail

Warnings and Safety

- The product is IPX0 and, as such, is not protected against water ingress. Therefore, we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure and the product warranty will become void.

Versions



TrueLine-Suspended-line-LE



TrueLine-SP534P



SP530P with U4 BK sensor



TrueLine-SP530 L2810 BK



TrueLine-SP530 U3 SNS210 L2850 Alu




SP530P with U4 BK sensor




TrueLine-SP530 L570 Alu

Dimensional drawing



Dimensional drawing



TrueLine, suspended

Product details



TrueLine_Suspended-line-side-view



TrueLine_Suspended-line-top-view



TrueLine Suspended black housing



TrueLine_Suspended-top-view



TrueLine_Suspended-U3



TrueLine_Suspended-U0



TrueLine Suspended-SP530P-LF-power-cable-03



TrueLine-SP-line-U3

Product details



TrueLine Suspended black housing



SP530P U4 BK DPP



TrueLine_SM_SP-line-connection-side-view-2

General Information	
CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Light Technical	
Beam angle of light source	120 degree(s)
Color rendering index (CRI)	>90
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Operating and Electrical	
Line Frequency	50 to 60 Hz
Temperature	
Ambient temperature range	+10 to +40 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Initial chromaticity	(0.38, 0.38) SDCM <3
Luminous flux tolerance	+/-10%
Application Conditions	
Maximum dim level	1%
Suitable for random switching	No

General Information

Order Code	Full Product Name	Number of gear units	Product family code
97252000	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
97272800	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	1 unit	SP534P
97240700	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP532P
97274200	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	1 unit	SP534P
97282700	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	1 unit	SP530P
97284100	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	1 unit	SP532P
97270400	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
97246900	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
97236000	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
97254400	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
97226100	SP530P LED25S/940 POE SW2 L1130 ALU	1 unit	SP530P
97237700	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP531P
97233900	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP530P
97265000	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
97250600	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
97260500	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
97227800	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
97267400	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
97258200	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
97264300	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
97251300	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	1 unit	SP532P
97268100	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	1 unit	SP533P
97273500	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP534P
97266700	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP533P
97239100	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
97269800	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
97245200	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
97261200	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP532P
97271100	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP533P
97259900	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP532P
97262900	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
97256800	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	1 unit	SP532P
97235300	SP530P LED31S/940 POE U3 SW2 L1450 ALU	1 unit	SP530P
97230800	SP530P LED40S/940 POE U3 SW2 L1170 ALU	1 unit	SP530P
97229200	SP530P LED40S/940 POE U0 SW2 L1170 ALU	1 unit	SP530P
97234600	SP530P LED43S/940 POE U0 SW2 L1450 ALU	1 unit	SP530P
97231500	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	1 unit	SP530P
97276600	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	1 unit	SP534P
97317600	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	2 units	SP532P
97281000	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	1 unit	SP531P
97285800	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	1 unit	SP533P
97292600	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	1 unit	SP530P
97318300	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	2 units	SP530P
97319000	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	2 units	SP532P
97293300	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	1 unit	SP531P
97296400	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP532P
97297100	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
97299500	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	1 unit	SP533P
97305300	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP530P
97309100	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP532P
97310700	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	1 unit	SP533P

Order Code	Full Product Name	Number of gear units	Product family code
97294000	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP530P
97298800	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	1 unit	SP532P
97306000	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	1 unit	SP530P
97280300	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	1 unit	SP530P
97283400	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	1 unit	SP532P
97295700	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	1 unit	SP530P
97307700	SP531P LED62S/930 PSD PI5 SM2L2810 WH	1 unit	SP531P
97308400	SP532P LED94S/940 PSD PI5 SM2L2810 WH	1 unit	SP532P
97255100	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	1 unit	SP532P
97238400	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	1 unit	SP531P
97228500	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	1 unit	SP530P
97243800	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
97244500	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	1 unit	SP532P
97249000	SP532P LED36S/940 PSD LF2 PI5SM TTL1130BK	1 unit	SP532P
97241400	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
97248300	SP532P LED36S/940 PSD LF2 PI5SM TTL1130AL	1 unit	SP532P
97242100	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	1 unit	SP532P
97275900	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP534P
97253700	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	1 unit	SP532P
97247600	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	1 unit	SP532P
97315200	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	1 unit	SP532P
97316900	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	2 units	SP533P
97257500	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P
97232200	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	1 unit	SP530P
97263600	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	1 unit	SP532P

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97252000	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97272800	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	4000 K	131 lm/W	3,400 lm	Asymmetrical mirror
97240700	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	4000 K	138 lm/W	2,900 lm	Wide beam
97274200	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
97282700	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	4000 K	139 lm/W	1,700 lm	Wide beam
97284100	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	3000 K	132 lm/W	2,450 lm	Wide beam
97270400	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	4000 K	115 lm/W	4,100 lm	Wide beam
97246900	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	2,900 lm	Wide beam
97236000	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	4000 K	139 lm/W	5,000 lm	Wide beam
97254400	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97226100	SP530P LED25S/940 POE SW2 L1130 ALU	4000 K	149 lm/W	2,500 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97237700	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	4000 K	104 lm/W	1,500 lm	Wide beam
97233900	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	4000 K	141 lm/W	4,300 lm	Wide beam
97265000	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	4000 K	135 lm/W	7,700 lm	Wide beam
97250600	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	4000 K	136 lm/W	3,600 lm	Wide beam
97260500	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	4000 K	133 lm/W	5,800 lm	Wide beam
97227800	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	4000 K	139 lm/W	3,400 lm	Wide beam
97267400	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	3000 K	112 lm/W	3,300 lm	Wide beam
97258200	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	3000 K	129 lm/W	4,950 lm	Wide beam
97264300	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	3000 K	128 lm/W	7,700 lm	Wide beam
97251300	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	4000 K	136 lm/W	3,600 lm	Wide beam
97268100	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	3000 K	112 lm/W	3,300 lm	Wide beam
97273500	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	4000 K	129 lm/W	4,000 lm	Asymmetrical mirror
97266700	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	4000 K	116 lm/W	2,400 lm	Wide beam
97239100	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	4000 K	132 lm/W	2,100 lm	Wide beam
97269800	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	4000 K	118 lm/W	3,300 lm	Wide beam
97245200	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	2,900 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97261200	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	4000 K	138 lm/W	6,600 lm	Wide beam
97271100	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	4000 K	116 lm/W	5,400 lm	Wide beam
97259900	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	4000 K	136 lm/W	4,950 lm	Wide beam
97262900	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	6,600 lm	Wide beam
97256800	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	4000 K	138 lm/W	4,700 lm	Wide beam
97235300	SP530P LED31S/940 POE U3 SW2 L1450 ALU	4000 K	148 lm/W	3,100 lm	Wide beam
97230800	SP530P LED40S/940 POE U3 SW2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
97229200	SP530P LED40S/940 POE U0 SW2 L1170 ALU	4000 K	143 lm/W	4,000 lm	Wide beam
97234600	SP530P LED43S/940 POE U0 SW2 L1450 ALU	4000 K	143 lm/W	4,300 lm	Wide beam
97231500	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	4000 K	140 lm/W	4,000 lm	Wide beam
97276600	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	4000 K	130 lm/W	5,000 lm	Asymmetrical mirror
97317600	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Tunable white 2700-6500 K	116 lm/W	6,600 lm	Wide beam
97281000	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	4000 K	104 lm/W	750 lm	Wide beam
97285800	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	3000 K	109 lm/W	1,200 lm	Wide beam
97292600	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	3000 K	130 lm/W	3,000 lm	Wide beam
97318300	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Tunable white 2700-6500 K	125 lm/W	5,000 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux	Optic type
		(Nom)	(Nom)		
97319000	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Tunable white 2700-6500 K	121 lm/W	8,600 lm	Wide beam
97293300	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	3000 K	103 lm/W	3,000 lm	Wide beam
97296400	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	4000 K	138 lm/W	7,200 lm	Wide beam
97297100	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	4000 K	122 lm/W	4,800 lm	Wide beam
97299500	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	4000 K	119 lm/W	8,200 lm	Wide beam
97305300	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	3000 K	136 lm/W	3,800 lm	Wide beam
97309100	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	3000 K	132 lm/W	5,800 lm	Wide beam
97310700	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	3000 K	114 lm/W	6,600 lm	Wide beam
97294000	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	4000 K	139 lm/W	5,000 lm	Wide beam
97298800	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	4000 K	138 lm/W	9,800 lm	Wide beam
97306000	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	4000 K	141 lm/W	6,200 lm	Wide beam
97280300	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	4000 K	125 lm/W	750 lm	Wide beam
97283400	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	3000 K	124 lm/W	1,050 lm	Wide beam
97295700	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	3000 K	133 lm/W	5,000 lm	Wide beam
97307700	SP531P LED62S/930 PSD PI5 SM2L2810 WH	3000 K	135 lm/W	6,200 lm	Wide beam

Order Code	Full Product Name	Correlated Color Temperature	Luminous Efficacy (rated)	Luminous Flux	Optic type
		(Nom)	(Nom)		
97308400	SP532P LED94S/940 PSD PI5 SM2L2810 WH	4000 K	140 lm/W	9,400 lm	Wide beam
97255100	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	4000 K	138 lm/W	4,700 lm	Wide beam
97238400	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	4000 K	104 lm/W	1,500 lm	Wide beam
97228500	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	4000 K	139 lm/W	3,400 lm	Wide beam
97243800	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	3000 K	132 lm/W	2,900 lm	Wide beam
97244500	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	4000 K	138 lm/W	2,900 lm	Wide beam
97249000	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	4000 K	136 lm/W	3,600 lm	Wide beam
97241400	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	4000 K	138 lm/W	2,900 lm	Wide beam
97248300	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	4000 K	136 lm/W	3,600 lm	Wide beam
97242100	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	4000 K	138 lm/W	2,900 lm	Wide beam
97275900	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	4000 K	132 lm/W	4,300 lm	Asymmetrical mirror
97253700	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	4000 K	138 lm/W	4,700 lm	Wide beam
97247600	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	4000 K	136 lm/W	3,600 lm	Wide beam

TrueLine, suspended

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97315200	SP532P	Tunable	124 lm/W	3,600 lm	Wide beam
	LED36S/TW9 DIA	white			
	LF1 PI5 L1130 ALU	2700-6500 K			
97316900	SP533P	Tunable	100 lm/W	3,300 lm	Wide beam
	LED33S/TW9 DIA	white			
	LF1 PI5 L1410 ALU	2700-6500 K			
97257500	SP532P	4000 K	138 lm/W	4,700 lm	Wide beam
	LED47S/940 SRD				

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux	Optic type
97232200	U4 PI3				
	SM2L1450ALU				
97232200	SP530P	4000 K	143 lm/W	4,000 lm	Wide beam
	LED40S/940 SRD				
	U4 PI3				
97263600	SP532P	4000 K	139 lm/W	6,600 lm	Wide beam
	LED66S/940 SRD				
	U4 PI3				
	SM2L1450ALU				

Operating and Electrical

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
97252000	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	34 W
97272800	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	220 to 240 V	26 W
97240700	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	21 W
97274200	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	220 to 240 V	32.5 W
97282700	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	220 to 240 V	12.2 W
97284100	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	220 to 240 V	18.6 W
97270400	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	35.5 W
97246900	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	21 W
97236000	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	36 W
97254400	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	34 W
97226100	SP530P LED25S/940 POE SW2 L1130 ALU	51 to 54 V	16.8 W
97237700	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	14.4 W
97233900	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	30.5 W
97265000	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	57 W
97250600	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	26.5 W
97260500	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	44 W
97227800	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	24.5 W

Order Code	Full Product Name	Power	
		Input Voltage	Consumption
97267400	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V	29.5 W
97258200	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	220 to 240 V	38.5 W
97264300	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	220 to 240 V	60 W
97251300	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	220 to 240 V	26.5 W
97268100	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	220 to 240 V	29.5 W
97273500	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	31 W
97266700	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	21 W
97239100	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	16.4 W
97269800	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	28 W
97245200	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	21 W
97261200	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	48 W
97271100	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	46.5 W
97259900	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	36.5 W
97262900	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	48 W
97256800	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	220 to 240 V	34 W
97235300	SP530P LED31S/940 POE U3 SW2 L1450 ALU	51 to 54 V	21 W
97230800	SP530P LED40S/940 POE U3 SW2 L1170 ALU	51 to 54 V	28 W

Order Code	Full Product Name	Input Voltage	Power
			Consumption
97229200	SP530P LED40S/940 POE U0 SW2 L1170 ALU	51 to 54 V	28 W
97234600	SP530P LED43S/940 POE U0 SW2 L1450 ALU	51 to 54 V	30 W
97231500	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	220 to 240 V	28.5 W
97276600	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	220 to 240 V	38.5 W
97317600	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	220 to 240 V	57 W
97281000	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	220 to 240 V	7.2 W
97285800	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	220 to 240 V	11 W
97292600	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	220 to 240 V	23 W
97318300	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	220 to 240 V	40 W
97319000	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	220 to 240 V	71 W
97293300	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	220 to 240 V	29 W
97296400	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	52 W
97297100	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	39.5 W
97299500	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	220 to 240 V	69 W
97305300	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	28 W
97309100	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	44 W
97310700	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	220 to 240 V	58 W
97294000	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V	36 W
97298800	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	220 to 240 V	71 W
97306000	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	220 to 240 V	44 W
97280300	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	220 to 240 V	6 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
97252000	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
97272800	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Aluminum
97240700	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
97274200	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Aluminum
97282700	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Black RAL 9004

Order Code	Full Product Name	Input Voltage	Power
			Consumption
97283400	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	220 to 240 V	8.5 W
97295700	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	220 to 240 V	37.5 W
97307700	SP531P LED62S/930 PSD PI5 SM2L2810 WH	220 to 240 V	46 W
97308400	SP532P LED94S/940 PSD PI5 SM2L2810 WH	220 to 240 V	67 W
97255100	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	220 to 240 V	34 W
97238400	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	220 to 240 V	14.4 W
97228500	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	220 to 240 V	24.5 W
97243800	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	220 to 240 V	22 W
97244500	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	220 to 240 V	21 W
97249000	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	220 to 240 V	26.5 W
97241400	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	21 W
97248300	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	220 to 240 V	26.5 W
97242100	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	220 to 240 V	21 W
97275900	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	32.5 W
97253700	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	220 to 240 V	34 W
97247600	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	220 to 240 V	26.5 W
97315200	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	220 to 240 V	29 W
97316900	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	220 to 240 V	33 W
97257500	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V	34 W
97232200	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	220 to 240 V	28 W
97263600	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	220 to 240 V	47.5 W

TrueLine, suspended

Order Code	Full Product Name	Housing Color
97226100	SP530P LED25S/940 POE SW2 L1130 ALU	Aluminum
97237700	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97233900	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97265000	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97250600	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97260500	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97227800	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97267400	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Aluminum
97258200	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Aluminum
97264300	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Aluminum
97251300	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	White RAL 9003
97268100	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	White RAL 9003
97273500	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97266700	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97239100	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97269800	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97245200	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97261200	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97271100	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97259900	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97262900	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
97256800	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	White RAL 9003
97235300	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Aluminum
97230800	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Aluminum
97229200	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Aluminum
97234600	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Aluminum
97231500	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Aluminum
97276600	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Aluminum
97317600	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Black RAL 9004
97281000	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	White RAL 9003
97285800	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	White RAL 9003
97292600	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Black RAL 9004
97318300	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Aluminum

Order Code	Full Product Name	Housing Color
97319000	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Aluminum
97293300	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	Aluminum
97296400	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Aluminum
97297100	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Aluminum
97299500	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Aluminum
97305300	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Aluminum
97309100	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Aluminum
97310700	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Aluminum
97294000	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Black RAL 9004
97298800	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Black RAL 9004
97306000	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Black RAL 9004
97280300	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Aluminum
97283400	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Aluminum
97295700	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	White RAL 9003
97307700	SP531P LED62S/930 PSD PI5 SM2L2810 WH	White RAL 9003
97308400	SP532P LED94S/940 PSD PI5 SM2L2810 WH	White RAL 9003
97255100	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Black RAL 9004
97238400	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Black RAL 9004
97228500	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Black RAL 9004
97243800	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Black RAL 9004
97244500	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Black RAL 9004
97249000	SP532P LED36S/940 PSD LF2 PI5SM2TL1130BK	Black RAL 9004
97241400	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
97248300	SP532P LED36S/940 PSD LF2 PI5SM2TL1130AL	Aluminum
97242100	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Aluminum
97275900	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
97253700	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Aluminum
97247600	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Aluminum
97315200	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Aluminum
97316900	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Aluminum
97257500	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Aluminum
97232200	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Aluminum
97263600	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Aluminum

Approval and Application

Order Code	Full Product Name	Protection class IEC
97252000	SP532P LED47S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
97272800	SP534P LED34S/940 PSD LE1 PI5SM2L1130ALU	Safety class I
97240700	SP532P LED29S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
97274200	SP534P LED43S/940 PSD LE1 PI5SM2L1410ALU	Safety class I
97282700	SP530P LED17S/940 PSD LE2PI5 SM2 L570 BK	Safety class I
97284100	SP532P LED24S/930 PSD LE2 PI5 SM2L570 BK	Safety class I
97270400	SP533P LED41S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97246900	SP532P LED29S/940 PSD PI5 SM2 L1410 WH	Safety class I
97236000	SP530P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97254400	SP532P LED47S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97226100	SP530P LED25S/940 POE SW2 L1130 ALU	Safety class III
97237700	SP531P LED15S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97233900	SP530P LED43S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97265000	SP532P LED77S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97250600	SP532P LED36S/940 PSD PI5 SM2 L1130 ALU	Safety class I

Order Code	Full Product Name	Protection class IEC
97260500	SP532P LED58S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97227800	SP530P LED34S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97267400	SP533P LED33S/930 PSD PI5 SM2 L1410 ALU	Safety class I
97258200	SP532P LED49S/930 PSD PI5 SM2 L1130 ALU	Safety class I
97264300	SP532P LED77S/930 PSD PI5 SM2 L1410 ALU	Safety class I
97251300	SP532P LED36S/940 PSD PI5 SM2 L1130 WH	Safety class I
97268100	SP533P LED33S/930 PSD PI5 SM2 L1410 WH	Safety class I
97273500	SP534P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97266700	SP533P LED24S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97239100	SP532P LED21S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97269800	SP533P LED33S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97245200	SP532P LED29S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97261200	SP532P LED66S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97271100	SP533P LED54S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97259900	SP532P LED49S/940 PSD PI5 SM2 L1130 ALU	Safety class I

TrueLine, suspended

Order Code	Full Product Name	Protection class IEC
97262900	SP532P LED66S/940 PSD PI5 SM2 L1410 WH	Safety class I
97256800	SP532P LED47S/940 PSD PI5 SM2 L1410 WH	Safety class I
97235300	SP530P LED31S/940 POE U3 SW2 L1450 ALU	Safety class III
97230800	SP530P LED40S/940 POE U3 SW2 L1170 ALU	Safety class III
97229200	SP530P LED40S/940 POE U0 SW2 L1170 ALU	Safety class III
97234600	SP530P LED43S/940 POE U0 SW2 L1450 ALU	Safety class III
97231500	SP530P LED40S/940 PSD PI5 SM2 L1130 ALU	Safety class I
97276600	SP534P LED50S/940 PSD PI5 SM2 L1410 ALU	Safety class I
97317600	SP532P LED66S/TW9 SIA PI3 U4 L1450 BK	Safety class I
97281000	SP531P LED7S/940 PSD LE2 PI5 SM2 L570 WH	Safety class I
97285800	SP533P LED12S/930 PSD LE2 PI5 SM2L570 WH	Safety class I
97292600	SP530P LED30S/930 PSD LF1 PI5 L2250 BK	Safety class I
97318300	SP530P LED50S/TW9 SIA SM2 U4 L2290 ALU	Safety class I
97319000	SP530P LED86S/TW9 SIA SM2 U4 L2850 ALU	Safety class I
97293300	SP531P LED30S/930 SRD U4LF1PI3 L2290 ALU	Safety class I
97296400	SP532P LED72S/940 PSD PI5 SM2 L2250 ALU	Safety class I
97297100	SP533P LED48S/940 PSD PI5 SM2 L2250 ALU	Safety class I
97299500	SP533P LED82S/940 PSD PI5 SM2 L2250 ALU	Safety class I
97305300	SP530P LED38S/930 PSD LF1 PI5 L2810 ALU	Safety class I
97309100	SP532P LED58S/930 PSD LF1 PI5 L2810 ALU	Safety class I
97310700	SP533P LED66S/930 PSD LF1 PI5 L2810 ALU	Safety class I
97294000	SP530P LED50S/940 SRD U4 PI5 SM2L2290 BK	Safety class I
97298800	SP532P LED98S/940 SRD U4 PI5 SM2L2290 BK	Safety class I

Order Code	Full Product Name	Protection class IEC
97306000	SP530P LED62S/940 SRD U4 PI5 SM2L2850 BK	Safety class I
97280300	SP530P LED7S/940 PSD LE2 PI5 SM2L570 ALU	Safety class I
97283400	SP532P LED10S/930 PSD LE2 PI5 L570 ALU	Safety class I
97295700	SP530P LED50S/930 PSD PI5 SM2 L2250 WH	Safety class I
97307700	SP531P LED62S/930 PSD PI5 SM2L2810 WH	Safety class I
97308400	SP532P LED94S/940 PSD PI5 SM2L2810 WH	Safety class I
97255100	SP532P LED47S/940 PSD PI5 SM2 L1410 BK	Safety class I
97238400	SP531P LED15S/940 PSD PI5 SM2 L1130 BK	Safety class I
97228500	SP530P LED34S/940 PSD PI5 SM2 L1130 BK	Safety class I
97243800	SP532P LED29S/930 PSD LF2 PI5 SM2L1410BK	Safety class I
97244500	SP532P LED29S/940 PSD LF2 PI5 SM2L1410BK	Safety class I
97249000	SP532P LED36S/940 PSD LF2 PI5SMTTL1130BK	Safety class I
97241400	SP532P LED29S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
97248300	SP532P LED36S/940 PSD LF2 PI5SMTTL1130AL	Safety class I
97242100	SP532P LED29S/940 PSD LF2 PI5 SM2L1410AL	Safety class I
97275900	SP534P LED43S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
97253700	SP532P LED47S/940 PSD LF1 PI5SW2L1410ALU	Safety class I
97247600	SP532P LED36S/940 PSD LF1 PI5SW2L1130ALU	Safety class I
97315200	SP532P LED36S/TW9 DIA LF1 PI5 L1130 ALU	Safety class I
97316900	SP533P LED33S/TW9 DIA LF1 PI5 L1410 ALU	Safety class I
97257500	SP532P LED47S/940 SRD U4 PI3 SM2L1450ALU	Safety class I
97232200	SP530P LED40S/940 SRD U4 PI3 SM2L1170ALU	Safety class I
97263600	SP532P LED66S/940 SRD U4 PI3 SM2L1450ALU	Safety class I

