



Menciptakan lingkungan ramah dan hangat dengan pencahayaan kualitas superior

MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor menciptakan lingkungan hangat dan nyaman untuk lokasi hospitality, rumah, dan restoran. Menciptakan lingkungan tersebut dengan pencahayaan superior yang memiliki spektrum kustom, CRI tinggi, dan fitur peredupan dalam. Hasilnya? Pengalaman pencahayaan indah. Kemudian, desain lensa tanpa trim dan inovatif juga cocok hampir semua dekor interior dengan tampilan bersih dan rapi. Selain itu, Anda dapat memanfaatkan penuh jajaran ExpertColor, yang juga termasuk lampu LEDspot LV dan LEDspot Par.

Benefits

- Menciptakan lingkungan hangat dan nyaman
- Dekor interior, perabotan dan kain terlihat bagus
- Solusi retrofit bebas gangguan untuk keberlanjutan dan efisiensi energi lebih besar

Features

- Spektrum warna kustomisasi meniru warna cahaya halogen
- Desain tanpa trim dengan lensa alur V yang indah
- Realisasi warna terbaik CRI97, R9>85
- Peredupan dalam dan halus
- Dapat ditingkatkan dengan lampu halogen GU10 tegangan utama

MASTER LEDspot ExpertColor MV


Application

- Hospitality: kamar tamu hotel, koridor, lobi, area resepsi, restoran, bar, kafe
- Rumah: ruang tamu, kamar tidur, lorong
- Ritel: pameran, meja pameran, toko, ruang ganti

Versions



Dimensional drawing



Product	D	C
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm

MASTER LEDspot ExpertColor MV

Penyetujuan dan Aplikasi

Penggunaan Energi kWh/1000 h	6 kWh
Label Efisiensi Energi (EEL)	A+

Kontrol dan Peredupan

Dapat diredupkan	Benar
------------------	-------

Pengoperasian dan Kelistrikan

Frekuensi Input	50 hingga 60 Hz
Tegangan (Nom)	220-240 V
Watt yang Setara	50 W
Daya (Terukur) (Nom)	5.5 W
Waktu Mulai (Nom)	0,5 s

Informasi Umum

Tutup-Dasar	GU10
Nominal Masa Pakai (Nom)	40000 h
Siklus Sakelar	50000X

Teknis Lampu

Indeks Renderasi Warna (Nom)	97
Llmf Di Akhir Masa Pakai Nominal (Nom)	70 %

Mekanis dan Housing

Bentuk Bohlam	PAR16
---------------	-------

Suhu


T-Case Maksimum (Nom)	80 °C
-----------------------	-------

Teknis Lampu (1/2)


Order Code	Full Product Name	Sudut	Kode	Suhu Warna	
		Cahaya (Nom)		Warna (Nom)	Terkorelasi (Nom)
929001347002	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	25 °	927	2700 K	355 lm
929001347008	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	24 °	927	2700 K	385 lm
929001347108	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	24 °	930	3000 K	405 lm
929001347308	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	36 °	927	2700 K	385 lm
929001347408	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	36 °	930	3000 K	405 lm

Teknis Lampu (2/2)

Order Code	Full Product Name	Intensitas Cahaya (Nom)
929001347002	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	1000 cd
929001347008	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	1000 cd
929001347108	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	1000 cd
929001347308	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	800 cd
929001347408	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	800 cd




MASTER LEDspot ExpertColor MV




MASTER LEDspot ExpertColor MV

Accent Diagrams



MASTER LEDspot ExpertColor MV 50W GU10
927 25D


MASTER LEDspot ExpertColor MV 50W GU10
930 25D




MASTER LEDspot ExpertColor MV 50W GU10
927 36D

MASTER LEDspot ExpertColor MV 50W GU10
930 36D


Beam Diagrams



MASTER LEDspot ExpertColor MV 50W GU10
927 25D




MASTER LEDspot ExpertColor MV 50W GU10
930 25D



MASTER LEDspot ExpertColor MV 50W GU10
927 36D

MASTER LEDspot ExpertColor MV

Beam Diagrams



MASTER LEDspot ExpertColor MV 50W GU10
930 36D

