



Crea un'atmosfera calda e accogliente con un'illuminazione di qualità superiore

MASTER LEDspot ExpertColor MV

MASTER LEDspot MV ExpertColor crea un'atmosfera calda e confortevole per hotel, ristoranti e bar con un'illuminazione di qualità superiore, caratterizzata da uno spettro di colore personalizzato, CRI elevato e una funzione avanzata di regolazione del flusso che consentono di produrre un'esperienza di illuminazione mozzafiato. Il design delle lenti trimless, che costituisce l'aspetto più innovativo di questa soluzione, si abbina perfettamente a qualsiasi tipo di arredamento grazie alle sue linee semplici e pulite. Inoltre, il cliente potrà avvalersi dell'intera famiglia ExpertColor, che include anche lampade LEDspot LV e LEDspot PAR.

Vantaggi

- Creazione di un'atmosfera calda e confortevole
- Complementi di arredo, mobili e tessuti appaiono al meglio
- Soluzione retrofit estremamente semplice per migliorare l'efficienza energetica e la sostenibilità

Caratteristiche

- Spettro di colore personalizzato che replica l'effetto alogeno
- Design trimless con belle lenti con scanalature a V
- Miglior resa cromatica CRI97, R9>85
- Regolazione del flusso avanzata e omogenea
- Sostituzione diretta per lampade alogene GU10 a tensione di rete

MASTER LEDspot ExpertColor MV

Applicazione


- Hotel, ristoranti e bar: camere d'albergo, corridoi, hall, reception, ristoranti, bar, caffè
- Casa: soggiorno, camera da letto, corridoio
- Negozi: esposizioni, espositori, punti vendita, camerini

Versions



MASTER LEDspot ExpertColor MV

Disegno tecnico



Product	D	C
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 25D	50 mm	54 mm
MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	50 mm	54 mm

MASTER LEDspot ExpertColor MV

Approvazione e applicazione

Marchio di efficienza energetica (EEL) A+

Controlli e regolazione del flusso

Regolabile Si

Funzionamento e parte elettrica

Frequenza di ingresso Da 50 a 60 Hz

Tensione (Nom) 220-240 V

Tempo di avvio (Nom) 0,5 s

Informazioni generali

Attacco GU10

Durata nominale (Nom) 40000 h

Ciclo di commutazione on/off 50.000 X

Dati tecnici di illuminazione

Indice di resa dei colori (Nom) 97

LLMF a fine durata nominale (Nom) 70 %

Meccanica e corpo

Forma lampadina PAR16

Temperatura

Temp. massima involucro (Nom) 80 °C

Approvazione e applicazione

Order Code	Full Product Name	Consumo energetico kWh/ 1000 h
70749400	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 25D	4 kWh
70751700	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 25D	4 kWh
70753100	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 25D	4 kWh
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	4 kWh
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	4 kWh
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	4 kWh
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	6 kWh
75586000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	6 kWh
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	6 kWh
75588400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	6 kWh
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	6 kWh
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
70733300	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	6 kWh
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
75590700	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	6 kWh
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	6 kWh

Funzionamento e parte elettrica

Order Code	Full Product Name	Wattaggio equivalente	Potenza (Specificata) (Nom)
70749400	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 25D	35 W	3.9 W
70751700	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 25D	35 W	3.9 W
70753100	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 25D	35 W	3.9 W
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	35 W	3.9 W
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	35 W	3.9 W
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	35 W	3.9 W
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	50 W	5.5 W
75586000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	50 W	5.5 W
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	50 W	5.5 W

Order Code	Full Product Name	Wattaggio equivalente	Potenza (Specificata) (Nom)
75588400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	50 W	5.5 W
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	50 W	5.5 W
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 W	5.5 W
70733300	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	50 W	5.5 W
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 W	5.5 W
75590700	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	50 W	5.5 W
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	50 W	5.5 W

Dati tecnici di illuminazione (1/2)

MASTER LEDspot ExpertColor MV

Order Code	Full Product Name	Angolo del fascio (Nom)	Codice colore	Temperatura di colore	
				correlata (Nom)	Flusso luminoso (Nom)
70749400	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 25D	25 °	927	2700 K	265 lm
70751700	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 25D	25 °	930	3000 K	280 lm
70753100	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 25D	25 °	940	4000 K	300 lm
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	36 °	927	2700 K	265 lm
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	36 °	930	3000 K	280 lm
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	36 °	940	4000 K	300 lm
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	25 °	927	2700 K	355 lm
75586000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	24 °	927	2700 K	385 lm
70763000	MASTER LED ExpertColor LED	25 °	930	3000 K	375 lm

Order Code	Full Product Name	Angolo del fascio (Nom)	Codice colore	Temperatura di colore	
				correlata (Nom)	Flusso luminoso (Nom)
	ExpertColor 5.5-50W GU10 930 25D				
75588400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	24 °	930	3000 K	405 lm
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	25 °	940	4000 K	400 lm
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	36 °	927	2700 K	355 lm
70733300	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	36 °	927	2700 K	385 lm
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	36 °	930	3000 K	375 lm
75590700	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	36 °	930	3000 K	405 lm
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	36 °	940	4000 K	400 lm










Dati tecnici di illuminazione (2/2)

Order Code	Full Product Name	Intensità luminosa (Nom)
70749400	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 25D	700 cd
70751700	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 25D	750 cd
70753100	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 25D	800 cd
70755500	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 927 36D	540 cd
70757900	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 930 36D	560 cd


Order Code	Full Product Name	Intensità luminosa (Nom)
70759300	MASTER LED ExpertColor LED ExpertColor 3.9-35W GU10 940 36D	600 cd
70761600	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 25D	1000 cd
75586000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 24D	1000 cd
70763000	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 25D	1000 cd
75588400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 24D	1000 cd

MASTER LEDspot ExpertColor MV



Order Code	Full Product Name	Intensità luminosa (Nom)
70765400	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 25D	1050 cd
70767800	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	800 cd
70733300	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 927 36D	800 cd
70769200	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	800 cd
75590700	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 930 36D	800 cd
70771500	MASTER LED ExpertColor LED ExpertColor 5.5-50W GU10 940 36D	800 cd




MASTER LEDspot ExpertColor MV




MASTER LEDspot ExpertColor MV




Accent Diagrams




**MASTER LEDspot ExpertColor MV 35W GU10
927 25D**




**MASTER LEDspot ExpertColor MV 35W GU10
930 25D**




**MASTER LEDspot ExpertColor MV 35W GU10
940 25D**




**MASTER LEDspot ExpertColor MV 35W GU10
927 36D**




**MASTER LEDspot ExpertColor MV 35W GU10
930 36D**




**MASTER LEDspot ExpertColor MV 35W GU10
940 36D**



**MASTER LEDspot ExpertColor MV 50W GU10
927 25D**




**MASTER LEDspot ExpertColor MV 50W GU10
930 25D**




**MASTER LEDspot ExpertColor MV 50W GU10
940 25D**

MASTER LEDspot ExpertColor MV

Accent Diagrams




MASTER LEDspot ExpertColor MV 50W GU10
927 36D



MASTER LEDspot ExpertColor MV 50W GU10
940 36D


Beam Diagrams




MASTER LEDspot ExpertColor MV 35W GU10
927 25D



MASTER LEDspot ExpertColor MV 35W GU10
930 25D




MASTER LEDspot ExpertColor MV 35W GU10
940 25D



MASTER LEDspot ExpertColor MV 35W GU10
927 36D


MASTER LEDspot ExpertColor MV 35W GU10
930 36D




MASTER LEDspot ExpertColor MV 35W GU10
940 36D

MASTER LEDspot ExpertColor MV

Beam Diagrams




MASTER LEDspot ExpertColor MV 50W GU10
927 25D




MASTER LEDspot ExpertColor MV 50W GU10
930 25D


MASTER LEDspot ExpertColor MV 50W GU10
940 25D



MASTER LEDspot ExpertColor MV 50W GU10
927 36D



MASTER LEDspot ExpertColor MV 50W GU10
930 36D



MASTER LEDspot ExpertColor MV 50W GU10
940 36D

