



# A flexible and affordable retail toolbox

## GreenSpace Accent Pendant

Thanks to the GreenSpace Accent family, retailers and building operators can now easily make the switch from CDM to LED and enjoy the benefits of Philips PerfectAccent light quality as well as significant energy savings – all for a reasonable initial investment. GreenSpace Accent Pendant can be installed on a regular 3C adaptor or onto a ceiling mount with track interface for quick and easy installation. The cable can be cut to length to perfectly match the installation height of the luminaire. For fashion and food retailers, a GreenSpace Accent Pendant is available with special light flavours and LED recipes to show the clothes and fresh food produce on offer in the very best light. Check out our Fashion and Food catalogue pages to discover more about CrispWhite, PremiumWhite, Fresh Food Meat and Fresh Food Champagne.

### Benefits

- Clean and robust design
- Full retail application coverage
- Lighting flexibility beyond CDM

### Features

- Driver integrated in a compact housing
- High quality of light enabled by the Philips PerfectAccent reflectors
- Light flavours for fashion and LED recipes for food included
- The cable can be cut to length and can be installed on track or ceiling

### Application

- Food retail
- Fashion retail
- Hospitality

# GreenSpace Accent Pendant

## Specifications

Aiming possibilities from the horizontal	to °
Aiming possibilities from the vertical	to °
Ambient Temperature	+10 to +40 °C
Beam angle lightsource	120 °
Beam spread luminaire	24°
Main colour of the luminaire	White
Connection	Flying leads/wires (Flying leads/wires)
Dimming	No
Driver	Power supply unit (PSU)
Initial correlated colour temperature	4000 K
Initial input power	14.4 W
Initial LED luminaire efficacy	125 lm/W

Initial luminous flux	1800 lm
Input frequency	50 to 60 Hz
Input voltage	220 to 240 V
Inrush current (A)	18.6 A
Light source colour	840 neutral white
Light source replaceable	No
Material	Bracket:
Material	Gear box:
Material	Housing: aluminum
Material	Reflector: polycarbonate aluminum coated
Optic	MB   Medium beam
Optical cover	Polycarbonate
Tilt angle housing	Standard tilt angle post-top: Standard tilt angle side entry:
Type	PT320C
Warranty period	5 years

## Versions



GSA Pendant Track Mounted

## Product details



GreenSpace\_Accent\_Pendant-PT320T\_C-1DPP.tif



GreenSpace\_Accent\_Pendant-PT320T\_C-2DPP.tif

# GreenSpace Accent Pendant

## Product details

GreenSpace\_Accent\_Pendant-  
PT320C-DPP.tif

