



Less hassle, More savings

Essential SmartBright G2 LED Floodlight

Essential SmartBright G2 LED floodlight comes with a compact and sturdy design. It is light weight with die-cast aluminium housing and corrosion-proof powder coating, suitable for general outdoor application. High efficiency designed with latest LED technology, achieves substantial energy savings comparing to conventional floodlights.

Benefits

- Ideal replacement for conventional halogen floodlights with substantial energy savings
- Uniform and less glare light output
- Reliable quality and brand promise guarantee hassle free for outdoor application

Features

- CCT: 3000K/4000K/6500K
- Power: 10w/20w/30w/50w/70w
- ~80lm/w system efficacy
- 15Khrs lifetime
- Operating temperature: $-40^{\circ}\text{C} < T_a < 45^{\circ}\text{C}$
- Complies IEC60598, EMC standards

Application

- Amenity/Security/Landscape/Plaza square/Parking/Architectural lighting

Essential SmartBright G2 LED Floodlight

Versions



Approval and Application

Mech. impact protection code IK06

Controls and Dimming

Dimmable No

General Information

Luminaire light beam spread 100°

CE mark CE mark

Optical cover/lens type Polycarbonate
bowl/cover flat

Driver included Yes

Light source replaceable No

Initial Performance (IEC Compliant)

Init. Colour Rendering Index >80

Mechanical and Housing

Colour Black

General Information

Order Code	Full Product Name	Light source colour	Flammability mark	Number of gear units	Optic type
911401859398	BVP133 LED24/WW 30W 220-240V WB	830 warm white	-	-	-
911401859498	BVP133 LED24/NW 30W 220-240V WB	840 neutral white	-	-	-
911401859598	BVP133 LED24/CW 30W 220-240V WB	865 cool daylight	-	-	-
911401859798	BVP135 LED40/NW 50W 220-240V WB	840 neutral white	-	-	-
911401859998	BVP137 LED56/WW 70W 220-240V WB	830 warm white	-	1 unit	Symmetrical wide beam
911401860098	BVP137 LED56/NW 70W 220-240V WB	840 neutral white	-	1 unit	Symmetrical wide beam
911401860198	BVP137 LED56/CW 70W 220-240V WB	865 cool daylight	-	1 unit	Symmetrical wide beam

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401859398	BVP133 LED24/WW 30W 220-240V WB	3000 K	2400 lm
911401859498	BVP133 LED24/NW 30W 220-240V WB	4000 K	2400 lm
911401859598	BVP133 LED24/CW 30W 220-240V WB	6500 K	2400 lm
911401859798	BVP135 LED40/NW 50W 220-240V WB	4000 K	4000 lm

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401859998	BVP137 LED56/WW 70W 220-240V WB	3000 K	5600 lm
911401860098	BVP137 LED56/NW 70W 220-240V WB	4000 K	5600 lm
911401860198	BVP137 LED56/CW 70W 220-240V WB	6500 K	5600 lm

Light Technical

Essential SmartBright G2 LED Floodlight

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401859398	BVP133 LED24/WW 30W 220-240V WB	-	-
911401859498	BVP133 LED24/NW 30W 220-240V WB	-	-
911401859598	BVP133 LED24/CW 30W 220-240V WB	-	-
911401859798	BVP135 LED40/NW 50W 220-240V WB	-	-

Order Code	Full Product Name	Standard tilt angle side entry	Standard tilt angle posttop
911401859998	BVP137 LED56/WW 70W 220-240V WB	-	-
911401860098	BVP137 LED56/NW 70W 220-240V WB	-	-
911401860198	BVP137 LED56/CW 70W 220-240V WB	-	-

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401859398	BVP133 LED24/WW 30W 220-240V WB	-
911401859498	BVP133 LED24/NW 30W 220-240V WB	-
911401859598	BVP133 LED24/CW 30W 220-240V WB	-
911401859798	BVP135 LED40/NW 50W 220-240V WB	-

Order Code	Full Product Name	Maximum dim level
911401859998	BVP137 LED56/WW 70W 220-240V WB	Not applicable
911401860098	BVP137 LED56/NW 70W 220-240V WB	Not applicable
911401860198	BVP137 LED56/CW 70W 220-240V WB	Not applicable

