



FlexAccent G2 – Excellent light quality

FlexAccent G2

FlexAccent G2 is a functional LED accent lighting product delivering high quality of light, outstanding colour, compact design and tailor mode option. It offers optimised colour spectrum that enhances look of merchandise with PremiumWhite CoB LED technology. FlexAccent G2 creates very “true” lighting effect – the real CDM-Elite replacement with 1000lm to 3500lm output/head. It could apply to shopping mall, retail store, fashion shop etc.

Benefits

- Quality of light, influence customer's shopping experience positively
- Compact and stylish design to ease installation
- Diversity: different lumen package, CCT, and type of mounting to cater for different customers' needs

Features

- 3 types of form factor: Track/Recess/Grid
- High CRI option, CRI80 or 90
- “True” light(3000K) – PremiumWhite
- High reliability, 30k hours (L70B50@25°C)

Application

- Shopping mall Retail store Fashion shop

FlexAccent G2

Versions



RS391B

