



FlexAccent G2 – Excellent light quality

FlexAccent G2

FlexAccent G2 is a functional LED accent lighting product delivering high quality of light, outstanding color, compact design and tailor mode option. It offers optimized color spectrum that enhances look of merchandise with PremiumWhite CoB LED technology. FlexAccent G2 creates very “true” lighting effect – the real CDM-Elite replacement with 1000lm to 3500lm output/head. It could apply to shopping mall, retail store, fashion shop etc.

Benefits

- Quality of light, influence customer's shopping experience positively
- Compact and stylish design to ease installation
- Diversity: different lumen package, CCT, and type of mounting to cater for different customers' needs

Features

- 3 types of form factor: Track/Recess/Grid
- High CRI option, CRI80 or 90
- “True” light(3000K) – PremiumWhite
- High reliability, 30k hours (L70B50@25°C)

Application

- Shopping mall Retail store Fashion shop

FlexAccent G2

Versions



ST391T TW



ST391T



RS391B



GD391B_2XLED



GD391B 3XLED



GD391B 1XLED

Application Conditions

Ambient temperature range	-15 to +35 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK03
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class II
Optical cover/lens type	Lens
Driver included	No
ENEC mark	-
Flammability mark	-
Glow-wire test	Temperature 600 °C, duration 30 s
Number of gear units	1 unit
Optic type	-

Initial Performance (IEC Compliant)

Initial chromaticity	SDCM<4
Luminous flux tolerance	+/-10%

Mechanical and Housing

Color	White
-------	-------

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401501641	ST391T LED30/840 PSU-E WB TW	4000 K	>80	83.78 lm/W	3100 lm
911401501741	ST391T LED30/840 PSU-E NB TW	4000 K	>80	83.78 lm/W	3100 lm
911401501841	ST391T LED30/830 PSU-E MB TW	3000 K	>80	83.78 lm/W	3100 lm
911401501941	ST391T LED20/940 PSU-E WB TW	4000 K	>90	78.43 lm/W	2000 lm
911401502041	ST391T LED30/830 PSU-E WB TW	3000 K	>80	83.78 lm/W	3100 lm
911401502141	ST391T LED20/940 PSU-E MB TW	4000 K	>90	78.43 lm/W	2000 lm
911401502241	ST391T LED30/830 PSU-E NB TW	3000 K	>80	83.78 lm/W	3100 lm
911401502341	ST391T LED30/840 PSU-E MB TW	4000 K	>80	83.78 lm/W	3100 lm
911401502441	ST391T LED30/930 PSU-E NB TW	3000 K	>90	83.78 lm/W	3100 lm
911401502541	ST391T LED30/940 PSU-E MB TW	4000 K	>90	83.78 lm/W	3100 lm
911401502641	ST391T LED30/940 PSU-E NB TW	4000 K	>90	83.78 lm/W	3100 lm
911401502741	ST391T LED30/930 PSU-E WB TW	3000 K	>90	83.78 lm/W	3100 lm
911401502841	ST391T LED20/940 PSU-E NB TW	4000 K	>90	78.43 lm/W	2000 lm
911401502941	ST391T LED30/930 PSU-E MB TW	3000 K	>90	83.78 lm/W	3100 lm
911401503041	ST391T LED20/930 PSU-E WB TW	3000 K	>90	78.43 lm/W	2000 lm
911401503141	ST391T LED20/930 PSU-E MB TW	3000 K	>90	78.43 lm/W	2000 lm
911401503241	ST391T LED30/940 PSU-E WB TW	4000 K	>90	83.78 lm/W	3100 lm
911401503341	ST391T LED20/930 PSU-E NB TW	3000 K	>90	78.43 lm/W	2000 lm
911401503441	ST391T LED20/840 PSU-E MB TW	4000 K	>80	78.43 lm/W	2000 lm
911401503541	ST391T LED20/840 PSU-E WB TW	4000 K	>80	78.43 lm/W	2000 lm
911401503641	ST391T LED20/840 PSU-E NB TW	4000 K	>80	78.43 lm/W	2000 lm
911401503741	ST391T LED20/830 PSU-E WB TW	3000 K	>80	78.43 lm/W	2000 lm
911401503841	ST391T LED20/830 PSU-E MB TW	3000 K	>80	78.43 lm/W	2000 lm
911401503941	ST391T LED20/830 PSU-E NB TW	3000 K	>80	78.43 lm/W	2000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401508641	ST391T LED10/830 PSU-E MB TW	3000 K	>80	86.96 lm/W	1000 lm
911401508941	ST391T LED10/830 PSU-E NB TW	3000 K	>80	86.96 lm/W	1000 lm
911401509041	ST391T LED10/840 PSU-E NB TW	4000 K	>80	86.96 lm/W	1000 lm
911401509141	ST391T LED10/840 PSU-E MB TW	4000 K	>80	86.96 lm/W	1000 lm
911401509241	ST391T LED10/830 PSU-E WB TW	3000 K	>80	86.96 lm/W	1000 lm
911401509341	ST391T LED10/930 PSU-E NB TW	3000 K	>90	86.96 lm/W	1000 lm
911401509441	ST391T LED10/840 PSU-E WB TW	4000 K	>80	86.96 lm/W	1000 lm
911401509541	ST391T LED10/930 PSU-E MB TW	3000 K	>90	86.96 lm/W	1000 lm
911401509641	ST391T LED10/940 PSU-E WB TW	4000 K	>90	86.96 lm/W	1000 lm
911401509741	ST391T LED10/940 PSU-E NB TW	4000 K	>90	86.96 lm/W	1000 lm
911401509841	ST391T LED10/940 PSU-E MB TW	4000 K	>90	86.96 lm/W	1000 lm
911401509941	ST391T LED10/930 PSU-E WB TW	3000 K	>90	86.96 lm/W	1000 lm
911401504041	ST391T LED10/840 PSU-E NB	4000 K	>80	86.96 lm/W	1000 lm
911401504141	ST391T LED20/830 PSU-E NB	3000 K	>80	78.43 lm/W	2000 lm
911401504241	ST391T LED10/830 PSU-E NB	3000 K	>80	86.96 lm/W	1000 lm
911401504341	ST391T LED10/830 PSU-E WB	3000 K	>80	86.96 lm/W	1000 lm
911401504441	ST391T LED10/840 PSU-E WB	4000 K	>80	86.96 lm/W	1000 lm
911401504541	ST391T LED10/840 PSU-E MB	4000 K	>80	86.96 lm/W	1000 lm
911401504641	ST391T LED10/830 PSU-E MB	3000 K	>80	86.96 lm/W	1000 lm
911401504741	ST391T LED20/830 PSU-E WB	3000 K	>80	78.43 lm/W	2000 lm
911401504841	ST391T LED20/840 PSU-E WB	4000 K	>80	78.43 lm/W	2000 lm
911401504941	ST391T LED20/840 PSU-E NB	4000 K	>80	78.43 lm/W	2000 lm
911401505041	ST391T LED20/840 PSU-E MB	4000 K	>80	78.43 lm/W	2000 lm
911401505141	ST391T LED20/830 PSU-E MB	3000 K	>80	78.43 lm/W	2000 lm
911401505241	ST391T LED30/840 PSU-E NB	4000 K	>80	83.78 lm/W	3100 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401505341	ST391T LED30/840 PSU-E MB	4000 K	>80	83.78 lm/W	3100 lm
911401505441	ST391T LED30/830 PSU-E NB	3000 K	>80	83.78 lm/W	3100 lm
911401505541	ST391T LED30/830 PSU-E WB	3000 K	>80	83.78 lm/W	3100 lm
911401505641	ST391T LED30/830 PSU-E MB	3000 K	>80	83.78 lm/W	3100 lm
911401505741	ST391T LED35/830 PSU-E NB	3000 K	>80	76.09 lm/W	3500 lm
911401505841	ST391T LED30/840 PSU-E WB	4000 K	>80	83.78 lm/W	3100 lm
911401505941	ST391T LED35/830 PSU-E MB	3000 K	>80	76.09 lm/W	3500 lm
911401506041	ST391T LED35/840 PSU-E NB	4000 K	>80	76.09 lm/W	3500 lm
911401506141	ST391T LED35/840 PSU-E MB	4000 K	>80	76.09 lm/W	3500 lm
911401506241	ST391T LED35/830 PSU-E WB	3000 K	>80	76.09 lm/W	3500 lm
911401506341	ST391T LED10/930 PSU-E NB	3000 K	>90	86.96 lm/W	1000 lm
911401506441	ST391T LED35/840 PSU-E WB	4000 K	>80	76.09 lm/W	3500 lm
911401506541	ST391T LED10/930 PSU-E MB	3000 K	>90	86.96 lm/W	1000 lm
911401506641	ST391T LED10/930 PSU-E WB	3000 K	>90	86.96 lm/W	1000 lm
911401506741	ST391T LED10/940 PSU-E NB	4000 K	>90	86.96 lm/W	1000 lm
911401506841	ST391T LED10/940 PSU-E MB	4000 K	>90	86.96 lm/W	1000 lm
911401506941	ST391T LED20/930 PSU-E MB	3000 K	>90	78.43 lm/W	2000 lm
911401507041	ST391T LED20/930 PSU-E NB	3000 K	>90	78.43 lm/W	2000 lm
911401507141	ST391T LED10/940 PSU-E WB	4000 K	>90	86.96 lm/W	1000 lm
911401507241	ST391T LED20/940 PSU-E MB	4000 K	>90	78.43 lm/W	2000 lm
911401507341	ST391T LED20/940 PSU-E NB	4000 K	>90	78.43 lm/W	2000 lm
911401507441	ST391T LED20/930 PSU-E WB	3000 K	>90	78.43 lm/W	2000 lm
911401507541	ST391T LED30/930 PSU-E MB	3000 K	>90	83.78 lm/W	3100 lm
911401507641	ST391T LED30/930 PSU-E NB	3000 K	>90	83.78 lm/W	3100 lm
911401507741	ST391T LED20/940 PSU-E WB	4000 K	>90	78.43 lm/W	2000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401507841	ST391T LED35/930 PSU-E MB	3000 K	>90	76.09 lm/W	3500 lm
911401507941	ST391T LED35/930 PSU-E WB	3000 K	>90	76.09 lm/W	3500 lm
911401508041	ST391T LED35/940 PSU-E NB	4000 K	>90	76.09 lm/W	3500 lm
911401508141	ST391T LED35/930 PSU-E NB	3000 K	>90	76.09 lm/W	3500 lm
911401508241	ST391T LED30/940 PSU-E WB	4000 K	>90	83.78 lm/W	3100 lm
911401508341	ST391T LED30/930 PSU-E WB	3000 K	>90	83.78 lm/W	3100 lm
911401508441	ST391T LED30/940 PSU-E MB	4000 K	>90	83.78 lm/W	3100 lm
911401508541	ST391T LED30/940 PSU-E NB	4000 K	>90	83.78 lm/W	3100 lm
911401508741	ST391T LED35/940 PSU-E MB	4000 K	>90	76.09 lm/W	3500 lm
911401508841	ST391T LED35/940 PSU-E WB	4000 K	>90	76.09 lm/W	3500 lm
911401836097	ST391T LED10/840 PSU-E WB 3C WH	4000 K	>80	86.96 lm/W	1000 lm
911401836197	ST391T LED10/840 PSU-E NB 3C WH	4000 K	>80	86.96 lm/W	1000 lm
911401836297	ST391T LED10/840 PSU-E MB 3C WH	4000 K	>80	86.96 lm/W	1000 lm
911401836397	ST391T LED10/830 PSU-E MB 3C WH	3000 K	>80	86.96 lm/W	1000 lm
911401836497	ST391T LED10/830 PSU-E WB 3C WH	3000 K	>80	86.96 lm/W	1000 lm
911401836597	ST391T LED10/930 PSU-E NB 3C WH	3000 K	>90	86.96 lm/W	1000 lm
911401836697	ST391T LED10/930 PSU-E WB 3C WH	3000 K	>90	86.96 lm/W	1000 lm
911401836797	ST391T LED10/940 PSU-E MB 3C WH	4000 K	>90	86.96 lm/W	1000 lm
911401836897	ST391T LED10/940 PSU-E NB 3C WH	4000 K	>90	86.96 lm/W	1000 lm
911401836997	ST391T LED10/930 PSU-E MB 3C WH	3000 K	>90	86.96 lm/W	1000 lm
911401837097	ST391T LED10/940 PSU-E WB 3C WH	4000 K	>90	86.96 lm/W	1000 lm
911401837197	ST391T LED10/840 PSU-E MB 1C WH	4000 K	>80	86.96 lm/W	1000 lm
911401837297	ST391T LED10/830 PSU-E WB 1C WH	3000 K	>80	86.96 lm/W	1000 lm
911401837397	ST391T LED10/830 PSU-E MB 1C WH	3000 K	>80	86.96 lm/W	1000 lm
911401837497	ST391T LED10/840 PSU-E NB 1C WH	4000 K	>80	86.96 lm/W	1000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401837597	ST391T LED10/840 PSU-E WB 1C WH	4000 K	>80	86.96 lm/W	1000 lm
911401837697	ST391T LED10/940 PSU-E MB 1C WH	4000 K	>90	86.96 lm/W	1000 lm
911401837797	ST391T LED10/930 PSU-E WB 1C WH	3000 K	>90	86.96 lm/W	1000 lm
911401837897	ST391T LED10/940 PSU-E NB 1C WH	4000 K	>90	86.96 lm/W	1000 lm
911401837997	ST391T LED10/940 PSU-E WB 1C WH	4000 K	>90	86.96 lm/W	1000 lm
911401838097	ST391T LED10/930 PSU-E NB 1C WH	3000 K	>90	86.96 lm/W	1000 lm
911401838197	ST391T LED10/930 PSU-E MB 1C WH	3000 K	>90	86.96 lm/W	1000 lm
911401838297	ST391T LED10/830 PSU-E NB 1C WH	3000 K	>80	86.96 lm/W	1000 lm
911401838397	ST391T LED20/830 PSU-E WB 1C WH	3000 K	>80	78.43 lm/W	2000 lm
911401838497	ST391T LED20/830 PSU-E MB 1C WH	3000 K	>80	78.43 lm/W	2000 lm
911401838597	ST391T LED20/830 PSU-E NB 1C WH	3000 K	>80	78.43 lm/W	2000 lm
911401838697	ST391T LED20/940 PSU-E MB 1C WH	4000 K	>90	78.43 lm/W	2000 lm
911401838797	ST391T LED20/840 PSU-E WB 1C WH	4000 K	>80	78.43 lm/W	2000 lm
911401838897	ST391T LED20/940 PSU-E NB 1C WH	4000 K	>90	78.43 lm/W	2000 lm
911401838997	ST391T LED20/940 PSU-E WB 1C WH	4000 K	>90	78.43 lm/W	2000 lm
911401839097	ST391T LED20/840 PSU-E NB 1C WH	4000 K	>80	78.43 lm/W	2000 lm
911401839197	ST391T LED20/840 PSU-E MB 1C WH	4000 K	>80	78.43 lm/W	2000 lm
911401839297	ST391T LED20/840 PSU-E WB 3C WH	4000 K	>80	78.43 lm/W	2000 lm
911401839397	ST391T LED20/930 PSU-E NB 1C WH	3000 K	>90	78.43 lm/W	2000 lm
911401839497	ST391T LED20/830 PSU-E NB 3C WH	3000 K	>80	78.43 lm/W	2000 lm
911401839597	ST391T LED20/930 PSU-E MB 1C WH	3000 K	>90	78.43 lm/W	2000 lm
911401839697	ST391T LED20/830 PSU-E MB 3C WH	3000 K	>80	78.43 lm/W	2000 lm
911401839797	ST391T LED20/830 PSU-E WB 3C WH	3000 K	>80	78.43 lm/W	2000 lm
911401839897	ST391T LED20/930 PSU-E MB 3C WH	3000 K	>90	78.43 lm/W	2000 lm
911401839997	ST391T LED20/930 PSU-E WB 1C WH	3000 K	>90	78.43 lm/W	2000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401840097	ST391T LED20/940 PSU-E NB 3C WH	4000 K	>90	78.43 lm/W	2000 lm
911401840197	ST391T LED20/930 PSU-E NB 3C WH	3000 K	>90	78.43 lm/W	2000 lm
911401840297	ST391T LED20/940 PSU-E WB 3C WH	4000 K	>90	78.43 lm/W	2000 lm
911401840397	ST391T LED20/930 PSU-E WB 3C WH	3000 K	>90	78.43 lm/W	2000 lm
911401840497	ST391T LED20/940 PSU-E MB 3C WH	4000 K	>90	78.43 lm/W	2000 lm
911401840597	ST391T LED20/840 PSU-E MB 3C WH	4000 K	>80	78.43 lm/W	2000 lm
911401840697	ST391T LED10/830 PSU-E NB 3C WH	3000 K	>80	86.96 lm/W	1000 lm
911401840797	ST391T LED20/840 PSU-E NB 3C WH	4000 K	>80	78.43 lm/W	2000 lm
911401840897	ST391T LED30/830 PSU-E NB 1C WH	3000 K	>80	83.78 lm/W	3100 lm
911401840997	ST391T LED30/830 PSU-E WB 1C WH	3000 K	>80	83.78 lm/W	3100 lm
911401841097	ST391T LED30/840 PSU-E MB 1C WH	4000 K	>80	83.78 lm/W	3100 lm
911401841197	ST391T LED30/930 PSU-E WB 1C WH	3000 K	>90	83.78 lm/W	3100 lm
911401841297	ST391T LED30/830 PSU-E MB 1C WH	3000 K	>80	83.78 lm/W	3100 lm
911401841397	ST391T LED30/840 PSU-E NB 1C WH	4000 K	>80	83.78 lm/W	3100 lm
911401841497	ST391T LED30/940 PSU-E NB 1C WH	4000 K	>90	83.78 lm/W	3100 lm
911401841597	ST391T LED30/940 PSU-E MB 1C WH	4000 K	>90	83.78 lm/W	3100 lm
911401841697	ST391T LED30/840 PSU-E WB 1C WH	4000 K	>80	83.78 lm/W	3100 lm
911401841797	ST391T LED30/940 PSU-E WB 1C WH	4000 K	>90	83.78 lm/W	3100 lm
911401841897	ST391T LED30/930 PSU-E MB 1C WH	3000 K	>90	83.78 lm/W	3100 lm
911401841997	ST391T LED30/830 PSU-E MB 3C WH	3000 K	>80	83.78 lm/W	3100 lm
911401842097	ST391T LED30/930 PSU-E NB 1C WH	3000 K	>90	83.78 lm/W	3100 lm
911401842197	ST391T LED30/930 PSU-E NB 3C WH	3000 K	>90	83.78 lm/W	3100 lm
911401842297	ST391T LED30/930 PSU-E MB 3C WH	3000 K	>90	83.78 lm/W	3100 lm
911401842397	ST391T LED30/830 PSU-E NB 3C WH	3000 K	>80	83.78 lm/W	3100 lm
911401842497	ST391T LED30/930 PSU-E WB 3C WH	3000 K	>90	83.78 lm/W	3100 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401842597	ST391T LED30/840 PSU-E WB 3C WH	4000 K	>80	83.78 lm/W	3100 lm
911401842697	ST391T LED30/830 PSU-E WB 3C WH	3000 K	>80	83.78 lm/W	3100 lm
911401842797	ST391T LED30/840 PSU-E NB 3C WH	4000 K	>80	83.78 lm/W	3100 lm
911401842897	ST391T LED30/940 PSU-E NB 3C WH	4000 K	>90	83.78 lm/W	3100 lm
911401842997	ST391T LED30/940 PSU-E MB 3C WH	4000 K	>90	83.78 lm/W	3100 lm
911401843097	ST391T LED30/840 PSU-E MB 3C WH	4000 K	>80	83.78 lm/W	3100 lm
911401843197	ST391T LED30/940 PSU-E WB 3C WH	4000 K	>90	83.78 lm/W	3100 lm
911401843297	ST391T LED35/840 PSU-E NB 1C WH	4000 K	>80	76.09 lm/W	3500 lm
911401843397	ST391T LED35/830 PSU-E WB 1C WH	3000 K	>80	76.09 lm/W	3500 lm
911401843497	ST391T LED35/830 PSU-E MB 1C WH	3000 K	>80	76.09 lm/W	3500 lm
911401843597	ST391T LED35/840 PSU-E MB 1C WH	4000 K	>80	76.09 lm/W	3500 lm
911401843697	ST391T LED35/840 PSU-E WB 1C WH	4000 K	>80	76.09 lm/W	3500 lm
911401843797	ST391T LED35/830 PSU-E NB 1C WH	3000 K	>80	76.09 lm/W	3500 lm
911401843897	ST391T LED35/940 PSU-E WB 1C WH	4000 K	>90	76.09 lm/W	3500 lm
911401843997	ST391T LED35/830 PSU-E MB 3C WH	3000 K	>80	76.09 lm/W	3500 lm
911401844097	ST391T LED35/940 PSU-E NB 1C WH	4000 K	>90	76.09 lm/W	3500 lm
911401844197	ST391T LED35/830 PSU-E NB 3C WH	3000 K	>80	76.09 lm/W	3500 lm
911401844297	ST391T LED35/830 PSU-E WB 3C WH	3000 K	>80	76.09 lm/W	3500 lm
911401844397	ST391T LED35/930 PSU-E WB 3C WH	3000 K	>90	76.09 lm/W	3500 lm
911401844497	ST391T LED35/930 PSU-E WB 1C WH	3000 K	>90	76.09 lm/W	3500 lm
911401844597	ST391T LED35/940 PSU-E MB 3C WH	4000 K	>90	76.09 lm/W	3500 lm
911401844697	ST391T LED35/940 PSU-E MB 1C WH	4000 K	>90	76.09 lm/W	3500 lm
911401844797	ST391T LED35/930 PSU-E MB 1C WH	3000 K	>90	76.09 lm/W	3500 lm
911401844897	ST391T LED35/930 PSU-E MB 3C WH	3000 K	>90	76.09 lm/W	3500 lm
911401844997	ST391T LED35/840 PSU-E MB 3C WH	4000 K	>80	76.09 lm/W	3500 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401845097	ST391T LED35/940 PSU-E WB 3C WH	4000 K	>90	76.09 lm/W	3500 lm
911401845197	ST391T LED35/840 PSU-E NB 3C WH	4000 K	>80	76.09 lm/W	3500 lm
911401845297	ST391T LED35/940 PSU-E NB 3C WH	4000 K	>90	76.09 lm/W	3500 lm
911401845397	ST391T LED35/930 PSU-E NB 3C WH	3000 K	>90	76.09 lm/W	3500 lm
911401845497	ST391T LED35/840 PSU-E WB 3C WH	4000 K	>80	76.09 lm/W	3500 lm
911401845597	ST391T LED35/930 PSU-E NB 1C WH	3000 K	>90	76.09 lm/W	3500 lm
911401556731	RS391B LED10/830 PSU-E WB	3000 K	>80	83.33 lm/W	1000 lm
911401556931	RS391B LED10/840 PSU-E MB	4000 K	>80	83.33 lm/W	1000 lm
911401557031	RS391B LED10/840 PSU-E NB	4000 K	>80	83.33 lm/W	1000 lm
911401557331	RS391B LED10/830 PSU-E NB	3000 K	>80	83.33 lm/W	1000 lm
911401557531	RS391B LED20/830 PSU- E MB	3000 K	>80	76.92 lm/W	2000 lm
911401557631	RS391B LED20/830 PSU- E WB	3000 K	>80	76.92 lm/W	2000 lm
911401557731	RS391B LED20/840 PSU- E NB	4000 K	>80	76.92 lm/W	2000 lm
911401557831	RS391B LED20/840 PSU- E MB	4000 K	>80	76.92 lm/W	2000 lm
911401557931	RS391B LED20/830 PSU- E NB	3000 K	>80	76.92 lm/W	2000 lm
911401558131	RS391B LED10/840 PSU-E WB	4000 K	>80	83.33 lm/W	1000 lm
911401561731	RS391B LED10/930 PSU-E WB	3000 K	>90	83.33 lm/W	1000 lm
911401562031	RS391B LED10/930 PSU-E MB	3000 K	>90	83.33 lm/W	1000 lm
911401562231	RS391B LED10/930 PSU-E NB	3000 K	>90	83.33 lm/W	1000 lm
911401562331	RS391B LED20/930 PSU- E NB	3000 K	>90	76.92 lm/W	2000 lm
911401562431	RS391B LED10/940 PSU-E NB	4000 K	>90	83.33 lm/W	1000 lm
911401562531	RS391B LED10/940 PSU-E WB	4000 K	>90	83.33 lm/W	1000 lm
911401562731	RS391B LED20/940 PSU- E MB	4000 K	>90	76.92 lm/W	2000 lm
911401562831	RS391B LED20/930 PSU- E WB	3000 K	>90	76.92 lm/W	2000 lm
911401563031	RS391B LED20/940 PSU- E NB	4000 K	>90	76.92 lm/W	2000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401563131	RS391B LED20/930 PSU-E MB	3000 K	>90	76.92 lm/W	2000 lm
911401564631	RS391B LED20/940 PSU-E WB	4000 K	>90	76.92 lm/W	2000 lm
911401567131	RS391B LED10/930 PSU-E WB TW	3000 K	>90	83.33 lm/W	1000 lm
911401571131	RS391B LED10/830 PSU-E WB TW	3000 K	>80	83.33 lm/W	1000 lm
911401571431	RS391B LED10/840 PSU-E WB TW	4000 K	>80	83.33 lm/W	1000 lm
911401571731	RS391B LED20/830 PSU-E WB TW	3000 K	>80	76.92 lm/W	2000 lm
911401572131	RS391B LED20/840 PSU-E WB TW	4000 K	>80	76.92 lm/W	2000 lm
911401583131	RS391B LED35/930 PSU-E WB	3000 K	>90	72.92 lm/W	3500 lm
911401583231	RS391B LED35/940 PSU-E MB	4000 K	>90	72.92 lm/W	3500 lm
911401583531	RS391B LED35/840 PSU-E WB	4000 K	>80	72.92 lm/W	3500 lm
911401583631	RS391B LED35/830 PSU-E WB	3000 K	>80	72.92 lm/W	3500 lm
911401583731	RS391B LED35/930 PSU-E NB	3000 K	>90	72.92 lm/W	3500 lm
911401584031	RS391B LED30/840 PSU-E WB	4000 K	>80	76.92 lm/W	3000 lm
911401584131	RS391B LED30/930 PSU-E MB	3000 K	>90	76.92 lm/W	3000 lm
911401584331	RS391B LED30/940 PSU-E NB	4000 K	>90	76.92 lm/W	3000 lm
911401584631	RS391B LED35/830 PSU-E NB	3000 K	>80	72.92 lm/W	3500 lm
911401584731	RS391B LED30/840 PSU-E MB	4000 K	>80	76.92 lm/W	3000 lm
911401584931	RS391B LED30/830 PSU-E NB	3000 K	>80	76.92 lm/W	3000 lm
911401585031	RS391B LED30/830 PSU-E WB	3000 K	>80	76.92 lm/W	3000 lm
911401585131	RS391B LED30/830 PSU-E MB	3000 K	>80	76.92 lm/W	3000 lm
911401585231	RS391B LED35/830 PSU-E MB	3000 K	>80	72.92 lm/W	3500 lm
911401585331	RS391B LED35/840 PSU-E MB	4000 K	>80	72.92 lm/W	3500 lm
911401876699	RS391B LED20/830 PSU-E MB GM	3000 K	>80	76.92 lm/W	2000 lm
911401876799	RS391B LED20/830 PSU-E NB GM	3000 K	>80	76.92 lm/W	2000 lm
911401876899	RS391B LED10/830 PSU-E MB GM	3000 K	>80	83.33 lm/W	1000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
91140187699 9	RS391B LED10/830 PSU-E WB GM	3000 K	>80	83.33 lm/W	1000 lm
911401877099	RS391B LED10/840 PSU-E NB GM	4000 K	>80	83.33 lm/W	1000 lm
911401877199	RS391B LED10/840 PSU-E MB GM	4000 K	>80	83.33 lm/W	1000 lm
911401877299	RS391B LED10/840 PSU-E WB GM	4000 K	>80	83.33 lm/W	1000 lm
911401877399	RS391B LED10/930 PSU-E NB GM	3000 K	>90	83.33 lm/W	1000 lm
911401877499	RS391B LED10/930 PSU-E WB GM	3000 K	>90	83.33 lm/W	1000 lm
911401877799	RS391B LED10/940 PSU-E MB GM	4000 K	>90	83.33 lm/W	1000 lm
911401877999	RS391B LED20/830 PSU- E WB GM	3000 K	>80	76.92 lm/W	2000 lm
91140187809 9	RS391B LED20/840 PSU- E NB GM	4000 K	>80	76.92 lm/W	2000 lm
911401878199	RS391B LED20/840 PSU- E MB GM	4000 K	>80	76.92 lm/W	2000 lm
911401878299	RS391B LED20/840 PSU- E WB GM	4000 K	>80	76.92 lm/W	2000 lm
911401878399	RS391B LED20/930 PSU- E NB GM	3000 K	>90	76.92 lm/W	2000 lm
911401878499	RS391B LED20/930 PSU- E MB GM	3000 K	>90	76.92 lm/W	2000 lm
911401878599	RS391B LED20/930 PSU- E WB GM	3000 K	>90	76.92 lm/W	2000 lm
91140187869 9	RS391B LED20/940 PSU- E NB GM	4000 K	>90	76.92 lm/W	2000 lm
911401878799	RS391B LED20/940 PSU- E MB GM	4000 K	>90	76.92 lm/W	2000 lm
911401878899	RS391B LED20/940 PSU- E WB GM	4000 K	>90	76.92 lm/W	2000 lm
91140187899 9	RS391B LED10/930 PSU-E MB GM	3000 K	>90	83.33 lm/W	1000 lm
91140189289 9	RS391B LED30/930 PSU- E NB GM	3000 K	>90	76.92 lm/W	3000 lm
91140189309 9	RS391B LED30/940 PSU- E MB GM	4000 K	>90	76.92 lm/W	3000 lm
911401893199	RS391B LED35/830 PSU- E WB GM	3000 K	>80	72.92 lm/W	3500 lm
91140189349 9	RS391B LED35/840 PSU- E WB GM	4000 K	>80	72.92 lm/W	3500 lm
91140189359 9	RS391B LED35/930 PSU- E MB GM	3000 K	>90	72.92 lm/W	3500 lm
91140189369 9	RS391B LED35/830 PSU- E MB GM	3000 K	>80	72.92 lm/W	3500 lm
91140189409 9	RS391B LED35/930 PSU- E WB GM	3000 K	>90	72.92 lm/W	3500 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401894199	RS391B LED30/940 PSU-E NB GM	4000 K	>90	76.92 lm/W	3000 lm
91140189429	RS391B LED35/940 PSU-E MB GM	4000 K	>90	72.92 lm/W	3500 lm
91140189529	RS391B LED35/830 PSU-E NB GM	3000 K	>80	72.92 lm/W	3500 lm
91140189689	RS391B LED30/830 PSU-E MB GM	3000 K	>80	76.92 lm/W	3000 lm
911401897399	RS391B LED30/930 PSU-E MB GM	3000 K	>90	76.92 lm/W	3000 lm
911401557431	GD391B 2XLED10/830 PSU-E MB	3000 K	>80	83.33 lm/W	2000 lm
911401558231	GD391B 2XLED10/830 PSU-E WB	3000 K	>80	83.33 lm/W	2000 lm
911401558731	GD391B 2XLED10/840 PSU-E WB	4000 K	>80	83.33 lm/W	2000 lm
911401559831	GD391B 2XLED20/830 PSU-E NB	3000 K	>80	76.92 lm/W	4000 lm
911401560531	GD391B 2XLED20/830 PSU-E MB	3000 K	>80	76.92 lm/W	4000 lm
911401561131	GD391B 2XLED20/840 PSU-E MB	4000 K	>80	76.92 lm/W	4000 lm
911401561331	GD391B 2XLED20/830 PSU-E WB	3000 K	>80	76.92 lm/W	4000 lm
911401561531	GD391B 2XLED20/840 PSU-E WB	4000 K	>80	76.92 lm/W	4000 lm
911401563331	GD391B 2XLED20/930 PSU-E MB	3000 K	>90	76.92 lm/W	4000 lm
911401564031	GD391B 2XLED20/940 PSU-E NB	4000 K	>90	76.92 lm/W	4000 lm
911401564831	GD391B 2XLED10/930 PSU-E WB	3000 K	>90	83.33 lm/W	2000 lm
911401564931	GD391B 2XLED10/940 PSU-E NB	4000 K	>90	83.33 lm/W	2000 lm
911401565031	GD391B 2XLED10/930 PSU-E MB	3000 K	>90	83.33 lm/W	2000 lm
911401568331	GD391B 2XLED20/930 PSU-E WB TW	3000 K	>90	76.92 lm/W	4000 lm
911401558531	GD391B 3XLED10/830 PSU-E MB	3000 K	>80	83.33 lm/W	3000 lm
911401559231	GD391B 3XLED10/840 PSU-E MB	4000 K	>80	83.33 lm/W	3000 lm
911401559331	GD391B 3XLED10/830 PSU-E WB	3000 K	>80	83.33 lm/W	3000 lm
911401559431	GD391B 3XLED10/840 PSU-E WB	4000 K	>80	83.33 lm/W	3000 lm
911401561231	GD391B 3XLED20/830 PSU-E WB	3000 K	>80	76.92 lm/W	6000 lm
911401561431	GD391B 3XLED20/830 PSU-E NB	3000 K	>80	76.92 lm/W	6000 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
911401561631	GD391B 3XLED20/830 PSU-E MB	3000 K	>80	76.92 lm/W	6000 lm
911401561831	GD391B 3XLED20/840 PSU-E MB	4000 K	>80	76.92 lm/W	6000 lm
911401562131	GD391B 3XLED20/840 PSU-E WB	4000 K	>80	76.92 lm/W	6000 lm
911401559131	GD391B 1XLED10/840 PSU-E WB	4000 K	>80	83.33 lm/W	1000 lm
911401559531	GD391B 1XLED10/840 PSU-E MB	4000 K	>80	83.33 lm/W	1000 lm
911401559931	GD391B 1XLED20/840 PSU-E MB	4000 K	>80	76.92 lm/W	2000 lm
911401560031	GD391B 1XLED20/840 PSU-E WB	4000 K	>80	76.92 lm/W	2000 lm
911401560631	GD391B 1XLED10/830 PSU-E MB	3000 K	>80	83.33 lm/W	1000 lm
911401560731	GD391B 1XLED20/830 PSU-E WB	3000 K	>80	76.92 lm/W	2000 lm
911401564431	GD391B 1XLED20/940 PSU-E MB	4000 K	>90	76.92 lm/W	2000 lm
911401569431	GD391B 1XLED20/830 PSU-E WB TW	3000 K	>80	76.92 lm/W	2000 lm
911401581731	GD391B 1XLED30/940 PSU-E MB	4000 K	>90	76.92 lm/W	3000 lm
911401581931	GD391B 1XLED30/940 PSU-E NB	4000 K	>90	76.92 lm/W	3000 lm
911401582031	GD391B 1XLED30/940 PSU-E WB	4000 K	>90	76.92 lm/W	3000 lm
911401582131	GD391B 1XLED30/930 PSU-E WB	3000 K	>90	76.92 lm/W	3000 lm
911401582231	GD391B 1XLED30/930 PSU-E NB	3000 K	>90	76.92 lm/W	3000 lm
911401582331	GD391B 1XLED30/930 PSU-E MB	3000 K	>90	76.92 lm/W	3000 lm
911401582531	GD391B 1XLED30/840 PSU-E WB	4000 K	>80	76.92 lm/W	3000 lm
911401582631	GD391B 1XLED30/830 PSU-E MB	3000 K	>80	76.92 lm/W	3000 lm
911401582731	GD391B 1XLED30/830 PSU-E NB	3000 K	>80	76.92 lm/W	3000 lm
911401582831	GD391B 1XLED30/840 PSU-E MB	4000 K	>80	76.92 lm/W	3000 lm
911401582931	GD391B 1XLED30/830 PSU-E WB	3000 K	>80	76.92 lm/W	3000 lm
911401583031	GD391B 1XLED30/840 PSU-E NB	4000 K	>80	76.92 lm/W	3000 lm
91140189399 9	GD391B 1XLED30/940 PSU-E NB GM	4000 K	>90	76.92 lm/W	3000 lm
91140189469 9	GD391B 1XLED35/830 PSU-E WB GM	3000 K	>80	72.92 lm/W	3500 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial LED luminaire efficacy	Initial luminous flux
91140189479 9	GD391B 1XLED30/940 PSU-E WB GM	4000 K	>90	76.92 lm/W	3000 lm
91140189589 9	GD391B 1XLED35/840 PSU-E WB GM	4000 K	>80	72.92 lm/W	3500 lm
91140189629 9	GD391B 1XLED35/830 PSU-E MB GM	3000 K	>80	72.92 lm/W	3500 lm
91140189699 9	GD391B 1XLED35/840 PSU-E MB GM	4000 K	>80	72.92 lm/W	3500 lm

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power	Order Code	Full Product Name	Initial input power
911401501641	ST391T LED30/840 PSU-E WB TW	37 W	911401504241	ST391T LED10/830 PSU-E NB	11.5 W
911401501741	ST391T LED30/840 PSU-E NB TW	37 W	911401504341	ST391T LED10/830 PSU-E WB	11.5 W
911401501841	ST391T LED30/830 PSU-E MB TW	37 W	911401504441	ST391T LED10/840 PSU-E WB	11.5 W
911401501941	ST391T LED20/940 PSU-E WB TW	25.5 W	911401504541	ST391T LED10/840 PSU-E MB	11.5 W
911401502041	ST391T LED30/830 PSU-E WB TW	37 W	911401504641	ST391T LED10/830 PSU-E MB	11.5 W
911401502141	ST391T LED20/940 PSU-E MB TW	25.5 W	911401504741	ST391T LED20/830 PSU-E WB	25.5 W
911401502241	ST391T LED30/830 PSU-E NB TW	37 W	911401504841	ST391T LED20/840 PSU-E WB	25.5 W
911401502341	ST391T LED30/840 PSU-E MB TW	37 W	911401504941	ST391T LED20/840 PSU-E NB	25.5 W
911401502441	ST391T LED30/930 PSU-E NB TW	37 W	911401505041	ST391T LED20/840 PSU-E MB	25.5 W
911401502541	ST391T LED30/940 PSU-E MB TW	37 W	911401505141	ST391T LED20/830 PSU-E MB	25.5 W
911401502641	ST391T LED30/940 PSU-E NB TW	37 W	911401505241	ST391T LED30/840 PSU-E NB	37 W
911401502741	ST391T LED30/930 PSU-E WB TW	37 W	911401505341	ST391T LED30/840 PSU-E MB	37 W
911401502841	ST391T LED20/940 PSU-E NB TW	25.5 W	911401505441	ST391T LED30/830 PSU-E NB	37 W
911401502941	ST391T LED30/930 PSU-E MB TW	37 W	911401505541	ST391T LED30/830 PSU-E WB	37 W
911401503041	ST391T LED20/930 PSU-E WB TW	25.5 W	911401505641	ST391T LED30/830 PSU-E MB	37 W
911401503141	ST391T LED20/930 PSU-E MB TW	25.5 W	911401505741	ST391T LED35/830 PSU-E NB	46 W
911401503241	ST391T LED30/940 PSU-E WB TW	37 W	911401505841	ST391T LED30/840 PSU-E WB	37 W
911401503341	ST391T LED20/930 PSU-E NB TW	25.5 W	911401505941	ST391T LED35/830 PSU-E MB	46 W
911401503441	ST391T LED20/840 PSU-E MB TW	25.5 W	911401506041	ST391T LED35/840 PSU-E NB	46 W
911401503541	ST391T LED20/840 PSU-E WB TW	25.5 W	911401506141	ST391T LED35/840 PSU-E MB	46 W
911401503641	ST391T LED20/840 PSU-E NB TW	25.5 W	911401506241	ST391T LED35/830 PSU-E WB	46 W
911401503741	ST391T LED20/830 PSU-E WB TW	25.5 W	911401506341	ST391T LED10/930 PSU-E NB	11.5 W
911401503841	ST391T LED20/830 PSU-E MB TW	25.5 W	911401506441	ST391T LED35/840 PSU-E WB	46 W
911401503941	ST391T LED20/830 PSU-E NB TW	25.5 W	911401506541	ST391T LED10/930 PSU-E MB	11.5 W
911401508641	ST391T LED10/830 PSU-E MB TW	11.5 W	911401506641	ST391T LED10/930 PSU-E WB	11.5 W
911401508941	ST391T LED10/830 PSU-E NB TW	11.5 W	911401506741	ST391T LED10/940 PSU-E NB	11.5 W
911401509041	ST391T LED10/840 PSU-E NB TW	11.5 W	911401506841	ST391T LED10/940 PSU-E MB	11.5 W
911401509141	ST391T LED10/840 PSU-E MB TW	11.5 W	911401506941	ST391T LED20/930 PSU-E MB	25.5 W
911401509241	ST391T LED10/830 PSU-E WB TW	11.5 W	911401507041	ST391T LED20/930 PSU-E NB	25.5 W
911401509341	ST391T LED10/930 PSU-E NB TW	11.5 W	911401507141	ST391T LED10/940 PSU-E WB	11.5 W
911401509441	ST391T LED10/840 PSU-E WB TW	11.5 W	911401507241	ST391T LED20/940 PSU-E MB	25.5 W
911401509541	ST391T LED10/930 PSU-E MB TW	11.5 W	911401507341	ST391T LED20/940 PSU-E NB	25.5 W
911401509641	ST391T LED10/940 PSU-E WB TW	11.5 W	911401507441	ST391T LED20/930 PSU-E WB	25.5 W
911401509741	ST391T LED10/940 PSU-E NB TW	11.5 W	911401507541	ST391T LED30/930 PSU-E MB	37 W
911401509841	ST391T LED10/940 PSU-E MB TW	11.5 W	911401507641	ST391T LED30/930 PSU-E NB	37 W
911401509941	ST391T LED10/930 PSU-E WB TW	11.5 W	911401507741	ST391T LED20/940 PSU-E WB	25.5 W
911401504041	ST391T LED10/840 PSU-E NB	11.5 W	911401507841	ST391T LED35/930 PSU-E MB	46 W
911401504141	ST391T LED20/830 PSU-E NB	25.5 W	911401507941	ST391T LED35/930 PSU-E WB	46 W

Order Code	Full Product Name	Initial input power
911401508041	ST391T LED35/940 PSU-E NB	46 W
911401508141	ST391T LED35/930 PSU-E NB	46 W
911401508241	ST391T LED30/940 PSU-E WB	37 W
911401508341	ST391T LED30/930 PSU-E WB	37 W
911401508441	ST391T LED30/940 PSU-E MB	37 W
911401508541	ST391T LED30/940 PSU-E NB	37 W
911401508741	ST391T LED35/940 PSU-E MB	46 W
911401508841	ST391T LED35/940 PSU-E WB	46 W
911401836097	ST391T LED10/840 PSU-E WB 3C WH	11.5 W
911401836197	ST391T LED10/840 PSU-E NB 3C WH	11.5 W
911401836297	ST391T LED10/840 PSU-E MB 3C WH	11.5 W
911401836397	ST391T LED10/830 PSU-E MB 3C WH	11.5 W
911401836497	ST391T LED10/830 PSU-E WB 3C WH	11.5 W
911401836597	ST391T LED10/930 PSU-E NB 3C WH	11.5 W
911401836697	ST391T LED10/930 PSU-E WB 3C WH	11.5 W
911401836797	ST391T LED10/940 PSU-E MB 3C WH	11.5 W
911401836897	ST391T LED10/940 PSU-E NB 3C WH	11.5 W
911401836997	ST391T LED10/930 PSU-E MB 3C WH	11.5 W
911401837097	ST391T LED10/940 PSU-E WB 3C WH	11.5 W
911401837197	ST391T LED10/840 PSU-E MB 1C WH	11.5 W
911401837297	ST391T LED10/830 PSU-E WB 1C WH	11.5 W
911401837397	ST391T LED10/830 PSU-E MB 1C WH	11.5 W
911401837497	ST391T LED10/840 PSU-E NB 1C WH	11.5 W
911401837597	ST391T LED10/840 PSU-E WB 1C WH	11.5 W
911401837697	ST391T LED10/940 PSU-E MB 1C WH	11.5 W
911401837797	ST391T LED10/930 PSU-E WB 1C WH	11.5 W
911401837897	ST391T LED10/940 PSU-E NB 1C WH	11.5 W
911401837997	ST391T LED10/940 PSU-E WB 1C WH	11.5 W
911401838097	ST391T LED10/930 PSU-E NB 1C WH	11.5 W
911401838197	ST391T LED10/930 PSU-E MB 1C WH	11.5 W
911401838297	ST391T LED10/830 PSU-E NB 1C WH	11.5 W
911401838397	ST391T LED20/830 PSU-E WB 1C WH	25.5 W
911401838497	ST391T LED20/830 PSU-E MB 1C WH	25.5 W
911401838597	ST391T LED20/830 PSU-E NB 1C WH	25.5 W
911401838697	ST391T LED20/940 PSU-E MB 1C WH	25.5 W
911401838797	ST391T LED20/840 PSU-E WB 1C WH	25.5 W
911401838897	ST391T LED20/940 PSU-E NB 1C WH	25.5 W
911401838997	ST391T LED20/940 PSU-E WB 1C WH	25.5 W
911401839097	ST391T LED20/840 PSU-E NB 1C WH	25.5 W
911401839197	ST391T LED20/840 PSU-E MB 1C WH	25.5 W
911401839297	ST391T LED20/840 PSU-E WB 3C WH	25.5 W
911401839397	ST391T LED20/930 PSU-E NB 1C WH	25.5 W
911401839497	ST391T LED20/830 PSU-E NB 3C WH	25.5 W
911401839597	ST391T LED20/930 PSU-E MB 1C WH	25.5 W
911401839697	ST391T LED20/830 PSU-E MB 3C WH	25.5 W
911401839797	ST391T LED20/830 PSU-E WB 3C WH	25.5 W
911401839897	ST391T LED20/930 PSU-E MB 3C WH	25.5 W
911401839997	ST391T LED20/930 PSU-E WB 1C WH	25.5 W
911401840097	ST391T LED20/940 PSU-E NB 3C WH	25.5 W
911401840197	ST391T LED20/930 PSU-E NB 3C WH	25.5 W
911401840297	ST391T LED20/940 PSU-E WB 3C WH	25.5 W
911401840397	ST391T LED20/930 PSU-E WB 3C WH	25.5 W

Order Code	Full Product Name	Initial input power
911401840497	ST391T LED20/940 PSU-E MB 3C WH	25.5 W
911401840597	ST391T LED20/840 PSU-E MB 3C WH	25.5 W
911401840697	ST391T LED10/830 PSU-E NB 3C WH	11.5 W
911401840797	ST391T LED20/840 PSU-E NB 3C WH	25.5 W
911401840897	ST391T LED30/830 PSU-E NB 1C WH	37 W
911401840997	ST391T LED30/830 PSU-E WB 1C WH	37 W
911401841097	ST391T LED30/840 PSU-E MB 1C WH	37 W
911401841197	ST391T LED30/930 PSU-E WB 1C WH	37 W
911401841297	ST391T LED30/830 PSU-E MB 1C WH	37 W
911401841397	ST391T LED30/840 PSU-E NB 1C WH	37 W
911401841497	ST391T LED30/940 PSU-E NB 1C WH	37 W
911401841597	ST391T LED30/940 PSU-E MB 1C WH	37 W
911401841697	ST391T LED30/840 PSU-E WB 1C WH	37 W
911401841797	ST391T LED30/940 PSU-E WB 1C WH	37 W
911401841897	ST391T LED30/930 PSU-E MB 1C WH	37 W
911401841997	ST391T LED30/830 PSU-E MB 3C WH	37 W
911401842097	ST391T LED30/930 PSU-E NB 1C WH	37 W
911401842197	ST391T LED30/930 PSU-E NB 3C WH	37 W
911401842297	ST391T LED30/930 PSU-E MB 3C WH	37 W
911401842397	ST391T LED30/830 PSU-E NB 3C WH	37 W
911401842497	ST391T LED30/930 PSU-E WB 3C WH	37 W
911401842597	ST391T LED30/840 PSU-E WB 3C WH	37 W
911401842697	ST391T LED30/830 PSU-E WB 3C WH	37 W
911401842797	ST391T LED30/840 PSU-E NB 3C WH	37 W
911401842897	ST391T LED30/940 PSU-E NB 3C WH	37 W
911401842997	ST391T LED30/940 PSU-E MB 3C WH	37 W
911401843097	ST391T LED30/840 PSU-E MB 3C WH	37 W
911401843197	ST391T LED30/940 PSU-E WB 3C WH	37 W
911401843297	ST391T LED35/840 PSU-E NB 1C WH	46 W
911401843397	ST391T LED35/830 PSU-E WB 1C WH	46 W
911401843497	ST391T LED35/830 PSU-E MB 1C WH	46 W
911401843597	ST391T LED35/840 PSU-E MB 1C WH	46 W
911401843697	ST391T LED35/840 PSU-E WB 1C WH	46 W
911401843797	ST391T LED35/830 PSU-E NB 1C WH	46 W
911401843897	ST391T LED35/940 PSU-E WB 1C WH	46 W
911401843997	ST391T LED35/830 PSU-E MB 3C WH	46 W
911401844097	ST391T LED35/940 PSU-E NB 1C WH	46 W
911401844197	ST391T LED35/830 PSU-E NB 3C WH	46 W
911401844297	ST391T LED35/830 PSU-E WB 3C WH	46 W
911401844397	ST391T LED35/930 PSU-E WB 3C WH	46 W
911401844497	ST391T LED35/930 PSU-E WB 1C WH	46 W
911401844597	ST391T LED35/940 PSU-E MB 3C WH	46 W
911401844697	ST391T LED35/940 PSU-E MB 1C WH	46 W
911401844797	ST391T LED35/930 PSU-E MB 1C WH	46 W
911401844897	ST391T LED35/930 PSU-E MB 3C WH	46 W
911401844997	ST391T LED35/840 PSU-E MB 3C WH	46 W
911401845097	ST391T LED35/940 PSU-E WB 3C WH	46 W
911401845197	ST391T LED35/840 PSU-E NB 3C WH	46 W
911401845297	ST391T LED35/940 PSU-E NB 3C WH	46 W
911401845397	ST391T LED35/930 PSU-E NB 3C WH	46 W
911401845497	ST391T LED35/840 PSU-E WB 3C WH	46 W
911401845597	ST391T LED35/930 PSU-E NB 1C WH	46 W

Order Code	Full Product Name	Initial input power
911401556731	RS391B LED10/830 PSU-E WB	12 W
911401556931	RS391B LED10/840 PSU-E MB	12 W
911401557031	RS391B LED10/840 PSU-E NB	12 W
911401557331	RS391B LED10/830 PSU-E NB	12 W
911401557531	RS391B LED20/830 PSU-E MB	26 W
911401557631	RS391B LED20/830 PSU-E WB	26 W
911401557731	RS391B LED20/840 PSU-E NB	26 W
911401557831	RS391B LED20/840 PSU-E MB	26 W
911401557931	RS391B LED20/830 PSU-E NB	26 W
911401558131	RS391B LED10/840 PSU-E WB	12 W
911401561731	RS391B LED10/930 PSU-E WB	12 W
911401562031	RS391B LED10/930 PSU-E MB	12 W
911401562231	RS391B LED10/930 PSU-E NB	12 W
911401562331	RS391B LED20/930 PSU-E NB	26 W
911401562431	RS391B LED10/940 PSU-E NB	12 W
911401562531	RS391B LED10/940 PSU-E WB	12 W
911401562731	RS391B LED20/940 PSU-E MB	26 W
911401562831	RS391B LED20/930 PSU-E WB	26 W
911401563031	RS391B LED20/940 PSU-E NB	26 W
911401563131	RS391B LED20/930 PSU-E MB	26 W
911401564631	RS391B LED20/940 PSU-E WB	26 W
911401567131	RS391B LED10/930 PSU-E WB TW	12 W
911401571131	RS391B LED10/830 PSU-E WB TW	12 W
911401571431	RS391B LED10/840 PSU-E WB TW	12 W
911401571731	RS391B LED20/830 PSU-E WB TW	26 W
911401572131	RS391B LED20/840 PSU-E WB TW	26 W
911401583131	RS391B LED35/930 PSU-E WB	48 W
911401583231	RS391B LED35/940 PSU-E MB	48 W
911401583531	RS391B LED35/840 PSU-E WB	48 W
911401583631	RS391B LED35/830 PSU-E WB	48 W
911401583731	RS391B LED35/930 PSU-E NB	48 W
911401584031	RS391B LED30/840 PSU-E WB	39 W
911401584131	RS391B LED30/930 PSU-E MB	39 W
911401584331	RS391B LED30/940 PSU-E NB	39 W
911401584631	RS391B LED35/830 PSU-E NB	48 W
911401584731	RS391B LED30/840 PSU-E MB	39 W
911401584931	RS391B LED30/830 PSU-E NB	39 W
911401585031	RS391B LED30/830 PSU-E WB	39 W
911401585131	RS391B LED30/830 PSU-E MB	39 W
911401585231	RS391B LED35/830 PSU-E MB	48 W
911401585331	RS391B LED35/840 PSU-E MB	48 W
911401876699	RS391B LED20/830 PSU-E MB GM	26 W
911401876799	RS391B LED20/830 PSU-E NB GM	26 W
911401876899	RS391B LED10/830 PSU-E MB GM	12 W
911401876999	RS391B LED10/830 PSU-E WB GM	12 W
911401877099	RS391B LED10/840 PSU-E NB GM	12 W
911401877199	RS391B LED10/840 PSU-E MB GM	12 W
911401877299	RS391B LED10/840 PSU-E WB GM	12 W
911401877399	RS391B LED10/930 PSU-E NB GM	12 W
911401877499	RS391B LED10/930 PSU-E WB GM	12 W
911401877799	RS391B LED10/940 PSU-E MB GM	12 W
911401877999	RS391B LED20/830 PSU-E WB GM	26 W

Order Code	Full Product Name	Initial input power
911401878099	RS391B LED20/840 PSU-E NB GM	26 W
911401878199	RS391B LED20/840 PSU-E MB GM	26 W
911401878299	RS391B LED20/840 PSU-E WB GM	26 W
911401878399	RS391B LED20/930 PSU-E NB GM	26 W
911401878499	RS391B LED20/930 PSU-E MB GM	26 W
911401878599	RS391B LED20/930 PSU-E WB GM	26 W
911401878699	RS391B LED20/940 PSU-E NB GM	26 W
911401878799	RS391B LED20/940 PSU-E MB GM	26 W
911401878899	RS391B LED20/940 PSU-E WB GM	26 W
911401878999	RS391B LED10/930 PSU-E MB GM	12 W
911401892899	RS391B LED30/930 PSU-E NB GM	39 W
911401893099	RS391B LED30/940 PSU-E MB GM	39 W
911401893199	RS391B LED35/830 PSU-E WB GM	48 W
911401893499	RS391B LED35/840 PSU-E WB GM	48 W
911401893599	RS391B LED35/930 PSU-E MB GM	48 W
911401893699	RS391B LED35/830 PSU-E MB GM	48 W
911401894099	RS391B LED35/930 PSU-E WB GM	48 W
911401894199	RS391B LED30/940 PSU-E NB GM	39 W
911401894299	RS391B LED35/940 PSU-E MB GM	48 W
911401895299	RS391B LED35/830 PSU-E NB GM	48 W
911401896899	RS391B LED30/830 PSU-E MB GM	39 W
911401897399	RS391B LED30/930 PSU-E MB GM	39 W
911401557431	GD391B 2XLED10/830 PSU-E MB	24 W
911401558231	GD391B 2XLED10/830 PSU-E WB	24 W
911401558731	GD391B 2XLED10/840 PSU-E WB	24 W
911401559831	GD391B 2XLED20/830 PSU-E NB	52 W
911401560531	GD391B 2XLED20/830 PSU-E MB	52 W
911401561131	GD391B 2XLED20/840 PSU-E MB	52 W
911401561331	GD391B 2XLED20/830 PSU-E WB	52 W
911401561531	GD391B 2XLED20/840 PSU-E WB	52 W
911401563331	GD391B 2XLED20/930 PSU-E MB	52 W
911401564031	GD391B 2XLED20/940 PSU-E NB	52 W
911401564831	GD391B 2XLED10/930 PSU-E WB	24 W
911401564931	GD391B 2XLED10/940 PSU-E NB	24 W
911401565031	GD391B 2XLED10/930 PSU-E MB	24 W
911401568331	GD391B 2XLED20/930 PSU-E WB TW	52 W
911401558531	GD391B 3XLED10/830 PSU-E MB	36 W
911401559231	GD391B 3XLED10/840 PSU-E MB	36 W
911401559331	GD391B 3XLED10/830 PSU-E WB	36 W
911401559431	GD391B 3XLED10/840 PSU-E WB	36 W
911401561231	GD391B 3XLED20/830 PSU-E WB	78 W
911401561431	GD391B 3XLED20/830 PSU-E NB	78 W
911401561631	GD391B 3XLED20/830 PSU-E MB	78 W
911401561831	GD391B 3XLED20/840 PSU-E MB	78 W
911401562131	GD391B 3XLED20/840 PSU-E WB	78 W
911401559131	GD391B 1XLED10/840 PSU-E WB	12 W
911401559531	GD391B 1XLED10/840 PSU-E MB	12 W
911401559931	GD391B 1XLED20/840 PSU-E MB	26 W
911401560031	GD391B 1XLED20/840 PSU-E WB	26 W
911401560631	GD391B 1XLED10/830 PSU-E MB	12 W
911401560731	GD391B 1XLED20/830 PSU-E WB	26 W
911401564431	GD391B 1XLED20/940 PSU-E MB	26 W

FlexAccent G2

Order Code	Full Product Name	Initial input power
911401569431	GD391B 1XLED20/830 PSU-E WB TW	26 W
911401581731	GD391B 1XLED30/940 PSU-E MB	39 W
911401581931	GD391B 1XLED30/940 PSU-E NB	39 W
911401582031	GD391B 1XLED30/940 PSU-E WB	39 W
911401582131	GD391B 1XLED30/930 PSU-E WB	39 W
911401582231	GD391B 1XLED30/930 PSU-E NB	39 W
911401582331	GD391B 1XLED30/930 PSU-E MB	39 W
911401582531	GD391B 1XLED30/840 PSU-E WB	39 W
911401582631	GD391B 1XLED30/830 PSU-E MB	39 W
911401582731	GD391B 1XLED30/830 PSU-E NB	39 W

Order Code	Full Product Name	Initial input power
911401582831	GD391B 1XLED30/840 PSU-E MB	39 W
911401582931	GD391B 1XLED30/830 PSU-E WB	39 W
911401583031	GD391B 1XLED30/840 PSU-E NB	39 W
911401893999	GD391B 1XLED30/940 PSU-E NB GM	39 W
911401894699	GD391B 1XLED35/830 PSU-E WB GM	48 W
911401894799	GD391B 1XLED30/940 PSU-E WB GM	39 W
911401895899	GD391B 1XLED35/840 PSU-E WB GM	48 W
911401896299	GD391B 1XLED35/830 PSU-E MB GM	48 W
911401896999	GD391B 1XLED35/840 PSU-E MB GM	48 W

