



Sleek and elegant design combined with full flexibility helps to create better spaces

SlimBalance

SlimBalance is a full range of product family with sleek and elegant design helps to create attractive and differentiated space for customers. The family covers different length (600mm, 1200mm, 1500mm), different end cap (round, square) and different light distribution (direct, indirect). Its office compliant version delivers comfortable light with good quality.

Benefits

- Create attractive/differentiated space
- Complete solution covering different mounting requirements, lengths, end cap including corners
- Good light quality
- Office compliant, Comfortable light

Features

- Sleek and elegant design
- Modular design offers uniform aesthetic for full family
- CRI > 80, SDCM < 4, Flicker free
- UGR 19 available

Application

- Open office
- Cell office
- Public area
- Meeting rooms

SlimBalance

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Versions



SlimBalance Standalone L120 L150

SlimBalance Standalone L60

SlimBalance Continuous

SlimBalance Standalone L120 L150

Application Conditions	
Ambient temperature range	-20 to +40 °C
Approval and Application	
Mech. impact protection code	IK03
Ingress protection code	IP20
Operating and Electrical	
Input Voltage	220/240 V
General Information	
Beam angle of light source	- °
CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
Flammability mark	-
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Optic type	Wide beam
Initial Performance (IEC Compliant)	
Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%
Mechanical and Housing	
Color	Silver

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401519241	SP550P LED25S 840 L120 PSU SD	Not applicable
911401519341	SP551P LED40S 840 L120 PSU SD	Not applicable
911401519841	SP550P LED28S 840 L120 PSU SI	Not applicable
911401519941	SP551P LED45S 840 L120 PSU SI	Not applicable
911401520141	RC551B LED40S 840 L120 PSU SD	Not applicable
911401521141	SP550P LED25S 840 L120 PSD SD	1%
911401521241	SP551P LED40S 840 L120 PSD SD	1%
911401521741	SP550P LED28S 840 L120 PSD SI	1%
911401521841	SP551P LED45S 840 L120 PSD SI	1%
911401528241	SP550P LED25S 840 L120 PSU SD SQ	Not applicable
911401528641	SP551P LED40S 840 L120 PSU SD SQ	Not applicable
911401528741	SP550P LED28S 840 L120 PSU SI SQ	Not applicable
911401528841	SP550P LED28S 840 L120 PSD SI SQ	1%
911401529041	SP551P LED40S 840 L120 PSD SD SQ	1%
911401529141	SP551P LED45S 840 L120 PSU SI SQ	Not applicable
911401529241	SP550P LED25S 840 L120 PSD SD SQ	1%
911401529441	SP551P LED45S 840 L120 PSD SI SQ	1%
911401519441	SP550P LED12S 840 L60 PSU SD	Not applicable
911401519541	SP551P LED20S 840 L60 PSU SD	Not applicable
911401520241	RC551B LED20S 840 L60 PSU SD	Not applicable
911401521441	SP551P LED20S 840 L60 PSD SD	1%
911401522941	RC550B LED20S 840 L60 PSU SD GM	Not applicable
911401523941	SP551P LED20S 840 L60 PSU SD GM	Not applicable
911401528341	SP551P LED20S 840 L60 PSU SD SQ	Not applicable
911401528441	SP550P LED12S 840 L60 PSU SD SQ	Not applicable
911401528941	SP551P LED20S 840 L60 PSD SD SQ	1%
911401529741	SP550P LED20S 840 L60 PSU SD CAU	Not applicable
911401530141	SP550P LED20S 840 L60 PSU SD GM SQ	Not applicable

Order Code	Full Product Name	Maximum dim level
911401530341	SP551P LED20S 840 L60 PSU SD GM SQ	Not applicable
911401531341	SP551P LED20S 840 L60 PSU SD CAU SQ	Not applicable
911401531641	SP550P LED20S 840 L60 PSU SD CAU SQ	Not applicable
911401532541	RC550B LED20S 840 L60 PSU SD CAU	Not applicable
911401532741	SP551P LED20S 840 L60 PSU SD CAU	Not applicable
911401533041	SP550P LED20S 840 L60 PSU SD GM	Not applicable
911401519641	SP550P LED25S 840 L120 PSU CD	Not applicable
911401519741	SP550P LED12S 840 L60 PSU CD	Not applicable
911401520041	SP550P LED28S 840 L120 PSU CI	Not applicable
911401520341	RC550B LED25S 840 L120 PSU CD	Not applicable
911401520441	RC550B LED12S 840 L60 PSU CD	Not applicable
911401520541	SM550C LED25S 840 L120 PSU CD	Not applicable
911401520641	SM550C LED12S 840 L60 PSU CD	Not applicable
911401521541	SP550P LED25S 840 L120 PSD CD	1%
911401521641	SP550P LED12S 840 L60 PSD CD	1%
911401521941	SP550P LED28S 840 L120 PSD CI	1%
911401522441	SM550C LED25S 840 L120 PSD CD	1%
911401522641	SM550C LED20S 840 L60 PSU CD GM	Not applicable
911401523641	RC550B LED40S 840 L120 PSU CD GM	Not applicable
911401523741	RC550B LED40S 865 L120 PSU CD GM	Not applicable
911401523841	SP550P LED20S 840 L60 PSU CD GM	Not applicable
911401524641	SP550P LED40S 840 L120 PSU CD GM	Not applicable
911401524741	SP550P LED40S 865 L120 PSU CD GM	Not applicable
911401524841	SP550P LED40S 840 L120 PSD CD GM	1%
911401524941	SP550P LED40S 865 L120 PSD CD GM	1%
911401525441	SM550C LED40S 840 L120 PSD CD GM	1%
911401534441	RC550B LED40S 840 L120 PSU CD CAU	Not applicable
911401534541	SP550P LED40S 840 L120 PSU CD CAU	Not applicable
911401534641	SP550P LED40S 840 L120 PSD CD CAU	1%
911401522841	SM551C LED40S 840 L120 PSD SD GM	1%
911401523141	RC550B LED40S 840 L120 PSU SD GM	Not applicable
911401523241	RC550B LED40S 865 L120 PSU SD GM	Not applicable
911401524141	SP550P LED40S 840 L120 PSU SD GM	Not applicable
911401524241	SP550P LED40S 865 L120 PSU SD GM	Not applicable
911401524341	SP550P LED40S 840 L120 PSD SD GM	1%
911401524441	SP550P LED40S 865 L120 PSD SD GM	1%
911401524541	SP551P LED40S 840 L120 PSD SD GM	1%
911401525041	SP550P LED40S 840 L150 PSU SD GM	Not applicable
911401525141	SP550P LED40S 840 L150 PSD SD GM	1%
911401525241	SP551P LED45S 840 L120 PSU SI GM	Not applicable
911401525341	SP551P LED45S 840 L120 PSD SI GM	1%
911401525541	SM550C LED40S 840 L120 PSD SD GM	1%
911401528541	SP550P LED40S 840 L150 PSU SD CAU	Not applicable
911401529341	SP550P LED40S 840 L150 PSD SD CAU	1%
911401529841	SP551P LED40S 840 L120 PSD SD CAU	1%
911401529941	SP550P LED40S 840 L120 PSU SD CAU	Not applicable
911401530041	SP550P LED40S 840 L120 PSD SD CAU	1%
911401530241	SP550P LED40S 840 L120 PSU SD GM SQ	Not applicable
911401530541	SP550P LED40S 840 L120 PSD SD GM SQ	1%
911401530641	SP550P LED40S 865 L120 PSU SD GM SQ	Not applicable
911401530741	SP550P LED40S 840 L150 PSD SD GM SQ	1%
911401530841	SP551P LED45S 840 L120 PSD SI GM SQ	1%

Order Code	Full Product Name	Maximum dim level
911401530941	SP551P LED40S 840 L120 PSD SD GM SQ	1%
911401531041	SP550P LED40S 840 L150 PSU SD GM SQ	Not applicable
911401531141	SP550P LED40S 865 L120 PSD SD GM SQ	1%
911401531241	SP551P LED45S 840 L120 PSU SI GM SQ	Not applicable
911401531441	SP550P LED40S 840 L120 PSU SD CAU SQ	Not applicable
911401531541	SP550P LED40S 840 L120 PSD SD CAU SQ	1%
911401531741	SP551P LED40S 840 L120 PSD SD CAU SQ	1%
911401531841	SP551P LED45S 840 L120 PSU SI CAU SQ	Not applicable
911401531941	SP550P LED40S 840 L150 PSD SD CAU SQ	1%
911401532141	SP550P LED40S 840 L150 PSU SD CAU SQ	Not applicable
911401532241	SP551P LED45S 840 L120 PSD SI CAU SQ	1%
911401532341	SP551P LED45S 840 L120 PSD SI CAU	1%
911401532441	SP551P LED45S 840 L120 PSU SI CAU	Not applicable
911401532641	RC550B LED40S 840 L120 PSU SD CAU	Not applicable
911401532841	SM551C LED40S 840 L120 PSD SD GM SQ	1%
911401532941	SM550C LED40S 840 L120 PSD SD GM SQ	1%
911401534141	SM550C LED40S 840 L120 PSD SD CAU SQ	1%
911401534241	SM551C LED40S 840 L120 PSD SD CAU SQ	1%

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401519241	SP550P LED25S 840 L120 PSU SD	No	911401531641	SP550P LED20S 840 L60 PSU SD CAU SQ	No
911401519341	SP551P LED40S 840 L120 PSU SD	No	911401532541	RC550B LED20S 840 L60 PSU SD CAU	No
911401519841	SP550P LED28S 840 L120 PSU SI	No	911401532741	SP551P LED20S 840 L60 PSU SD CAU	No
911401519941	SP551P LED45S 840 L120 PSU SI	No	911401533041	SP550P LED20S 840 L60 PSU SD GM	No
911401520141	RC551B LED40S 840 L120 PSU SD	No	911401519641	SP550P LED25S 840 L120 PSU CD	No
911401521141	SP550P LED25S 840 L120 PSD SD	Yes	911401519741	SP550P LED12S 840 L60 PSU CD	No
911401521241	SP551P LED40S 840 L120 PSD SD	Yes	911401520041	SP550P LED28S 840 L120 PSU CI	No
911401521741	SP550P LED28S 840 L120 PSD SI	Yes	911401520341	RC550B LED25S 840 L120 PSU CD	No
911401521841	SP551P LED45S 840 L120 PSD SI	Yes	911401520441	RC550B LED12S 840 L60 PSU CD	No
911401528241	SP550P LED25S 840 L120 PSU SD SQ	No	911401520541	SM550C LED25S 840 L120 PSU CD	No
911401528641	SP551P LED40S 840 L120 PSU SD SQ	No	911401520641	SM550C LED12S 840 L60 PSU CD	No
911401528741	SP550P LED28S 840 L120 PSU SI SQ	No	911401521541	SP550P LED25S 840 L120 PSD CD	Yes
911401528841	SP550P LED28S 840 L120 PSD SI SQ	Yes	911401521641	SP550P LED12S 840 L60 PSD CD	Yes
911401529041	SP551P LED40S 840 L120 PSD SD SQ	Yes	911401521941	SP550P LED28S 840 L120 PSD CI	Yes
911401529141	SP551P LED45S 840 L120 PSU SI SQ	No	911401522441	SM550C LED25S 840 L120 PSD CD	Yes
911401529241	SP550P LED25S 840 L120 PSD SD SQ	Yes	911401522641	SM550C LED20S 840 L60 PSU CD GM	No
911401529441	SP551P LED45S 840 L120 PSD SI SQ	Yes	911401523641	RC550B LED40S 840 L120 PSU CD GM	No
911401519441	SP550P LED12S 840 L60 PSU SD	No	911401523741	RC550B LED40S 865 L120 PSU CD GM	No
911401519541	SP551P LED20S 840 L60 PSU SD	No	911401523841	SP550P LED20S 840 L60 PSU CD GM	No
911401520241	RC551B LED20S 840 L60 PSU SD	No	911401524641	SP550P LED40S 840 L120 PSU CD GM	No
911401521441	SP551P LED20S 840 L60 PSD SD	Yes	911401524741	SP550P LED40S 865 L120 PSU CD GM	No
911401522941	RC550B LED20S 840 L60 PSU SD GM	No	911401524841	SP550P LED40S 840 L120 PSD CD GM	Yes
911401523941	SP551P LED20S 840 L60 PSU SD GM	No	911401524941	SP550P LED40S 865 L120 PSD CD GM	Yes
911401528341	SP551P LED20S 840 L60 PSU SD SQ	No	911401525441	SM550C LED40S 840 L120 PSD CD GM	Yes
911401528441	SP550P LED12S 840 L60 PSU SD SQ	No	911401534441	RC550B LED40S 840 L120 PSU CD CAU	No
911401528941	SP551P LED20S 840 L60 PSD SD SQ	Yes	911401534541	SP550P LED40S 840 L120 PSU CD CAU	No
911401529741	SP550P LED20S 840 L60 PSU SD CAU	No	911401534641	SP550P LED40S 840 L120 PSD CD CAU	Yes
911401530141	SP550P LED20S 840 L60 PSU SD GM SQ	No	911401522841	SM551C LED40S 840 L120 PSD SD GM	Yes
911401530341	SP551P LED20S 840 L60 PSU SD GM SQ	No	911401523141	RC550B LED40S 840 L120 PSU SD GM	No
911401531341	SP551P LED20S 840 L60 PSU SD CAU SQ	No	911401523241	RC550B LED40S 865 L120 PSU SD GM	No

Order Code	Full Product Name	Dimmable
911401524141	SP550P LED40S 840 L120 PSU SD GM	No
911401524241	SP550P LED40S 865 L120 PSU SD GM	No
911401524341	SP550P LED40S 840 L120 PSD SD GM	Yes
911401524441	SP550P LED40S 865 L120 PSD SD GM	Yes
911401524541	SP551P LED40S 840 L120 PSD SD GM	Yes
911401525041	SP550P LED40S 840 L150 PSU SD GM	No
911401525141	SP550P LED40S 840 L150 PSD SD GM	Yes
911401525241	SP551P LED45S 840 L120 PSU SI GM	No
911401525341	SP551P LED45S 840 L120 PSD SI GM	Yes
911401525541	SM550C LED40S 840 L120 PSD SD GM	Yes
911401528541	SP550P LED40S 840 L150 PSU SD CAU	No
911401529341	SP550P LED40S 840 L150 PSD SD CAU	Yes
911401529841	SP551P LED40S 840 L120 PSD SD CAU	Yes
911401529941	SP550P LED40S 840 L120 PSU SD CAU	No
911401530041	SP550P LED40S 840 L120 PSD SD CAU	Yes
911401530241	SP550P LED40S 840 L120 PSU SD GM SQ	No
911401530541	SP550P LED40S 840 L120 PSD SD GM SQ	Yes
911401530641	SP550P LED40S 865 L120 PSU SD GM SQ	No
911401530741	SP550P LED40S 840 L150 PSD SD GM SQ	Yes

Order Code	Full Product Name	Dimmable
911401530841	SP551P LED45S 840 L120 PSD SI GM SQ	Yes
911401530941	SP551P LED40S 840 L120 PSD SD GM SQ	Yes
911401531041	SP550P LED40S 840 L150 PSU SD GM SQ	No
911401531141	SP550P LED40S 865 L120 PSD SD GM SQ	Yes
911401531241	SP551P LED45S 840 L120 PSU SI GM SQ	No
911401531441	SP550P LED40S 840 L120 PSU SD CAU SQ	No
911401531541	SP550P LED40S 840 L120 PSD SD CAU SQ	Yes
911401531741	SP551P LED40S 840 L120 PSD SD CAU SQ	Yes
911401531841	SP551P LED45S 840 L120 PSU SI CAU SQ	No
911401531941	SP550P LED40S 840 L150 PSD SD CAU SQ	Yes
911401532141	SP550P LED40S 840 L150 PSU SD CAU SQ	No
911401532241	SP551P LED45S 840 L120 PSD SI CAU SQ	Yes
911401532341	SP551P LED45S 840 L120 PSD SI CAU	Yes
911401532441	SP551P LED45S 840 L120 PSU SI CAU	No
911401532641	RC550B LED40S 840 L120 PSU SD CAU	No
911401532841	SM551C LED40S 840 L120 PSD SD GM SQ	Yes
911401532941	SM550C LED40S 840 L120 PSD SD GM SQ	Yes
911401534141	SM550C LED40S 840 L120 PSD SD CAU SQ	Yes
911401534241	SM551C LED40S 840 L120 PSD SD CAU SQ	Yes

General Information

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401519241	SP550P LED25S 840 L120 PSU SD	Opal	-
911401519341	SP551P LED40S 840 L120 PSU SD	Linear-lens array in polycarbonate cover	-
911401519841	SP550P LED28S 840 L120 PSU SI	Opal	-
911401519941	SP551P LED45S 840 L120 PSU SI	Linear-lens array in polycarbonate cover	-
911401520141	RC551B LED40S 840 L120 PSU SD	Linear-lens array in polycarbonate cover	-
911401521141	SP550P LED25S 840 L120 PSD SD	Opal	-
911401521241	SP551P LED40S 840 L120 PSD SD	Linear-lens array in polycarbonate cover	-
911401521741	SP550P LED28S 840 L120 PSD SI	Opal	-
911401521841	SP551P LED45S 840 L120 PSD SI	Linear-lens array in polycarbonate cover	-
911401528241	SP550P LED25S 840 L120 PSU SD SQ	Opal	-
911401528641	SP551P LED40S 840 L120 PSU SD SQ	Linear-lens array in polycarbonate cover	-
911401528741	SP550P LED28S 840 L120 PSU SI SQ	Opal	-
911401528841	SP550P LED28S 840 L120 PSD SI SQ	Opal	-
911401529041	SP551P LED40S 840 L120 PSD SD SQ	Linear-lens array in polycarbonate cover	-
911401529141	SP551P LED45S 840 L120 PSU SI SQ	Linear-lens array in polycarbonate cover	-
911401529241	SP550P LED25S 840 L120 PSD SD SQ	Opal	-

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401529441	SP551P LED45S 840 L120 PSD SI SQ	Linear-lens array in polycarbonate cover	-
911401519441	SP550P LED12S 840 L60 PSU SD	Opal	-
911401519541	SP551P LED20S 840 L60 PSU SD	Linear-lens array in polycarbonate cover	-
911401520241	RC551B LED20S 840 L60 PSU SD	Linear-lens array in polycarbonate cover	-
911401521441	SP551P LED20S 840 L60 PSD SD	Linear-lens array in polycarbonate cover	-
911401522941	RC550B LED20S 840 L60 PSU SD GM	Opal	-
911401523941	SP551P LED20S 840 L60 PSU SD GM	Linear-lens array in polycarbonate cover	-
911401528341	SP551P LED20S 840 L60 PSU SD SQ	Linear-lens array in polycarbonate cover	-
911401528441	SP550P LED12S 840 L60 PSU SD SQ	Opal	-
911401528941	SP551P LED20S 840 L60 PSD SD SQ	Linear-lens array in polycarbonate cover	-
911401529741	SP550P LED20S 840 L60 PSU SD CAU	Opal	ENEC mark
911401530141	SP550P LED20S 840 L60 PSU SD GM SQ	Opal	-
911401530341	SP551P LED20S 840 L60 PSU SD GM SQ	Linear-lens array in polycarbonate cover	-
911401531341	SP551P LED20S 840 L60 PSU SD CAU SQ	Linear-lens array in polycarbonate cover	ENEC mark

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401531641	SP550P LED20S 840 L60 PSU SD CAU SQ	Opal	ENEC mark
911401532541	RC550B LED20S 840 L60 PSU SD CAU	Opal	ENEC mark
911401532741	SP551P LED20S 840 L60 PSU SD CAU	Linear-lens array in polycarbonate cover	ENEC mark
911401533041	SP550P LED20S 840 L60 PSU SD GM	Opal	-
911401519641	SP550P LED25S 840 L120 PSU CD	Opal	-
911401519741	SP550P LED12S 840 L60 PSU CD	Opal	-
911401520041	SP550P LED28S 840 L120 PSU CI	Opal	-
911401520341	RC550B LED25S 840 L120 PSU CD	Opal	-
911401520441	RC550B LED12S 840 L60 PSU CD	Opal	-
911401520541	SM550C LED25S 840 L120 PSU CD	Opal	-
911401520641	SM550C LED12S 840 L60 PSU CD	Opal	-
911401521541	SP550P LED25S 840 L120 PSD CD	Opal	-
911401521641	SP550P LED12S 840 L60 PSD CD	Opal	-
911401521941	SP550P LED28S 840 L120 PSD CI	Opal	-
911401522441	SM550C LED25S 840 L120 PSD CD	Opal	-
911401522641	SM550C LED20S 840 L60 PSU CD GM	Opal	-
911401523641	RC550B LED40S 840 L120 PSU CD GM	Opal	-
911401523741	RC550B LED40S 865 L120 PSU CD GM	Opal	-
911401523841	SP550P LED20S 840 L60 PSU CD GM	Opal	-
911401524641	SP550P LED40S 840 L120 PSU CD GM	Opal	-
911401524741	SP550P LED40S 865 L120 PSU CD GM	Opal	-
911401524841	SP550P LED40S 840 L120 PSD CD GM	Opal	-
911401524941	SP550P LED40S 865 L120 PSD CD GM	Opal	-
911401525441	SM550C LED40S 840 L120 PSD CD GM	Opal	-
911401534441	RC550B LED40S 840 L120 PSU CD CAU	Opal	-
911401534541	SP550P LED40S 840 L120 PSU CD CAU	Opal	-
911401534641	SP550P LED40S 840 L120 PSD CD CAU	Opal	-
911401522841	SM551C LED40S 840 L120 PSD SD GM	Linear-lens array in polycarbonate cover	-
911401523141	RC550B LED40S 840 L120 PSU SD GM	Opal	-
911401523241	RC550B LED40S 865 L120 PSU SD GM	Opal	-
911401524141	SP550P LED40S 840 L120 PSU SD GM	Opal	-

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401524241	SP550P LED40S 865 L120 PSU SD GM	Opal	-
911401524341	SP550P LED40S 840 L120 PSD SD GM	Opal	-
911401524441	SP550P LED40S 865 L120 PSD SD GM	Opal	-
911401524541	SP551P LED40S 840 L120 PSD SD GM	Linear-lens array in polycarbonate cover	-
911401525041	SP550P LED40S 840 L150 PSU SD GM	Opal	-
911401525141	SP550P LED40S 840 L150 PSD SD GM	Opal	-
911401525241	SP551P LED45S 840 L120 PSU SI GM	Linear-lens array in polycarbonate cover	-
911401525341	SP551P LED45S 840 L120 PSD SI GM	Linear-lens array in polycarbonate cover	-
911401525541	SM550C LED40S 840 L120 PSD SD GM	Opal	-
911401528541	SP550P LED40S 840 L150 PSU SD CAU	Opal	ENEC mark
911401529341	SP550P LED40S 840 L150 PSD SD CAU	Opal	ENEC mark
911401529841	SP551P LED40S 840 L120 PSD SD CAU	Linear-lens array in polycarbonate cover	ENEC mark
911401529941	SP550P LED40S 840 L120 PSU SD CAU	Opal	ENEC mark
911401530041	SP550P LED40S 840 L120 PSD SD CAU	Opal	ENEC mark
911401530241	SP550P LED40S 840 L120 PSU SD GM SQ	Opal	-
911401530541	SP550P LED40S 840 L120 PSD SD GM SQ	Opal	-
911401530641	SP550P LED40S 865 L120 PSU SD GM SQ	Opal	-
911401530741	SP550P LED40S 840 L150 PSD SD GM SQ	Opal	-
911401530841	SP551P LED45S 840 L120 PSD SI GM SQ	Linear-lens array in polycarbonate cover	-
911401530941	SP551P LED40S 840 L120 PSD SD GM SQ	Linear-lens array in polycarbonate cover	-
911401531041	SP550P LED40S 840 L150 PSU SD GM SQ	Opal	-
911401531141	SP550P LED40S 865 L120 PSD SD GM SQ	Opal	-
911401531241	SP551P LED45S 840 L120 PSU SI GM SQ	Linear-lens array in polycarbonate cover	-
911401531441	SP550P LED40S 840 L120 PSU SD CAU SQ	Opal	ENEC mark
911401531541	SP550P LED40S 840 L120 PSD SD CAU SQ	Opal	ENEC mark

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401531741	SP551P LED40S 840 L120 PSD SD CAU SQ	Linear-lens array in polycarbonate cover	ENEC mark
911401531841	SP551P LED45S 840 L120 PSU SI CAU SQ	Linear-lens array in polycarbonate cover	ENEC mark
911401531941	SP550P LED40S 840 L150 PSD SD CAU SQ	Opal	ENEC mark
911401532141	SP550P LED40S 840 L150 PSU SD CAU SQ	Opal	ENEC mark
911401532241	SP551P LED45S 840 L120 PSD SI CAU SQ	Linear-lens array in polycarbonate cover	ENEC mark
911401532341	SP551P LED45S 840 L120 PSD SI CAU	Linear-lens array in polycarbonate cover	ENEC mark

Order Code	Full Product Name	Optical cover/lens type	ENEC mark
911401532441	SP551P LED45S 840 L120 PSU SI CAU	Linear-lens array in polycarbonate cover	ENEC mark
911401532641	RC550B LED40S 840 L120 PSU SD CAU	Opal	ENEC mark
911401532841	SM551C LED40S 840 L120 PSD SD GM SQ	Linear-lens array in polycarbonate cover	-
911401532941	SM550C LED40S 840 L120 PSD SD GM SQ	Opal	-
911401534141	SM550C LED40S 840 L120 PSD SD CAU SQ	Opal	ENEC mark
911401534241	SM551C LED40S 840 L120 PSD SD CAU SQ	Linear-lens array in polycarbonate cover	ENEC mark

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401519241	SP550P LED25S 840 L120 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401519341	SP551P LED40S 840 L120 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401519841	SP550P LED28S 840 L120 PSU SI	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	107.69 lm/W	2800 lm
911401519941	SP551P LED45S 840 L120 PSU SI	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401520141	RC551B LED40S 840 L120 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401521141	SP550P LED25S 840 L120 PSD SD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401521241	SP551P LED40S 840 L120 PSD SD	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401521741	SP550P LED28S 840 L120 PSD SI	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	107.69 lm/W	2800 lm
911401521841	SP551P LED45S 840 L120 PSD SI	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401528241	SP550P LED25S 840 L120 PSU SD SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401528641	SP551P LED40S 840	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401528741	SP550P LED28S 840 L120 PSU SI SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	107.69 lm/W	2800 lm
911401528841	SP550P LED28S 840 L120 PSD SI SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	107.69 lm/W	2800 lm
911401529041	SP551P LED40S 840 L120 PSD SD SQ	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401529141	SP551P LED45S 840 L120 PSU SI SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401529241	SP550P LED25S 840 L120 PSD SD SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401529441	SP551P LED45S 840 L120 PSD SI SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401519441	SP550P LED12S 840 L60 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401519541	SP551P LED20S 840 L60 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401520241	RC551B LED20S 840 L60 PSU SD	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401521441	SP551P LED20S 840 L60 PSD SD	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401522941	RC550B LED20S 840 L60 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401523941	SP551P LED20S 840 L60 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401528341	SP551P LED20S 840 L60 PSU SD SQ	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401528441	SP550P LED12S 840 L60 PSU SD SQ	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401528941	SP551P LED20S 840 L60 PSD SD SQ	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401529741	SP550P LED20S 840 L60 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401530141	SP550P LED20S 840 L60 PSU SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401530341	SP551P LED20S 840 L60 PSU SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401531341	SP551P LED20S 840 L60 PSU SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401531641	SP550P LED20S 840 L60 PSU SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401532541	RC550B LED20S 840 L60 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401532741	SP551P LED20S 840 L60 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	111.11 lm/W	2000 lm
911401533041	SP550P LED20S 840 L60 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401519641	SP550P LED25S 840 L120 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401519741	SP550P LED12S 840 L60 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401520041	SP550P LED28S 840 L120 PSU CI (uplight< 4)	(0.38, 0.38) SDCM< 3	4000 K	153.85 lm/W	4000 lm
911401520341	RC550B LED25S 840 L120 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401520441	RC550B LED12S 840 L60 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401520541	SM550C LED25S 840 L120 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401520641	SM550C LED12S 840 L60 PSU CD	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401521541	SP550P LED25S 840 L120 PSD CD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401521641	SP550P LED12S 840 L60 PSD CD	(0.38, 0.38) SDCM< 3	4000 K	89.29 lm/W	1250 lm
911401521941	SP550P LED28S 840 L120 PSD CI (uplight< 4)	(0.38, 0.38) SDCM< 3	4000 K	107.69 lm/W	2800 lm
911401522441	SM550C LED25S 840 L120 PSD CD	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	2500 lm
911401522641	SM550C LED20S 840 L60 PSU CD GM	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401523641	RC550B LED40S 840 L120 PSU CD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401523741	RC550B LED40S 865 L120 PSU CD GM	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401523841	SP550P LED20S 840 L60 PSU CD GM	(0.38, 0.38) SDCM< 3	4000 K	90.91 lm/W	2000 lm
911401524641	SP550P LED40S 840 L120 PSU CD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401524741	SP550P LED40S 865 L120 PSU CD GM	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401524841	SP550P LED40S 840 L120 PSD CD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401524941	SP550P LED40S 865 L120 PSD CD GM	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401525441	SM550C LED40S 840 L120 PSD CD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401534441	RC550B LED40S 840 L120 PSU CD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401534541	SP550P LED40S 840 L120 PSU CD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401534641	SP550P LED40S 840 L120 PSD CD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401522841	SM551C LED40S 840 L120 PSD SD GM	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401523141	RC550B LED40S 840 L120 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401523241	RC550B LED40S 865	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	L120 PSU SD GM				
911401524141	SP550P LED40S 840 L120 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401524241	SP550P LED40S 865 L120 PSU SD GM	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401524341	SP550P LED40S 840 L120 PSD SD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401524441	SP550P LED40S 865 L120 PSD SD GM	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401524541	SP551P LED40S 840 L120 PSD SD GM	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401525041	SP550P LED40S 840 L150 PSU SD GM	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401525141	SP550P LED40S 840 L150 PSD SD GM	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401525241	SP551P LED45S 840 L120 PSU SI GM	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401525341	SP551P LED45S 840 L120 PSD SI GM	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401525541	SM550C LED40S 840 L120 PSD SD GM	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401528541	SP550P LED40S 840 L150 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401529341	SP550P LED40S 840 L150 PSD SD CAU	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401529841	SP551P LED40S 840 L120 PSD SD CAU	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401529941	SP550P LED40S 840 L120 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401530041	SP550P LED40S 840 L120 PSD SD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401530241	SP550P LED40S 840 L120 PSU SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401530541	SP550P LED40S 840 L120 PSD SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401530641	SP550P LED40S 865 L120 PSU SD GM SQ	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401530741	SP550P LED40S 840 L150 PSD SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401530841	SP551P LED45S 840 L120 PSD SI GM SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401530941	SP551P LED40S 840 L120 PSD SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401531041	SP550P LED40S 840 L150 PSU SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401531141	SP550P LED40S 865 L120 PSD SD GM SQ	(0.31, 0.33) SDCM< 3	6500 K	97.56 lm/W	4000 lm
911401531241	SP551P LED45S 840 L120 PSU SI GM SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401531441	SP550P LED40S 840	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	L120 PSU SD CAU SQ				
911401531541	SP550P LED40S 840 L120 PSD SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401531741	SP551P LED40S 840 L120 PSD SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401531841	SP551P LED45S 840 L120 PSU SI CAU SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401531941	SP550P LED40S 840 L150 PSD SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401532141	SP550P LED40S 840 L150 PSU SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	100 lm/W	4000 lm
911401532241	SP551P LED45S 840 L120 PSD SI CAU SQ	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401532341	SP551P LED45S 840 L120 PSD SI CAU	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401532441	SP551P LED45S 840 L120 PSU SI CAU	(0.38, 0.38) SDCM< 3 (uplight< 4)	4000 K	125 lm/W	4500 lm
911401532641	RC550B LED40S 840 L120 PSU SD CAU	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401532841	SM551C LED40S 840 L120 PSD SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	117.65 lm/W	4000 lm
911401532941	SM550C LED40S 840 L120 PSD SD GM SQ	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm
911401534141	SM550C LED40S 840 L120 PSD SD CAU SQ	(0.38, 0.38) SDCM< 3	4000 K	97.56 lm/W	4000 lm

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
911401534241	SM551C LED40S 840	(0.38, 0.38)	4000 K	117.65 lm/W	4000 lm
	SDCM < 3				

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux
	L120 PSD SD				
	CAU SQ				

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401519241	SP550P LED25S 840 L120 PSU SD	25 W
911401519341	SP551P LED40S 840 L120 PSU SD	34 W
911401519841	SP550P LED28S 840 L120 PSU SI	26 W
911401519941	SP551P LED45S 840 L120 PSU SI	36 W
911401520141	RC551B LED40S 840 L120 PSU SD	34 W
911401521141	SP550P LED25S 840 L120 PSD SD	25 W
911401521241	SP551P LED40S 840 L120 PSD SD	34 W
911401521741	SP550P LED28S 840 L120 PSD SI	26 W
911401521841	SP551P LED45S 840 L120 PSD SI	36 W
911401528241	SP550P LED25S 840 L120 PSU SD SQ	25 W
911401528641	SP551P LED40S 840 L120 PSU SD SQ	34 W
911401528741	SP550P LED28S 840 L120 PSU SI SQ	26 W
911401528841	SP550P LED28S 840 L120 PSD SI SQ	26 W
911401529041	SP551P LED40S 840 L120 PSD SD SQ	34 W
911401529141	SP551P LED45S 840 L120 PSU SI SQ	36 W
911401529241	SP550P LED25S 840 L120 PSD SD SQ	25 W
911401529441	SP551P LED45S 840 L120 PSD SI SQ	36 W
911401519441	SP550P LED12S 840 L60 PSU SD	14 W
911401519541	SP551P LED20S 840 L60 PSU SD	18 W
911401520241	RC551B LED20S 840 L60 PSU SD	18 W
911401521441	SP551P LED20S 840 L60 PSD SD	18 W
911401522941	RC550B LED20S 840 L60 PSU SD GM	22 W
911401523941	SP551P LED20S 840 L60 PSU SD GM	18 W
911401528341	SP551P LED20S 840 L60 PSU SD SQ	18 W
911401528441	SP550P LED12S 840 L60 PSU SD SQ	14 W
911401528941	SP551P LED20S 840 L60 PSD SD SQ	18 W
911401529741	SP550P LED20S 840 L60 PSU SD CAU	22 W
911401530141	SP550P LED20S 840 L60 PSU SD GM SQ	22 W
911401530341	SP551P LED20S 840 L60 PSU SD GM SQ	18 W
911401531341	SP551P LED20S 840 L60 PSU SD CAU SQ	18 W
911401531641	SP550P LED20S 840 L60 PSU SD CAU SQ	22 W
911401532541	RC550B LED20S 840 L60 PSU SD CAU	22 W
911401532741	SP551P LED20S 840 L60 PSU SD CAU	18 W
911401533041	SP550P LED20S 840 L60 PSU SD GM	22 W
911401519641	SP550P LED25S 840 L120 PSU CD	25 W
911401519741	SP550P LED12S 840 L60 PSU CD	14 W
911401520041	SP550P LED28S 840 L120 PSU CI	26 W
911401520341	RC550B LED25S 840 L120 PSU CD	25 W
911401520441	RC550B LED12S 840 L60 PSU CD	14 W
911401520541	SM550C LED25S 840 L120 PSU CD	25 W
911401520641	SM550C LED12S 840 L60 PSU CD	14 W
911401521541	SP550P LED25S 840 L120 PSD CD	25 W
911401521641	SP550P LED12S 840 L60 PSD CD	14 W
911401521941	SP550P LED28S 840 L120 PSD CI	26 W

Order Code	Full Product Name	Initial input power
911401522441	SM550C LED25S 840 L120 PSD CD	25 W
911401522641	SM550C LED20S 840 L60 PSU CD GM	22 W
911401523641	RC550B LED40S 840 L120 PSU CD GM	41 W
911401523741	RC550B LED40S 865 L120 PSU CD GM	41 W
911401523841	SP550P LED20S 840 L60 PSU CD GM	22 W
911401524641	SP550P LED40S 840 L120 PSU CD GM	41 W
911401524741	SP550P LED40S 865 L120 PSU CD GM	41 W
911401524841	SP550P LED40S 840 L120 PSD CD GM	41 W
911401524941	SP550P LED40S 865 L120 PSD CD GM	41 W
911401525441	SM550C LED40S 840 L120 PSD CD GM	41 W
911401534441	RC550B LED40S 840 L120 PSU CD CAU	41 W
911401534541	SP550P LED40S 840 L120 PSU CD CAU	41 W
911401534641	SP550P LED40S 840 L120 PSD CD CAU	41 W
911401522841	SM551C LED40S 840 L120 PSD SD GM	34 W
911401523141	RC550B LED40S 840 L120 PSU SD GM	41 W
911401523241	RC550B LED40S 865 L120 PSU SD GM	41 W
911401524141	SP550P LED40S 840 L120 PSU SD GM	41 W
911401524241	SP550P LED40S 865 L120 PSU SD GM	41 W
911401524341	SP550P LED40S 840 L120 PSD SD GM	41 W
911401524441	SP550P LED40S 865 L120 PSD SD GM	41 W
911401524541	SP551P LED40S 840 L120 PSD SD GM	34 W
911401525041	SP550P LED40S 840 L150 PSU SD GM	40 W
911401525141	SP550P LED40S 840 L150 PSD SD GM	40 W
911401525241	SP551P LED45S 840 L120 PSU SI GM	36 W
911401525341	SP551P LED45S 840 L120 PSD SI GM	36 W
911401525541	SM550C LED40S 840 L120 PSD SD GM	41 W
911401528541	SP550P LED40S 840 L150 PSU SD CAU	40 W
911401529341	SP550P LED40S 840 L150 PSD SD CAU	40 W
911401529841	SP551P LED40S 840 L120 PSD SD CAU	34 W
911401529941	SP550P LED40S 840 L120 PSU SD CAU	41 W
911401530041	SP550P LED40S 840 L120 PSD SD CAU	41 W
911401530241	SP550P LED40S 840 L120 PSU SD GM SQ	41 W
911401530541	SP550P LED40S 840 L120 PSD SD GM SQ	41 W
911401530641	SP550P LED40S 865 L120 PSU SD GM SQ	41 W
911401530741	SP550P LED40S 840 L150 PSD SD GM SQ	40 W
911401530841	SP551P LED45S 840 L120 PSD SI GM SQ	36 W
911401530941	SP551P LED40S 840 L120 PSD SD GM SQ	34 W
911401531041	SP550P LED40S 840 L150 PSU SD GM SQ	40 W
911401531141	SP550P LED40S 865 L120 PSD SD GM SQ	41 W
911401531241	SP551P LED45S 840 L120 PSU SI GM SQ	36 W
911401531441	SP550P LED40S 840 L120 PSU SD CAU SQ	41 W
911401531541	SP550P LED40S 840 L120 PSD SD CAU SQ	41 W
911401531741	SP551P LED40S 840 L120 PSD SD CAU SQ	34 W
911401531841	SP551P LED45S 840 L120 PSU SI CAU SQ	36 W

SlimBalance

Order Code	Full Product Name	Initial input power
911401531941	SP550P LED40S 840 L150 PSD SD CAU SQ	40 W
911401532141	SP550P LED40S 840 L150 PSU SD CAU SQ	40 W
911401532241	SP551P LED45S 840 L120 PSD SI CAU SQ	36 W
911401532341	SP551P LED45S 840 L120 PSD SI CAU	36 W
911401532441	SP551P LED45S 840 L120 PSU SI CAU	36 W

Order Code	Full Product Name	Initial input power
911401532641	RC550B LED40S 840 L120 PSU SD CAU	41 W
911401532841	SM551C LED40S 840 L120 PSD SD GM SQ	34 W
911401532941	SM550C LED40S 840 L120 PSD SD GM SQ	41 W
911401534141	SM550C LED40S 840 L120 PSD SD CAU SQ	41 W
911401534241	SM551C LED40S 840 L120 PSD SD CAU SQ	34 W

