



Miniaturised downlight with leading optical performance and great diversity

LuxSpace G4

LuxSpace Gen4 is the a new LED downlight range combining light comfort and leading performance with luxury appearance

Benefits

- Visual comfort
- Multiple options for various applications
- Smart lighting

Features

- Miniaturised form factor
- High optical efficiency
- Great product diversity
- Tunable white

Application

- Office
- shopping centre
- hotel
- retail

Versions



DN58XB DN59XB D100 D125

Application Conditions	
Ambient temperature range	-20 to +40 °C
Approval and Application	
Mech. impact protection code	IK03
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
CE mark	CE mark
Optical cover/lens type	Reflector
Driver included	Yes
Flammability mark	F
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Mechanical and Housing	
Colour	White and black
Over Time Performance (IEC Compliant)	
Median useful life L80B50	50000 h
Median useful life L90B50	21000 h

Application Conditions

Order Code	Full Product Name	Maximum dim level
01539941	DN590B LED15/840 PSD C D125 WH WB GC	1%
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	Not applicable
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	Not applicable
01548741	DN588B LED6/840 PSD C D125 WH WB GM	1%
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	Not applicable
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	Not applicable
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	1%
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	1%
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	1%
01543341	DN591B LED20/830 PSD C D150 WH WB GC	1%
01545441	DN592B LED25/840 PSD C D150 WH MB GC	1%
01546241	DN593B LED30/940 PSU C D200 WH WB GC	Not applicable
01546441	DN593B LED30/840 PSU C D200 WH MB GC	Not applicable
01546841	DN594B LED40/840 PSU C D200 WH WB GC	Not applicable
01547741	DN589B LED10/830 PSU C D150 WH WB GM	Not applicable
01547841	DN589B LED10/840 PSU C D150 WH WB GM	Not applicable
01547941	DN590B LED15/830 PSU C D150 WH WB GM	Not applicable
01548041	DN590B LED15/840 PSU C D150 WH WB GM	Not applicable
01548141	DN591B LED20/830 PSU C D200 WH WB GM	Not applicable
01548241	DN591B LED20/840 PSU C D200 WH WB GM	Not applicable
01548341	DN593B LED30/830 PSU C D200 WH WB GM	Not applicable
01548441	DN593B LED30/840 PSU C D200 WH WB GM	Not applicable
01548541	DN594B LED40/830 PSU C D200 WH WB GM	Not applicable
01548641	DN594B LED40/840 PSU C D200 WH WB GM	Not applicable
01548841	DN589B LED10/830 PSD C D150 WH WB GM	1%
01548941	DN589B LED10/840 PSD C D150 WH WB GM	1%
01549041	DN590B LED15/840 PSD C D150 WH WB GM	1%
01549141	DN591B LED20/830 PSD C D200 WH WB GM	1%
01549241	DN591B LED20/840 PSD C D200 WH WB GM	1%
01549341	DN593B LED30/840 PSD C D200 WH WB GM	1%
01549441	DN594B LED40/840 PSD C D200 WH WB GM	1%
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	Not applicable
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	Not applicable
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	Not applicable
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	Not applicable

Order Code	Full Product Name	Maximum dim level
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	Not applicable
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	Not applicable
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	Not applicable
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	Not applicable
01550641	DN589B LED10/830 PSD C D150 WH WB WP GM	1%
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	1%
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	1%
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	1%
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	1%
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	1%
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	1%
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	Not applicable

Approval and Application

Order Code	Full Product Name	Ingress protection code
01539941	DN590B LED15/840 PSD C D125 WH WB GC	IP20
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	IP20
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	IP20
01548741	DN588B LED6/840 PSD C D125 WH WB GM	IP20
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	IP54/20
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	IP54/20
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	IP54/20
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	IP20
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	IP20
01543341	DN591B LED20/830 PSD C D150 WH WB GC	IP20
01545441	DN592B LED25/840 PSD C D150 WH MB GC	IP20
01546241	DN593B LED30/940 PSU C D200 WH WB GC	IP20
01546441	DN593B LED30/840 PSU C D200 WH MB GC	IP20
01546841	DN594B LED40/840 PSU C D200 WH WB GC	IP20
01547741	DN589B LED10/830 PSU C D150 WH WB GM	IP20
01547841	DN589B LED10/840 PSU C D150 WH WB GM	IP20
01547941	DN590B LED15/830 PSU C D150 WH WB GM	IP20
01548041	DN590B LED15/840 PSU C D150 WH WB GM	IP20
01548141	DN591B LED20/830 PSU C D200 WH WB GM	IP20
01548241	DN591B LED20/840 PSU C D200 WH WB GM	IP20
01548341	DN593B LED30/830 PSU C D200 WH WB GM	IP20
01548441	DN593B LED30/840 PSU C D200 WH WB GM	IP20
01548541	DN594B LED40/830 PSU C D200 WH WB GM	IP20
01548641	DN594B LED40/840 PSU C D200 WH WB GM	IP20

Order Code	Full Product Name	Ingress protection code
01548841	DN589B LED10/830 PSD C D150 WH WB GM	IP20
01548941	DN589B LED10/840 PSD C D150 WH WB GM	IP20
01549041	DN590B LED15/840 PSD C D150 WH WB GM	IP20
01549141	DN591B LED20/830 PSD C D200 WH WB GM	IP20
01549241	DN591B LED20/840 PSD C D200 WH WB GM	IP20
01549341	DN593B LED30/840 PSD C D200 WH WB GM	IP20
01549441	DN594B LED40/840 PSD C D200 WH WB GM	IP20
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	IP54/20
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	IP54/20
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	IP54/20
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	IP54/20
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	IP54/20
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	IP54/20
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	IP54/20
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	IP54/20
01550641	DN589B LED10/830 PSD C D150 WH WB WP GM	IP54/20
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	IP54/20
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	IP54/20
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	IP54/20
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	IP54/20
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	IP54/20
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	IP54/20
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	IP20

Controls and Dimming

Order Code	Full Product Name	Dimmable
01539941	DN590B LED15/840 PSD C D125 WH WB GC	Yes
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	No
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	No
01548741	DN588B LED6/840 PSD C D125 WH WB GM	Yes
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	No
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	No

Order Code	Full Product Name	Dimmable
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	Yes
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	Yes
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	Yes
01543341	DN591B LED20/830 PSD C D150 WH WB GC	Yes
01545441	DN592B LED25/840 PSD C D150 WH MB GC	Yes
01546241	DN593B LED30/940 PSU C D200 WH WB GC	No

Order Code	Full Product Name	Dimmable
01546441	DN593B LED30/840 PSU C D200 WH MB GC	No
01546841	DN594B LED40/840 PSU C D200 WH WB GC	No
01547741	DN589B LED10/830 PSU C D150 WH WB GM	No
01547841	DN589B LED10/840 PSU C D150 WH WB GM	No
01547941	DN590B LED15/830 PSU C D150 WH WB GM	No
01548041	DN590B LED15/840 PSU C D150 WH WB GM	No
01548141	DN591B LED20/830 PSU C D200 WH WB GM	No
01548241	DN591B LED20/840 PSU C D200 WH WB GM	No
01548341	DN593B LED30/830 PSU C D200 WH WB GM	No
01548441	DN593B LED30/840 PSU C D200 WH WB GM	No
01548541	DN594B LED40/830 PSU C D200 WH WB GM	No
01548641	DN594B LED40/840 PSU C D200 WH WB GM	No
01548841	DN589B LED10/830 PSD C D150 WH WB GM	Yes
01548941	DN589B LED10/840 PSD C D150 WH WB GM	Yes
01549041	DN590B LED15/840 PSD C D150 WH WB GM	Yes
01549141	DN591B LED20/830 PSD C D200 WH WB GM	Yes
01549241	DN591B LED20/840 PSD C D200 WH WB GM	Yes
01549341	DN593B LED30/840 PSD C D200 WH WB GM	Yes

Order Code	Full Product Name	Dimmable
01549441	DN594B LED40/840 PSD C D200 WH WB GM	Yes
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	No
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	No
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	No
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	No
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	No
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	No
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	No
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	No
01550641	DN589B LED10/830 PSD C D150 WH WB WP GM	Yes
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	Yes
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	Yes
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	Yes
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	Yes
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	Yes
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	Yes
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	No

General Information

Order Code	Full Product Name	Beam angle of light source	Protection class IEC	ENEC mark	Optic type
01539941	DN590B LED15/840 PSD C D125 WH WB GC	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548741	DN588B LED6/840 PSD C D125 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	32°	Safety class II (II)	-	Faceted reflector with beam angle 36°
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	62°	Safety class II (II)	-	Faceted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Protection class IEC	ENEC mark	Optic type
01543341	DN591B LED20/830 PSD C D150 WH WB GC	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01545441	DN592B LED25/840 PSD C D150 WH MB GC	-	Safety class I (I)	-	Faceted reflector with beam angle 30°
01546241	DN593B LED30/940 PSU C D200 WH WB GC	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01546441	DN593B LED30/840 PSU C D200 WH MB GC	-	Safety class II (II)	-	Faceted reflector with beam angle 30°
01546841	DN594B LED40/840 PSU C D200 WH WB GC	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01547741	DN589B LED10/830 PSU C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01547841	DN589B LED10/840 PSU C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01547941	DN590B LED15/830 PSU C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548041	DN590B LED15/840 PSU C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Protection class IEC	ENEC mark	Optic type
01548141	DN591B LED20/830 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548241	DN591B LED20/840 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548341	DN593B LED30/830 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548441	DN593B LED30/840 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548541	DN594B LED40/830 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548641	DN594B LED40/840 PSU C D200 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548841	DN589B LED10/830 PSD C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01548941	DN589B LED10/840 PSD C D150 WH WB GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01549041	DN590B LED15/840 PSD C D150 WH WB GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01549141	DN591B LED20/830 PSD C D200 WH WB GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01549241	DN591B LED20/840 PSD C D200 WH WB GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01549341	DN593B LED30/840 PSD C D200 WH WB GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01549441	DN594B LED40/840 PSD C D200 WH WB GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°

Order Code	Full Product Name	Beam angle of light source	Protection class IEC	ENEC mark	Optic type
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550641	DN589B LED10/830 PSD C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	-	Safety class II (II)	-	Faceted reflector with beam angle 60°
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	-	Safety class I (I)	-	Faceted reflector with beam angle 60°
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	-	Safety class II (II)	-	Faceted reflector with beam angle 60°

Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
01539941	DN590B LED15/840 PSD C D125 WH WB GC	-	4000 K	>90	111 lm/W
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	-	3000 K	>80	109 lm/W
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	-	4000 K	>80	114 lm/W
01548741	DN588B LED6/840 PSD C D125 WH WB GM	-	4000 K	>80	114 lm/W
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	-	3000 K	>80	103 lm/W
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	-	4000 K	>80	108 lm/W
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	-	4000 K	>80	108 lm/W
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	-	6500 K	>80	88 lm/W
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	-	2700 K	>80	88 lm/W
01543341	DN591B LED20/830 PSD C D150 WH WB GC	-	3000 K	>80	109 lm/W
01545441	DN592B LED25/840 PSD C D150 WH MB GC	-	4000 K	>90	113 lm/W
01546241	DN593B LED30/940 PSU C D200 WH WB GC	-	4000 K	>90	91 lm/W
01546441	DN593B LED30/840 PSU C D200 WH MB GC	-	4000 K	>80	105 lm/W
01546841	DN594B LED40/840 PSU C D200 WH WB GC	-	4000 K	>80	108 lm/W
01547741	DN589B LED10/830 PSU C D150 WH WB GM	-	3000 K	>80	118 lm/W
01547841	DN589B LED10/840 PSU C D150 WH WB GM	-	4000 K	>80	125 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
01547941	DN590B LED15/830 PSU C D150 WH WB GM	-	3000 K	>80	176 lm/W
01548041	DN590B LED15/840 PSU C D150 WH WB GM	-	4000 K	>80	185 lm/W
01548141	DN591B LED20/830 PSU C D200 WH WB GM	-	3000 K	>80	113 lm/W
01548241	DN591B LED20/840 PSU C D200 WH WB GM	-	4000 K	>80	119 lm/W
01548341	DN593B LED30/830 PSU C D200 WH WB GM	-	3000 K	>80	102 lm/W
01548441	DN593B LED30/840 PSU C D200 WH WB GM	-	4000 K	>80	105 lm/W
01548541	DN594B LED40/830 PSU C D200 WH WB GM	-	3000 K	>80	103 lm/W
01548641	DN594B LED40/840 PSU C D200 WH WB GM	-	4000 K	>80	108 lm/W
01548841	DN589B LED10/830 PSD C D150 WH WB GM	-	3000 K	>80	118 lm/W
01548941	DN589B LED10/840 PSD C D150 WH WB GM	-	4000 K	>80	125 lm/W
01549041	DN590B LED15/840 PSD C D150 WH WB GM	-	4000 K	>80	115 lm/W
01549141	DN591B LED20/830 PSD C D200 WH WB GM	-	3000 K	>80	105 lm/W
01549241	DN591B LED20/840 PSD C D200 WH WB GM	-	4000 K	>80	111 lm/W
01549341	DN593B LED30/840 PSD C D200 WH WB GM	-	4000 K	>80	105 lm/W
01549441	DN594B LED40/840 PSD C D200 WH WB GM	-	4000 K	>80	108 lm/W
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	-	3000 K	>80	112 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	-	4000 K	>80	119 lm/W
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	-	3000 K	>80	104 lm/W
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	-	4000 K	>80	109 lm/W
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	-	3000 K	>80	107 lm/W
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	-	4000 K	>80	113 lm/W
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	-	4000 K	>80	99 lm/W
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	-	4000 K	>80	103 lm/W
01550641	DN589B LED10/830 PSD C	-	3000 K	>80	112 lm/W

Order Code	Full Product Name	Initial chromaticity	Init. Corr. Colour Temperature	Init. Colour Rendering Index	Initial LED luminaire efficacy
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	-	4000 K	>80	119 lm/W
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	-	4000 K	>80	109 lm/W
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	-	3000 K	>80	107 lm/W
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	-	4000 K	>80	113 lm/W
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	-	4000 K	>80	99 lm/W
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	-	4000 K	>80	103 lm/W
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	-	4000 K	>80	132 lm/W

Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial luminous flux	Luminous flux tolerance	Initial input power
01539941	DN590B LED15/840 PSD C D125 WH WB GC	1500 lm	+/-10%	13.5 W
01547541	DN588B LED6/830 PSU C D125 C WH WB GM	720 lm	+/-10%	6.6 W
01547641	DN588B LED6/840 PSU C D125 C WH WB GM	750 lm	+/-10%	6.6 W
01548741	DN588B LED6/840 PSD C D125 WH WB GM	750 lm	+/-10%	6.6 W
01549541	DN588B LED6/830 PSU C D125 WH WB WP GM	680 lm	+/-10%	6.6 W
01549641	DN588B LED6/840 PSU C D125 WH WB WP GM	710 lm	+/-10%	6.6 W
01550541	DN588B LED6/840 PSD C D125 WH WB WP GM	710 lm	+/-10%	6.6 W

Order Code	Full Product Name	Initial luminous flux	Luminous flux tolerance	Initial input power
01542251	DN591B LED20/TWH PSD C D150 WH MB GM	2200 lm	+/-15%	25 W
01542551	DN591B LED20/TWH PSD C D150 WH WB GM	2200 lm	+/-15%	25 W
01543341	DN591B LED20/830 PSD C D150 WH WB GC	2100 lm	+/-10%	19.3 W
01545441	DN592B LED25/840 PSD C D150 WH MB GC	2600 lm	+/-10%	23 W
01546241	DN593B LED30/940 PSU C D200 WH WB GC	2970 lm	+/-10%	32.5 W
01546441	DN593B LED30/840 PSU C D200 WH MB GC	3400 lm	+/-10%	32.5 W
01546841	DN594B LED40/840 PSU C D200 WH WB GC	4300 lm	+/-10%	39.7 W

Order Code	Full Product Name	Initial luminous flux	Luminous flux tolerance	Initial input power
01547741	DN589B LED10/830 PSU C D150 WH WB GM	990 lm	+/-10%	8.4 W
01547841	DN589B LED10/840 PSU C D150 WH WB GM	1050 lm	+/-10%	8.4 W
01547941	DN590B LED15/830 PSU C D150 WH WB GM	1480 lm	+/-10%	8.4 W
01548041	DN590B LED15/840 PSU C D150 WH WB GM	1550 lm	+/-10%	8.4 W
01548141	DN591B LED20/830 PSU C D200 WH WB GM	2030 lm	+/-10%	18 W
01548241	DN591B LED20/840 PSU C D200 WH WB GM	2150 lm	+/-10%	18 W
01548341	DN593B LED30/830 PSU C D200 WH WB GM	3300 lm	+/-10%	32.5 W
01548441	DN593B LED30/840 PSU C D200 WH WB GM	3400 lm	+/-10%	32.5 W
01548541	DN594B LED40/830 PSU C D200 WH WB GM	4100 lm	+/-10%	39.7 W
01548641	DN594B LED40/840 PSU C D200 WH WB GM	4300 lm	+/-10%	39.7 W
01548841	DN589B LED10/830 PSD C D150 WH WB GM	990 lm	+/-10%	8.4 W
01548941	DN589B LED10/840 PSD C D150 WH WB GM	1050 lm	+/-10%	8.4 W
01549041	DN590B LED15/840 PSD C D150 WH WB GM	1550 lm	+/-10%	13.5 W
01549141	DN591B LED20/830 PSD C D200 WH WB GM	2030 lm	+/-10%	19.3 W
01549241	DN591B LED20/840 PSD C D200 WH WB GM	2150 lm	+/-10%	19.3 W
01549341	DN593B LED30/840 PSD C D200 WH WB GM	3400 lm	+/-10%	32.5 W
01549441	DN594B LED40/840 PSD C D200 WH WB GM	4300 lm	+/-10%	39.7 W

Order Code	Full Product Name	Initial luminous flux	Luminous flux tolerance	Initial input power
01549741	DN589B LED10/830 PSU C D150 WH WB WP GM	940 lm	+/-10%	8.4 W
01549841	DN589B LED10/840 PSU C D150 WH WB WP GM	1000 lm	+/-10%	8.4 W
01549941	DN590B LED15/830 PSU C D150 WH WB WP GM	1410 lm	+/-10%	13.5 W
01550041	DN590B LED15/840 PSU C D150 WH WB WP GM	1470 lm	+/-10%	13.5 W
01550141	DN591B LED20/830 PSU C D200 WH WB WP GM	1930 lm	+/-10%	18 W
01550241	DN591B LED20/840 PSU C D200 WH WB WP GM	2040 lm	+/-10%	18 W
01550341	DN593B LED30/840 PSU C D200 WH WB WP GM	3230 lm	+/-10%	32.5 W
01550441	DN594B LED40/840 PSU C D200 WH WB WP GM	4090 lm	+/-10%	39.7 W
01550641	DN589B LED10/830 PSD C D150 WH WB WP GM	940 lm	+/-10%	8.4 W
01550741	DN589B LED10/840 PSD C D150 WH WB WP GM	1000 lm	+/-10%	8.4 W
01550841	DN590B LED15/840 PSD C D150 WH WB WP GM	1470 lm	+/-10%	13.5 W
01550941	DN591B LED20/830 PSD C D200 WH WB WP GM	1930 lm	+/-10%	18 W
01551041	DN591B LED20/840 PSD C D200 WH WB WP GM	2040 lm	+/-10%	18 W
01551141	DN593B LED30/840 PSD C D200 WH WB WP GM	3230 lm	+/-10%	32.5 W
01551241	DN594B LED40/840 PSD C D200 WH WB WP GM	4090 lm	+/-10%	39.7 W
01551941	DN594B LED40/840 PSU C D200 WH WB CAU	4300 lm	+/-10%	32.5 W

