



Your everyday LEDspot GU10

Essential LEDspot GU10

Essential LEDspots are compatible with most existing fixtures with a GU10 socket and are designed as a retrofit replacement for halogen spots. Essential LEDspots deliver significant energy savings and minimize initial investment.

Benefits

- Up to 90% energy saving compared with traditional halogen lamps
- Lower maintenance costs
- Low initial investment

Features

- Easy retrofit
- Lifetime up to 15,000 hours
- Non-dimmable
- UV- and IR-free light

Application

- Domestic applications

Essential LEDspot GU10

Versions



LEDspot 25W GU10 MR11 827 36D ND



LEDspots LATAM1 AR111 GU10






MZD LED 50W GU10 830 60D ND



LEDspots MV PAR16 GU10

Dimensional drawing







Product	D	C
LEDspot GU10 6-50W D 830 35D 120V 1PF/6	50 mm	53 mm
LEDspot GU10 6-50W D 830 35D 120V 3CT/6	50 mm	53 mm
LEDspot GU10 6-50W D 830 35D 120V PF	50 mm	53 mm
LEDspot GU10 6-50W D 865 35D 120V 1BC	50 mm	54 mm
LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50 mm	54 mm
LEDspot GU10 6-50W D 865 35D 120V 3CT/6	50 mm	54 mm

Product	D	C
ESS LEDspots 50W GU10 827 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 830 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 840 36D ND TR	50 mm	54 mm
ESS LEDspots 50W GU10 865 36D ND TR	50 mm	54 mm
EcoBright LED GU10 50W 827 36D 2BC/5	50 mm	54 mm
LEDspot 5-50W GU10 827 100-240V 36D ND	50 mm	54 mm
LEDspot 5-50W GU10 865 100-240V 36D ND	50 mm	54 mm
LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	50 mm	54 mm
LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	50 mm	54 mm
LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	50 mm	54 mm
LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	50 mm	54 mm

Product	D	C
LEDspot GU10 6-50W D 850 35D 120V 3CT/6	50 mm	53 mm
LEDspot GU10 6-50W D 850 36D 120V 1PF/6	50 mm	53 mm

Essential LEDspot GU10

Dimensional drawing



Product	D	C
LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50.5 mm	54.5 mm
LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50.5 mm	54.5 mm
LEDClassic 35W GU10 827 100-240V 36D ND	50.5 mm	54.5 mm
LEDClassic 35W GU10 865 100-240V 36D ND	50.5 mm	54.5 mm
LEDClassic 50W GU10 827 100-240V 40D ND	50.5 mm	54.5 mm
LEDClassic 50W GU10 865 100-240V 40D ND	50.5 mm	54.5 mm
LEDClassic 70W GU10 827 100-240V 40D ND	50.5 mm	54.5 mm
LEDClassic 70W GU10 865 100-240V 40D ND	50.5 mm	54.5 mm
LEDspot 4-50W GU10 827 100-240V 36D ND	50.5 mm	54.5 mm
LEDspot 4-50W GU10 865 100-240V 36D ND	50.5 mm	54.5 mm



Product	D	C
LEDspot50W GU10Kit_R 827 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 827 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 827 100-240V 36D PF	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 mm	54 mm
LEDspot50W GU10Kit_R 865 100-240V 36D PF	50 mm	54 mm

Product	D	C
LEDCLA 100W GU10 865 230V 60D ND 1PF/12	50 mm	54 mm

Product	D	C
LED MR11 GU10 25W 36D 6500K ND	36 mm	50 mm
MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 mm	50 mm
MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 mm	50 mm

Essential LEDspot GU10

Dimensional drawing



Product	D	C
LEDspot50W GU10Kit_S 827 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_S 827 100-240V 36D PF	50 mm	54 mm
LEDspot50W GU10Kit_S 865 100-240V 36D	50 mm	54 mm
LEDspot50W GU10Kit_S 865 100-240V 36D PF	50 mm	54 mm

Product	D	C
LEDspot 70W AR111GU10 827 220-240V 30DND	111 mm	65 mm
LEDspot 70W AR111GU10 865 220-240V 30DND	111 mm	65 mm

General Information

Cap-Base GU10

Light Technical

Color rendering index (CRI) 80

LLMF At End Of Nominal Lifetime (Nom) 70 %

Operating and Electrical

Starting Time (Nom) 0.5 s

General Information

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	50,000	25,000 hour(s)
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50,000	25,000 hour(s)
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50,000	25,000 hour(s)
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	50,000	25,000 hour(s)
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	50,000	25,000 hour(s)
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50,000	25,000 hour(s)

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50,000	25,000 hour(s)
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	50,000	25,000 hour(s)
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	50,000	25,000 hour(s)
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	50,000	25,000 hour(s)
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	50,000	25,000 hour(s)
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	50,000	25,000 hour(s)

Essential LEDspot GU10

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	50,000	15,000 hour(s)
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	50,000	15,000 hour(s)
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	50,000	15,000 hour(s)
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	50,000	15,000 hour(s)
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	50,000	15,000 hour(s)
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	50,000	15,000 hour(s)
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50,000	15,000 hour(s)
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	50,000	15,000 hour(s)
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	15,000	15,000 hour(s)
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	15,000	15,000 hour(s)
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	50,000	15,000 hour(s)
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	50,000	15,000 hour(s)
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	50,000	10,000 hour(s)
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	50,000	10,000 hour(s)
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	50,000	10,000 hour(s)
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	50,000	10,000 hour(s)
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	15,000	15,000 hour(s)
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50,000	25,000 hour(s)
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50,000	25,000 hour(s)

Order Code	Full Product Name	Switching Cycle	Nominal lifetime
929001912141	LED MR11 GU10 25W 36D 6500K ND	50,000	25,000 hour(s)
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	50,000	25,000 hour(s)
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	50,000	25,000 hour(s)
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	15,000	15,000 hour(s)
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	15,000	15,000 hour(s)
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	50,000	15,000 hour(s)
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	50,000	15,000 hour(s)
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	50,000	15,000 hour(s)
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	50,000	15,000 hour(s)
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50,000	15,000 hour(s)
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	50,000	15,000 hour(s)
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	50,000	15,000 hour(s)
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50,000	15,000 hour(s)
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	50,000	15,000 hour(s)
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	50,000	15,000 hour(s)
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	50,000	15,000 hour(s)
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	50,000	15,000 hour(s)
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	50,000	25,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	36 degree(s)	2700 K	827	350 lm	540 cd
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	36 degree(s)	2700 K	827	350 lm	540 cd
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	36 degree(s)	2700 K	827	350 lm	540 cd
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	36 degree(s)	2700 K	827	350 lm	540 cd
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	36 degree(s)	6500 K	865	350 lm	540 cd
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	36 degree(s)	6500 K	865	350 lm	540 cd
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	36 degree(s)	6500 K	865	350 lm	540 cd
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	36 degree(s)	6500 K	865	350 lm	540 cd
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	40 degree(s)	2700 K	827	525 lm	540 cd

Essential LEDspot GU10

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color Temperature (Nom)	Color Code	Luminous Flux	Luminous Intensity (Nom)
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	40 degree(s)	2700 K	827	525 lm	540 cd
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	40 degree(s)	6500 K	865	525 lm	540 cd
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	40 degree(s)	6500 K	865	525 lm	540 cd
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	35 degree(s)	3000 K	830	400 lm	600 cd
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	35 degree(s)	3000 K	830	400 lm	600 cd
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	35 degree(s)	3000 K	830	400 lm	600 cd
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	36 degree(s)	5000 K	850	400 lm	600 cd
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	35 degree(s)	5000 K	850	400 lm	600 cd
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	35 degree(s)	6500 K	865	400 lm	600 cd
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	35 degree(s)	6500 K	865	400 lm	600 cd
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	35 degree(s)	6500 K	865	400 lm	600 cd
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	36 degree(s)	4000 K	840	430 lm	750 cd
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	36 degree(s)	6500 K	865	430 lm	750 cd
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	36 degree(s)	2700 K	827	350 lm	600 cd
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	36 degree(s)	6500 K	865	350 lm	600 cd
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	36 degree(s)	2700 K	827	340 lm	600 cd
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	36 degree(s)	2700 K	827	340 lm	600 cd
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	36 degree(s)	6500 K	865	370 lm	600 cd
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	36 degree(s)	6500 K	865	370 lm	600 cd
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	36 degree(s)	3000 K	830	400 lm	700 cd
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 degree(s)	2700 K	827	250 lm	450 cd
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	36 degree(s)	2700 K	827	250 lm	450 cd
929001912141	LED MR11 GU10 25W 36D 6500K ND	36 degree(s)	6500 K	865	250 lm	450 cd
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	30 degree(s)	2700 K	827	1,000 lm	3,500 cd
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	30 degree(s)	6500 K	865	1,100 lm	3,500 cd
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	36 degree(s)	2700 K	827	400 lm	700 cd
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	36 degree(s)	2700 K	827	400 lm	700 cd
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	36 degree(s)	2700 K	827	350 lm	600 cd
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	36 degree(s)	2700 K	827	350 lm	600 cd
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	36 degree(s)	2700 K	827	350 lm	600 cd
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	36 degree(s)	6500 K	865	350 lm	600 cd
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	36 degree(s)	6500 K	865	350 lm	600 cd
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	36 degree(s)	6500 K	865	350 lm	600 cd
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	36 degree(s)	6500 K	865	350 lm	600 cd
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	36 degree(s)	6500 K	865	350 lm	600 cd
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	36 degree(s)	6500 K	865	350 lm	600 cd
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	36 degree(s)	6500 K	865	350 lm	600 cd
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	36 degree(s)	2700 K	827	350 lm	600 cd
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	36 degree(s)	2700 K	827	350 lm	600 cd
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	60 degree(s)	6500 K	865	900 lm	750 cd

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	35 W	929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	50 W
						929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	35 W

Essential LEDspot GU10

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	50 to 60 Hz	50 to 60 Hz	3.8 W	50 W
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929003132387	ESS LEDspots 50W GU10 830 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	4 W	50 W	929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50 to 60 Hz	50 to 60 Hz	3.5 W	25 W
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	4.8 W	50 W	929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	50 to 60 Hz	50 to 60 Hz	3.5 W	25 W
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	6 W	70 W	929001912141	LED MR11 GU10 25W 36D 6500K ND	50 to 60 Hz	50 to 60 Hz	3.5 W	25 W
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	4.8 W	50 W	929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	50 to 60 Hz	50 to 60 Hz	12 W	70 W
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	50 to 60 Hz	50 to 60 Hz	6 W	70 W	929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	50 to 60 Hz	50 to 60 Hz	12 W	70 W
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	60 Hz	60 Hz	6 W	50 W	929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	60 Hz	60 Hz	6 W	50 W	929001250487	ESS LEDspots 50W GU10 827 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	60 Hz	60 Hz	6 W	50 W	929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	60 Hz	60 Hz	6 W	50 W	929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	60 Hz	60 Hz	6 W	50 W	929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	50 to 60 Hz	50 to 60 Hz	6 W	50 W	929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	50 to 60 Hz	50 to 60 Hz	6 W	50 W	929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	50 to 60 Hz	50 to 60 Hz	6 W	50 W	929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W	929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	50 to 60 Hz	50 to 60 Hz	4.7 W	50 W	929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	5 W	50 W	929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	50 to 60 Hz	50 to 60 Hz	5 W	50 W	929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	50 to 60 Hz	50 to 60 Hz	3.8 W	50 W						
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	50 to 60 Hz	50 to 60 Hz	3.8 W	50 W						
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	50 to 60 Hz	50 to 60 Hz	3.8 W	50 W						

Essential LEDspot GU10

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent	Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	50 to 60 Hz	50 to 60 Hz	5 W	50 W	929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	50 to 60 Hz	50 to 60 Hz	6.7 W	100 W
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	50 to 60 Hz	50 to 60 Hz	5 W	50 W						

Temperature

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	-	70 °C
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	-	70 °C
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	-	70 °C
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	-	70 °C
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	-	70 °C
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	-	70 °C
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	-	70 °C
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	-	70 °C
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	-	70 °C
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	-	70 °C
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	-	70 °C
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	-	70 °C
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	-20 °C to 45 °C	85 °C
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	-	85 °C
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	-	85 °C
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	-	85 °C
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	-	85 °C
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	-	65 °C
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	-	65 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	-	65 °C
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	-20 °C to 40 °C	75 °C
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	-	75 °C
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	-	75 °C
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	-	75 °C
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	-	70 °C
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	-	70 °C
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	-	70 °C
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	-	70 °C
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	-	75 °C
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-	70 °C
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-20 °C to 40 °C	70 °C
929001912141	LED MR11 GU10 25W 36D 6500K ND	-	70 °C
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	-	70 °C
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	-	70 °C
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	-	75 °C
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	-20 °C to 40 °C	75 °C
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	-	75 °C
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	-	75 °C
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	-	75 °C

Essential LEDspot GU10

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	-	75 °C
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	75 °C
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	-	75 °C
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	-	75 °C
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	75 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	No
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	No
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	No
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	No
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	No
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	No
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	No
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	No
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	No
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	No
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	No
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	No
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	Yes
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	Only with specific dimmers
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	Only with specific dimmers
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	Only with specific dimmers
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	Only with specific dimmers
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	Yes
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	Only with specific dimmers
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	Only with specific dimmers
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	No
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	No

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	-	PAR16
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	-	PAR16

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	-	75 °C
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	-	75 °C
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	-	75 °C
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	-	75 °C
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	-	75 °C

Order Code	Full Product Name	Dimmable
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	No
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	No
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	No
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	No
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	No
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	No
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	No
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	No
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	No
929001912141	LED MR11 GU10 25W 36D 6500K ND	No
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	No
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	No
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	No
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	No
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	No
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	No
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	No
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	No
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	No
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	No
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	No
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	No
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	No
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	No
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	No
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	No
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	No

Essential LEDspot GU10

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	-	PAR16
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	-	PAR16
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	-	PAR16
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	-	PAR16
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	-	PAR16
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	-	PAR16
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	-	PAR16
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	-	PAR16
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	Clear	PAR16
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	-	PAR16
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	-	PAR16
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	-	PAR16
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	-	PAR16
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	-	PAR16
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	-	PAR16
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	-	PAR16
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	-	PAR16
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	-	PAR16
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	-	PAR16
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	-	PAR16
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	-	PAR16
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	-	PAR16

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	-	PAR16
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	-	PAR16
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	-	PAR16
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-	MR11
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-	MR11
929001912141	LED MR11 GU10 25W 36D 6500K ND	-	MR11
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	-	AR111
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	-	AR111
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	-	GU10
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	-	PAR16
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	-	PAR16
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	-	PAR16
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	-	PAR16
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	-	PAR16
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	PAR16
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	-	PAR16
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	-	PAR16
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-	PAR16
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	-	PAR16
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	-	PAR16
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	-	PAR16
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	-	PAR16
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	-	PAR16










Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929002350311	LEDClassic 35W GU10 827 100-240V 36D ND	- kWh
929002350371	LEDCLA 50W GU10 827 100-240V 36D ND1PF/6	- kWh
929002350372	LEDCLA 50W GU10 827 100-240V 36D ND2PF/6	- kWh
929002350381	LEDspot 4-50W GU10 827 100-240V 36D ND	- kWh
929002350411	LEDClassic 35W GU10 865 100-240V 36D ND	- kWh
929002350471	LEDCLA 50W GU10 865 100-240V 36D ND1PF/6	- kWh
929002350472	LEDCLA 50W GU10 865 100-240V 36D ND2PF/6	- kWh
929002350481	LEDspot 4-50W GU10 865 100-240V 36D ND	- kWh
929002350511	LEDClassic 50W GU10 827 100-240V 40D ND	- kWh
929002350519	LEDClassic 70W GU10 827 100-240V 40D ND	-
929002350611	LEDClassic 50W GU10 865 100-240V 40D ND	- kWh
929002350619	LEDClassic 70W GU10 865 100-240V 40D ND	-
929001266441	LEDspot GU10 6-50W D 830 35D 120V PF	- kWh
929001266461	LEDspot GU10 6-50W D 830 35D 120V 1PF/6	-
929001266483	LEDspot GU10 6-50W D 830 35D 120V 3CT/6	-
929001266541	LEDspot GU10 6-50W D 850 36D 120V 1PF/6	-
929001266583	LEDspot GU10 6-50W D 850 35D 120V 3CT/6	-
929002055811	LEDspot GU10 6-50W D 865 35D 120V 1BC	- kWh
929002055861	LEDspot GU10 6-50W D 865 35D 120V 1PF/6	-
929002055863	LEDspot GU10 6-50W D 865 35D 120V 3CT/6	-
929001247087	ESS LEDspots 50W GU10 840 36D ND TR	5 kWh








Order Code	Full Product Name	Energy Consumption kWh/ 1000 h
929001259187	ESS LEDspots 50W GU10 865 36D ND TR	5 kWh
929001971241	LEDspot 5-50W GU10 827 100-240V 36D ND	- kWh
929001971341	LEDspot 5-50W GU10 865 100-240V 36D ND	- kWh
929002057371	LEDspotGU10EcoHome 50W 827 36D HV 1CT/20	- kWh
929002057397	LEDspotGU10EcoHome 50W 827 36D HV 4CT/8	-
929002057571	LEDspotGU10EcoHome 50W 865 36D HV 1CT/20	- kWh
929002057597	LEDspotGU10EcoHome 50W 865 36D HV 4CT/8	-
929003132387	ESS LEDspots 50W GU10 830 36D ND TR	5 kWh
929001364641	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	-
929001364642	MR11 3.5W-25W 250lm 36D 2700K GU10 ND	- kWh
929001912141	LED MR11 GU10 25W 36D 6500K ND	-
929002499612	LEDspot 70W AR111GU10 827 220-240V 30DND	-
929002499712	LEDspot 70W AR111GU10 865 220-240V 30DND	-
929001250437	EcoBright LED GU10 50W 827 36D 2BC/5	5 kWh
929001250487	ESS LEDspots 50W GU10 827 36D ND TR	5 kWh
929001970841	LEDspot50W GU10Kit_R 827 100-240V 36D	-
929001970861	LEDspot50W GU10Kit_R 827 100-240V 36D PF	- kWh
929001970871	LEDspot50W GU10Kit_R 827 100-240V 36D	- kWh
929001970941	LEDspot50W GU10Kit_R 865 100-240V 36D	-
929001970942	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	-
929001970961	LEDspot50W GU10Kit_R 865 100-240V 36D PF	- kWh

Essential LEDspot GU10


Order Code	Full Product Name	Energy
		Consumption kWh/ 1000 h
929001970971	LEDspot50W GU10Kit_R 865 100-240V 36D	- kWh
929001970972	LEDspot50W GU10Kit_R 865 100-240V 36D 2P	- kWh
929001971061	LEDspot50W GU10Kit_S 865 100-240V 36D PF	- kWh
929001971081	LEDspot50W GU10Kit_S 865 100-240V 36D	-
929001971161	LEDspot50W GU10Kit_S 827 100-240V 36D PF	- kWh
929001971181	LEDspot50W GU10Kit_S 827 100-240V 36D	-
929002466971	LEDCLA 100W GU10 865 230V 60D ND 1PF/12	-




Essential LEDspot GU10




Accent Diagrams




Accent Diagram - LEDspot 70W AR111GU10 827
220-240V 30DND




Accent Diagram - LEDspot GU10 6-50W D 830
35D 120V 1PF/6




Accent Diagram - LEDspotGU10EcoHome 50W
827 36D HV 1CT/20




Accent Diagram - LEDClassic 50W GU10 827
100-240V 40D ND




Accent Diagram - LEDspotGU10EcoHome 50W
865 36D HV 4CT/8




Accent Diagram - LEDspot GU10 6-50W D 850
35D 120V 3CT/6



Accent Diagram - EcoBright LED GU10 50W 827
36D 2BC/5




Accent Diagram - LEDspot 70W AR111GU10 865
220-240V 30DND




Accent Diagram - LEDspot GU10 6-50W D 865
35D 120V 3CT/6


Accent Diagrams




Accent Diagram - LED MR11 GU10 25W 36D 6500K ND




Accent Diagram - LEDCLA 100W GU10 865 230V 60D ND 1PF/12




Accent Diagram - LEDspot50W GU10Kit_R 827 100-240V 36D PF




Accent Diagram - ESS LEDspots 50W GU10 865 36D ND TR



Accent Diagram - ESS LEDspots 50W GU10 830 36D ND TR




Accent Diagram - MR11 3.5W-25W 250lm 36D 2700K GU10 ND




Accent Diagram - LEDClassic 35W GU10 865 100-240V 36D ND

Essential LEDspot GU10


Beam Diagrams




Beam diagram - LEDClassic 35W GU10 865
100-240V 36D ND




Beam diagram - ESS LEDspots 50W GU10 865
36D ND TR




Beam diagram - LEDspot GU10 6-50W D 865
35D 120V 3CT/6




Beam diagram - LEDClassic 50W GU10 827
100-240V 40D ND




Beam diagram - MR11 3.5W-25W 250lm 36D
2700K GU10 ND




Beam diagram - LEDspotGU10EcoHome 50W
865 36D HV 4CT/8



Beam diagram - LEDspot GU10 6-50W D 850
35D 120V 3CT/6




Beam diagram - LEDspot GU10 6-50W D 830
35D 120V 1PF/6




Beam diagram - LEDCLA 100W GU10 865 230V
60D ND 1PF/12

Essential LEDspot GU10


Beam Diagrams




Beam diagram - EcoBright LED GU10 50W 827
36D 2BC/5




Beam diagram - ESS LEDspots 50W GU10 830
36D ND TR




Beam diagram - LEDspot50W GU10Kit_R 827
100-240V 36D PF




Beam diagram - LEDspot 70W AR111GU10 827
220-240V 30DND



Beam diagram - LEDspotGU10EcoHome 50W
827 36D HV 1CT/20



Beam diagram - LED MR11 GU10 25W 36D
6500K ND



Beam diagram - LEDspot 70W AR111GU10 865
220-240V 30DND

Essential LEDspot GU10

