



The affordable LEDTube T8 solution

Ecofit Ledtubes T8

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Benefits

- Up to 50% energy saving compared with conventional fluorescent systems
- Easy installation: retrofit replacement of existing T8 lamps improving the quality of light
- Low initial investment

Features

- Retrofit solution with Long lifetime of 15.000hs
- Up to 50% of energy saving
- Instant on, no flicker or buzz

Application

- Domestic applications
- Small offices and retailers

Ecofit Ledtubes T8

Versions



Standard Product Photo

Dimensional drawing

Product	D1	D2	A1	A2	A3	C	D
LEDtube 1200mm 16W 740 T8 AP C G	25.68 mm	28 mm	1,198 mm	1,205 mm	1,212 mm	1,212 mm	27.8 mm
LEDtube 1500mm 20W 765 T8 AP SL G	25.7 mm	28 mm	1,498.5 mm	1,505.9 mm	1,513 mm		

General Information	
Cap-Base	G13
Switching Cycle	50,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Beam Angle (Nom)	240 degree(s)
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Temperature	
Ambient temperature range	-20 °C to 45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	T8

Order Code	Full Product Name	Rated Lifetime (Hours)
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	15,000 hour(s)
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	-

Ecofit Ledtubes T8

Light Technical

Order Code	Full Product Name	Correlated Color		Color rendering index (CRI)	Color Code	Luminous Flux
		Temperature (Nom)	rendering (Nom)			
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	4000 K	73	740		1,600 lm

Order Code	Full Product Name	Correlated Color		Color rendering index (CRI)	Color Code	Luminous Flux
		Temperature (Nom)	rendering (Nom)			
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	6500 K	70	765		2,000 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	16 W

Order Code	Full Product Name	Power Consumption
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	20 W

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	60 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	45 °C



Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	Frosted

Order Code	Full Product Name	Bulb Finish
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	-

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
929001184508	LEDtube 1200mm 16W 740 T8 AP C G	16 kWh
929001940668	LEDtube 1500mm 20W 765 T8 AP SL G	20 kWh



Ecofit Ledtubes T8

