



# Switch light settings without switching bulbs

## Premium LED bulbs SceneSwitch

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED bulbs, adapt your room ambiance to suit whatever you're doing, by changing the setting from cool day light to warm white, or dimming the brightness. All you need is your existing switch no extra installation is required.

### Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Up to 95% energy saving compared with traditional incandescent lamps

### Features

- Multiple light settings in one lamp
- Plug and play with existing E27
- Long lifetime and lumen maintenance

### Application

- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)


# Premium LED bulbs SceneSwitch

## Versions



Single Contact Medium Screw A  
19mm Frosted

## Dimensional drawing



Product	D	C
9.5A19/PER/827-50-22/FR/ND/SSCC 4/1BC	61 mm	111 mm
9A19/PER/850/FR/ND SSDL 4/1BC	61 mm	111 mm

# Premium LED bulbs SceneSwitch

## Controls and dimming

Dimmable No

## Operating and electrical

Voltage (Nom) 120 V

Wattage Equivalent 60 W

Starting Time (Nom) 0.5 s

## General information

Cap-Base E26

Nominal Lifetime (Nom) 15000 h

Switching Cycle 100000

## Light technical

Beam Angle (Nom) 200 °

Color Rendering Index (Nom) 80

Llmf At End Of Nominal Lifetime (Nom) 70 %

## Mechanical and housing

Bulb Finish Frosted

Bulb Shape A19

## Temperature

T-Ambient (Max) 45 °C

T-Ambient (Min) -20 °C

## Operating and electrical


Order Code	Full Product Name	Input Frequency	Power (Nom)
929001261443	9A19/PER/850/FR/ND SSDL 4/1BC	50 to 60 Hz	9, 3, 1 W
929001263243	9.5A19/PER/827-50-22/FR/ND/SSCC 4/1BC	60 Hz	9.5, 8, 3 W

## Light technical

Order Code	Full Product Name	Color Code	Correlated Color	
			Temperature (Nom)	Luminous Flux (Nom)
929001261443	9A19/PER/850/FR/ND SSDL 4/1BC	850	5000 K	800-320-80 lm
929001263243	9.5A19/PER/827-50-22/FR/ND/SSCC 4/1BC	827/850/822	2700, 5000, 2200 K	800-800-80 lm

## Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001261443	9A19/PER/850/FR/ND SSDL 4/1BC	80 °C
929001263243	9.5A19/PER/827-50-22/FR/ND/SSCC 4/1BC	89 °C



## Premium LED bulbs SceneSwitch

