



# Switch light settings without switching bulbs

## Premium LED bulbs SceneSwitch

Some situations call for cool light, others benefit from the ambiance of a warm cozy glow. With Philips SceneSwitch LED bulbs, adapt your room ambiance to suit whatever you're doing, by changing the setting from cool day light to warm white, or dimming the brightness. All you need is your existing switch no extra installation is required.

### Benefits

- Create your own scene with one lamp simply using your existing light switch
- No dimmer or additional installation needed
- Up to 95% energy saving compared with traditional incandescent lamps

### Features


- Multiple light settings in one lamp
- Plug and play with existing E27
- Long lifetime and lumen maintenance

### Application


- Indoor applications in open luminaires (with an open/free air gap of min. 10 mm)

# Premium LED bulbs SceneSwitch

## Versions




E27 A60 Frosted



E27 A60 FR




E26 A19 Frosted





LEDBulb E27 A60 Clear

## Dimensional drawing



Product	D	C
SceneSwitch 3Step A60 9-70W E27 CDL	61 mm	111 mm
SceneSwitch 3Step A60 9-70W E27 WW	61 mm	111 mm




Product	D	C
SceneSwitch Color A60 9.5-70W E27 WW/CDL	61 mm	111 mm
SceneSwitch 3Step A60 9-60W E27 WG 120V	61 mm	111 mm
SceneSwitch 3Step A60 9-60W E27 CW 120V	61 mm	111 mm
SceneSwitch Color A60 9.5-60W E27 120V	61 mm	111 mm
SceneSwitch Color A60 9.5-70W E27 WW/CDL	61 mm	111 mm
SceneSwitch Color A60 9.5-70W E27 WW/CDL	61 mm	111 mm

Product	D	C
LED classic SSW 60W A60 E27 WW CL 1BC/6	60 mm	104 mm

# Premium LED bulbs SceneSwitch

## Dimensional drawing



Product	D	C
BC9A19/AMB/850/ND SSDL 120V	61.0 mm	111 mm

Controls and Dimming	
Dimmable	No
Operating and Electrical	
Starting Time (Nom)	0.5 s
General Information	
Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Light Technical	
Color Rendering Index (Nom)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h	Energy Efficiency Label (EEL)
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	10 kWh	A+
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	10 kWh	A+
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	10 kWh	A+
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	-	-
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	-	-

Order Code	Full Product Name	Energy Consumption kWh/ 1000 h	Energy Efficiency Label (EEL)
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	-	-
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	9-3.5-1.5 kWh	A+
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	9-3.5-1.5 kWh	A+
929001261403	BC9A19/AMB/850/ND SSDL 120V	-	-
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	8 kWh	-

## Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	50 to 60 Hz	220-240 V	70 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	50 to 60 Hz	220-240 V	70 W

## Premium LED bulbs SceneSwitch

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	50 to 60 Hz	220-240 V	70 W
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	60 Hz	120 V	60 W
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	50 to 60 Hz	120 V	60 W
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	50 to 60 Hz	120 V	60 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	50 to 60 Hz	220-240 V	-
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	50 to 60 Hz	220-240 V	-
929001261403	BC9A19/AMB/850/ND SSDL 120V	50 to 60 Hz	120 V	60 W
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	50 to 60 Hz	220-240 V	-

### General Information

Order Code	Full Product Name	Switching	
		Cap-Base	Cycle
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	E27	100000X
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	E27	100000X
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	E27	100000X
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	E27	100000X
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	E27	100000X

Order Code	Full Product Name	Switching	
		Cap-Base	Cycle
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	E27	100000X
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	E27	100000X
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	E27	100000X
929001261403	BC9A19/AMB/850/ND SSDL 120V	E26	100000X
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	E27	20000X

### Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature		Luminous Flux (Rated)	
				(Nom)	Luminous Flux (Nom)	(Nom)	(Nom)
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	-	865/830	-	806 lm	806 lm	
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	150°	865/830	-	-	-	
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	150°	865/830	-	-	-	
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	300°	827/850/822	-	-	-	
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	300°	827/825/822	-	-	-	
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	300°	850	-	-	-	
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	150°	865	6500 K	-	-	
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	150°	830	3000 K	-	-	
929001261403	BC9A19/AMB/850/ND SSDL 120V	300°	850	5000 K	-	-	
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	280°	827/825/822	-	-	-	

### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	Frosted	A60
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	Frosted	A60
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	Frosted	A60
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	Frosted	A60

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	Frosted	A60
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	Frosted	A60
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	Frosted	A60
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	Frosted	A60
929001261403	BC9A19/AMB/850/ND SSDL 120V	Frosted	A19 (A19)
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	Clear	A60

### Temperature

## Premium LED bulbs SceneSwitch

Order Code	Full Product Name	T-Case Maximum (Nom)
929001155971	SceneSwitch Color A60 9.5-70W E27 WW/CDL	-
929001155991	SceneSwitch Color A60 9.5-70W E27 WW/CDL	90 °C
929001155997	SceneSwitch Color A60 9.5-70W E27 WW/CDL	90 °C
929001373591	SceneSwitch Color A60 9.5-60W E27 120V	89 °C
929001373691	SceneSwitch 3Step A60 9-60W E27 WG 120V	89 °C
929001373791	SceneSwitch 3Step A60 9-60W E27 CW 120V	89 °C
929001208491	SceneSwitch 3Step A60 9-70W E27 CDL	-
929001208791	SceneSwitch 3Step A60 9-70W E27 WW	90 °C
929001261403	BC9A19/AMB/850/ND SSDL 120V	80 °C
929001888642	LED classic SSW 60W A60 E27 WW CL 1BC/6	65 °C

