



# Designed to be seen - Looks good on & off

## Premium LED bulbs Vintage Filament

Featuring a classic heritage design, the new Philips Vintage LED lamp family is reminiscent of familiar incandescent bulbs. Available in an array of giant shapes, candles and other familiar form factors, they provide a seamless fit across your space. When used as a statement piece, they add a sense of nostalgia and create a highly desirable atmosphere for socialization and relaxing.

### Benefits

- Perfect sustainable replacement for conventional bulbs with up to 90% of energy saving
- Dimmable versions can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels
- Warm light effect to create a cozy atmosphere

### Features

- Extra warm light with Vintage design
- Available in an array of shapes and familiar form factors
- Light all around with improved light distribution effect

### Application


- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Premium LED bulbs Vintage Filament


Versions



LEDbulb E27 A60 400lm






LEDclassic G93 E27 POS2



LEDbulb E27 ST64 400lm

Dimensional drawing



Product	D	C
LEDClassic 35W ST64 E27 825 100-240VND BR	64 mm	142 mm

Product	D	C
LEDClassic 35W G93 E27 825 100-240 ND BR	95 mm	140 mm

Product	D	C
LEDClassic 35W A60 E27 825 100-240V NDBR	60 mm	106 mm

# Premium LED bulbs Vintage Filament

General Information	
Cap-Base	E27
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	2500 K
Color rendering index (CRI)	80
Color Code	825
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	400 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Power Consumption	4 W
Starting Time (Nom)	0.5 s
Wattage Equivalent	35 W
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Transparent amber
Approval and Application	
Energy Consumption kWh/1000 h	- kWh

## Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001941546	LEDClassic 35W A60 E27 825 100-240V NDBR	52 °C
929001948246	LEDClassic 35W G93 E27 825 100-240 ND BR	45 °C
929001941646	LEDClassic 35W ST64 E27 825 100-240VNDBR	50 °C

## Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001941546	LEDClassic 35W A60 E27 825 100-240V NDBR	A60
929001948246	LEDClassic 35W G93 E27 825 100-240 ND BR	G93
929001941646	LEDClassic 35W ST64 E27 825 100-240VNDBR	ST64



## Premium LED bulbs Vintage Filament

