



The most competitive specification downlight for TCO attractiveness with diversity and system compatibility

GreenSpace G5

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Benefits

- Energy efficient
- Design compactness
- Smart lighting

Features

- High optical efficiency
- Compact form factor
- DALI/DALI-VLC/POE compatible

Application







- Office
- shopping mall
- hotel
- retail etc.

Versions







GreenSpace Gen5 DN39XB D150 ALU

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Optical cover type	Transparent bowl with white cover
Color rendering index (CRI)	>80
Optic type	High-gloss high reflectance
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +40 °C
Mechanical and Housing	
Housing Color	Black and white
Approval and Application	
Protection class IEC	Safety class I
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

General Information

Order Code	Full Product Name	CE mark
01575141	DN391B LED11/830 PSU D100 ALU WP GC	-
72036700	DN390B LED6/840 PSU D100 ALU GM	CE mark
72000800	DN390B LED6/865 PSU D100 ALU GM	CE mark
52097400	DN390B LED6/830 PSU D100 ALU WP GM	CE mark
52098100	DN390B LED6/840 PSU D100 ALU WP GM	CE mark
72003900	DN390B LED6/865 PSU D100 ALU WP GM	CE mark
54999900	DN390B LED6/830 PSU D100 WH GM	CE mark
72029900	DN390B LED6/840 PSU D100 WH GM	CE mark
72051000	DN390B LED6/865 PSU D100 WH GM	CE mark
01575441	DN392B LED16/830 PSU D150 ALU WP GC	-
01575541	DN392B LED16/840 PSU D150 ALU WP GC	-
72008400	DN391B LED11/830 PSU D150 ALU GM	CE mark
72023700	DN391B LED11/840 PSU D150 ALU GM	CE mark
72017600	DN391B LED11/865 PSU D150 ALU GM	CE mark
72024400	DN392B LED16/830 PSU D150 ALU GM	CE mark
72018300	DN392B LED16/840 PSU D150 ALU GM	CE mark
72012100	DN391B LED11/830 PSU D150 ALU WP GM	CE mark
52102500	DN391B LED11/865 PSU D150 ALU WP GM	CE mark
72013800	DN391B LED11/830 PSD D150 ALU GM	CE mark
72027500	DN391B LED11/840 PSD D150 ALU GM	CE mark
72042800	DN392B LED16/840 PSD D150 ALU GM	CE mark
52100100	DN391B LED11/830 PSU D150 WH GM	CE mark
72045900	DN391B LED11/865 PSU D150 WH GM	CE mark
72037400	DN392B LED16/830 PSU D150 WH GM	CE mark
72009100	DN392B LED16/865 PSU D150 WH GM	CE mark
52101800	DN391B LED11/840 PSD D150 WH GM	CE mark
72007700	DN392B LED16/840 PSD D150 WH GM	CE mark
72047300	DN392B LED16/830 PSU D200 ALU GM	CE mark
72010700	DN392B LED16/840 PSU D200 ALU GM	CE mark
72039800	DN392B LED16/865 PSU D200 ALU GM	CE mark
72048000	DN393B LED22/830 PSU D200 ALU GM	CE mark
72011400	DN393B LED22/840 PSU D200 ALU GM	CE mark
72025100	DN393B LED22/865 PSU D200 ALU GM	CE mark
72040400	DN393B LED22/830 PSU D200 ALU WP GM	CE mark
72004600	DN393B LED22/840 PSU D200 ALU WP GM	CE mark
72032900	DN393B LED22/865 PSU D200 ALU WP GM	CE mark
72041100	DN393B LED22/830 PSD D200 ALU GM	CE mark
72005300	DN393B LED22/840 PSD D200 ALU GM	CE mark
01574141	DN393B LED22/840 PSU D200 WH GC	-
72001500	DN392B LED16/830 PSU D200 WH GM	CE mark
72030500	DN392B LED16/840 PSU D200 WH GM	CE mark
72053400	DN392B LED16/865 PSU D200 WH GM	CE mark
72002200	DN393B LED22/830 PSU D200 WH GM	CE mark
72054100	DN393B LED22/865 PSU D200 WH GM	CE mark
72056500	DN392B LED16/840 PSD D200 WH GM	CE mark
72028200	DN393B LED22/830 PSD D200 WH GM	CE mark
72019000	DN393B LED22/840 PSD D200 WH GM	CE mark

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01575141	DN391B LED11/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
72036700	DN390B LED6/840 PSU D100 ALU GM	60 degree(s)	4000 K	109 lm/W	600 lm
72000800	DN390B LED6/865 PSU D100 ALU GM	60 degree(s)	6500 K	109 lm/W	600 lm
52097400	DN390B LED6/830 PSU D100 ALU WP GM	60 degree(s)	3000 K	104 lm/W	570 lm
52098100	DN390B LED6/840 PSU D100 ALU WP GM	60 degree(s)	4000 K	109 lm/W	600 lm
72003900	DN390B LED6/865 PSU D100 ALU WP GM	60 degree(s)	6500 K	109 lm/W	600 lm
54999900	DN390B LED6/830 PSU D100 WH GM	72 degree(s)	3000 K	104 lm/W	570 lm
72029900	DN390B LED6/840 PSU D100 WH GM	72 degree(s)	4000 K	109 lm/W	600 lm
72051000	DN390B LED6/865 PSU D100 WH GM	72 degree(s)	6500 K	109 lm/W	600 lm
01575441	DN392B LED16/830 PSU D150 ALU WP GC	60 degree(s)	3000 K	103 lm/W	1,500 lm
01575541	DN392B LED16/840 PSU D150 ALU WP GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
72008400	DN391B LED11/830 PSU D150 ALU GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
72023700	DN391B LED11/840 PSU D150 ALU GM	60 degree(s)	4000 K	116 lm/W	1,100 lm
72017600	DN391B LED11/865 PSU D150 ALU GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
72024400	DN392B LED16/830 PSU D150 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
72018300	DN392B LED16/840 PSU D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
72012100	DN391B LED11/830 PSU D150 ALU WP GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
52102500	DN391B LED11/865 PSU D150 ALU WP GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
72013800	DN391B LED11/830 PSD D150 ALU GM	60 degree(s)	3000 K	91 lm/W	1,050 lm
72027500	DN391B LED11/840 PSD D150 ALU GM	60 degree(s)	4000 K	96 lm/W	1,100 lm
72042800	DN392B LED16/840 PSD D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
52100100	DN391B LED11/830 PSU D150 WH GM	85 degree(s)	3000 K	111 lm/W	1,050 lm
72045900	DN391B LED11/865 PSU D150 WH GM	85 degree(s)	6500 K	116 lm/W	1,100 lm
72037400	DN392B LED16/830 PSU D150 WH GM	85 degree(s)	3000 K	103 lm/W	1,500 lm
72009100	DN392B LED16/865 PSU D150 WH GM	85 degree(s)	6500 K	110 lm/W	1,600 lm
52101800	DN391B LED11/840 PSD D150 WH GM	85 degree(s)	4000 K	96 lm/W	1,100 lm
72007700	DN392B LED16/840 PSD D150 WH GM	85 degree(s)	4000 K	110 lm/W	1,600 lm
72047300	DN392B LED16/830 PSU D200 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm
72010700	DN392B LED16/840 PSU D200 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
72039800	DN392B LED16/865 PSU D200 ALU GM	60 degree(s)	6500 K	110 lm/W	1,600 lm
72048000	DN393B LED22/830 PSU D200 ALU GM	60 degree(s)	3000 K	111 lm/W	2,100 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
72011400	DN393B LED22/840 PSU D200 ALU GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
72025100	DN393B LED22/865 PSU D200 ALU GM	60 degree(s)	6500 K	116 lm/W	2,200 lm
72040400	DN393B LED22/830 PSU D200 ALU WP GM	60 degree(s)	3000 K	111 lm/W	2,100 lm
72004600	DN393B LED22/840 PSU D200 ALU WP GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
72032900	DN393B LED22/865 PSU D200 ALU WP GM	60 degree(s)	6500 K	116 lm/W	2,200 lm
72041100	DN393B LED22/830 PSD D200 ALU GM	60 degree(s)	3000 K	102 lm/W	2,100 lm
72005300	DN393B LED22/840 PSD D200 ALU GM	60 degree(s)	4000 K	107 lm/W	2,200 lm
01574141	DN393B LED22/840 PSU D200 WH GC	92 degree(s)	4000 K	116 lm/W	2,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01575141	DN391B LED11/830 PSU D100 ALU WP GC	9.5 W
72036700	DN390B LED6/840 PSU D100 ALU GM	5.5 W
72000800	DN390B LED6/865 PSU D100 ALU GM	5.5 W
52097400	DN390B LED6/830 PSU D100 ALU WP GM	5.5 W
52098100	DN390B LED6/840 PSU D100 ALU WP GM	5.5 W
72003900	DN390B LED6/865 PSU D100 ALU WP GM	5.5 W
54999900	DN390B LED6/830 PSU D100 WH GM	5.5 W
72029900	DN390B LED6/840 PSU D100 WH GM	5.5 W
72051000	DN390B LED6/865 PSU D100 WH GM	5.5 W
01575441	DN392B LED16/830 PSU D150 ALU WP GC	14.5 W
01575541	DN392B LED16/840 PSU D150 ALU WP GC	14.5 W
72008400	DN391B LED11/830 PSU D150 ALU GM	9.5 W
72023700	DN391B LED11/840 PSU D150 ALU GM	9.5 W
72017600	DN391B LED11/865 PSU D150 ALU GM	9.5 W
72024400	DN392B LED16/830 PSU D150 ALU GM	14.5 W
72018300	DN392B LED16/840 PSU D150 ALU GM	14.5 W
72012100	DN391B LED11/830 PSU D150 ALU WP GM	9.5 W
52102500	DN391B LED11/865 PSU D150 ALU WP GM	9.5 W

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
72001500	DN392B LED16/830 PSU D200 WH GM	92 degree(s)	3000 K	103 lm/W	1,500 lm
72030500	DN392B LED16/840 PSU D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm
72053400	DN392B LED16/865 PSU D200 WH GM	92 degree(s)	6500 K	110 lm/W	1,600 lm
72002200	DN393B LED22/830 PSU D200 WH GM	92 degree(s)	3000 K	111 lm/W	2,100 lm
72054100	DN393B LED22/865 PSU D200 WH GM	92 degree(s)	6500 K	116 lm/W	2,200 lm
72056500	DN392B LED16/840 PSD D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm
72028200	DN393B LED22/830 PSD D200 WH GM	92 degree(s)	3000 K	102 lm/W	2,100 lm
72019000	DN393B LED22/840 PSD D200 WH GM	92 degree(s)	4000 K	107 lm/W	2,200 lm

Order Code	Full Product Name	Power Consumption
72041100	DN393B LED22/830 PSD D200 ALU GM	20.5 W
72005300	DN393B LED22/840 PSD D200 ALU GM	20.5 W
01574141	DN393B LED22/840 PSU D200 WH GC	19 W
72001500	DN392B LED16/830 PSU D200 WH GM	14.5 W
72030500	DN392B LED16/840 PSU D200 WH GM	14.5 W
72053400	DN392B LED16/865 PSU D200 WH GM	14.5 W

Order Code	Full Product Name	Power Consumption
72002200	DN393B LED22/830 PSU D200 WH GM	19 W
72054100	DN393B LED22/865 PSU D200 WH GM	19 W
72056500	DN392B LED16/840 PSD D200 WH GM	15.5 W
72028200	DN393B LED22/830 PSD D200 WH GM	20.5 W
72019000	DN393B LED22/840 PSD D200 WH GM	20.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
01575141	DN391B LED11/830 PSU D100 ALU WP GC	No
72036700	DN390B LED6/840 PSU D100 ALU GM	No
72000800	DN390B LED6/865 PSU D100 ALU GM	No
52097400	DN390B LED6/830 PSU D100 ALU WP GM	No
52098100	DN390B LED6/840 PSU D100 ALU WP GM	No
72003900	DN390B LED6/865 PSU D100 ALU WP GM	No
54999900	DN390B LED6/830 PSU D100 WH GM	No
72029900	DN390B LED6/840 PSU D100 WH GM	No
72051000	DN390B LED6/865 PSU D100 WH GM	No
01575441	DN392B LED16/830 PSU D150 ALU WP GC	No
01575541	DN392B LED16/840 PSU D150 ALU WP GC	No
72008400	DN391B LED11/830 PSU D150 ALU GM	No
72023700	DN391B LED11/840 PSU D150 ALU GM	No
72017600	DN391B LED11/865 PSU D150 ALU GM	No
72024400	DN392B LED16/830 PSU D150 ALU GM	No
72018300	DN392B LED16/840 PSU D150 ALU GM	No
72012100	DN391B LED11/830 PSU D150 ALU WP GM	No
52102500	DN391B LED11/865 PSU D150 ALU WP GM	No
72013800	DN391B LED11/830 PSD D150 ALU GM	Yes
72027500	DN391B LED11/840 PSD D150 ALU GM	Yes
72042800	DN392B LED16/840 PSD D150 ALU GM	Yes
52100100	DN391B LED11/830 PSU D150 WH GM	No
72045900	DN391B LED11/865 PSU D150 WH GM	No
72037400	DN392B LED16/830 PSU D150 WH GM	No

Order Code	Full Product Name	Dimmable
72009100	DN392B LED16/865 PSU D150 WH GM	No
52101800	DN391B LED11/840 PSD D150 WH GM	Yes
72007700	DN392B LED16/840 PSD D150 WH GM	Yes
72047300	DN392B LED16/830 PSU D200 ALU GM	No
72010700	DN392B LED16/840 PSU D200 ALU GM	No
72039800	DN392B LED16/865 PSU D200 ALU GM	No
72048000	DN393B LED22/830 PSU D200 ALU GM	No
72011400	DN393B LED22/840 PSU D200 ALU GM	No
72025100	DN393B LED22/865 PSU D200 ALU GM	No
72040400	DN393B LED22/830 PSU D200 ALU WP GM	No
72004600	DN393B LED22/840 PSU D200 ALU WP GM	No
72032900	DN393B LED22/865 PSU D200 ALU WP GM	No
72041100	DN393B LED22/830 PSD D200 ALU GM	Yes
72005300	DN393B LED22/840 PSD D200 ALU GM	Yes
01574141	DN393B LED22/840 PSU D200 WH GC	No
72001500	DN392B LED16/830 PSU D200 WH GM	No
72030500	DN392B LED16/840 PSU D200 WH GM	No
72053400	DN392B LED16/865 PSU D200 WH GM	No
72002200	DN393B LED22/830 PSU D200 WH GM	No
72054100	DN393B LED22/865 PSU D200 WH GM	No
72056500	DN392B LED16/840 PSD D200 WH GM	Yes
72028200	DN393B LED22/830 PSD D200 WH GM	Yes
72019000	DN393B LED22/840 PSD D200 WH GM	Yes

Approval and Application

Order Code	Full Product Name	Ingress protection code
01575141	DN391B LED11/830 PSU D100 ALU WP GC	IP20/54
72036700	DN390B LED6/840 PSU D100 ALU GM	IP20
72000800	DN390B LED6/865 PSU D100 ALU GM	IP20
52097400	DN390B LED6/830 PSU D100 ALU WP GM	IP20/54
52098100	DN390B LED6/840 PSU D100 ALU WP GM	IP20/54
72003900	DN390B LED6/865 PSU D100 ALU WP GM	IP20/54
54999900	DN390B LED6/830 PSU D100 WH GM	IP20
72029900	DN390B LED6/840 PSU D100 WH GM	IP20
72051000	DN390B LED6/865 PSU D100 WH GM	IP20
01575441	DN392B LED16/830 PSU D150 ALU WP GC	IP20/54
01575541	DN392B LED16/840 PSU D150 ALU WP GC	IP20/54
72008400	DN391B LED11/830 PSU D150 ALU GM	IP20
72023700	DN391B LED11/840 PSU D150 ALU GM	IP20

Order Code	Full Product Name	Ingress protection code
72017600	DN391B LED11/865 PSU D150 ALU GM	IP20
72024400	DN392B LED16/830 PSU D150 ALU GM	IP20
72018300	DN392B LED16/840 PSU D150 ALU GM	IP20
72012100	DN391B LED11/830 PSU D150 ALU WP GM	IP20/54
52102500	DN391B LED11/865 PSU D150 ALU WP GM	IP20/54
72013800	DN391B LED11/830 PSD D150 ALU GM	IP20
72027500	DN391B LED11/840 PSD D150 ALU GM	IP20
72042800	DN392B LED16/840 PSD D150 ALU GM	IP20
52100100	DN391B LED11/830 PSU D150 WH GM	IP20
72045900	DN391B LED11/865 PSU D150 WH GM	IP20
72037400	DN392B LED16/830 PSU D150 WH GM	IP20
72009100	DN392B LED16/865 PSU D150 WH GM	IP20
52101800	DN391B LED11/840 PSD D150 WH GM	IP20

Order Code	Full Product Name	Ingress protection code
72007700	DN392B LED16/840 PSD D150 WH GM	IP20
72047300	DN392B LED16/830 PSU D200 ALU GM	IP20
72010700	DN392B LED16/840 PSU D200 ALU GM	IP20
72039800	DN392B LED16/865 PSU D200 ALU GM	IP20
72048000	DN393B LED22/830 PSU D200 ALU GM	IP20
72011400	DN393B LED22/840 PSU D200 ALU GM	IP20
72025100	DN393B LED22/865 PSU D200 ALU GM	IP20
72040400	DN393B LED22/830 PSU D200 ALU WP GM	IP20/54
72004600	DN393B LED22/840 PSU D200 ALU WP GM	IP20/54
72032900	DN393B LED22/865 PSU D200 ALU WP GM	IP20/54
72041100	DN393B LED22/830 PSD D200 ALU GM	IP20

Order Code	Full Product Name	Ingress protection code
72005300	DN393B LED22/840 PSD D200 ALU GM	IP20
01574141	DN393B LED22/840 PSU D200 WH GC	IP20
72001500	DN392B LED16/830 PSU D200 WH GM	IP20
72030500	DN392B LED16/840 PSU D200 WH GM	IP20
72053400	DN392B LED16/865 PSU D200 WH GM	IP20
72002200	DN393B LED22/830 PSU D200 WH GM	IP20
72054100	DN393B LED22/865 PSU D200 WH GM	IP20
72056500	DN392B LED16/840 PSD D200 WH GM	IP20
72028200	DN393B LED22/830 PSD D200 WH GM	IP20
72019000	DN393B LED22/840 PSD D200 WH GM	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01575141	DN391B LED11/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
72036700	DN390B LED6/840 PSU D100 ALU GM	(0.38,0.38) SDCM<5
72000800	DN390B LED6/865 PSU D100 ALU GM	(0.31,0.32) SDCM<5
52097400	DN390B LED6/830 PSU D100 ALU WP GM	(0.44,0.403) SDCM<5
52098100	DN390B LED6/840 PSU D100 ALU WP GM	(0.38,0.38) SDCM<5
72003900	DN390B LED6/865 PSU D100 ALU WP GM	(0.31,0.32) SDCM<5
54999900	DN390B LED6/830 PSU D100 WH GM	(0.44,0.403) SDCM<5
72029900	DN390B LED6/840 PSU D100 WH GM	(0.38,0.38) SDCM<5
72051000	DN390B LED6/865 PSU D100 WH GM	(0.31,0.32) SDCM<5
01575441	DN392B LED16/830 PSU D150 ALU WP GC	(0.44,0.403) SDCM<5
01575541	DN392B LED16/840 PSU D150 ALU WP GC	(0.38,0.38) SDCM<5
72008400	DN391B LED11/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
72023700	DN391B LED11/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
72017600	DN391B LED11/865 PSU D150 ALU GM	(0.31,0.32) SDCM<5
72024400	DN392B LED16/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
72018300	DN392B LED16/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
72012100	DN391B LED11/830 PSU D150 ALU WP GM	(0.44,0.403) SDCM<5
52102500	DN391B LED11/865 PSU D150 ALU WP GM	(0.31,0.32) SDCM<5
72013800	DN391B LED11/830 PSD D150 ALU GM	(0.44,0.403) SDCM<5
72027500	DN391B LED11/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
72042800	DN392B LED16/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
52100100	DN391B LED11/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
72045900	DN391B LED11/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
72037400	DN392B LED16/830 PSU D150 WH GM	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
72009100	DN392B LED16/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
52101800	DN391B LED11/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
72007700	DN392B LED16/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
72047300	DN392B LED16/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
72010700	DN392B LED16/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
72039800	DN392B LED16/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
72048000	DN393B LED22/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
72011400	DN393B LED22/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
72025100	DN393B LED22/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
72040400	DN393B LED22/830 PSU D200 ALU WP GM	(0.44,0.403) SDCM<5
72004600	DN393B LED22/840 PSU D200 ALU WP GM	(0.38,0.38) SDCM<5
72032900	DN393B LED22/865 PSU D200 ALU WP GM	(0.31,0.32) SDCM<5
72041100	DN393B LED22/830 PSD D200 ALU GM	(0.44,0.403) SDCM<5
72005300	DN393B LED22/840 PSD D200 ALU GM	(0.38,0.38) SDCM<5
01574141	DN393B LED22/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
72001500	DN392B LED16/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
72030500	DN392B LED16/840 PSU D200 WH GM	(0.38,0.38) SDCM<5
72053400	DN392B LED16/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
72002200	DN393B LED22/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
72054100	DN393B LED22/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
72056500	DN392B LED16/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
72028200	DN393B LED22/830 PSD D200 WH GM	(0.44,0.403) SDCM<5
72019000	DN393B LED22/840 PSD D200 WH GM	(0.38,0.38) SDCM<5

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
01575141	DN391B LED11/830 PSU D100 ALU WP GC	0.12 %
72036700	DN390B LED6/840 PSU D100 ALU GM	0.12 %
72000800	DN390B LED6/865 PSU D100 ALU GM	0.12 %
52097400	DN390B LED6/830 PSU D100 ALU WP GM	0.12 %
52098100	DN390B LED6/840 PSU D100 ALU WP GM	0.12 %
72003900	DN390B LED6/865 PSU D100 ALU WP GM	0.12 %
54999900	DN390B LED6/830 PSU D100 WH GM	0.12 %
72029900	DN390B LED6/840 PSU D100 WH GM	0.12 %

Order Code	Full Product Name	Driver failure rate at 5000 h
72051000	DN390B LED6/865 PSU D100 WH GM	0.12 %
01575441	DN392B LED16/830 PSU D150 ALU WP GC	0.16 %
01575541	DN392B LED16/840 PSU D150 ALU WP GC	0.16 %
72008400	DN391B LED11/830 PSU D150 ALU GM	0.12 %
72023700	DN391B LED11/840 PSU D150 ALU GM	0.12 %
72017600	DN391B LED11/865 PSU D150 ALU GM	0.12 %
72024400	DN392B LED16/830 PSU D150 ALU GM	0.16 %
72018300	DN392B LED16/840 PSU D150 ALU GM	0.16 %

Order Code	Full Product Name	Driver failure rate at 5000 h
72012100	DN391B LED11/830 PSU D150 ALU WP GM	0.12 %
52102500	DN391B LED11/865 PSU D150 ALU WP GM	0.12 %
72013800	DN391B LED11/830 PSD D150 ALU GM	0.12 %
72027500	DN391B LED11/840 PSD D150 ALU GM	0.12 %
72042800	DN392B LED16/840 PSD D150 ALU GM	0.16 %
52100100	DN391B LED11/830 PSU D150 WH GM	0.12 %
72045900	DN391B LED11/865 PSU D150 WH GM	0.12 %
72037400	DN392B LED16/830 PSU D150 WH GM	0.16 %
72009100	DN392B LED16/865 PSU D150 WH GM	0.16 %
52101800	DN391B LED11/840 PSD D150 WH GM	0.12 %
72007700	DN392B LED16/840 PSD D150 WH GM	0.16 %
72047300	DN392B LED16/830 PSU D200 ALU GM	0.16 %
72010700	DN392B LED16/840 PSU D200 ALU GM	0.16 %
72039800	DN392B LED16/865 PSU D200 ALU GM	0.16 %
72048000	DN393B LED22/830 PSU D200 ALU GM	0.12 %
72011400	DN393B LED22/840 PSU D200 ALU GM	0.12 %

Application Conditions

Order Code	Full Product Name	Maximum dim level
01575141	DN391B LED11/830 PSU D100 ALU WP GC	Not applicable
72036700	DN390B LED6/840 PSU D100 ALU GM	Not applicable
72000800	DN390B LED6/865 PSU D100 ALU GM	Not applicable
52097400	DN390B LED6/830 PSU D100 ALU WP GM	Not applicable
52098100	DN390B LED6/840 PSU D100 ALU WP GM	Not applicable
72003900	DN390B LED6/865 PSU D100 ALU WP GM	Not applicable
54999900	DN390B LED6/830 PSU D100 WH GM	Not applicable
72029900	DN390B LED6/840 PSU D100 WH GM	Not applicable
72051000	DN390B LED6/865 PSU D100 WH GM	Not applicable
01575441	DN392B LED16/830 PSU D150 ALU WP GC	Not applicable
01575541	DN392B LED16/840 PSU D150 ALU WP GC	Not applicable
72008400	DN391B LED11/830 PSU D150 ALU GM	Not applicable
72023700	DN391B LED11/840 PSU D150 ALU GM	Not applicable
72017600	DN391B LED11/865 PSU D150 ALU GM	Not applicable
72024400	DN392B LED16/830 PSU D150 ALU GM	Not applicable
72018300	DN392B LED16/840 PSU D150 ALU GM	Not applicable
72012100	DN391B LED11/830 PSU D150 ALU WP GM	Not applicable
52102500	DN391B LED11/865 PSU D150 ALU WP GM	Not applicable
72013800	DN391B LED11/830 PSD D150 ALU GM	-
72027500	DN391B LED11/840 PSD D150 ALU GM	-
72042800	DN392B LED16/840 PSD D150 ALU GM	-
52100100	DN391B LED11/830 PSU D150 WH GM	Not applicable
72045900	DN391B LED11/865 PSU D150 WH GM	Not applicable
72037400	DN392B LED16/830 PSU D150 WH GM	Not applicable

Order Code	Full Product Name	Driver failure rate at 5000 h
72025100	DN393B LED22/865 PSU D200 ALU GM	0.12 %
72040400	DN393B LED22/830 PSU D200 ALU WP GM	0.12 %
72004600	DN393B LED22/840 PSU D200 ALU WP GM	0.12 %
72032900	DN393B LED22/865 PSU D200 ALU WP GM	0.12 %
72041100	DN393B LED22/830 PSD D200 ALU GM	0.12 %
72005300	DN393B LED22/840 PSD D200 ALU GM	0.12 %
01574141	DN393B LED22/840 PSU D200 WH GC	0.12 %
72001500	DN392B LED16/830 PSU D200 WH GM	0.16 %
72030500	DN392B LED16/840 PSU D200 WH GM	0.16 %
72053400	DN392B LED16/865 PSU D200 WH GM	0.16 %
72002200	DN393B LED22/830 PSU D200 WH GM	0.12 %
72054100	DN393B LED22/865 PSU D200 WH GM	0.12 %
72056500	DN392B LED16/840 PSD D200 WH GM	0.16 %
72028200	DN393B LED22/830 PSD D200 WH GM	0.12 %
72019000	DN393B LED22/840 PSD D200 WH GM	0.12 %

Order Code	Full Product Name	Maximum dim level
72009100	DN392B LED16/865 PSU D150 WH GM	Not applicable
52101800	DN391B LED11/840 PSD D150 WH GM	-
72007700	DN392B LED16/840 PSD D150 WH GM	-
72047300	DN392B LED16/830 PSU D200 ALU GM	Not applicable
72010700	DN392B LED16/840 PSU D200 ALU GM	Not applicable
72039800	DN392B LED16/865 PSU D200 ALU GM	Not applicable
72048000	DN393B LED22/830 PSU D200 ALU GM	Not applicable
72011400	DN393B LED22/840 PSU D200 ALU GM	Not applicable
72025100	DN393B LED22/865 PSU D200 ALU GM	Not applicable
72040400	DN393B LED22/830 PSU D200 ALU WP GM	Not applicable
72004600	DN393B LED22/840 PSU D200 ALU WP GM	Not applicable
72032900	DN393B LED22/865 PSU D200 ALU WP GM	Not applicable
72041100	DN393B LED22/830 PSD D200 ALU GM	-
72005300	DN393B LED22/840 PSD D200 ALU GM	-
01574141	DN393B LED22/840 PSU D200 WH GC	Not applicable
72001500	DN392B LED16/830 PSU D200 WH GM	Not applicable
72030500	DN392B LED16/840 PSU D200 WH GM	Not applicable
72053400	DN392B LED16/865 PSU D200 WH GM	Not applicable
72002200	DN393B LED22/830 PSU D200 WH GM	Not applicable
72054100	DN393B LED22/865 PSU D200 WH GM	Not applicable
72056500	DN392B LED16/840 PSD D200 WH GM	-
72028200	DN393B LED22/830 PSD D200 WH GM	-
72019000	DN393B LED22/840 PSD D200 WH GM	-

