



The most competitive specification downlight for TCO attractiveness with diversity and system compatibility

GreenSpace G5

GreenSpace Gen5 is a new LED downlight range combining light efficiency and comfort with product diversity and system compatibility

Benefits

- Energy efficient
- Design compactness
- Smart lighting


Features

- High optical efficiency
- Compact form factor
- DALI/DALI-VLC/POE compatible




Application

- Office
- shopping mall
- hotel
- retail etc.

Dimensional drawing



Dimensional drawing



General Information	
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit
Light Technical	
Optical cover type	Transparent bowl with white cover
Color rendering index (CRI)	>80
Optic type	High-gloss high reflectance
Mechanical and Housing	
Housing Color	Black and white
Approval and Application	
Mech. impact protection code	IK02
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L80B50	43,000 hour(s)
Median useful life L90B50	20,000 hour(s)

General Information

Order Code	Full Product Name	CE mark
911401571941	DN390B LED6/840 PSU D100 ALU GC	-
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-
911401576541	DN391B LED11/830 PSU D100 ALU GC	-
911401576641	DN391B LED11/840 PSU D100 ALU GC	-
911401576841	DN391B LED11/840 PSD D100 ALU GC	-
911401578141	DN390B LED6/840 PSU D100 ALU GM	CE mark
911401578241	DN390B LED6/865 PSU D100 ALU GM	CE mark
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	CE mark
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	CE mark
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	CE mark
911401571641	DN390B LED6/830 PSU D100 WH GC	-
911401571741	DN390B LED6/840 PSU D100 WH GC	-
911401577741	DN390B LED6/830 PSU D100 WH GM	CE mark
911401577841	DN390B LED6/840 PSU D100 WH GM	CE mark
911401577941	DN390B LED6/865 PSU D100 WH GM	CE mark
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	CE mark
911401572341	DN391B LED11/830 PSU D150 ALU GC	-
911401572441	DN391B LED11/840 PSU D150 ALU GC	-
911401572541	DN391B LED11/865 PSU D150 ALU GC	-
911401572841	DN391B LED11/830 PSD D150 ALU GC	-
911401572941	DN391B LED11/840 PSD D150 ALU GC	-
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-
911401577141	DN392B LED16/830 PSU D150 ALU GC	-
911401577241	DN392B LED16/840 PSU D150 ALU GC	-
911401577641	DN392B LED16/840 PSD D150 ALU GC	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	CE mark
911401578741	DN391B LED11/840 PSU D150 ALU GM	CE mark
911401578841	DN391B LED11/865 PSU D150 ALU GM	CE mark
911401579241	DN392B LED16/830 PSU D150 ALU GM	CE mark
911401579341	DN392B LED16/840 PSU D150 ALU GM	CE mark
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	CE mark
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	CE mark
911401581841	DN391B LED11/830 PSD D150 ALU GM	CE mark
911401581941	DN391B LED11/840 PSD D150 ALU GM	CE mark
911401584441	DN391B LED11/830 PSD D150 ALU CAU	CE mark
911401585741	DN392B LED16/840 PSD D150 ALU GM	CE mark
911401572041	DN391B LED11/830 PSU D150 WH GC	-
911401572141	DN391B LED11/840 PSU D150 WH GC	-
911401572241	DN391B LED11/865 PSU D150 WH GC	-
911401572741	DN391B LED11/840 PSD D150 WH GC	-
911401575741	DN392B LED16/830 POE D150 WH GC	-
911401576941	DN392B LED16/830 PSU D150 WH GC	-
911401577041	DN392B LED16/840 PSU D150 WH GC	-
911401577341	DN392B LED16/830 PSD D150 WH GC	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-

Order Code	Full Product Name	CE mark
911401578341	DN391B LED11/830 PSU D150 WH GM	CE mark
911401578541	DN391B LED11/865 PSU D150 WH GM	CE mark
911401578941	DN392B LED16/830 PSU D150 WH GM	CE mark
911401579141	DN392B LED16/865 PSU D150 WH GM	CE mark
911401581741	DN391B LED11/840 PSD D150 WH GM	CE mark
911401583041	DN391B LED11/830 PSU D150 WH CAU	CE mark
911401583141	DN391B LED11/840 PSU D150 WH CAU	CE mark
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	CE mark
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	CE mark
911401584241	DN391B LED11/830 PSD D150 WH CAU	CE mark
911401584341	DN391B LED11/840 PSD D150 WH CAU	CE mark
911401585541	DN392B LED16/840 PSD D150 WH GM	CE mark
911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401574241	DN393B LED22/830 PSU D200 ALU GC	-
911401574341	DN393B LED22/840 PSU D200 ALU GC	-
911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401579841	DN392B LED16/830 PSU D200 ALU GM	CE mark
911401579941	DN392B LED16/840 PSU D200 ALU GM	CE mark
911401580041	DN392B LED16/865 PSU D200 ALU GM	CE mark
911401580441	DN393B LED22/830 PSU D200 ALU GM	CE mark
911401580541	DN393B LED22/840 PSU D200 ALU GM	CE mark
911401580641	DN393B LED22/865 PSU D200 ALU GM	CE mark
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	CE mark
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	CE mark
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	CE mark
911401582641	DN393B LED22/830 PSD D200 ALU GM	CE mark
911401582741	DN393B LED22/840 PSD D200 ALU GM	CE mark
911401585241	DN393B LED22/830 PSD D200 ALU CAU	CE mark
911401585341	DN393B LED22/840 PSD D200 ALU CAU	CE mark
911401573041	DN392B LED16/830 PSU D200 WH GC	-
911401573141	DN392B LED16/840 PSU D200 WH GC	-
911401573241	DN392B LED16/865 PSU D200 WH GC	-
911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401574041	DN393B LED22/830 PSU D200 WH GC	-
911401574141	DN393B LED22/840 PSU D200 WH GC	-
911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401579541	DN392B LED16/830 PSU D200 WH GM	CE mark
911401579641	DN392B LED16/840 PSU D200 WH GM	CE mark
911401579741	DN392B LED16/865 PSU D200 WH GM	CE mark
911401580141	DN393B LED22/830 PSU D200 WH GM	CE mark
911401580341	DN393B LED22/865 PSU D200 WH GM	CE mark
911401582141	DN392B LED16/840 PSD D200 WH GM	CE mark
911401582441	DN393B LED22/830 PSD D200 WH GM	CE mark
911401582541	DN393B LED22/840 PSD D200 WH GM	CE mark
911401583341	DN392B LED16/840 PSU D200 WH CAU	CE mark
911401583441	DN393B LED22/830 PSU D200 WH CAU	CE mark
911401583541	DN393B LED22/840 PSU D200 WH CAU	CE mark
911401584741	DN392B LED16/840 PSD D200 WH CAU	CE mark
911401585141	DN393B LED22/840 PSD D200 WH CAU	CE mark

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401571941	DN390B LED6/840 PSU D100 ALU GC	60 degree(s)	4000 K	109 lm/W	600 lm
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	104 lm/W	570 lm
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	109 lm/W	600 lm
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401576541	DN391B LED11/830 PSU D100 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401576641	DN391B LED11/840 PSU D100 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401576841	DN391B LED11/840 PSD D100 ALU GC	60 degree(s)	4000 K	82 lm/W	950 lm
911401578141	DN390B LED6/840 PSU D100 ALU GM	60 degree(s)	4000 K	109 lm/W	600 lm
911401578241	DN390B LED6/865 PSU D100 ALU GM	60 degree(s)	6500 K	109 lm/W	600 lm
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	60 degree(s)	3000 K	104 lm/W	570 lm
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	60 degree(s)	4000 K	109 lm/W	600 lm
911401580941	DN390B LED6/865 PSU	60 degree(s)	6500 K	109 lm/W	600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	D100 ALU WP GM				
911401571641	DN390B LED6/830 PSU D100 WH GC	72 degree(s)	3000 K	104 lm/W	570 lm
911401571741	DN390B LED6/840 PSU D100 WH GC	72 degree(s)	4000 K	109 lm/W	600 lm
911401577741	DN390B LED6/830 PSU D100 WH GM	72 degree(s)	3000 K	104 lm/W	570 lm
911401577841	DN390B LED6/840 PSU D100 WH GM	72 degree(s)	4000 K	109 lm/W	600 lm
911401577941	DN390B LED6/865 PSU D100 WH GM	72 degree(s)	6500 K	109 lm/W	600 lm
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	72 degree(s)	3000 K	104 lm/W	570 lm
911401572341	DN391B LED11/830 PSU D150 ALU GC	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401572441	DN391B LED11/840 PSU D150 ALU GC	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401572541	DN391B LED11/865 PSU D150 ALU GC	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401572841	DN391B LED11/830 PSD D150 ALU GC	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401572941	DN391B LED11/840 PSD D150 ALU GC	60 degree(s)	4000 K	96 lm/W	1,100 lm
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	60 degree(s)	6500 K	110 lm/W	1,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401577141	DN392B LED16/830 PSU D150 ALU GC	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401577241	DN392B LED16/840 PSU D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401577641	DN392B LED16/840 PSD D150 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401578641	DN391B LED11/830 PSU D150 ALU GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401578741	DN391B LED11/840 PSU D150 ALU GM	60 degree(s)	4000 K	116 lm/W	1,100 lm
911401578841	DN391B LED11/865 PSU D150 ALU GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401579241	DN392B LED16/830 PSU D150 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401579341	DN392B LED16/840 PSU D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	60 degree(s)	3000 K	111 lm/W	1,050 lm
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	60 degree(s)	6500 K	116 lm/W	1,100 lm
911401581841	DN391B LED11/830 PSD D150 ALU GM	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401581941	DN391B LED11/840 PSD D150 ALU GM	60 degree(s)	4000 K	96 lm/W	1,100 lm
911401584441	DN391B LED11/830 PSD D150 ALU CAU	60 degree(s)	3000 K	91 lm/W	1,050 lm
911401585741	DN392B LED16/840 PSD D150 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401572041	DN391B LED11/830 PSU D150 WH GC	85 degree(s)	3000 K	111 lm/W	1,050 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401572141	DN391B LED11/840 PSU D150 WH GC	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401572241	DN391B LED11/865 PSU D150 WH GC	85 degree(s)	6500 K	116 lm/W	1,100 lm
911401572741	DN391B LED11/840 PSD D150 WH GC	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401575741	DN392B LED16/830 POE D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401576941	DN392B LED16/830 PSU D150 WH GC	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401577041	DN392B LED16/840 PSU D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401577341	DN392B LED16/830 PSD D150 WH GC	85 degree(s)	3000 K	97 lm/W	1,500 lm
911401577441	DN392B LED16/840 PSD D150 WH GC	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401578341	DN391B LED11/830 PSU D150 WH GM	85 degree(s)	3000 K	111 lm/W	1,050 lm
911401578541	DN391B LED11/865 PSU D150 WH GM	85 degree(s)	6500 K	116 lm/W	1,100 lm
911401578941	DN392B LED16/830 PSU D150 WH GM	85 degree(s)	3000 K	103 lm/W	1,500 lm
911401579141	DN392B LED16/865 PSU D150 WH GM	85 degree(s)	6500 K	110 lm/W	1,600 lm
911401581741	DN391B LED11/840 PSD D150 WH GM	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401583041	DN391B LED11/830 PSU D150 WH CAU	85 degree(s)	3000 K	111 lm/W	1,050 lm
911401583141	DN391B LED11/840 PSU D150 WH CAU	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	85 degree(s)	3000 K	111 lm/W	1,050 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	85 degree(s)	4000 K	116 lm/W	1,100 lm
911401584241	DN391B LED11/830 PSD D150 WH CAU	85 degree(s)	3000 K	91 lm/W	1,050 lm
911401584341	DN391B LED11/840 PSD D150 WH CAU	85 degree(s)	4000 K	96 lm/W	1,100 lm
911401585541	DN392B LED16/840 PSD D150 WH GM	85 degree(s)	4000 K	110 lm/W	1,600 lm
911401573941	DN392B LED16/840 PSD D200 ALU GC	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401574241	DN393B LED22/830 PSU D200 ALU GC	60 degree(s)	3000 K	111 lm/W	2,100 lm
911401574341	DN393B LED22/840 PSU D200 ALU GC	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401574641	DN393B LED22/830 PSD D200 ALU GC	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401574741	DN393B LED22/840 PSD D200 ALU GC	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401579841	DN392B LED16/830 PSU D200 ALU GM	60 degree(s)	3000 K	103 lm/W	1,500 lm
911401579941	DN392B LED16/840 PSU D200 ALU GM	60 degree(s)	4000 K	110 lm/W	1,600 lm
911401580041	DN392B LED16/865 PSU D200 ALU GM	60 degree(s)	6500 K	110 lm/W	1,600 lm
911401580441	DN393B LED22/830 PSU D200 ALU GM	60 degree(s)	3000 K	111 lm/W	2,100 lm
911401580541	DN393B LED22/840 PSU D200 ALU GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401580641	DN393B LED22/865 PSU D200 ALU GM	60 degree(s)	6500 K	116 lm/W	2,200 lm
911401581341	DN393B LED22/830 PSU	60 degree(s)	3000 K	111 lm/W	2,100 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
	D200 ALU WP GM				
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	60 degree(s)	4000 K	116 lm/W	2,200 lm
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	60 degree(s)	6500 K	116 lm/W	2,200 lm
911401582641	DN393B LED22/830 PSD D200 ALU GM	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401582741	DN393B LED22/840 PSD D200 ALU GM	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401585241	DN393B LED22/830 PSD D200 ALU CAU	60 degree(s)	3000 K	102 lm/W	2,100 lm
911401585341	DN393B LED22/840 PSD D200 ALU CAU	60 degree(s)	4000 K	107 lm/W	2,200 lm
911401573041	DN392B LED16/830 PSU D200 WH GC	92 degree(s)	3000 K	103 lm/W	1,500 lm
911401573141	DN392B LED16/840 PSU D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401573241	DN392B LED16/865 PSU D200 WH GC	92 degree(s)	6500 K	110 lm/W	1,600 lm
911401573741	DN392B LED16/840 PSD D200 WH GC	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401574041	DN393B LED22/830 PSU D200 WH GC	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401574141	DN393B LED22/840 PSU D200 WH GC	92 degree(s)	4000 K	116 lm/W	2,200 lm
911401574541	DN393B LED22/840 PSD D200 WH GC	92 degree(s)	4000 K	107 lm/W	2,200 lm
911401579541	DN392B LED16/830 PSU D200 WH GM	92 degree(s)	3000 K	103 lm/W	1,500 lm
911401579641	DN392B LED16/840 PSU D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401579741	DN392B LED16/865 PSU D200 WH GM	92 degree(s)	6500 K	110 lm/W	1,600 lm
911401580141	DN393B LED22/830 PSU D200 WH GM	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401580341	DN393B LED22/865 PSU D200 WH GM	92 degree(s)	6500 K	116 lm/W	2,200 lm
911401582141	DN392B LED16/840 PSD D200 WH GM	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401582441	DN393B LED22/830 PSD D200 WH GM	92 degree(s)	3000 K	102 lm/W	2,100 lm
911401582541	DN393B LED22/840 PSD D200 WH GM	92 degree(s)	4000 K	107 lm/W	2,200 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
911401583341	DN392B LED16/840 PSU D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401583441	DN393B LED22/830 PSU D200 WH CAU	92 degree(s)	3000 K	111 lm/W	2,100 lm
911401583541	DN393B LED22/840 PSU D200 WH CAU	92 degree(s)	4000 K	116 lm/W	2,200 lm
911401584741	DN392B LED16/840 PSD D200 WH CAU	92 degree(s)	4000 K	110 lm/W	1,600 lm
911401585141	DN393B LED22/840 PSD D200 WH CAU	92 degree(s)	4000 K	107 lm/W	2,200 lm

Operating and Electrical

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption
911401571941	DN390B LED6/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	5.5 W
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	5.5 W
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	220-240 V	50 or 60 Hz	9.5 W
911401576541	DN391B LED11/830 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576641	DN391B LED11/840 PSU D100 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401576841	DN391B LED11/840 PSD D100 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401578141	DN390B LED6/840 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401578241	DN390B LED6/865 PSU D100 ALU GM	220-240 V	50 or 60 Hz	5.5 W
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W

Order Code	Full Product Name	Input Voltage	Line Frequency	Power Consumption
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	220-240 V	50 or 60 Hz	5.5 W
911401571641	DN390B LED6/830 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401571741	DN390B LED6/840 PSU D100 WH GC	220-240 V	50 or 60 Hz	5.5 W
911401577741	DN390B LED6/830 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577841	DN390B LED6/840 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401577941	DN390B LED6/865 PSU D100 WH GM	220-240 V	50 or 60 Hz	5.5 W
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	220-240 V	50 or 60 Hz	5.5 W
911401572341	DN391B LED11/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572441	DN391B LED11/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572541	DN391B LED11/865 PSU D150 ALU GC	220-240 V	50 or 60 Hz	9.5 W
911401572841	DN391B LED11/830 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401572941	DN391B LED11/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	11.5 W
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	220-240 V	50 or 60 Hz	14.5 W
911401577141	DN392B LED16/830 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577241	DN392B LED16/840 PSU D150 ALU GC	220-240 V	50 or 60 Hz	14.5 W
911401577641	DN392B LED16/840 PSD D150 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401578641	DN391B LED11/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578741	DN391B LED11/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401578841	DN391B LED11/865 PSU D150 ALU GM	220-240 V	50 or 60 Hz	9.5 W
911401579241	DN392B LED16/830 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579341	DN392B LED16/840 PSU D150 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	220-240 V	50 or 60 Hz	9.5 W
911401581841	DN391B LED11/830 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401581941	DN391B LED11/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	11.5 W
911401584441	DN391B LED11/830 PSD D150 ALU CAU	220-240 V	50 or 60 Hz	11.5 W
911401585741	DN392B LED16/840 PSD D150 ALU GM	220-240 V	50 or 60 Hz	15.5 W
911401572041	DN391B LED11/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572141	DN391B LED11/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572241	DN391B LED11/865 PSU D150 WH GC	220-240 V	50 or 60 Hz	9.5 W
911401572741	DN391B LED11/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	11.5 W
911401575741	DN392B LED16/830 POE D150 WH GC	53 V	- Hz	14.5 W
911401576941	DN392B LED16/830 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577041	DN392B LED16/840 PSU D150 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401577341	DN392B LED16/830 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401577441	DN392B LED16/840 PSD D150 WH GC	220-240 V	50 or 60 Hz	15.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401578341	DN391B LED11/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578541	DN391B LED11/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	9.5 W
911401578941	DN392B LED16/830 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579141	DN392B LED16/865 PSU D150 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401581741	DN391B LED11/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	11.5 W
911401583041	DN391B LED11/830 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583141	DN391B LED11/840 PSU D150 WH CAU	220-240 V	50 or 60 Hz	9.5 W
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	220-240 V	50 or 60 Hz	9.5 W
911401584241	DN391B LED11/830 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401584341	DN391B LED11/840 PSD D150 WH CAU	220-240 V	50 or 60 Hz	11.5 W
911401585541	DN392B LED16/840 PSD D150 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401573941	DN392B LED16/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	15.5 W
911401574241	DN393B LED22/830 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574341	DN393B LED22/840 PSU D200 ALU GC	220-240 V	50 or 60 Hz	19 W
911401574641	DN393B LED22/830 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401574741	DN393B LED22/840 PSD D200 ALU GC	220-240 V	50 or 60 Hz	20.5 W
911401579841	DN392B LED16/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401579941	DN392B LED16/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401580041	DN392B LED16/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	14.5 W
911401580441	DN393B LED22/830 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580541	DN393B LED22/840 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401580641	DN393B LED22/865 PSU D200 ALU GM	220-240 V	50 or 60 Hz	19 W
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	220-240 V	50 or 60 Hz	19 W
911401582641	DN393B LED22/830 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401582741	DN393B LED22/840 PSD D200 ALU GM	220-240 V	50 or 60 Hz	20.5 W
911401585241	DN393B LED22/830 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401585341	DN393B LED22/840 PSD D200 ALU CAU	220-240 V	50 or 60 Hz	20.5 W
911401573041	DN392B LED16/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573141	DN392B LED16/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573241	DN392B LED16/865 PSU D200 WH GC	220-240 V	50 or 60 Hz	14.5 W
911401573741	DN392B LED16/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	15.5 W
911401574041	DN393B LED22/830 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574141	DN393B LED22/840 PSU D200 WH GC	220-240 V	50 or 60 Hz	19 W
911401574541	DN393B LED22/840 PSD D200 WH GC	220-240 V	50 or 60 Hz	20.5 W
911401579541	DN392B LED16/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W

Order Code	Full Product Name	Input		Power
		Voltage	Line Frequency	Consumption
911401579641	DN392B LED16/840 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401579741	DN392B LED16/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	14.5 W
911401580141	DN393B LED22/830 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401580341	DN393B LED22/865 PSU D200 WH GM	220-240 V	50 or 60 Hz	19 W
911401582141	DN392B LED16/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	15.5 W
911401582441	DN393B LED22/830 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401582541	DN393B LED22/840 PSD D200 WH GM	220-240 V	50 or 60 Hz	20.5 W
911401583341	DN392B LED16/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	14.5 W
911401583441	DN393B LED22/830 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401583541	DN393B LED22/840 PSU D200 WH CAU	220-240 V	50 or 60 Hz	19 W
911401584741	DN392B LED16/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	15.5 W
911401585141	DN393B LED22/840 PSD D200 WH CAU	220-240 V	50 or 60 Hz	20.5 W

Temperature

Order Code	Full Product Name	Ambient temperature range
911401571941	DN390B LED6/840 PSU D100 ALU GC	-20 to +40 °C
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	-20 to +40 °C
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	-20 to +40 °C
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	-20 to +40 °C
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	-20 to +40 °C
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	-20 to +40 °C
911401576541	DN391B LED11/830 PSU D100 ALU GC	-20 to +40 °C
911401576641	DN391B LED11/840 PSU D100 ALU GC	-20 to +40 °C
911401576841	DN391B LED11/840 PSD D100 ALU GC	-20 to +40 °C
911401578141	DN390B LED6/840 PSU D100 ALU GM	-20 to +40 °C
911401578241	DN390B LED6/865 PSU D100 ALU GM	-20 to +40 °C
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	-20 to +40 °C
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	-20 to +40 °C
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	-20 to +40 °C
911401571641	DN390B LED6/830 PSU D100 WH GC	-20 to +40 °C
911401571741	DN390B LED6/840 PSU D100 WH GC	-20 to +40 °C
911401577741	DN390B LED6/830 PSU D100 WH GM	-20 to +40 °C
911401577841	DN390B LED6/840 PSU D100 WH GM	-20 to +40 °C
911401577941	DN390B LED6/865 PSU D100 WH GM	-20 to +40 °C
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	-20 to +40 °C
911401572341	DN391B LED11/830 PSU D150 ALU GC	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401572441	DN391B LED11/840 PSU D150 ALU GC	-20 to +40 °C
911401572541	DN391B LED11/865 PSU D150 ALU GC	-20 to +40 °C
911401572841	DN391B LED11/830 PSD D150 ALU GC	-20 to +40 °C
911401572941	DN391B LED11/840 PSD D150 ALU GC	-20 to +40 °C
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	-20 to +40 °C
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	-20 to +40 °C
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	-20 to +40 °C
911401577141	DN392B LED16/830 PSU D150 ALU GC	-20 to +40 °C
911401577241	DN392B LED16/840 PSU D150 ALU GC	-20 to +40 °C
911401577641	DN392B LED16/840 PSD D150 ALU GC	-20 to +40 °C
911401578641	DN391B LED11/830 PSU D150 ALU GM	-20 to +40 °C
911401578741	DN391B LED11/840 PSU D150 ALU GM	-20 to +40 °C
911401578841	DN391B LED11/865 PSU D150 ALU GM	-20 to +40 °C
911401579241	DN392B LED16/830 PSU D150 ALU GM	-20 to +40 °C
911401579341	DN392B LED16/840 PSU D150 ALU GM	-20 to +40 °C
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	-20 to +40 °C
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	-20 to +40 °C
911401581841	DN391B LED11/830 PSD D150 ALU GM	-20 to +40 °C
911401581941	DN391B LED11/840 PSD D150 ALU GM	-20 to +40 °C
911401584441	DN391B LED11/830 PSD D150 ALU CAU	-20 to +40 °C
911401585741	DN392B LED16/840 PSD D150 ALU GM	-20 to +40 °C

Order Code	Full Product Name	Ambient temperature range
911401572041	DN391B LED11/830 PSU D150 WH GC	-20 to +40 °C
911401572141	DN391B LED11/840 PSU D150 WH GC	-20 to +40 °C
911401572241	DN391B LED11/865 PSU D150 WH GC	-20 to +40 °C
911401572741	DN391B LED11/840 PSD D150 WH GC	-20 to +40 °C
911401575741	DN392B LED16/830 POE D150 WH GC	0 to +40 °C
911401576941	DN392B LED16/830 PSU D150 WH GC	-20 to +40 °C
911401577041	DN392B LED16/840 PSU D150 WH GC	-20 to +40 °C
911401577341	DN392B LED16/830 PSD D150 WH GC	-20 to +40 °C
911401577441	DN392B LED16/840 PSD D150 WH GC	-20 to +40 °C
911401578341	DN391B LED11/830 PSU D150 WH GM	-20 to +40 °C
911401578541	DN391B LED11/865 PSU D150 WH GM	-20 to +40 °C
911401578941	DN392B LED16/830 PSU D150 WH GM	-20 to +40 °C
911401579141	DN392B LED16/865 PSU D150 WH GM	-20 to +40 °C
911401581741	DN391B LED11/840 PSD D150 WH GM	-20 to +40 °C
911401583041	DN391B LED11/830 PSU D150 WH CAU	-20 to +40 °C
911401583141	DN391B LED11/840 PSU D150 WH CAU	-20 to +40 °C
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	-20 to +40 °C
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	-20 to +40 °C
911401584241	DN391B LED11/830 PSD D150 WH CAU	-20 to +40 °C
911401584341	DN391B LED11/840 PSD D150 WH CAU	-20 to +40 °C
911401585541	DN392B LED16/840 PSD D150 WH GM	-20 to +40 °C
911401573941	DN392B LED16/840 PSD D200 ALU GC	-20 to +40 °C
911401574241	DN393B LED22/830 PSU D200 ALU GC	-20 to +40 °C
911401574341	DN393B LED22/840 PSU D200 ALU GC	-20 to +40 °C
911401574641	DN393B LED22/830 PSD D200 ALU GC	-20 to +40 °C
911401574741	DN393B LED22/840 PSD D200 ALU GC	-20 to +40 °C
911401579841	DN392B LED16/830 PSU D200 ALU GM	-20 to +40 °C
911401579941	DN392B LED16/840 PSU D200 ALU GM	-20 to +40 °C
911401580041	DN392B LED16/865 PSU D200 ALU GM	-20 to +40 °C
911401580441	DN393B LED22/830 PSU D200 ALU GM	-20 to +40 °C
911401580541	DN393B LED22/840 PSU D200 ALU GM	-20 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
911401571941	DN390B LED6/840 PSU D100 ALU GC	No
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	No
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	No
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	No
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	No
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	No
911401576541	DN391B LED11/830 PSU D100 ALU GC	No
911401576641	DN391B LED11/840 PSU D100 ALU GC	No
911401576841	DN391B LED11/840 PSD D100 ALU GC	Yes
911401578141	DN390B LED6/840 PSU D100 ALU GM	No
911401578241	DN390B LED6/865 PSU D100 ALU GM	No
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	No
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	No
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	No
911401571641	DN390B LED6/830 PSU D100 WH GC	No
911401571741	DN390B LED6/840 PSU D100 WH GC	No
911401577741	DN390B LED6/830 PSU D100 WH GM	No

Order Code	Full Product Name	Ambient temperature range
911401580641	DN393B LED22/865 PSU D200 ALU GM	-20 to +40 °C
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	-20 to +40 °C
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	-20 to +40 °C
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	-20 to +40 °C
911401582641	DN393B LED22/830 PSD D200 ALU GM	-20 to +40 °C
911401582741	DN393B LED22/840 PSD D200 ALU GM	-20 to +40 °C
911401585241	DN393B LED22/830 PSD D200 ALU CAU	-20 to +40 °C
911401585341	DN393B LED22/840 PSD D200 ALU CAU	-20 to +40 °C
911401573041	DN392B LED16/830 PSU D200 WH GC	-20 to +40 °C
911401573141	DN392B LED16/840 PSU D200 WH GC	-20 to +40 °C
911401573241	DN392B LED16/865 PSU D200 WH GC	-20 to +40 °C
911401573741	DN392B LED16/840 PSD D200 WH GC	-20 to +40 °C
911401574041	DN393B LED22/830 PSU D200 WH GC	-20 to +40 °C
911401574141	DN393B LED22/840 PSU D200 WH GC	-20 to +40 °C
911401574541	DN393B LED22/840 PSD D200 WH GC	-20 to +40 °C
911401579541	DN392B LED16/830 PSU D200 WH GM	-20 to +40 °C
911401579641	DN392B LED16/840 PSU D200 WH GM	-20 to +40 °C
911401579741	DN392B LED16/865 PSU D200 WH GM	-20 to +40 °C
911401580141	DN393B LED22/830 PSU D200 WH GM	-20 to +40 °C
911401580341	DN393B LED22/865 PSU D200 WH GM	-20 to +40 °C
911401582141	DN392B LED16/840 PSD D200 WH GM	-20 to +40 °C
911401582441	DN393B LED22/830 PSD D200 WH GM	-20 to +40 °C
911401582541	DN393B LED22/840 PSD D200 WH GM	-20 to +40 °C
911401583341	DN392B LED16/840 PSU D200 WH CAU	-20 to +40 °C
911401583441	DN393B LED22/830 PSU D200 WH CAU	-20 to +40 °C
911401583541	DN393B LED22/840 PSU D200 WH CAU	-20 to +40 °C
911401584741	DN392B LED16/840 PSD D200 WH CAU	-20 to +40 °C
911401585141	DN393B LED22/840 PSD D200 WH CAU	-20 to +40 °C

Order Code	Full Product Name	Dimmable
911401579241	DN392B LED16/830 PSU D150 ALU GM	No
911401579341	DN392B LED16/840 PSU D150 ALU GM	No
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	No
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	No
911401581841	DN391B LED11/830 PSD D150 ALU GM	Yes
911401581941	DN391B LED11/840 PSD D150 ALU GM	Yes
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Yes
911401585741	DN392B LED16/840 PSD D150 ALU GM	Yes
911401572041	DN391B LED11/830 PSU D150 WH GC	No
911401572141	DN391B LED11/840 PSU D150 WH GC	No
911401572241	DN391B LED11/865 PSU D150 WH GC	No
911401572741	DN391B LED11/840 PSD D150 WH GC	Yes
911401575741	DN392B LED16/830 POE D150 WH GC	Yes
911401576941	DN392B LED16/830 PSU D150 WH GC	No
911401577041	DN392B LED16/840 PSU D150 WH GC	No
911401577341	DN392B LED16/830 PSD D150 WH GC	Yes
911401577441	DN392B LED16/840 PSD D150 WH GC	Yes
911401578341	DN391B LED11/830 PSU D150 WH GM	No
911401578541	DN391B LED11/865 PSU D150 WH GM	No
911401578941	DN392B LED16/830 PSU D150 WH GM	No
911401579141	DN392B LED16/865 PSU D150 WH GM	No
911401581741	DN391B LED11/840 PSD D150 WH GM	Yes
911401583041	DN391B LED11/830 PSU D150 WH CAU	No
911401583141	DN391B LED11/840 PSU D150 WH CAU	No
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	No
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	No
911401584241	DN391B LED11/830 PSD D150 WH CAU	Yes
911401584341	DN391B LED11/840 PSD D150 WH CAU	Yes
911401585541	DN392B LED16/840 PSD D150 WH GM	Yes
911401573941	DN392B LED16/840 PSD D200 ALU GC	Yes
911401574241	DN393B LED22/830 PSU D200 ALU GC	No
911401574341	DN393B LED22/840 PSU D200 ALU GC	No
911401574641	DN393B LED22/830 PSD D200 ALU GC	Yes
911401574741	DN393B LED22/840 PSD D200 ALU GC	Yes

Order Code	Full Product Name	Dimmable
911401579841	DN392B LED16/830 PSU D200 ALU GM	No
911401579941	DN392B LED16/840 PSU D200 ALU GM	No
911401580041	DN392B LED16/865 PSU D200 ALU GM	No
911401580441	DN393B LED22/830 PSU D200 ALU GM	No
911401580541	DN393B LED22/840 PSU D200 ALU GM	No
911401580641	DN393B LED22/865 PSU D200 ALU GM	No
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	No
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	No
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	No
911401582641	DN393B LED22/830 PSD D200 ALU GM	Yes
911401582741	DN393B LED22/840 PSD D200 ALU GM	Yes
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Yes
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Yes
911401573041	DN392B LED16/830 PSU D200 WH GC	No
911401573141	DN392B LED16/840 PSU D200 WH GC	No
911401573241	DN392B LED16/865 PSU D200 WH GC	No
911401573741	DN392B LED16/840 PSD D200 WH GC	Yes
911401574041	DN393B LED22/830 PSU D200 WH GC	No
911401574141	DN393B LED22/840 PSU D200 WH GC	No
911401574541	DN393B LED22/840 PSD D200 WH GC	Yes
911401579541	DN392B LED16/830 PSU D200 WH GM	No
911401579641	DN392B LED16/840 PSU D200 WH GM	No
911401579741	DN392B LED16/865 PSU D200 WH GM	No
911401580141	DN393B LED22/830 PSU D200 WH GM	No
911401580341	DN393B LED22/865 PSU D200 WH GM	No
911401582141	DN392B LED16/840 PSD D200 WH GM	Yes
911401582441	DN393B LED22/830 PSD D200 WH GM	Yes
911401582541	DN393B LED22/840 PSD D200 WH GM	Yes
911401583341	DN392B LED16/840 PSU D200 WH CAU	No
911401583441	DN393B LED22/830 PSU D200 WH CAU	No
911401583541	DN393B LED22/840 PSU D200 WH CAU	No
911401584741	DN392B LED16/840 PSD D200 WH CAU	Yes
911401585141	DN393B LED22/840 PSD D200 WH CAU	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401571941	DN390B LED6/840 PSU D100 ALU GC	Safety class I	IP20
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Safety class I	IP20/54
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401576541	DN391B LED11/830 PSU D100 ALU GC	Safety class I	IP20
911401576641	DN391B LED11/840 PSU D100 ALU GC	Safety class I	IP20
911401576841	DN391B LED11/840 PSD D100 ALU GC	Safety class I	IP20
911401578141	DN390B LED6/840 PSU D100 ALU GM	Safety class I	IP20
911401578241	DN390B LED6/865 PSU D100 ALU GM	Safety class I	IP20
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Safety class I	IP20/54
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Safety class I	IP20/54
911401571641	DN390B LED6/830 PSU D100 WH GC	Safety class I	IP20
911401571741	DN390B LED6/840 PSU D100 WH GC	Safety class I	IP20
911401577741	DN390B LED6/830 PSU D100 WH GM	Safety class I	IP20
911401577841	DN390B LED6/840 PSU D100 WH GM	Safety class I	IP20
911401577941	DN390B LED6/865 PSU D100 WH GM	Safety class I	IP20
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Safety class I	IP20/54
911401572341	DN391B LED11/830 PSU D150 ALU GC	Safety class I	IP20
911401572441	DN391B LED11/840 PSU D150 ALU GC	Safety class I	IP20
911401572541	DN391B LED11/865 PSU D150 ALU GC	Safety class I	IP20
911401572841	DN391B LED11/830 PSD D150 ALU GC	Safety class I	IP20
911401572941	DN391B LED11/840 PSD D150 ALU GC	Safety class I	IP20
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Safety class I	IP20/54
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Safety class I	IP20/54
911401577141	DN392B LED16/830 PSU D150 ALU GC	Safety class I	IP20
911401577241	DN392B LED16/840 PSU D150 ALU GC	Safety class I	IP20
911401577641	DN392B LED16/840 PSD D150 ALU GC	Safety class I	IP20
911401578641	DN391B LED11/830 PSU D150 ALU GM	Safety class I	IP20
911401578741	DN391B LED11/840 PSU D150 ALU GM	Safety class I	IP20
911401578841	DN391B LED11/865 PSU D150 ALU GM	Safety class I	IP20
911401579241	DN392B LED16/830 PSU D150 ALU GM	Safety class I	IP20
911401579341	DN392B LED16/840 PSU D150 ALU GM	Safety class I	IP20
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Safety class I	IP20/54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Safety class I	IP20/54
911401581841	DN391B LED11/830 PSD D150 ALU GM	Safety class I	IP20
911401581941	DN391B LED11/840 PSD D150 ALU GM	Safety class I	IP20
911401584441	DN391B LED11/830 PSD D150 ALU CAU	Safety class I	IP20
911401585741	DN392B LED16/840 PSD D150 ALU GM	Safety class I	IP20
911401572041	DN391B LED11/830 PSU D150 WH GC	Safety class I	IP20
911401572141	DN391B LED11/840 PSU D150 WH GC	Safety class I	IP20
911401572241	DN391B LED11/865 PSU D150 WH GC	Safety class I	IP20
911401572741	DN391B LED11/840 PSD D150 WH GC	Safety class I	IP20
911401575741	DN392B LED16/830 POE D150 WH GC	Safety class III	IP20
911401576941	DN392B LED16/830 PSU D150 WH GC	Safety class I	IP20
911401577041	DN392B LED16/840 PSU D150 WH GC	Safety class I	IP20
911401577341	DN392B LED16/830 PSD D150 WH GC	Safety class I	IP20
911401577441	DN392B LED16/840 PSD D150 WH GC	Safety class I	IP20
911401578341	DN391B LED11/830 PSU D150 WH GM	Safety class I	IP20
911401578541	DN391B LED11/865 PSU D150 WH GM	Safety class I	IP20
911401578941	DN392B LED16/830 PSU D150 WH GM	Safety class I	IP20
911401579141	DN392B LED16/865 PSU D150 WH GM	Safety class I	IP20
911401581741	DN391B LED11/840 PSD D150 WH GM	Safety class I	IP20
911401583041	DN391B LED11/830 PSU D150 WH CAU	Safety class I	IP20
911401583141	DN391B LED11/840 PSU D150 WH CAU	Safety class I	IP20
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Safety class I	IP20/54
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Safety class I	IP20/54
911401584241	DN391B LED11/830 PSD D150 WH CAU	Safety class I	IP20
911401584341	DN391B LED11/840 PSD D150 WH CAU	Safety class I	IP20

			Ingress protection
Order Code	Full Product Name	Protection class IEC	code
911401585541	DN392B LED16/840 PSD D150 WH GM	Safety class I	IP20
911401573941	DN392B LED16/840 PSD D200 ALU GC	Safety class I	IP20
911401574241	DN393B LED22/830 PSU D200 ALU GC	Safety class I	IP20
911401574341	DN393B LED22/840 PSU D200 ALU GC	Safety class I	IP20
911401574641	DN393B LED22/830 PSD D200 ALU GC	Safety class I	IP20
911401574741	DN393B LED22/840 PSD D200 ALU GC	Safety class I	IP20
911401579841	DN392B LED16/830 PSU D200 ALU GM	Safety class I	IP20
911401579941	DN392B LED16/840 PSU D200 ALU GM	Safety class I	IP20
911401580041	DN392B LED16/865 PSU D200 ALU GM	Safety class I	IP20
911401580441	DN393B LED22/830 PSU D200 ALU GM	Safety class I	IP20
911401580541	DN393B LED22/840 PSU D200 ALU GM	Safety class I	IP20
911401580641	DN393B LED22/865 PSU D200 ALU GM	Safety class I	IP20
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Safety class I	IP20/54
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Safety class I	IP20/54
911401582641	DN393B LED22/830 PSD D200 ALU GM	Safety class I	IP20
911401582741	DN393B LED22/840 PSD D200 ALU GM	Safety class I	IP20
911401585241	DN393B LED22/830 PSD D200 ALU CAU	Safety class I	IP20
911401585341	DN393B LED22/840 PSD D200 ALU CAU	Safety class I	IP20
911401573041	DN392B LED16/830 PSU D200 WH GC	Safety class I	IP20

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
911401571941	DN390B LED6/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	(0.44,0.403) SDCM<5
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	(0.38,0.38) SDCM<5
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	(0.31,0.32) SDCM<5

			Ingress protection
Order Code	Full Product Name	Protection class IEC	code
911401573141	DN392B LED16/840 PSU D200 WH GC	Safety class I	IP20
911401573241	DN392B LED16/865 PSU D200 WH GC	Safety class I	IP20
911401573741	DN392B LED16/840 PSD D200 WH GC	Safety class I	IP20
911401574041	DN393B LED22/830 PSU D200 WH GC	Safety class I	IP20
911401574141	DN393B LED22/840 PSU D200 WH GC	Safety class I	IP20
911401574541	DN393B LED22/840 PSD D200 WH GC	Safety class I	IP20
911401579541	DN392B LED16/830 PSU D200 WH GM	Safety class I	IP20
911401579641	DN392B LED16/840 PSU D200 WH GM	Safety class I	IP20
911401579741	DN392B LED16/865 PSU D200 WH GM	Safety class I	IP20
911401580141	DN393B LED22/830 PSU D200 WH GM	Safety class I	IP20
911401580341	DN393B LED22/865 PSU D200 WH GM	Safety class I	IP20
911401582141	DN392B LED16/840 PSD D200 WH GM	Safety class I	IP20
911401582441	DN393B LED22/830 PSD D200 WH GM	Safety class I	IP20
911401582541	DN393B LED22/840 PSD D200 WH GM	Safety class I	IP20
911401583341	DN392B LED16/840 PSU D200 WH CAU	Safety class I	IP20
911401583441	DN393B LED22/830 PSU D200 WH CAU	Safety class I	IP20
911401583541	DN393B LED22/840 PSU D200 WH CAU	Safety class I	IP20
911401584741	DN392B LED16/840 PSD D200 WH CAU	Safety class I	IP20
911401585141	DN393B LED22/840 PSD D200 WH CAU	Safety class I	IP20

Order Code	Full Product Name	Initial chromaticity
911401576541	DN391B LED11/830 PSU D100 ALU GC	(0.44,0.403) SDCM<5
911401576641	DN391B LED11/840 PSU D100 ALU GC	(0.38,0.38) SDCM<5
911401576841	DN391B LED11/840 PSD D100 ALU GC	(0.38,0.38) SDCM<5
911401578141	DN390B LED6/840 PSU D100 ALU GM	(0.38,0.38) SDCM<5
911401578241	DN390B LED6/865 PSU D100 ALU GM	(0.31,0.32) SDCM<5
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	(0.38,0.38) SDCM<5
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	(0.31,0.32) SDCM<5
911401571641	DN390B LED6/830 PSU D100 WH GC	(0.44,0.403) SDCM<5
911401571741	DN390B LED6/840 PSU D100 WH GC	(0.38,0.38) SDCM<5
911401577741	DN390B LED6/830 PSU D100 WH GM	(0.44,0.403) SDCM<5
911401577841	DN390B LED6/840 PSU D100 WH GM	(0.38,0.38) SDCM<5
911401577941	DN390B LED6/865 PSU D100 WH GM	(0.31,0.32) SDCM<5
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	(0.44,0.403) SDCM<5
911401572341	DN391B LED11/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401572441	DN391B LED11/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401572541	DN391B LED11/865 PSU D150 ALU GC	(0.31,0.32) SDCM<5
911401572841	DN391B LED11/830 PSD D150 ALU GC	(0.44,0.403) SDCM<5
911401572941	DN391B LED11/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	(0.44,0.403) SDCM<5
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	(0.38,0.38) SDCM<5
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	(0.31,0.32) SDCM<5
911401577141	DN392B LED16/830 PSU D150 ALU GC	(0.44,0.403) SDCM<5
911401577241	DN392B LED16/840 PSU D150 ALU GC	(0.38,0.38) SDCM<5
911401577641	DN392B LED16/840 PSD D150 ALU GC	(0.38,0.38) SDCM<5
911401578641	DN391B LED11/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401578741	DN391B LED11/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401578841	DN391B LED11/865 PSU D150 ALU GM	(0.31,0.32) SDCM<5
911401579241	DN392B LED16/830 PSU D150 ALU GM	(0.44,0.403) SDCM<5
911401579341	DN392B LED16/840 PSU D150 ALU GM	(0.38,0.38) SDCM<5
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	(0.44,0.403) SDCM<5
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	(0.31,0.32) SDCM<5
911401581841	DN391B LED11/830 PSD D150 ALU GM	(0.44,0.403) SDCM<5
911401581941	DN391B LED11/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401584441	DN391B LED11/830 PSD D150 ALU CAU	(0.44,0.403) SDCM<5
911401585741	DN392B LED16/840 PSD D150 ALU GM	(0.38,0.38) SDCM<5
911401572041	DN391B LED11/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401572141	DN391B LED11/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401572241	DN391B LED11/865 PSU D150 WH GC	(0.31,0.32) SDCM<5
911401572741	DN391B LED11/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401575741	DN392B LED16/830 POE D150 WH GC	(0.44,0.403) SDCM<5
911401576941	DN392B LED16/830 PSU D150 WH GC	(0.44,0.403) SDCM<5
911401577041	DN392B LED16/840 PSU D150 WH GC	(0.38,0.38) SDCM<5
911401577341	DN392B LED16/830 PSD D150 WH GC	(0.44,0.403) SDCM<5
911401577441	DN392B LED16/840 PSD D150 WH GC	(0.38,0.38) SDCM<5
911401578341	DN391B LED11/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401578541	DN391B LED11/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
911401578941	DN392B LED16/830 PSU D150 WH GM	(0.44,0.403) SDCM<5
911401579141	DN392B LED16/865 PSU D150 WH GM	(0.31,0.32) SDCM<5
911401581741	DN391B LED11/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401583041	DN391B LED11/830 PSU D150 WH CAU	(0.44,0.403) SDCM<5

Order Code	Full Product Name	Initial chromaticity
911401583141	DN391B LED11/840 PSU D150 WH CAU	(0.38,0.38) SDCM<5
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	(0.44,0.403) SDCM<5
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	(0.38,0.38) SDCM<5
911401584241	DN391B LED11/830 PSD D150 WH CAU	(0.44,0.403) SDCM<5
911401584341	DN391B LED11/840 PSD D150 WH CAU	(0.38,0.38) SDCM<5
911401585541	DN392B LED16/840 PSD D150 WH GM	(0.38,0.38) SDCM<5
911401573941	DN392B LED16/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401574241	DN393B LED22/830 PSU D200 ALU GC	(0.44,0.403) SDCM<5
911401574341	DN393B LED22/840 PSU D200 ALU GC	(0.38,0.38) SDCM<5
911401574641	DN393B LED22/830 PSD D200 ALU GC	(0.44,0.403) SDCM<5
911401574741	DN393B LED22/840 PSD D200 ALU GC	(0.38,0.38) SDCM<5
911401579841	DN392B LED16/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401579941	DN392B LED16/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580041	DN392B LED16/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401580441	DN393B LED22/830 PSU D200 ALU GM	(0.44,0.403) SDCM<5
911401580541	DN393B LED22/840 PSU D200 ALU GM	(0.38,0.38) SDCM<5
911401580641	DN393B LED22/865 PSU D200 ALU GM	(0.31,0.32) SDCM<5
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	(0.44,0.403) SDCM<5
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	(0.38,0.38) SDCM<5
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	(0.31,0.32) SDCM<5
911401582641	DN393B LED22/830 PSD D200 ALU GM	(0.44,0.403) SDCM<5
911401582741	DN393B LED22/840 PSD D200 ALU GM	(0.38,0.38) SDCM<5
911401585241	DN393B LED22/830 PSD D200 ALU CAU	(0.44,0.403) SDCM<5
911401585341	DN393B LED22/840 PSD D200 ALU CAU	(0.38,0.38) SDCM<5
911401573041	DN392B LED16/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401573141	DN392B LED16/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401573241	DN392B LED16/865 PSU D200 WH GC	(0.31,0.32) SDCM<5
911401573741	DN392B LED16/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401574041	DN393B LED22/830 PSU D200 WH GC	(0.44,0.403) SDCM<5
911401574141	DN393B LED22/840 PSU D200 WH GC	(0.38,0.38) SDCM<5
911401574541	DN393B LED22/840 PSD D200 WH GC	(0.38,0.38) SDCM<5
911401579541	DN392B LED16/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401579641	DN392B LED16/840 PSU D200 WH GM	(0.38,0.38) SDCM<5
911401579741	DN392B LED16/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401580141	DN393B LED22/830 PSU D200 WH GM	(0.44,0.403) SDCM<5
911401580341	DN393B LED22/865 PSU D200 WH GM	(0.31,0.32) SDCM<5
911401582141	DN392B LED16/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401582441	DN393B LED22/830 PSD D200 WH GM	(0.44,0.403) SDCM<5
911401582541	DN393B LED22/840 PSD D200 WH GM	(0.38,0.38) SDCM<5
911401583341	DN392B LED16/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401583441	DN393B LED22/830 PSU D200 WH CAU	(0.44,0.403) SDCM<5
911401583541	DN393B LED22/840 PSU D200 WH CAU	(0.38,0.38) SDCM<5
911401584741	DN392B LED16/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5
911401585141	DN393B LED22/840 PSD D200 WH CAU	(0.38,0.38) SDCM<5

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
911401571941	DN390B LED6/840 PSU D100 ALU GC	0.12 %
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	0.12 %

Order Code	Full Product Name	Driver failure rate at 5000 h
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	0.12 %
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	0.12 %

		Driver failure rate at 5000
Order Code	Full Product Name	h
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	0.12 %
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	0.12 %
911401576541	DN391B LED11/830 PSU D100 ALU GC	0.12 %
911401576641	DN391B LED11/840 PSU D100 ALU GC	0.12 %
911401576841	DN391B LED11/840 PSD D100 ALU GC	0.12 %
911401578141	DN390B LED6/840 PSU D100 ALU GM	0.12 %
911401578241	DN390B LED6/865 PSU D100 ALU GM	0.12 %
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	0.12 %
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	0.12 %
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	0.12 %
911401571641	DN390B LED6/830 PSU D100 WH GC	0.12 %
911401571741	DN390B LED6/840 PSU D100 WH GC	0.12 %
911401577741	DN390B LED6/830 PSU D100 WH GM	0.12 %
911401577841	DN390B LED6/840 PSU D100 WH GM	0.12 %
911401577941	DN390B LED6/865 PSU D100 WH GM	0.12 %
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	0.12 %
911401572341	DN391B LED11/830 PSU D150 ALU GC	0.12 %
911401572441	DN391B LED11/840 PSU D150 ALU GC	0.12 %
911401572541	DN391B LED11/865 PSU D150 ALU GC	0.12 %
911401572841	DN391B LED11/830 PSD D150 ALU GC	0.12 %
911401572941	DN391B LED11/840 PSD D150 ALU GC	0.12 %
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	0.16 %
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	0.16 %
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	0.16 %
911401577141	DN392B LED16/830 PSU D150 ALU GC	0.16 %
911401577241	DN392B LED16/840 PSU D150 ALU GC	0.16 %
911401577641	DN392B LED16/840 PSD D150 ALU GC	0.16 %
911401578641	DN391B LED11/830 PSU D150 ALU GM	0.12 %
911401578741	DN391B LED11/840 PSU D150 ALU GM	0.12 %
911401578841	DN391B LED11/865 PSU D150 ALU GM	0.12 %
911401579241	DN392B LED16/830 PSU D150 ALU GM	0.16 %
911401579341	DN392B LED16/840 PSU D150 ALU GM	0.16 %
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	0.12 %
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	0.12 %
911401581841	DN391B LED11/830 PSD D150 ALU GM	0.12 %
911401581941	DN391B LED11/840 PSD D150 ALU GM	0.12 %
911401584441	DN391B LED11/830 PSD D150 ALU CAU	0.12 %
911401585741	DN392B LED16/840 PSD D150 ALU GM	0.16 %
911401572041	DN391B LED11/830 PSU D150 WH GC	0.12 %
911401572141	DN391B LED11/840 PSU D150 WH GC	0.12 %
911401572241	DN391B LED11/865 PSU D150 WH GC	0.12 %
911401572741	DN391B LED11/840 PSD D150 WH GC	0.12 %
911401575741	DN392B LED16/830 POE D150 WH GC	0.16 %
911401576941	DN392B LED16/830 PSU D150 WH GC	0.16 %
911401577041	DN392B LED16/840 PSU D150 WH GC	0.16 %
911401577341	DN392B LED16/830 PSD D150 WH GC	0.16 %
911401577441	DN392B LED16/840 PSD D150 WH GC	0.16 %
911401578341	DN391B LED11/830 PSU D150 WH GM	0.12 %
911401578541	DN391B LED11/865 PSU D150 WH GM	0.12 %

		Driver failure rate at 5000
Order Code	Full Product Name	h
911401578941	DN392B LED16/830 PSU D150 WH GM	0.16 %
911401579141	DN392B LED16/865 PSU D150 WH GM	0.16 %
911401581741	DN391B LED11/840 PSD D150 WH GM	0.12 %
911401583041	DN391B LED11/830 PSU D150 WH CAU	0.12 %
911401583141	DN391B LED11/840 PSU D150 WH CAU	0.12 %
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	0.12 %
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	0.12 %
911401584241	DN391B LED11/830 PSD D150 WH CAU	0.12 %
911401584341	DN391B LED11/840 PSD D150 WH CAU	0.12 %
911401585541	DN392B LED16/840 PSD D150 WH GM	0.16 %
911401573941	DN392B LED16/840 PSD D200 ALU GC	0.16 %
911401574241	DN393B LED22/830 PSU D200 ALU GC	0.12 %
911401574341	DN393B LED22/840 PSU D200 ALU GC	0.12 %
911401574641	DN393B LED22/830 PSD D200 ALU GC	0.12 %
911401574741	DN393B LED22/840 PSD D200 ALU GC	0.12 %
911401579841	DN392B LED16/830 PSU D200 ALU GM	0.16 %
911401579941	DN392B LED16/840 PSU D200 ALU GM	0.16 %
911401580041	DN392B LED16/865 PSU D200 ALU GM	0.16 %
911401580441	DN393B LED22/830 PSU D200 ALU GM	0.12 %
911401580541	DN393B LED22/840 PSU D200 ALU GM	0.12 %
911401580641	DN393B LED22/865 PSU D200 ALU GM	0.12 %
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	0.12 %
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	0.12 %
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	0.12 %
911401582641	DN393B LED22/830 PSD D200 ALU GM	0.12 %
911401582741	DN393B LED22/840 PSD D200 ALU GM	0.12 %
911401585241	DN393B LED22/830 PSD D200 ALU CAU	0.12 %
911401585341	DN393B LED22/840 PSD D200 ALU CAU	0.12 %
911401573041	DN392B LED16/830 PSU D200 WH GC	0.16 %
911401573141	DN392B LED16/840 PSU D200 WH GC	0.16 %
911401573241	DN392B LED16/865 PSU D200 WH GC	0.16 %
911401573741	DN392B LED16/840 PSD D200 WH GC	0.16 %
911401574041	DN393B LED22/830 PSU D200 WH GC	0.12 %
911401574141	DN393B LED22/840 PSU D200 WH GC	0.12 %
911401574541	DN393B LED22/840 PSD D200 WH GC	0.12 %
911401579541	DN392B LED16/830 PSU D200 WH GM	0.16 %
911401579641	DN392B LED16/840 PSU D200 WH GM	0.16 %
911401579741	DN392B LED16/865 PSU D200 WH GM	0.16 %
911401580141	DN393B LED22/830 PSU D200 WH GM	0.12 %
911401580341	DN393B LED22/865 PSU D200 WH GM	0.12 %
911401582141	DN392B LED16/840 PSD D200 WH GM	0.16 %
911401582441	DN393B LED22/830 PSD D200 WH GM	0.12 %
911401582541	DN393B LED22/840 PSD D200 WH GM	0.12 %
911401583341	DN392B LED16/840 PSU D200 WH CAU	0.16 %
911401583441	DN393B LED22/830 PSU D200 WH CAU	0.12 %
911401583541	DN393B LED22/840 PSU D200 WH CAU	0.12 %
911401584741	DN392B LED16/840 PSD D200 WH CAU	0.16 %
911401585141	DN393B LED22/840 PSD D200 WH CAU	0.12 %

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401571941	DN390B LED6/840 PSU D100 ALU GC	Not applicable
911401574841	DN390B LED6/830 PSU D100 ALU WP GC	Not applicable
911401574941	DN390B LED6/840 PSU D100 ALU WP GC	Not applicable
911401575141	DN391B LED11/830 PSU D100 ALU WP GC	Not applicable
911401575241	DN391B LED11/840 PSU D100 ALU WP GC	Not applicable
911401575341	DN391B LED11/865 PSU D100 ALU WP GC	Not applicable
911401576541	DN391B LED11/830 PSU D100 ALU GC	Not applicable
911401576641	DN391B LED11/840 PSU D100 ALU GC	Not applicable
911401576841	DN391B LED11/840 PSD D100 ALU GC	-
911401578141	DN390B LED6/840 PSU D100 ALU GM	Not applicable
911401578241	DN390B LED6/865 PSU D100 ALU GM	Not applicable
911401580741	DN390B LED6/830 PSU D100 ALU WP GM	Not applicable
911401580841	DN390B LED6/840 PSU D100 ALU WP GM	Not applicable
911401580941	DN390B LED6/865 PSU D100 ALU WP GM	Not applicable
911401571641	DN390B LED6/830 PSU D100 WH GC	Not applicable
911401571741	DN390B LED6/840 PSU D100 WH GC	Not applicable
911401577741	DN390B LED6/830 PSU D100 WH GM	Not applicable
911401577841	DN390B LED6/840 PSU D100 WH GM	Not applicable
911401577941	DN390B LED6/865 PSU D100 WH GM	Not applicable
911401583641	DN390B LED6/830 PSU D100 WH WP CAU	Not applicable
911401572341	DN391B LED11/830 PSU D150 ALU GC	Not applicable
911401572441	DN391B LED11/840 PSU D150 ALU GC	Not applicable
911401572541	DN391B LED11/865 PSU D150 ALU GC	Not applicable
911401572841	DN391B LED11/830 PSD D150 ALU GC	-
911401572941	DN391B LED11/840 PSD D150 ALU GC	-
911401575441	DN392B LED16/830 PSU D150 ALU WP GC	Not applicable
911401575541	DN392B LED16/840 PSU D150 ALU WP GC	Not applicable
911401575641	DN392B LED16/865 PSU D150 ALU WP GC	Not applicable
911401577141	DN392B LED16/830 PSU D150 ALU GC	Not applicable
911401577241	DN392B LED16/840 PSU D150 ALU GC	Not applicable
911401577641	DN392B LED16/840 PSD D150 ALU GC	-
911401578641	DN391B LED11/830 PSU D150 ALU GM	Not applicable
911401578741	DN391B LED11/840 PSU D150 ALU GM	Not applicable
911401578841	DN391B LED11/865 PSU D150 ALU GM	Not applicable
911401579241	DN392B LED16/830 PSU D150 ALU GM	Not applicable
911401579341	DN392B LED16/840 PSU D150 ALU GM	Not applicable
911401581041	DN391B LED11/830 PSU D150 ALU WP GM	Not applicable
911401581241	DN391B LED11/865 PSU D150 ALU WP GM	Not applicable
911401581841	DN391B LED11/830 PSD D150 ALU GM	-
911401581941	DN391B LED11/840 PSD D150 ALU GM	-
911401584441	DN391B LED11/830 PSD D150 ALU CAU	-
911401585741	DN392B LED16/840 PSD D150 ALU GM	-
911401572041	DN391B LED11/830 PSU D150 WH GC	Not applicable
911401572141	DN391B LED11/840 PSU D150 WH GC	Not applicable
911401572241	DN391B LED11/865 PSU D150 WH GC	Not applicable
911401572741	DN391B LED11/840 PSD D150 WH GC	-
911401575741	DN392B LED16/830 POE D150 WH GC	-
911401576941	DN392B LED16/830 PSU D150 WH GC	Not applicable
911401577041	DN392B LED16/840 PSU D150 WH GC	Not applicable
911401577341	DN392B LED16/830 PSD D150 WH GC	-
911401577441	DN392B LED16/840 PSD D150 WH GC	-

Order Code	Full Product Name	Maximum dim level
911401578341	DN391B LED11/830 PSU D150 WH GM	Not applicable
911401578541	DN391B LED11/865 PSU D150 WH GM	Not applicable
911401578941	DN392B LED16/830 PSU D150 WH GM	Not applicable
911401579141	DN392B LED16/865 PSU D150 WH GM	Not applicable
911401581741	DN391B LED11/840 PSD D150 WH GM	-
911401583041	DN391B LED11/830 PSU D150 WH CAU	Not applicable
911401583141	DN391B LED11/840 PSU D150 WH CAU	Not applicable
911401583841	DN391B LED11/830 PSU D150 WH WP CAU	Not applicable
911401583941	DN391B LED11/840 PSU D150 WH WP CAU	Not applicable
911401584241	DN391B LED11/830 PSD D150 WH CAU	-
911401584341	DN391B LED11/840 PSD D150 WH CAU	-
911401585541	DN392B LED16/840 PSD D150 WH GM	-
911401573941	DN392B LED16/840 PSD D200 ALU GC	-
911401574241	DN393B LED22/830 PSU D200 ALU GC	Not applicable
911401574341	DN393B LED22/840 PSU D200 ALU GC	Not applicable
911401574641	DN393B LED22/830 PSD D200 ALU GC	-
911401574741	DN393B LED22/840 PSD D200 ALU GC	-
911401579841	DN392B LED16/830 PSU D200 ALU GM	Not applicable
911401579941	DN392B LED16/840 PSU D200 ALU GM	Not applicable
911401580041	DN392B LED16/865 PSU D200 ALU GM	Not applicable
911401580441	DN393B LED22/830 PSU D200 ALU GM	Not applicable
911401580541	DN393B LED22/840 PSU D200 ALU GM	Not applicable
911401580641	DN393B LED22/865 PSU D200 ALU GM	Not applicable
911401581341	DN393B LED22/830 PSU D200 ALU WP GM	Not applicable
911401581441	DN393B LED22/840 PSU D200 ALU WP GM	Not applicable
911401581541	DN393B LED22/865 PSU D200 ALU WP GM	Not applicable
911401582641	DN393B LED22/830 PSD D200 ALU GM	-
911401582741	DN393B LED22/840 PSD D200 ALU GM	-
911401585241	DN393B LED22/830 PSD D200 ALU CAU	-
911401585341	DN393B LED22/840 PSD D200 ALU CAU	-
911401573041	DN392B LED16/830 PSU D200 WH GC	Not applicable
911401573141	DN392B LED16/840 PSU D200 WH GC	Not applicable
911401573241	DN392B LED16/865 PSU D200 WH GC	Not applicable
911401573741	DN392B LED16/840 PSD D200 WH GC	-
911401574041	DN393B LED22/830 PSU D200 WH GC	Not applicable
911401574141	DN393B LED22/840 PSU D200 WH GC	Not applicable
911401574541	DN393B LED22/840 PSD D200 WH GC	-
911401579541	DN392B LED16/830 PSU D200 WH GM	Not applicable
911401579641	DN392B LED16/840 PSU D200 WH GM	Not applicable
911401579741	DN392B LED16/865 PSU D200 WH GM	Not applicable
911401580141	DN393B LED22/830 PSU D200 WH GM	Not applicable
911401580341	DN393B LED22/865 PSU D200 WH GM	Not applicable
911401582141	DN392B LED16/840 PSD D200 WH GM	-
911401582441	DN393B LED22/830 PSD D200 WH GM	-
911401582541	DN393B LED22/840 PSD D200 WH GM	-
911401583341	DN392B LED16/840 PSU D200 WH CAU	Not applicable
911401583441	DN393B LED22/830 PSU D200 WH CAU	Not applicable
911401583541	DN393B LED22/840 PSU D200 WH CAU	Not applicable
911401584741	DN392B LED16/840 PSD D200 WH CAU	-
911401585141	DN393B LED22/840 PSD D200 WH CAU	-

