

FlexBlend – Unlocking the potential of LED lighting in offices

FlexBlend Recessed

Office owners and staff responsible for lighting operations are searching for high-quality yet energy-efficient lighting that complies with norms and regulations. Designed to support these needs, Philips FlexBlend is enabling building owners to fully optimise their lighting operations, by offering office-compliant lighting with an attractive return on investment. Furthermore, FlexBlend provides the required flexibility by being easy to use with different ceiling lights, as well as in different office spaces like open office or meeting rooms. Though technology is changing fast, the ideal lighting solution is also expected to be ready to incorporate innovations and future advances that can help optimise operations further. For this reason, Philips FlexBlend is also ready to be connected to controls such as Actilume or used together with the Philips SpaceWise lighting system. It can also be connected to software-based lighting systems like Interact Office, which provides the luminaire with further intelligence and enables it to collect valuable data about its environment

Benefits

- High-quality office-compliant lighting
- Choice of three different exit-windows
- Fast return on investment
- Application flexibility
- Scalable and ready to be connected to controls and lighting systems

FlexBlend Recessed

Features

- Fully office-compliant (UGR <19)
- Homogenous and uniform light effect
- Dimensional variety, local options
- Various mounting options
- Integrated sensors
- Can be combined with Philips ActiLume and SpaceWise systems
- Ready to be connected to software based lighting systems such as Interact Office


Application

- Offices
- Education
- Healthcare
- Banks

Versions



Upgradable sensor




FlexBlend Recessed RC340B
W60L60 MLO CPC




FlexBlend Recessed RC340B
W60L60 PCS VPC

Dimensional drawing



FlexBlend Recessed

Dimensional drawing



Product details



Upgradable sensor



O_FlexBlend Recessed-RC342B_W62L62_MLO_VPC



FlexBlend Recessed-RC340B_MLO_DPP



FlexBlend Recessed-RC340B_W60L60_Backcover_VPC




FlexBlend Recessed-RC340B_W60L60_CPC brackets



FlexBlend Recessed-RC340B_W60L60_CPC brackets_B

FlexBlend Recessed

Product details



FlexBlend Recessed-
RC340B_OPA_DPP



FlexBlend Recessed-
RC340B_PCS_DPP




O_FlexBlend Recessed-
RC340B_W60L60_PCS_VPC



FlexBlend Recessed-
RC340B_W60L60_CPC
brackets_A



FlexBlend Recessed RC340B PIP
Open



FlexBlend Recessed-
RC340B_W60L60_backcover_PC
V



O_FlexBlend Recessed-
RC340B_W60L60_MLO_VPC



O_FlexBlend Recessed-
RC340B_W60L60_MLO_CPC

FlexBlend Recessed

Product details



FlexBlend Recessed-RC340B PIP
Closed



Upgradable sensor



FlexBlend Recessed-
RC340B_W60L60_backcover_CP
C

FlexBlend Recessed

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	No
Number of gear units	1 unit
Service tag	Yes

Light Technical

Beam angle of light source	120 degree(s)
Correlated Color Temperature (Nom)	4000 K
Color rendering index (CRI)	≥90
Optic type	Wide beam
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz

Temperature

Ambient temperature range	+10 to +40 °C
---------------------------	---------------

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Mech. impact protection code	IK02
------------------------------	------

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.37) SDCM <3
Luminous flux tolerance	+/-10%

Application Conditions

Maximum dim level	1%
-------------------	----

General Information

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Temperature 650 °C, duration 30 s	-	RC340B
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	Temperature 650 °C, duration 30 s	-	RC342B
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	Temperature 650 °C, duration 30 s	-	RC342B
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC340B
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Temperature 650 °C, duration 30 s	-	RC342B

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Temperature 850 °C, duration 30 s	-	RC342B
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	Temperature 650 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	Temperature 850 °C, duration 30 s	Interact Ready light source with multi-sensor (upgradable)	RC340B
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Temperature 850 °C, duration 30 s	-	RC340B
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Temperature 850 °C, duration 30 s	-	RC340B
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Temperature 850 °C, duration 30 s	-	RC340B
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC340B
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC340B
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Temperature 650 °C, duration 30 s	-	RC340B
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Temperature 850 °C, duration 30 s	-	RC340B
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Temperature 650 °C, duration 30 s	-	RC340B
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B

FlexBlend Recessed

Order Code	Full Product Name	Glow-wire test	Embedded control	Product family code
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Temperature 650 °C, duration 30 s	-	RC340B
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Temperature 850 °C, duration 30 s	-	RC340B
10481500	RC340B LED36S/940 POE W60L60 VPC MLO UO	Temperature 650 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B
10484600	RC340B LED36S/940 POE W60L60 VPC PCS UO	Temperature 850 °C, duration 30 s	Upgradable sensor slot empty with cover	RC340B
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Temperature 650 °C, duration 30 s	-	RC340B
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Temperature 650 °C, duration 30 s	-	RC342B
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Temperature 850 °C, duration 30 s	-	RC342B
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Temperature 850 °C, duration 30 s	-	RC342B
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	Temperature 850 °C, duration 30 s	-	RC342B

Light Technical

Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux	Order Code	Full Product Name	Luminous Efficacy (rated) (Nom)	Luminous Flux
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	96 lm/W	3,600 lm	10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	88 lm/W	3,600 lm
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	97.5 lm/W	3,600 lm	10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	86.5 lm/W	3,600 lm
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	95.5 lm/W	4,200 lm	10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	87.5 lm/W	4,200 lm
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	94.5 lm/W	4,200 lm	10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	85.5 lm/W	4,200 lm

FlexBlend Recessed

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	96 lm/W	3,600 lm
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	94.5 lm/W	4,200 lm
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	100 lm/W	2,800 lm
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	97.5 lm/W	3,600 lm
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	97.5 lm/W	3,600 lm
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	140 lm/W	2,800 lm
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	97 lm/W	3,600 lm
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	140 lm/W	4,200 lm
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	144 lm/W	3,600 lm
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	124 lm/W	2,800 lm
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	124 lm/W	3,600 lm
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	125 lm/W	4,200 lm
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	97.5 lm/W	3,600 lm
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	97.5 lm/W	3,600 lm
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	97.5 lm/W	3,600 lm
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	100 lm/W	2,800 lm
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	140 lm/W	2,800 lm
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	97 lm/W	3,600 lm
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	140 lm/W	4,200 lm
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	124 lm/W	2,800 lm
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	124 lm/W	3,600 lm
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	125 lm/W	4,200 lm
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	97.5 lm/W	3,600 lm
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	144 lm/W	3,600 lm
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	111 lm/W	3,600 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	109 lm/W	3,600 lm
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	127 lm/W	4,200 lm
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	125 lm/W	4,200 lm
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	114 lm/W	4,200 lm
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	112 lm/W	4,200 lm
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	125 lm/W	4,200 lm
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	120 lm/W	3,600 lm
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	124 lm/W	3,600 lm
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	97.5 lm/W	3,600 lm
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	96 lm/W	3,600 lm
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	95.5 lm/W	4,200 lm
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	94.5 lm/W	4,200 lm
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	140 lm/W	4,200 lm
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	124 lm/W	3,600 lm
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	144 lm/W	3,600 lm
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	144 lm/W	3,600 lm
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	97.5 lm/W	3,600 lm
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	124 lm/W	3,600 lm
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	122 lm/W	3,600 lm
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	141 lm/W	3,600 lm
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	140 lm/W	4,200 lm
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	140 lm/W	4,200 lm
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	125 lm/W	4,200 lm
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	124 lm/W	4,200 lm
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	144 lm/W	3,600 lm

FlexBlend Recessed

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	144 lm/W	3,600 lm
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	140 lm/W	4,200 lm
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	140 lm/W	4,200 lm
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	144 lm/W	3,600 lm
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	144 lm/W	3,600 lm
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	120 lm/W	3,600 lm
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	97.5 lm/W	3,600 lm
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	88 lm/W	3,600 lm
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	86.5 lm/W	3,600 lm
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	124 lm/W	3,600 lm
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	96 lm/W	3,600 lm
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	94.5 lm/W	4,200 lm
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	94.5 lm/W	4,200 lm
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	95.5 lm/W	4,200 lm
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	96 lm/W	3,600 lm

Order Code	Full Product Name	Luminous Efficacy	
		(rated) (Nom)	Luminous Flux
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	97.5 lm/W	3,600 lm
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	97.5 lm/W	3,600 lm
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	142 lm/W	4,200 lm
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	97.5 lm/W	3,600 lm
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	144 lm/W	3,600 lm
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	96 lm/W	3,600 lm
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	97.5 lm/W	3,600 lm
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	97.5 lm/W	3,600 lm
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	100 lm/W	2,800 lm
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	140 lm/W	2,800 lm
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	144 lm/W	3,600 lm
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	140 lm/W	4,200 lm
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	124 lm/W	2,800 lm
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	124 lm/W	3,600 lm
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	125 lm/W	4,200 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	37.5 W
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	37 W
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	44 W
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	44.5 W
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	41 W
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	41.5 W
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	48 W
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	49 W
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	37.5 W
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	44.5 W
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	28 W
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	37 W
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	37 W
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	20 W
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	25 W
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	30 W
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	25 W

Order Code	Full Product Name	Power Consumption
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	22.5 W
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	29 W
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	33.5 W
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	37 W
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	37 W
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	37 W
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	28 W
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	20 W
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	25 W
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	30 W
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	22.5 W
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	29 W
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	33.5 W
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	37 W
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	25 W
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	32.5 W
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	33 W

FlexBlend Recessed

Order Code	Full Product Name	Power Consumption
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	33 W
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	33.5 W
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	37 W
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	37.5 W
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	33.5 W
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	30 W
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	29 W
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	37.5 W
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	44 W
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	44.5 W
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	30 W
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	29 W
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	37 W
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	29 W
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	29.5 W
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	25.5 W
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	30 W
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	30 W
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	33.5 W
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	34 W
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	25 W
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	25 W
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	30 W
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	30 W

Order Code	Full Product Name	Power Consumption
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	25 W
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	25 W
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	30 W
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	37 W
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	41 W
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	41.5 W
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	29 W
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	37.5 W
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	44.5 W
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	44.5 W
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	44 W
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	37 W
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	37 W
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	29.5 W
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	37 W
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	25 W
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	37.5 W
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	37 W
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	37 W
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	28 W
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	20 W
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	25 W
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	30 W
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	22.5 W
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	29 W
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	33.5 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	No
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	No
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	No
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	No
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Yes
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	Yes
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	Yes
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Yes
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes

Order Code	Full Product Name	Dimmable
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	No
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	No
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	No
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	No
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	No
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes

FlexBlend Recessed

Order Code	Full Product Name	Dimmable
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	No
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	No
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	No
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	No
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	No
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	No
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	No
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	No
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	No
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	No

Order Code	Full Product Name	Dimmable
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	No
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	No
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Yes
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	No
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

Approval and Application

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Safety class I	IP20
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Safety class I	IP20
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Safety class I	IP20
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Safety class I	IP20
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	Safety class I	IP20
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	Safety class I	IP20
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Safety class I	IP54
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Safety class I	IP54
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	Safety class I	IP54
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Safety class I	IP20
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Safety class I	IP20

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Safety class I	IP20
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Safety class I	IP54
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	Safety class I	IP54
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	Safety class III	IP20
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	Safety class III	IP20/54
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Safety class I	IP54
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Safety class I	IP54
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Safety class I	IP54
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Safety class I	IP54
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Safety class I	IP54
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Safety class I	IP20
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Safety class I	IP54
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Safety class I	IP54

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Safety class I	IP20
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Safety class I	IP54
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Safety class I	IP54
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Safety class I	IP54
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Safety class I	IP54
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Safety class I	IP54
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Safety class I	IP54
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	Safety class I	IP54
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Safety class I	IP20
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Safety class I	IP20
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Safety class I	IP20
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Safety class I	IP54
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Safety class I	IP20
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20

FlexBlend Recessed

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Safety class I	IP20
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Safety class I	IP20
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Safety class I	IP54
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	Safety class III	IP20
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	Safety class III	IP20/54
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Safety class I	IP20
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Safety class I	IP20

Order Code	Full Product Name	Protection class IEC	Ingress protection code
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Safety class I	IP20
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Safety class I	IP54
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Safety class I	IP54
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	Safety class I	IP54
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	Safety class I	IP54

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	0.01 %
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	0.01 %
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	0.01 %
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	0.01 %
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	0.01 %
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	0.01 %
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	0.01 %
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	0.01 %
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	-
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	-
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	-
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	-
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	-
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	-
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	-
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	-
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	-
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	-
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	0.01 %
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	0.01 %
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	0.01 %
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	-
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	-
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	-
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	-
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	-
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	-

Order Code	Full Product Name	Driver failure rate at 5000 h
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	-
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	-
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	-
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	0.01 %
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	0.01 %
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	0.01 %
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	0.01 %
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	0.01 %
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	0.01 %
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	0.01 %
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	0.01 %
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	0.01 %
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	0.01 %
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	0.01 %
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	0.01 %
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	-
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	0.01 %
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	0.01 %
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	0.01 %
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	0.01 %
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	0.01 %
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	0.01 %
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	0.01 %
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	0.01 %
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	0.01 %
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	0.01 %

FlexBlend Recessed

Order Code	Full Product Name	Driver failure rate at 5000 h
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	0.01 %
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	0.01 %
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	0.01 %
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	0.01 %
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	0.01 %
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	0.01 %
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	0.01 %
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	0.01 %
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	0.01 %
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	0.01 %
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	0.01 %
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	0.01 %
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	0.01 %
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	0.01 %
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %

Order Code	Full Product Name	Driver failure rate at 5000 h
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	0.01 %
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	0.01 %
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	0.01 %
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	-
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	-
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	0.01 %
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	0.01 %
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	0.01 %
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	-
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	-
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	-
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	-
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	-
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	-
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	-

Application Conditions

Order Code	Full Product Name	Suitable for random switching
10277400	RC340B LED36S/940 PSU W15L120 VPC MLO PI	Yes
10278100	RC340B LED36S/940 PSD W15L120 VPC MLO PI	Yes
10279800	RC340B LED42S/940 PSU W15L120 VPC MLO PI	Yes
10280400	RC340B LED42S/940 PSD W15L120 VPC MLO PI	Yes
10281100	RC340B LED36S/940 PSU W15L120 VPC MLO EL	Yes
10282800	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10283500	RC340B LED42S/940 PSU W15L120 VPC MLO EL	Yes
10284200	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10286600	RC340B LED36S/940 PSD W15L120 VPC MLO EL	Yes
10288000	RC340B LED42S/940 PSD W15L120 VPC MLO EL	Yes
10410500	RC342B LED28S/940 PSD W15L125 VPC MLO PI	Yes
10411200	RC342B LED36S/940 PSD W15L125 VPC MLO	Yes
10414300	RC342B LED36S/940 PSD W17L125 PCV MLO	Yes
10425900	RC342B LED28S/940 PSD W15L125 VPC PCS PI	Yes
10426600	RC342B LED36S/940 PSD W15L125 VPC PCS PI	Yes
10427300	RC342B LED42S/940 PSD W15L125 VPC PCS PI	Yes
10430300	RC342B LED36S/940 PSD W17L125 PCV PCS PI	Yes
10441900	RC342B LED28S/940 PSD W15L125 VPC O PIP	Yes
10442600	RC342B LED36S/940 PSD W15L125 VPC O PIP	Yes
10443300	RC342B LED42S/940 PSD W15L125 VPC O PIP	Yes
10242200	RC340B LED36S/940 PSD W30L120 VPC MLO PI	Yes
10245300	RC342B LED36S/940 PSU W31L125 VPC MLO PI	Yes
10246000	RC342B LED36S/940 PSD W31L125 VPC MLO PI	Yes
10408200	RC342B LED28S/940 PSD W31L125 VPC MLO PI	Yes
10422800	RC342B LED28S/940 PSD W31L125 VPC PCS PI	Yes
10423500	RC342B LED36S/940 PSD W31L125 VPC PCS PI	Yes
10424200	RC342B LED42S/940 PSD W31L125 VPC PCS PI	Yes
10438900	RC342B LED28S/940 PSD W31L125 VPC O PIP	Yes
10439600	RC342B LED36S/940 PSD W31L125 VPC O PIP	Yes
10440200	RC342B LED42S/940 PSD W31L125 VPC O PIP	Yes

Order Code	Full Product Name	Suitable for random switching
10482200	RC340B LED36S/940 POE W60L60 VPC MLO U3	Yes (relates to presence/ movement detection and daylight harvesting)
10485300	RC340B LED36S/940 POE W60L60 VPC PCS U3	Yes (relates to presence/ movement detection and daylight harvesting)
10249100	RC340B LED36S/940 PSU W60L60 VPC O ELP3	Yes
10250700	RC340B LED36S/940 PSD W60L60 VPC O ELP3	Yes
10263700	RC340B LED42S/940 PSU W60L60 VPC O PIP	Yes
10264400	RC340B LED42S/940 PSD W60L60 VPC O PIP	Yes
10268200	RC340B LED42S/940 PSU W60L60 VPC O ELP3	Yes
10269900	RC340B LED42S/940 PSD W60L60 VPC O ELP3	Yes
10274300	RC340B LED42S/940 PSD W60L60 VPC O ELD3	Yes
10323800	RC340B LED36S/940 PSU W60L60 VPC O PIP S	Yes
10324500	RC340B LED36S/940 PSD W60L60 VPC O PIP S	Yes
10232300	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
10308500	RC340B LED36S/940 PSU W60L60 CPC MLO PIP	Yes
10309200	RC340B LED42S/940 PSU W60L60 CPC MLO PIP	Yes
10310800	RC340B LED42S/940 PSD W60L60 CPC MLO PIP	Yes
10428000	RC342B LED42S/940 PSD W62L62 CPC PCS PIP	Yes
10230900	RC340B LED36S/940 PSD W60L60 VPC O PIP	Yes
10235400	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
10236100	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10240800	RC340B LED36S/940 PSD W60L60 CPC MLO PIP	Yes
10253800	RC340B LED36S/940 PSU W60L60 VPC PCS ELP	Yes
10254500	RC340B LED36S/940 PSD W60L60 VPC PCS ELP	Yes
10260600	RC340B LED36S/940 PSD W60L60 VPC PCS ELD	Yes
10265100	RC340B LED42S/940 PSU W60L60 VPC PCS PIP	Yes
10266800	RC340B LED42S/940 PSD W60L60 VPC PCS PIP	Yes

FlexBlend Recessed

Order Code	Full Product Name	Suitable for random switching
10270500	RC340B LED42S/940 PSU W60L60 VPC PCS ELP	Yes
10271200	RC340B LED42S/940 PSD W60L60 VPC PCS ELP	Yes
10306100	RC340B LED36S/940 PSU W60L60 CPC PCS PIP	Yes
10307800	RC340B LED36S/940 PSD W60L60 CPC PCS PIP	Yes
10311500	RC340B LED42S/940 PSU W60L60 CPC PCS PIP	Yes
10312200	RC340B LED42S/940 PSD W60L60 CPC PCS PIP	Yes
10327600	RC340B LED36S/940 PSU W60L60 VPC PCS PIP	Yes
10328300	RC340B LED36S/940 PSD W60L60 VPC PCS PIP	Yes
10229300	RC340B LED36S/940 PSU W60L60 VPC O PIP	Yes
10243900	RC342B LED36S/940 PSU W62L62 VPC MLO PIP	Yes
10251400	RC340B LED36S/940 PSU W60L60 VPC MLO ELP	Yes
10252100	RC340B LED36S/940 PSD W60L60 VPC MLO ELP	Yes
10256900	RC340B LED36S/940 PSD W60L60 VPC O ELD3	Yes
10258300	RC340B LED36S/940 PSD W60L60 VPC MLO ELD	Yes
10262000	RC340B LED42S/940 PSD W60L60 VPC MLO PIP	Yes
10272900	RC340B LED42S/940 PSD W60L60 VPC MLO ELD	Yes
10305400	RC340B LED42S/940 PSU W60L60 VPC MLO PIP	Yes
10325200	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
10326900	RC340B LED36S/940 PSD W60L60 VPC MLO PIP	Yes
10233000	RC340B LED36S/940 POE W60L60 VPC MLO	Yes

Order Code	Full Product Name	Suitable for random switching
10276700	RC340B LED42S/940 PSD W60L60 VPC PCS ELD	Yes
10481500	RC340B LED36S/940 POE W60L60 VPC MLO U0	Yes (relates to presence/ movement detection and daylight harvesting)
10484600	RC340B LED36S/940 POE W60L60 VPC PCS U0	Yes (relates to presence/ movement detection and daylight harvesting)
10231600	RC340B LED36S/940 PSU W60L60 VPC MLO PIP	Yes
10241500	RC340B LED36S/940 PSD W60L60 PCV MLO PIP	Yes
10244600	RC342B LED36S/940 PSD W62L62 VPC MLO PIP	Yes
10406800	RC342B LED28S/940 PSD W62L62 VPC MLO PIP	Yes
10419800	RC342B LED28S/940 PSD W62L62 VPC PCS PIP	Yes
10420400	RC342B LED36S/940 PSD W62L62 VPC PCS	Yes
10421100	RC342B LED42S/940 PSD W62L62 VPC PCS PIP	Yes
10435800	RC342B LED28S/940 PSD W62L62 VPC O PIP	Yes
10436500	RC342B LED36S/940 PSD W62L62 VPC O PIP	Yes
10437200	RC342B LED42S/940 PSD W62L62 VPC O PIP	Yes

