



Adaptable high-bay lighting offering high efficiency and connectivity options to lighting systems and software applications.

GentleSpace Gen3

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

GentleSpace Gen3

Benefits

- High-quality visibility combined with great uniformity and reduced glare
- A robust and reliable solution for a long service life
- A highly efficient solution, offering an attractive total cost of ownership
- Flexibility enabled by a high degree of adaptability to changing application needs
- Ready to be connected to existing and upcoming system and software applications
- Extensive application coverage including food production, manufacturing different height ceilings, hallways

Features

- High efficiency of up to 155 lm/W
- Long service life of the L80 at 100 K hrs
- Detachable mounting system for ease of installation
- Fully compliant with EN-12464-1; low-glare rating and colour rendering of ≥ 80
- Option for dust cover to meet the requirements of the food industry
- Suitable for new builds or point-for-point replacement of HPI 250 W, HPL 400 W or HPI 400 W, reducing energy consumption by up to 65%
- Wide variety of optics to meet application requirements, also with the option of adjustable optics variant with the flexibility to shift from NB to WB with a easy adjustment mechanism
- Interact Industry and Philips GreenWarehouse-ready

Application

- Food production and manufacturing
- Warehouses and logistics centres
- Indoor sports halls, swimming pools and exhibition halls

Versions



New Highbay



New Highbay



New Highbay



New Highbay

GentleSpace Gen3

Versions



GentleSpace Gen3

New Highbay

GentleSpace Gen3 - -

Application Conditions

Ambient temperature range	-30 to +45 °C
Maximum dim level	10%

Approval and Application

Ingress protection code	IP65
-------------------------	------

Controls and Dimming

Dimmable	Yes
----------	-----

Operating and Electrical

Input Voltage	220-240 V
---------------	-----------

General Information

Beam angle of light source	114 °
CE mark	CE mark
Protection class IEC	Safety class I (I)
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	D
Glow-wire test	850/5
Light source replaceable	Yes
Number of gear units	1 unit

Initial Performance (IEC Compliant)

Initial chromaticity	(0.38, 0.38) SDCM <3
Init. Corr. Colour Temperature	4000 K
Init. Colour Rendering Index	≥80
Luminous flux tolerance	+/-10%

Over Time Performance (IEC Compliant)

Median useful life L90B50	50000 h
---------------------------	---------

Application Conditions

Order Code	Full Product Name	Suitable for random switching
40730800	BY481P LED250S/840 PSD WB GC SI	No
40731500	BY481P LED250S/840 PSD MB GC SI	No
40732200	BY481P LED350S/840 PSD MB GC SI	No
40734600	BY481P LED250S/840 PSD NB GC SI	No
40741400	BY481P LED250S/840 PSD WB PC SI	No
40743800	BY481P LED350S/840 PSD WB GC SI	No
40744500	BY481P LED250S/840 PSD MB PC SI	No
40763600	BY481P LED250S/840 PSD HRO GC SI	No
40767400	BY481P LED350S/840 PSD HRO GC SI	No
40768100	BY481P LED350S/840 PSD NB GC SI	No
40769800	BY481P LED250S/840 PSD HRO PC SI	No
40793300	BY481P LED350S/840 PSD WB PC SI	No
40795700	BY481P LED250S/840 PSD NB PC SI	No
40798800	BY481P LED350S/840 PSD MB PC SI	No
40799500	BY481P LED350S/840 PSD HRO PC SI	No
40733900	BY480P LED130S/840 PSD WB GC SI	No
40736000	BY480P LED170S/840 PSD WB GC SI	No
40738400	BY480P LED130S/840 PSD MB GC SI	No
40742100	BY480P LED130S/840 PSD HRO GC SI	No
40785800	BY480P LED130S/840 PSD NB GC SI	No
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	Yes
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	Yes
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	Yes
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	Yes
40750600	BY481P LED250S/840 PSD MB GC SI BR	No
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	Yes
40758200	BY481P LED250S/840 PSD WB GC SI BR	No
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	Yes
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	Yes
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	Yes
40778000	BY481P LED250S/840 PSD NB GC SI BR	No
40786500	BY481P LED250S/840 PSD HRO GC SI BR	No
40790200	BY481P LED350S/840 PSD MB GC SI BR	No
40801500	BY481P LED350S/840 PSD WB GC SI BR	No
40757500	BY481P LED250S/840 PSD MB GC WH	No

Order Code	Full Product Name	Suitable for random switching
40771100	BY481P LED250S/840 PSD MB PC WH	No
40777300	BY481P LED250S/840 PSD WB GC WH	No
40800800	BY481P LED250S/840 PSD HRO GC WH	No
40760500	BY480P LED130S/840 PSD WB GC WH	No
40781000	BY481P LED250S/840 PSD MB GC WH BR	No
40788900	BY481P LED250S/840 PSD WB GC WH BR	No
41463400	BY480P LED130S/840 PSD NBA GC SI	No
41464100	BY480P LED170S/840 PSD NBA GC SI	No
41465800	BY481P LED250S/840 PSD NBA GC SI	No
41466500	BY481P LED350S/840 PSD NBA GC SI	No
41467200	BY481P LED350S/840 PSD NBA PC SI	No
41468900	BY481P LED250S/840 PSD NBA PC SI	No
41469600	BY480P LED130S/840 PSD NBA PC SI	No
41470200	BY480P LED170S/840 PSD NBA PC SI	No

Approval and Application

Order Code	Full Product Name	Mech. impact protection code
40730800	BY481P LED250S/840 PSD WB GC SI	IK07
40731500	BY481P LED250S/840 PSD MB GC SI	IK07
40732200	BY481P LED350S/840 PSD MB GC SI	IK07
40734600	BY481P LED250S/840 PSD NB GC SI	IK07
40741400	BY481P LED250S/840 PSD WB PC SI	IK08
40743800	BY481P LED350S/840 PSD WB GC SI	IK07
40744500	BY481P LED250S/840 PSD MB PC SI	IK08
40763600	BY481P LED250S/840 PSD HRO GC SI	IK07
40767400	BY481P LED350S/840 PSD HRO GC SI	IK07
40768100	BY481P LED350S/840 PSD NB GC SI	IK07
40769800	BY481P LED250S/840 PSD HRO PC SI	IK08
40793300	BY481P LED350S/840 PSD WB PC SI	IK08
40795700	BY481P LED250S/840 PSD NB PC SI	IK08
40798800	BY481P LED350S/840 PSD MB PC SI	IK08
40799500	BY481P LED350S/840 PSD HRO PC SI	IK08
40733900	BY480P LED130S/840 PSD WB GC SI	IK07
40736000	BY480P LED170S/840 PSD WB GC SI	IK07
40738400	BY480P LED130S/840 PSD MB GC SI	IK07
40742100	BY480P LED130S/840 PSD HRO GC SI	IK07
40785800	BY480P LED130S/840 PSD NB GC SI	IK07
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	IK07
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	IK07
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	IK07
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	IK07
40750600	BY481P LED250S/840 PSD MB GC SI BR	IK07

Order Code	Full Product Name	Mech. impact protection code
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	IK07
40758200	BY481P LED250S/840 PSD WB GC SI BR	IK07
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	IK07
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	IK07
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	IK07
40778000	BY481P LED250S/840 PSD NB GC SI BR	IK07
40786500	BY481P LED250S/840 PSD HRO GC SI BR	IK07
40790200	BY481P LED350S/840 PSD MB GC SI BR	IK07
40801500	BY481P LED350S/840 PSD WB GC SI BR	IK07
40757500	BY481P LED250S/840 PSD MB GC WH	IK07
40771100	BY481P LED250S/840 PSD MB PC WH	IK08
40777300	BY481P LED250S/840 PSD WB GC WH	IK07
40800800	BY481P LED250S/840 PSD HRO GC WH	IK07
40760500	BY480P LED130S/840 PSD WB GC WH	IK07
40781000	BY481P LED250S/840 PSD MB GC WH BR	IK07
40788900	BY481P LED250S/840 PSD WB GC WH BR	IK07
41463400	BY480P LED130S/840 PSD NBA GC SI	IK07
41464100	BY480P LED170S/840 PSD NBA GC SI	IK07
41465800	BY481P LED250S/840 PSD NBA GC SI	IK07
41466500	BY481P LED350S/840 PSD NBA GC SI	IK07
41467200	BY481P LED350S/840 PSD NBA PC SI	IK08
41468900	BY481P LED250S/840 PSD NBA PC SI	IK08
41469600	BY480P LED130S/840 PSD NBA PC SI	IK08
41470200	BY480P LED170S/840 PSD NBA PC SI	IK08

General Information (1/2)

GentleSpace Gen3

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
40730800	BY481P LED250S/840 PSD WB GC SI	-	-	-	WB
40731500	BY481P LED250S/840 PSD MB GC SI	-	-	-	MB
40732200	BY481P LED350S/840 PSD MB GC SI	-	-	-	MB
40734600	BY481P LED250S/840 PSD NB GC SI	-	-	-	NB
40741400	BY481P LED250S/840 PSD WB PC SI	-	-	-	WB
40743800	BY481P LED350S/840 PSD WB GC SI	-	-	-	WB
40744500	BY481P LED250S/840 PSD MB PC SI	-	-	-	MB
40763600	BY481P LED250S/840 PSD HRO GC SI	-	-	-	HRO
40767400	BY481P LED350S/840 PSD HRO GC SI	-	-	-	HRO
40768100	BY481P LED350S/840 PSD NB GC SI	-	-	-	NB
40769800	BY481P LED250S/840 PSD HRO PC SI	-	-	-	HRO
40793300	BY481P LED350S/840 PSD WB PC SI	-	-	-	WB
40795700	BY481P LED250S/840 PSD NB PC SI	-	-	-	NB
40798800	BY481P LED350S/840 PSD MB PC SI	-	-	-	MB
40799500	BY481P LED350S/840 PSD HRO PC SI	-	-	-	HRO
40733900	BY480P LED130S/840 PSD WB GC SI	-	-	-	WB
40736000	BY480P LED170S/840 PSD WB GC SI	-	-	-	MB
40738400	BY480P LED130S/840 PSD MB GC SI	-	-	-	MB
40742100	BY480P LED130S/840 PSD HRO GC SI	-	-	-	HRO
40785800	BY480P LED130S/840 PSD NB GC SI	-	-	-	NB
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	-	-	-	MB
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	-	-	-	WB
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	-	-	-	HRO
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	-	-	-	MB
40750600	BY481P LED250S/840 PSD MB GC SI BR	-	-	-	MB

Order Code	Full Product Name	Cap-Base	Optical cover/ lens type	Lamp family code	Optic type
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	-	-	-	WB
40758200	BY481P LED250S/840 PSD WB GC SI BR	-	-	-	WB
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	-	-	-	HRO
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	-	-	-	NB
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	-	-	-	NB
40778000	BY481P LED250S/840 PSD NB GC SI BR	-	-	-	NB
40786500	BY481P LED250S/840 PSD HRO GC SI BR	-	-	-	HRO
40790200	BY481P LED350S/840 PSD MB GC SI BR	-	-	-	MB
40801500	BY481P LED350S/840 PSD WB GC SI BR	-	-	-	WB
40757500	BY481P LED250S/840 PSD MB GC WH	-	-	-	MB
40771100	BY481P LED250S/840 PSD MB PC WH	-	-	-	MB
40777300	BY481P LED250S/840 PSD WB GC WH	-	-	-	WB
40800800	BY481P LED250S/840 PSD HRO GC WH	-	-	-	HRO
40760500	BY480P LED130S/840 PSD WB GC WH	-	-	-	WB
40781000	BY481P LED250S/840 PSD MB GC WH BR	-	-	-	WB
40788900	BY481P LED250S/840 PSD WB GC WH BR	-	-	-	WB
41463400	BY480P LED130S/840 PSD NBA GC SI	-	PM	-	WB
41464100	BY480P LED170S/840 PSD NBA GC SI	-	PM	-	WB
41465800	BY481P LED250S/840 PSD NBA GC SI	-	PM	-	WB
41466500	BY481P LED350S/840 PSD NBA GC SI	-	PM	-	WB
41467200	BY481P LED350S/840 PSD NBA PC SI	-	PM	-	WB
41468900	BY481P LED250S/840 PSD NBA PC SI	-	PM	-	WB
41469600	BY480P LED130S/840 PSD NBA PC SI	-	PM	-	WB
41470200	BY480P LED170S/840 PSD NBA PC SI	-	PM	-	WB

General Information (2/2)

Order Code	Full Product Name	Product Family	
		Code	UL mark
40730800	BY481P LED250S/840 PSD WB GC SI	BY481P	-
40731500	BY481P LED250S/840 PSD MB GC SI	BY481P	-
40732200	BY481P LED350S/840 PSD MB GC SI	BY481P	-
40734600	BY481P LED250S/840 PSD NB GC SI	BY481P	-
40741400	BY481P LED250S/840 PSD WB PC SI	BY481P	-
40743800	BY481P LED350S/840 PSD WB GC SI	BY481P	-
40744500	BY481P LED250S/840 PSD MB PC SI	BY481P	-
40763600	BY481P LED250S/840 PSD HRO GC SI	BY481P	-
40767400	BY481P LED350S/840 PSD HRO GC SI	BY481P	-
40768100	BY481P LED350S/840 PSD NB GC SI	BY481P	-
40769800	BY481P LED250S/840 PSD HRO PC SI	BY481P	-
40793300	BY481P LED350S/840 PSD WB PC SI	BY481P	-
40795700	BY481P LED250S/840 PSD NB PC SI	BY481P	-
40798800	BY481P LED350S/840 PSD MB PC SI	BY481P	-
40799500	BY481P LED350S/840 PSD HRO PC SI	BY481P	-
40733900	BY480P LED130S/840 PSD WB GC SI	BY481P	-
40736000	BY480P LED170S/840 PSD WB GC SI	BY480P	-
40738400	BY480P LED130S/840 PSD MB GC SI	BY480P	-
40742100	BY480P LED130S/840 PSD HRO GC SI	BY480P	-
40785800	BY480P LED130S/840 PSD NB GC SI	BY480P	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	BY481X	-
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	BY481X	-
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	BY481X	-
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	BY481X	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	BY481P	-

Order Code	Full Product Name	Product Family	
		Code	UL mark
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	BY481X	-
40758200	BY481P LED250S/840 PSD WB GC SI BR	BY481P	-
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	BY481X	-
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	BY481X	-
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	BY481X	-
40778000	BY481P LED250S/840 PSD NB GC SI BR	BY481P	-
40786500	BY481P LED250S/840 PSD HRO GC SI BR	BY481P	-
40790200	BY481P LED350S/840 PSD MB GC SI BR	BY481P	-
40801500	BY481P LED350S/840 PSD WB GC SI BR	BY481P	-
40757500	BY481P LED250S/840 PSD MB GC WH	BY481P	-
40771100	BY481P LED250S/840 PSD MB PC WH	BY481P	-
40777300	BY481P LED250S/840 PSD WB GC WH	BY481P	-
40800800	BY481P LED250S/840 PSD HRO GC WH	BY481P	-
40760500	BY480P LED130S/840 PSD WB GC WH	BY480P	-
40781000	BY481P LED250S/840 PSD MB GC WH BR	BY481P	-
40788900	BY481P LED250S/840 PSD WB GC WH BR	BY481P	-
41463400	BY480P LED130S/840 PSD NBA GC SI	BY480P	-
41464100	BY480P LED170S/840 PSD NBA GC SI	BY480P	-
41465800	BY481P LED250S/840 PSD NBA GC SI	BY480P	-
41466500	BY481P LED350S/840 PSD NBA GC SI	BY480P	-
41467200	BY481P LED350S/840 PSD NBA PC SI	BY480P	-
41468900	BY481P LED250S/840 PSD NBA PC SI	BY480P	-
41469600	BY480P LED130S/840 PSD NBA PC SI	BY480P	-
41470200	BY480P LED170S/840 PSD NBA PC SI	BY480P	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial LED	Initial	Initial
		luminaire efficacy	luminous flux	input power
40730800	BY481P LED250S/840 PSD WB GC SI	154 lm/W	25000 lm	160 W
40731500	BY481P LED250S/840 PSD MB GC SI	154 lm/W	25000 lm	160 W
40732200	BY481P LED350S/840 PSD MB GC SI	148 lm/W	35000 lm	235 W
40734600	BY481P LED250S/840 PSD NB GC SI	154 lm/W	25000 lm	160 W
40741400	BY481P LED250S/840 PSD WB PC SI	154 lm/W	25000 lm	160 W
40743800	BY481P LED350S/840 PSD WB GC SI	148 lm/W	35000 lm	235 W
40744500	BY481P LED250S/840 PSD MB PC SI	154 lm/W	25000 lm	160 W
40763600	BY481P LED250S/840 PSD HRO GC SI	154 lm/W	25000 lm	160 W
40767400	BY481P LED350S/840 PSD HRO GC SI	148 lm/W	35000 lm	235 W

Order Code	Full Product Name	Initial LED	Initial	Initial
		luminaire efficacy	luminous flux	input power
40768100	BY481P LED350S/840 PSD NB GC SI	148 lm/W	35000 lm	235 W
40769800	BY481P LED250S/840 PSD HRO PC SI	154 lm/W	25000 lm	160 W
40793300	BY481P LED350S/840 PSD WB PC SI	148 lm/W	35000 lm	235 W
40795700	BY481P LED250S/840 PSD NB PC SI	154 lm/W	25000 lm	160 W
40798800	BY481P LED350S/840 PSD MB PC SI	148 lm/W	35000 lm	235 W
40799500	BY481P LED350S/840 PSD HRO PC SI	148 lm/W	35000 lm	235 W
40733900	BY480P LED130S/840 PSD WB GC SI	153 lm/W	13000 lm	84 W
40736000	BY480P LED170S/840 PSD WB GC SI	142 lm/W	17000 lm	120 W
40738400	BY480P LED130S/840 PSD MB GC SI	153 lm/W	13000 lm	84 W

GentleSpace Gen3

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40742100	BY480P LED130S/840 PSD HRO GC SI	153 lm/W	13000 lm	84 W
40785800	BY480P LED130S/840 PSD NB GC SI	153 lm/W	13000 lm	84 W
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	154 lm/W	25000 lm	160 W
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	154 lm/W	25000 lm	160 W
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	154 lm/W	25000 lm	160 W
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	148 lm/W	35000 lm	235 W
40750600	BY481P LED250S/840 PSD MB GC SI BR	154 lm/W	25000 lm	160 W
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	148 lm/W	35000 lm	235 W
40758200	BY481P LED250S/840 PSD WB GC SI BR	154 lm/W	25000 lm	160 W
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	148 lm/W	35000 lm	235 W
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	154 lm/W	25000 lm	160 W
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	148 lm/W	35000 lm	235 W
40778000	BY481P LED250S/840 PSD NB GC SI BR	154 lm/W	25000 lm	160 W
40786500	BY481P LED250S/840 PSD HRO GC SI BR	154 lm/W	25000 lm	160 W
40790200	BY481P LED350S/840 PSD MB GC SI BR	148 lm/W	35000 lm	235 W
40801500	BY481P LED350S/840 PSD WB GC SI BR	148 lm/W	35000 lm	235 W

Order Code	Full Product Name	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
40757500	BY481P LED250S/840 PSD MB GC WH	154 lm/W	25000 lm	160 W
40771100	BY481P LED250S/840 PSD MB PC WH	154 lm/W	25000 lm	160 W
40777300	BY481P LED250S/840 PSD WB GC WH	154 lm/W	25000 lm	160 W
40800800	BY481P LED250S/840 PSD HRO GC WH	154 lm/W	25000 lm	160 W
40760500	BY480P LED130S/840 PSD WB GC WH	153 lm/W	13000 lm	84 W
40781000	BY481P LED250S/840 PSD MB GC WH BR	154 lm/W	25000 lm	160 W
40788900	BY481P LED250S/840 PSD WB GC WH BR	154 lm/W	25000 lm	160 W
41463400	BY480P LED130S/840 PSD NBA GC SI	155 lm/W	13000 lm	84 W
41464100	BY480P LED170S/840 PSD NBA GC SI	142 lm/W	17000 lm	120 W
41465800	BY481P LED250S/840 PSD NBA GC SI	154 lm/W	25000 lm	160 W
41466500	BY481P LED350S/840 PSD NBA GC SI	151 lm/W	35000 lm	235 W
41467200	BY481P LED350S/840 PSD NBA PC SI	151 lm/W	35000 lm	235 W
41468900	BY481P LED250S/840 PSD NBA PC SI	154 lm/W	25000 lm	160 W
41469600	BY480P LED130S/840 PSD NBA PC SI	155 lm/W	13000 lm	84 W
41470200	BY480P LED170S/840 PSD NBA PC SI	142 lm/W	17000 lm	120 W

Mechanical and Housing

Order Code	Full Product Name	Colour	Diameter
40730800	BY481P LED250S/840 PSD WB GC SI	Silver	-
40731500	BY481P LED250S/840 PSD MB GC SI	Silver	-
40732200	BY481P LED350S/840 PSD MB GC SI	Silver	-
40734600	BY481P LED250S/840 PSD NB GC SI	Silver	-
40741400	BY481P LED250S/840 PSD WB PC SI	Silver	-
40743800	BY481P LED350S/840 PSD WB GC SI	Silver	-
40744500	BY481P LED250S/840 PSD MB PC SI	Silver	-
40763600	BY481P LED250S/840 PSD HRO GC SI	Silver	-
40767400	BY481P LED350S/840 PSD HRO GC SI	Silver	-
40768100	BY481P LED350S/840 PSD NB GC SI	Silver	-
40769800	BY481P LED250S/840 PSD HRO PC SI	Silver	-
40793300	BY481P LED350S/840 PSD WB PC SI	Silver	-
40795700	BY481P LED250S/840 PSD NB PC SI	Silver	-
40798800	BY481P LED350S/840 PSD MB PC SI	Silver	-

Order Code	Full Product Name	Colour	Diameter
40799500	BY481P LED350S/840 PSD HRO PC SI	Silver	-
40733900	BY480P LED130S/840 PSD WB GC SI	Silver	-
40736000	BY480P LED170S/840 PSD WB GC SI	Silver	-
40738400	BY480P LED130S/840 PSD MB GC SI	Silver	-
40742100	BY480P LED130S/840 PSD HRO GC SI	Silver	-
40785800	BY480P LED130S/840 PSD NB GC SI	Silver	-
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	Silver	-
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	Silver	-
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	Silver	-
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	Silver	-
40750600	BY481P LED250S/840 PSD MB GC SI BR	Silver	-
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	Silver	-
40758200	BY481P LED250S/840 PSD WB GC SI BR	Silver	-
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	Silver	-

GentleSpace Gen3

Order Code	Full Product Name	Colour	Diameter
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	Silver	-
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	Silver	-
40778000	BY481P LED250S/840 PSD NB GC SI BR	Silver	-
40786500	BY481P LED250S/840 PSD HRO GC SI BR	Silver	-
40790200	BY481P LED350S/840 PSD MB GC SI BR	Silver	-
40801500	BY481P LED350S/840 PSD WB GC SI BR	Silver	-
40757500	BY481P LED250S/840 PSD MB GC WH	White	-
40771100	BY481P LED250S/840 PSD MB PC WH	White	-
40777300	BY481P LED250S/840 PSD WB GC WH	White	-
40800800	BY481P LED250S/840 PSD HRO GC WH	White	-
40760500	BY480P LED130S/840 PSD WB GC WH	White	-

Order Code	Full Product Name	Colour	Diameter
40781000	BY481P LED250S/840 PSD MB GC WH BR	White	-
40788900	BY481P LED250S/840 PSD WB GC WH BR	White	-
41463400	BY480P LED130S/840 PSD NBA GC SI	Silver	-
41464100	BY480P LED170S/840 PSD NBA GC SI	Silver	-
41465800	BY481P LED250S/840 PSD NBA GC SI	Silver	-
41466500	BY481P LED350S/840 PSD NBA GC SI	Silver	-
41467200	BY481P LED350S/840 PSD NBA PC SI	Silver	-
41468900	BY481P LED250S/840 PSD NBA PC SI	Silver	-
41469600	BY480P LED130S/840 PSD NBA PC SI	Silver	-
41470200	BY480P LED170S/840 PSD NBA PC SI	Silver	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
40730800	BY481P LED250S/840 PSD WB GC SI	70000 h
40731500	BY481P LED250S/840 PSD MB GC SI	100000 h
40732200	BY481P LED350S/840 PSD MB GC SI	100000 h
40734600	BY481P LED250S/840 PSD NB GC SI	100000 h
40741400	BY481P LED250S/840 PSD WB PC SI	100000 h
40743800	BY481P LED350S/840 PSD WB GC SI	100000 h
40744500	BY481P LED250S/840 PSD MB PC SI	100000 h
40763600	BY481P LED250S/840 PSD HRO GC SI	100000 h
40767400	BY481P LED350S/840 PSD HRO GC SI	100000 h
40768100	BY481P LED350S/840 PSD NB GC SI	100000 h
40769800	BY481P LED250S/840 PSD HRO PC SI	100000 h
40793300	BY481P LED350S/840 PSD WB PC SI	100000 h
40795700	BY481P LED250S/840 PSD NB PC SI	100000 h
40798800	BY481P LED350S/840 PSD MB PC SI	100000 h
40799500	BY481P LED350S/840 PSD HRO PC SI	100000 h
40733900	BY480P LED130S/840 PSD WB GC SI	100000 h
40736000	BY480P LED170S/840 PSD WB GC SI	100000 h
40738400	BY480P LED130S/840 PSD MB GC SI	100000 h
40742100	BY480P LED130S/840 PSD HRO GC SI	100000 h
40785800	BY480P LED130S/840 PSD NB GC SI	100000 h
40735300	BY481X LED250S/840 MB GC SI ACW-L BR	100000 h
40737700	BY481X LED250S/840 WB GC SI ACW-L BR	100000 h
40747600	BY481X LED250S/840 HRO GC SI ACW-L BR	100000 h
40749000	BY481X LED350S/840 MB GC SI ACW-L BR	100000 h
40750600	BY481P LED250S/840 PSD MB GC SI BR	100000 h

Order Code	Full Product Name	Median useful life L80B50
40751300	BY481X LED350S/840 WB GC SI ACW-L BR	100000 h
40758200	BY481P LED250S/840 PSD WB GC SI BR	100000 h
40759900	BY481X LED350S/840 HRO GC SI ACW-L BR	100000 h
40761200	BY481X LED250S/840 NB GC SI ACW-L BR	100000 h
40765000	BY481X LED350S/840 NB GC SI ACW-L BR	100000 h
40778000	BY481P LED250S/840 PSD NB GC SI BR	100000 h
40786500	BY481P LED250S/840 PSD HRO GC SI BR	100000 h
40790200	BY481P LED350S/840 PSD MB GC SI BR	100000 h
40801500	BY481P LED350S/840 PSD WB GC SI BR	100000 h
40757500	BY481P LED250S/840 PSD MB GC WH	100000 h
40771100	BY481P LED250S/840 PSD MB PC WH	100000 h
40777300	BY481P LED250S/840 PSD WB GC WH	100000 h
40800800	BY481P LED250S/840 PSD HRO GC WH	100000 h
40760500	BY480P LED130S/840 PSD WB GC WH	100000 h
40781000	BY481P LED250S/840 PSD MB GC WH BR	100000 h
40788900	BY481P LED250S/840 PSD WB GC WH BR	100000 h
41463400	BY480P LED130S/840 PSD NBA GC SI	70000 h
41464100	BY480P LED170S/840 PSD NBA GC SI	70000 h
41465800	BY481P LED250S/840 PSD NBA GC SI	70000 h
41466500	BY481P LED350S/840 PSD NBA GC SI	70000 h
41467200	BY481P LED350S/840 PSD NBA PC SI	70000 h
41468900	BY481P LED250S/840 PSD NBA PC SI	70000 h
41469600	BY480P LED130S/840 PSD NBA PC SI	70000 h
41470200	BY480P LED170S/840 PSD NBA PC SI	70000 h

