



Classic LED filament lamps for decorative lighting

Classic filament LED candles and lustres

Featuring a classic heritage design, Classic filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high-quality finishing
- High colour rendering (CRI above 80) for vivid colours
- Environmentally friendly: contains no mercury or other hazardous substances

Application


- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

Classic filament LED candles and lustres

Versions



Dimensional drawing




Product	D	C
Classic LEDLuster D 5-40W P45 E27 827 CL	45 mm	80 mm

Product	D	C
Classic LEDLuster D 4.5-40W P45 E27 827 CL	45 mm	80 mm

Classic filament LED candles and lustres

Dimensional drawing



Product	D	C
Classic LEDCandle D 4.5-40W B35 E14 827 CL	35 mm	99 mm
Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	35 mm	99 mm
MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	35 mm	97 mm

Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
General Information	
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20,000X
Light Technical	
LLmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and Housing	
Bulb Finish	Clear

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	5 kWh
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	5 kWh
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	5 kWh
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	4 kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	4 kWh

Controls and Dimming

Order Code	Full Product Name	Dimmable
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	Yes
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	-
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	Yes

Order Code	Full Product Name	Dimmable
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	Yes
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	-

Operating and Electrical

Classic filament LED candles and lustres

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	40 W	5 W
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	40 W	4.5 W
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	40 W	4.5 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	25 W	3.2 W
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	40 W	3.4 W

General Information

Order Code	Full Product Name	Cap-Base
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	E27
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	E14
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	E27

Order Code	Full Product Name	Cap-Base
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	E14
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	E14

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Colour Code (Nom)	Correlated Colour Temperature (Nom)	Colour Rendering Index (Nom)	Luminous Flux (Nom)
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	-	827	2700 K	80	470 lm
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	270 °	827	2700 K	80	470 lm
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	270 °	827	2700 K	80	470 lm
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	270 °	927-922	2700, 2200 K	90	250 lm
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	-	927	2700 K	90	470 lm


Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	P45
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	B35
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	P45

Order Code	Full Product Name	Bulb Shape
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	B35
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	B35

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	60 °C
929002391102	Classic LEDCandle D 4.5-40W B35 E14 827 CL	55 °C
929002391402	Classic LEDLuster D 4.5-40W P45 E27 827 CL	55 °C
929002393202	Classic LEDCandleDT 3.2-25W E14 CRI90 B35CL	45 °C
929003059502	MAS VLE LEDCandleD3.4-40W E14 B35 927CLG	80 °C



Classic filament LED candles and lustres

