



# Classic LED filament lamps for decorative lighting

## Classic filament LED candles and lusters

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

### Features


- Heritage design with classic shape
- Designed to be seen, they look good on and off
- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances

### Application

- Perfect for decorative installations
- Domestic applications
- Hospitality: restaurants and hotels

# Classic filament LED candles and lusters

## Versions




E14 B35 Clear




E14 BA35 Clear




E14 ST35 Clear




E14 P45 Clear




E27 P45 Clear



E14 B35 CL




E14 B35 CL




B22 B35 CL

# Classic filament LED candles and lusters


## Versions




E14 P45 CL




E27 P45 CL




E14 P45 CL




E27 P45 CL




B22 P45 CL



E14 BA35 CL




E27 A60 CL



B15 B35 CL

# Classic filament LED candles and lusters


## Versions




B22 B35 CL




B22 P45 CL




LEDcandle E14 B35 Clear




B22 B35 CL




LEDLuster E14 P45 Clear



LEDLuster E27 P45 Clear




LEDBulb E27 G120 Amber




E14 T 25mm Clear

# Classic filament LED candles and lusters


## Versions




Candelabra Screw BA11 35mm Clear




Single Contact Medium Screw BA11 35mm Clear




Candelabra Screw B 35mm Clear




E14 B 35mm Clear




E14 BA35 Clear



E27 P 45mm Clear




E14 P 45mm Clear




E27 A 60mm Clear

# Classic filament LED candles and lusters


## Versions



E14 B 35mm Clear




E27 A 60mm Frosted




E14 B 35mm Clear




E14 B 35mm Frosted




E14 P 45mm Clear



E14 P 45mm Frosted




E27 P 45mm Clear




E27 P 45mm Frosted

# Classic filament LED candles and lusters


## Versions




Single Contact Medium Screw B  
35mm Clear




Single Contact Medium Screw  
G16.5 Clear




Candelabra Screw G16.5 Clear




Single Contact Medium Screw  
G16.5 Clear




Candelabra Screw G16.5 Clear



Single Contact Medium Screw  
G16.5 Frosted




E27 P 45mm Transparent Amber



E14 B 35mm Transparent Amber




# Classic filament LED candles and lusters

## Versions



E14 P 45mm Transparent Amber

## Dimensional drawing



Product	D	C
Classic LEDLuster ND 6.5-60W P45 E27 840 FR	45 mm	78 mm
Classic LEDLuster ND 6.5-60W P45 E27 827 FR	45 mm	78 mm
Classic LEDLuster ND 4.3-40W E27 827 P45 CL	45 mm	82 mm





Product	D	C
Classic LEDLuster ND 6.5-60W P45 E14 840 FR	45 mm	80 mm
Classic LEDLuster ND 6.5-60W P45 E14 827 FR	45 mm	80 mm
Classic LEDLuster ND 4.3-40W E14 840 P45 CL	45 mm	80 mm
Classic LEDLuster ND 4.3-40W E14 827 P45 CL	45 mm	82 mm
Classic LEDLuster ND 6.5-60W P45 E14 865 FR	45 mm	80 mm

Product	D	C
Classic LEDCandle ND 6.5-60W B35 E14 840 CL	35 mm	97 mm
Classic LEDCandle ND 6.5-60W B35 E14 827 CL	35 mm	97 mm



## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
Classic LEDCandle ND 6.5-60W B35 E14 840 FR	35 mm	97 mm
Classic LEDCandle ND 2.2-25W E14 840 B35 CL	35 mm	97 mm
Classic LEDCandle ND 6.5-60W B35 E14 827 FR	35 mm	97 mm
LED classic 25W B35 E14 WW CL ND 1CT/6	35 mm	97 mm
Classic LEDCandle ND 2-25W B35 E14 827 CL	35 mm	97 mm
Classic LEDCandle ND 6.5-60W B35 E14 865 FR	35 mm	97 mm


Product	D	C
Classic LEDCandle ND 2-25W B22 827 B35 CL	35 mm	94 mm
Classic LEDCandle ND 4.3-40W B22 827 B35 CL	35 mm	93 mm
Classic LEDCandle ND 2-25W B35 B22 827 CL	35 mm	93 mm

Product	D	C
Classic LEDCandle ND 4.3-40W E14 840 B35 CL	35 mm	97 mm
Classic LEDCandle ND 4.3-40W E14 827 B35 CL	35 mm	97 mm
LED classic 40W B35 E14 WW CL ND3CTDisc	35 mm	97 mm
Classic LEDCandle D 5-40W B35 E14 827 CL	35 mm	103 mm
Classic LEDCandle D 2.7-25W B35 E14 827 CL	35 mm	103 mm


Product	D	C
Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	45 mm	93 mm

## Classic filament LED candles and lusters


### Dimensional drawing




Product	D	C
Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	35 mm	131 mm



Product	D	C
Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	45 mm	80 mm
Classic LEDLuster DT6-40W E27 CRI90 P45 CL	45 mm	80 mm







Product	D	C
Classic LEDCandle DT6-40W E14 CRI90 B35 CL	35 mm	104 mm
Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	35 mm	104 mm



Product	D	C
Classic LEDCandle ND 4.3-40W B15 827 B35 CL	35 mm	97 mm
Classic LEDCandle D 5-40W B35 B22 827 CL	35 mm	97 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
LED classic 50W G120 E27 2200K GOLD 1PF	120 mm	168 mm


Product	D	C
LED classic 60W A60 E27 WW CL ND3CTDisc	60 mm	104 mm

Product	D	C
Classic LEDLuster ND 2-25W P45 B22 827 CL	45 mm	78 mm


Product	D	C
Classic LEDCandle ND 2-25W B35 B15 827 CL	35 mm	97 mm

## Classic filament LED candles and lusters


### Dimensional drawing




Product	D	C
Classic LEDCandle D 5-40W BA35 E14 827 CL	35 mm	129 mm



Product	D	C
Classic LEDLuster D 5-40W P45 E27 827 CL	45 mm	80 mm
Classic LEDLuster D 2.7-25W P45 E27 827 CL	45 mm	80 mm







Product	D	C
Classic LEDLuster D 5-40W P45 B22 827 CL	45 mm	78 mm



Product	D	C
Classic LEDLuster D 2.7-25W P45 E14 827 CL	45 mm	85 mm
Classic LEDLuster D 5-40W P45 E14 827 CL	45 mm	85 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
Classic LEDLuster ND 2.2-25W E14 840 P45 CL	45 mm	80 mm
Classic LEDLuster ND 2-25W P45 E14 827 CL	45 mm	80 mm





Product	D	C
LED classic 25W E27 WWA60 CL ND 1PF/6	60 mm	104 mm

Product	D	C
LED classic 25W E27 WWA60 FR ND 1PF/6	60 mm	104 mm

Product	D	C
LED classic 25W T25 E14 CL ND 1PF/6	25 mm	85 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
2B11/PER/927-922/CL/G/E12/WGX1FB T20	35 mm	100 mm
5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	100 mm
3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	100 mm





Product	D	C
3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	110 mm
2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	110 mm
5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	35 mm	110 mm

Product	D	C
3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	35 mm	102 mm
5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	35 mm	102 mm

Product	D	C
3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	35 mm	92 mm
5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	35 mm	92 mm

# Classic filament LED candles and lusters

## Dimensional drawing



Product	D	C
LED classic 15W P45 E27 GOLD SP D SRT4	45 mm	80 mm
Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	45 mm	80 mm





Product	D	C
5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	52 mm	84 mm
3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	52 mm	84 mm
3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	52 mm	84 mm
2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	52 mm	84 mm

Product	D	C
3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	52 mm	92 mm
5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	52 mm	92 mm
2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	52 mm	92 mm

Product	D	C
Classic LEDCandle ND 2-25W BA35 E14 827 CL	35 mm	123 mm

## Classic filament LED candles and lusters

### Dimensional drawing



Product	D	C
Classic LEDCandle ND 2-25W ST35 E14 827 CL	35 mm	97 mm

Product	D	C
Classic LEDLuster ND 2-25W P45 E27 827 CL	45 mm	78 mm



Product	D	C
Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	45 mm	92 mm

Product	D	C
Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	35 mm	106 mm



# Classic filament LED candles and lusters

## Dimensional drawing



Product	D	C
Classic LEDLuster ND 6.5-60W P45 E14 840 CL	45 mm	80 mm
Classic LEDLuster ND 6.5-60W P45 E14 827 CL	45 mm	80 mm

Product	D	C
Classic LEDLuster ND 6.5-60W P45 E27 827 CL	45 mm	78 mm

Operating and Electrical	
Starting Time (Nom)	0.5 s
General Information	
Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Light Technical	
Llmf At End Of Nominal Lifetime (Nom)	70 %

## Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	2 kWh	A++
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	2 kWh	A++
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	2 kWh	A++
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	2 kWh	A++
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	2 kWh	A++

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	3 kWh	A++
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	2 kWh	A++
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	3 kWh	A++
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	5 kWh	A+
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	5 kWh	A+

## Classic filament LED candles and lusters

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	5 kWh	A++
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	3 kWh	A++
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	3 kWh	A++
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	5 kWh	A+
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	5 kWh	A+
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	5 kWh	A+
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	5 kWh	A+
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	7 kWh	A++
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	2 kWh	A++
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	2 kWh	A++
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	2 kWh	A++
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	2 kWh	A++
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	5 kWh	A++
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	5 kWh	A++
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	5 kWh	A++
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	5 kWh	A++
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	5 kWh	A++
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	5 kWh	A++
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	5 kWh	A++
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	8 kWh	A+
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	3 kWh	A++
929001969204	3.3BA11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	-
929002051304	5.5BA11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	-
929002204304	2BA11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929001969304	3.3BA11/PER/ 927-922/CL/G/E26/WGX 1FB T20	-	-
929001970104	5.5BA11/PER/ 927-922/CL/G/E26/WGX 1FB T20	-	-
929001969404	3.3B11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	-
929002204404	2B11/PER/927-922/CL/G/E12/ WX1FB T20	-	-
929002204504	5.5B11/PER/ 927-922/CL/G/E12/WGX 1FB T20	-	-
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	4 kWh	A+
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	6 kWh	A+
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	6 kWh	A+
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	4 kWh	A+
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	6 kWh	A+
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	4 kWh	A+
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	3 kWh	A++
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	3 kWh	A++
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	3 kWh	A++
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	7 kWh	A++
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	7 kWh	A++
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	7 kWh	A++
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	7 kWh	A++
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	7 kWh	A++
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	7 kWh	A++
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	7 kWh	A++
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	7 kWh	A++
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	7 kWh	A++
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	7 kWh	A++

## Classic filament LED candles and lusters

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	7 kWh	A++
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	7 kWh	A++
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	7 kWh	A++
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	-	-
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	-	-
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	-
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	-
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h	Energy Efficiency Label (EEL)
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	-
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	-
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	-
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	-	-
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	4 kWh	A
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	4 kWh	A
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	4 kWh	A
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	4 kWh	A

### Controls and Dimming

Order Code	Full Product Name	Dimmable
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	No
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	No
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	No
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	No
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	No
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	No
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	No
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	Yes
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	Yes
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	Yes
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	No
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	Yes
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	Yes
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	Yes
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	Yes
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	Yes
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	Yes
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	No
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	No
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	No
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	No
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	No
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	No
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	No
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	No
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	No
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	No
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	No
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	No

Order Code	Full Product Name	Dimmable
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	Yes
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	No
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes
929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes
929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes
929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes
929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	Yes
929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	Yes
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	Yes
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	Yes
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	Yes
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	Yes
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	Yes
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	Yes
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	No
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	No
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	No
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	No
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	No
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	No
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	No
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	No
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	No
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	No
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	No
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	No
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	No

## Classic filament LED candles and lusters

Order Code	Full Product Name	Dimmable
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	No
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	No
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	No
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	Yes
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	Yes
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Yes
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Yes
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Yes

Order Code	Full Product Name	Dimmable
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Yes
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Yes
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Yes
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	Yes
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	Yes
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	Yes
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	Yes
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	Yes

### Operating and Electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	50 to 60 Hz	220-240 V	25 W	2 W
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	50 to 60 Hz	220-240 V	25 W	2.2 W
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2.7 W
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001889802	Classic LEDCandle ND	50 to 60 Hz	220-240 V	40 W	4.3 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	50 to 60 Hz	220-240 V	25 W	2.7 W
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	50 to 60 Hz	220-240 V	25 W	2.7 W
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	50 to 60 Hz	220-240 V	40 W	5 W
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	50 to 60 Hz	220-240 V	60 W	7 W
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	50 to 60 Hz	220-240 V	25 W	2 W

## Classic filament LED candles and lusters

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	50 to 60 Hz	220-240 V	25 W	2 W
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	50 to 60 Hz	220-240 V	40 W	4.3 W
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	50 to 60 Hz	220-240 V	40 W	4.3 W
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	50 to 60 Hz	220-240 V	50 W	8 W
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	50 to 60 Hz	230 V	25 W	2.1 W
929001969204	3.3BA11/PER/ 927-922/CL/G/E1 2/WGX 1FB T20	-	120 V	40 W	3.3 W
929002051304	5.5BA11/PER/ 927-922/CL/G/E1 2/WGX 1FB T20	-	120 V	60 W	5.5 W
929002204304	2BA11/PER/ 927-922/CL/G/E1 2/WGX 1FB T20	-	120 V	25 W	2 W
929001969304	3.3BA11/PER/ 927-922/CL/G/E2 6/WGX 1FB T20	-	120 V	40 W	3.3 W
929001970104	5.5BA11/PER/ 927-922/CL/G/E2 6/WGX 1FB T20	-	120 V	60 W	5.5 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001969404	3.3B11/PER/ 927-922/CL/G/E1 2/WGX 1FB T20	-	120 V	40 W	3.3 W
929002204404	2B11/PER/ 927-922/CL/G/E1 2/WGX1FB T20	-	120 V	25 W	2 W
929002204504	5.5B11/PER/ 927-922/CL/G/E1 2/WGX 1FB T20	-	120 V	60 W	5.5 W
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	50 to 60 Hz	220-240 V	25 W	3.5 W
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	50 to 60 Hz	220-240 V	40 W	6 W
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	50 to 60 Hz	220-240 V	40 W	6 W
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	50 to 60 Hz	220-240 V	25 W	3.5 W
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	50 to 60 Hz	220-240 V	40 W	6 W
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	50 to 60 Hz	220-240 V	25 W	3.5 W
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	50 to 60 Hz	220-240 V	25 W	2.2 W
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	50 to 60 Hz	220-240 V	25 W	2.2 W
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	50 to 60 Hz	220-240 V	25 W	2.2 W
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028202	Classic LEDCandle ND	50 to 60 Hz	220-240 V	60 W	6.5 W

## Classic filament LED candles and lusters

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
	6.5-60W B35 E14 827 FR				
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	50 to 60 Hz	220-240 V	60 W	6.5 W
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	50 to 60 Hz	220-240 V	60 W	6.5 W
929002047204	3.3B11/PER/927-922/CL/G/E2 6/WGX1FB T20	-	120 V	40 W	3.3 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929002204604	5.5B11/PER/927-922/CL/G/E2 6/WGX 1FB T20	-	120 V	60 W	5.5 W
929002204804	2.7G16.5/PER/927-922/CL/G/E2 6/WGX 1FBT20	50 to 60 Hz	120 V	25 W	2.7 W
929002204904	2.7G16.5/PER/927-922/CL/G/E1 2/WGX 1FBT20	50 to 60 Hz	120 V	25 W	2.7 W
929002205004	3.8G16.5/PER/927-922/CL/G/E2 6/WGX 1FBT20	50 to 60 Hz	120 V	40 W	3.8 W
929002205204	5.5G16.5/PER/927-922/CL/G/E2 6/WGX 1FBT20	50 to 60 Hz	120 V	60 W	5.5 W
929002205104	3.8G16.5/PER/927-922/CL/G/E1 2/WGX 1FBT20	50 to 60 Hz	120 V	40 W	3.8 W
929002205304	5.5G16.5/PER/927-922/CL/G/E1 2/WGX 1FBT20	50 to 60 Hz	120 V	60 W	5.5 W
929002205404	3.8G16.5/PER/927-922/FR/G/E2 6/WGX 1FBT20	50 to 60 Hz	120 V	40 W	3.8 W
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	50 to 60 Hz	220-240 V	-	3.5 W
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	50 to 60 Hz	220-240 V	-	3.5 W
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	50 to 60 Hz	220-240 V	-	3.5 W
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	50 to 60 Hz	220-240 V	-	3.5 W

### General Information

Order Code	Full Product Name	Cap-Base	Switching Cycle
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	E14	20000X
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	E14	20000X
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	E14	20000X
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	E14	20000X
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	E14	20000X

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	E14	20000X
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	E27	20000X
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	E14	20000X
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	E14	20000X
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	B22	20000X

## Classic filament LED candles and lusters

Order Code	Full Product Name	Cap-Base	Switching Cycle
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	B15	20000X
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	E14	20000X
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	E27	20000X
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	E14	20000X
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	E27	20000X
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	B22	20000X
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	E14	20000X
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	E27	20000X
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	B15	20000X
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	B22	20000X
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	B22	20000X
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	B22	20000X
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	E14	20000X
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	E14	20000X
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	E14	20000X
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	B22	20000X
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	E14	20000X
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	E14	20000X
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	E27	20000X
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	E27	20000X
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	E14	50000X
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	20000X
929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	20000X
929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	20000X
929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	E26	20000X
929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	E26	20000X
929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	20000X
929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	E12	20000X
929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	20000X
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	E14	20000X

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	E14	20000X
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	E14	20000X
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	E27	20000X
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	E27	20000X
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	E14	20000X
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	E27	20000X
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	E14	20000X
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	E27	20000X
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	E14	20000X
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	E14	20000X
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	E14	20000X
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	E14	20000X
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	E14	20000X
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	E14	20000X
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	E14	20000X
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	E14	20000X
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	E14	20000X
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	E14	20000X
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	E27	20000X
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	E27	20000X
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	E27	20000X
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	E26	20000X
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	E26	20000X
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	E26	20000X
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	E12	20000X
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	E26	20000X

## Classic filament LED candles and lusters

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	E26	20000X
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	E12	20000X
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	E12	20000X
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	E26	20000X

Order Code	Full Product Name	Cap-Base	Switching Cycle
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	E27	20000X
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	E27	20000X
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	E14	20000X
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	E14	20000X

### Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Correlated Color		Color		Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
			Color Code	Temperature (Nom)	Rendering Index (Nom)	Luminous Flux		
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	-	827	2700 K	80	250 lm	250 lm	
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	-	840	4000 K	80	250 lm	250 lm	
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	-	827	2700 K	80	470 lm	470 lm	
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	-	827	2700 K	80	470 lm	470 lm	
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	-	827	2700 K	80	806 lm	806 lm	
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	-	827	2700 K	80	250 lm	250 lm	
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	-	827	2700 K	80	250 lm	250 lm	
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	-	827	2700 K	80	250 lm	250 lm	
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	-	827	2700 K	80	470 lm	470 lm	
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	-	827	2700 K	80	470 lm	470 lm	
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	-	840	4000 K	80	470 lm	470 lm	
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	-	827	2700 K	80	470 lm	470 lm	
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	-	827	2700 K	80	470 lm	470 lm	
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	-	840	4000 K	80	470 lm	470 lm	
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	-	827	2700 K	80	470 lm	470 lm	
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	-	822	2200 K	80	630 lm	630 lm	
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	-	827	2700 K	80	250 lm	250 lm	
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	-	927-922	2700-2200 K	90	300 lm	300 lm	
929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	-	927-922	2700-2200 K	90	500 lm	500 lm	
929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	-	927-922	2700-2200 K	90	180 lm	180 lm	
929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	-	927-922	2700-2200 K	90	300 lm	300 lm	
929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	300 °	927-922	2700-2200 K	90	500 lm	500 lm	
929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	-	927-922	2700-2200 K	90	300 lm	300 lm	



## Classic filament LED candles and lusters

Order Code	Full Product Name	Beam	Color Code	Correlated Color	Color	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
		Angle (Nom)		Temperature (Nom)	Rendering Index (Nom)		
929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	-	927-922	2700-2200 K	90	180 lm	180 lm
929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	-	927-922	2700-2200 K	90	500 lm	500 lm
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	-	927-922	2700-2200 K	90	250 lm	250 lm
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	-	927-922	2700-2200 K	90	470 lm	470 lm
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	-	927-922	2700-2200 K	90	470 lm	470 lm
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	-	927-922	2700-2200 K	90	250 lm	250 lm
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	-	927-922	2700-2200 K	90	470 lm	470 lm
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	-	927-922	2700-2200 K	90	250 lm	250 lm
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	-	827	2700 K	80	250 lm	250 lm
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	-	840	4000 K	80	250 lm	250 lm
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	-	827	2700 K	80	250 lm	250 lm
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	-	827	2700 K	80	806 lm	806 lm
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	-	840	4000 K	80	806 lm	806 lm
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	-	827	2700 K	80	806 lm	806 lm
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	-	840	4000 K	80	806 lm	806 lm
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	-	865	6500 K	80	806 lm	806 lm
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	-	827	2700 K	80	806 lm	806 lm
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	-	840	4000 K	80	806 lm	806 lm
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	-	827	2700 K	80	806 lm	806 lm
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	-	840	4000 K	80	806 lm	806 lm
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	-	865	6500 K	80	806 lm	806 lm
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	-	827	2700 K	80	806 lm	806 lm
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	-	827	2700 K	80	806 lm	806 lm
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	-	840	4000 K	80	806 lm	806 lm
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	-	927-922	2700-2200 K	90	300 lm	300 lm
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	-	927-922	2700-2200 K	90	500 lm	500 lm
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	927-922	2700-2200 K	90	250 lm	250 lm
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	927-922	2700-2200 K	90	250 lm	250 lm
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	927-922	2700-2200 K	90	350 lm	350 lm
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	-	927-922	2700-2200 K	90	500 lm	500 lm
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	927-922	2700-2200 K	90	350 lm	350 lm
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	-	927-922	2700-2200 K	90	500 lm	500 lm
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	-	927-922	2700-2200 K	90	350 lm	350 lm
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	-	820	2000 K	80	136 lm	136 lm
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	-	820	2000 K	80	136 lm	136 lm
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	-	820	2000 K	80	136 lm	136 lm
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	-	820	2000 K	80	136 lm	136 lm

### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish	Bulb Shape	Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	Clear	B35	929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	Clear	P45
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	Clear	B35	929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	Clear	P45
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	Clear	BA35	929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	Clear	P45
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	Clear	ST35	929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	Clear	B35

## Classic filament LED candles and lusters

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	Clear	B35
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	Clear	B35
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	Clear	B35
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	Clear	P45
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	Clear	P45
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	Clear	P45
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	Clear	P45
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	Clear	P45
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	Clear	BA35
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	Clear	A60
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	Clear	B35
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	Clear	B35
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	Clear	B35
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	Clear	P45
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	Clear	B35
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	Clear	B35
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	Clear	B35
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	Clear	B35
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	Clear	P45
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	Clear	P45
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	Clear	P45
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	Amber	G120
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	Clear	T25
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	BA11
929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	BA11
929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	BA11

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	BA11
929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	BA11
929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	B11
929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	Clear	B11
929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	Clear	B11
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	Clear	B35
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	Clear	B35
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	Clear	BA35
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	Clear	P45
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	Clear	P45
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	Clear	P45
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	Clear	A60
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	Clear	B35
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	Frosted	A60
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	Clear	B35
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	Clear	B35
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	Frosted	B35
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	Frosted	B35
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	Frosted	B35
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	Clear	P45
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	Clear	P45
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	Frosted	P45
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	Frosted	P45
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	Frosted	P45
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	Clear	P45

## Classic filament LED candles and lusters

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	Frosted	P45
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	Frosted	P45
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	Clear	B11
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	Clear	B11
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Clear	G16.5
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Clear	G16.5
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Clear	G16.5
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	Clear	G16.5

Order Code	Full Product Name	Bulb Finish	Bulb Shape
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Clear	G16.5
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	Clear	G16.5
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	Frosted	G16.5
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	Transparent Amber	P45
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	Transparent Amber	P45
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	Transparent Amber	B35
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	Transparent Amber	P45

### Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001238302	Classic LEDCandle ND 2-25W B35 E14 827 CL	36 °C
929001238391	LED classic 25W B35 E14 WW CL ND 1CT/6	36 °C
929001238402	Classic LEDCandle ND 2-25W BA35 E14 827 CL	36 °C
929001238502	Classic LEDCandle ND 2-25W ST35 E14 827 CL	36 °C
929001238602	Classic LEDLuster ND 2-25W P45 E14 827 CL	36 °C
929002024002	Classic LEDLuster ND 2.2-25W E14 840 P45 CL	30 °C
929001238702	Classic LEDLuster ND 2-25W P45 E27 827 CL	30 °C
929001332002	Classic LEDCandle D 2.7-25W B35 E14 827 CL	40 °C
929001332102	Classic LEDCandle D 5-40W B35 E14 827 CL	60 °C
929001332202	Classic LEDCandle D 5-40W B35 B22 827 CL	60 °C
929001889802	Classic LEDCandle ND 4.3-40W B15 827 B35 CL	45 °C
929001332302	Classic LEDLuster D 2.7-25W P45 E14 827 CL	40 °C
929001332402	Classic LEDLuster D 2.7-25W P45 E27 827 CL	40 °C
929001332502	Classic LEDLuster D 5-40W P45 E14 827 CL	60 °C
929001332602	Classic LEDLuster D 5-40W P45 E27 827 CL	60 °C
929001332702	Classic LEDLuster D 5-40W P45 B22 827 CL	60 °C
929001332802	Classic LEDCandle D 5-40W BA35 E14 827 CL	60 °C
929001387351	LED classic 60W A60 E27 WW CL ND3CTDisc	45 °C
929001815502	Classic LEDCandle ND 2-25W B35 B15 827 CL	36 °C
929001815602	Classic LEDCandle ND 2-25W B35 B22 827 CL	36 °C
929002023902	Classic LEDCandle ND 2-25W B22 827 B35 CL	36 °C
929001815902	Classic LEDLuster ND 2-25W P45 B22 827 CL	30 °C
929001889702	Classic LEDCandle ND 4.3-40W E14 827 B35 CL	45 °C
929001889751	LED classic 40W B35 E14 WW CL ND3CTDisc	45 °C
929002024302	Classic LEDCandle ND 4.3-40W E14 840 B35 CL	55 °C
929001889902	Classic LEDCandle ND 4.3-40W B22 827 B35 CL	45 °C
929001890402	Classic LEDLuster ND 4.3-40W E14 827 P45 CL	45 °C
929002024602	Classic LEDLuster ND 4.3-40W E14 840 P45 CL	45 °C
929001890502	Classic LEDLuster ND 4.3-40W E27 827 P45 CL	45 °C
929001896101	LED classic 50W G120 E27 2200K GOLD 1PF	40 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001949021	LED classic 25W T25 E14 CL ND 1PF/6	38 °C
929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX 1FB T20	50 °C
929002051304	5.5BA11/PER/927-922/CL/G/E12/WGX 1FB T20	60 °C
929002204304	2BA11/PER/927-922/CL/G/E12/WGX 1FB T20	45 °C
929001969304	3.3BA11/PER/927-922/CL/G/E26/WGX 1FB T20	50 °C
929001970104	5.5BA11/PER/927-922/CL/G/E26/WGX 1FB T20	60 °C
929001969404	3.3B11/PER/927-922/CL/G/E12/WGX 1FB T20	50 °C
929002204404	2B11/PER/927-922/CL/G/E12/WGX1FB T20	45 °C
929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	60 °C
929002017902	Classic LEDCandle DT3.5-25W E14 CRI90 B35 CL	55 °C
929002018002	Classic LEDCandle DT6-40W E14 CRI90 B35 CL	55 °C
929002018302	Classic LEDCandle DT6-40W E14 CRI90 BA35 CL	55 °C
929002018402	Classic LEDLuster DT3.5-25W E27 CRI90 P45 CL	55 °C
929002018602	Classic LEDLuster DT6-40W E27 CRI90 P45 CL	55 °C
929002018502	Classic LEDLuster DT3.5-25W E14 CRI90 P45 CL	55 °C
929002023021	LED classic 25W E27 WWA60 CL ND 1PF/6	30 °C
929002023702	Classic LEDCandle ND 2.2-25W E14 840 B35 CL	36 °C
929002025021	LED classic 25W E27 WWA60 FR ND 1PF/6	30 °C
929002028002	Classic LEDCandle ND 6.5-60W B35 E14 827 CL	55 °C
929002028102	Classic LEDCandle ND 6.5-60W B35 E14 840 CL	55 °C
929002028202	Classic LEDCandle ND 6.5-60W B35 E14 827 FR	55 °C
929002028302	Classic LEDCandle ND 6.5-60W B35 E14 840 FR	55 °C
929002028402	Classic LEDCandle ND 6.5-60W B35 E14 865 FR	55 °C
929002028502	Classic LEDLuster ND 6.5-60W P45 E14 827 CL	55 °C
929002028602	Classic LEDLuster ND 6.5-60W P45 E14 840 CL	55 °C
929002028702	Classic LEDLuster ND 6.5-60W P45 E14 827 FR	55 °C
929002028802	Classic LEDLuster ND 6.5-60W P45 E14 840 FR	55 °C
929002028902	Classic LEDLuster ND 6.5-60W P45 E14 865 FR	55 °C
929002029002	Classic LEDLuster ND 6.5-60W P45 E27 827 CL	55 °C
929002029202	Classic LEDLuster ND 6.5-60W P45 E27 827 FR	55 °C

## Classic filament LED candles and lusters

Order Code	Full Product Name	T-Case Maximum (Nom)
929002029302	Classic LEDLuster ND 6.5-60W P45 E27 840 FR	55 °C
929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	50 °C
929002204604	5.5B11/PER/927-922/CL/G/E26/WGX 1FB T20	60 °C
929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	45 °C
929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	45 °C
929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	50 °C
929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX 1FBT20	60 °C
929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	50 °C
929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX 1FBT20	60 °C
929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX 1FBT20	50 °C
929002224201	LED classic 15W P45 E27 GOLD SP D SRT4	38 °C
929002224202	Classic LEDLuster D 3.5-15W P45 E27 GOLD SP	38 °C
929002224302	Classic LEDCandle D 3.5-15W B35 E14 GOLD SP	38 °C
929002224402	Classic LEDLuster D 3.5-15W P45 E14 GOLD SP	38 °C

