



Classic look and feel

Classic frosted LED candles and lusters

Featuring a classic heritage design, Classic frosted LED candles and lusters deliver beautiful, decorative warm-white light while saving around 90% on energy costs. The familiar shapes of Classic frosted LED candles and lusters are a perfect fit for your existing fixtures.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features

- Pure and elegant heritage design with classic shape
- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Environmentally friendly: contains no mercury or other hazardous substances
- Instant full light on: Philips LED candles and lusters provide their full level of brightness immediately upon switching on

Application


- Domestic applications
- Hospitality: restaurants and hotels

Classic frosted LED candles and lusters


Versions




E14 B35 FR



E14 P45 FR






E27 P45 FR



E14 BA35 FR

Dimensional drawing




Product	D	C
Classic LEDLuster ND 2.2-25W P45 E14 FR	45 mm	80 mm
Classic LEDLuster ND 4.3-40W E14 827 P45 FR	45 mm	80 mm

Product	D	C
Classic LEDCandle ND 4.3-40W E14 827 B35 FR	35 mm	97 mm
Classic LEDCandle ND 2.2-25W B35 E14 FR	35 mm	97 mm

Product	D	C
Classic LEDLuster ND 2.2-25W P45 E27 FR	45 mm	78 mm
Classic LEDLuster ND 4.3-40W E27 827 P45 FR	45 mm	78 mm

Classic frosted LED candles and lusters

Dimensional drawing



Product	D	C
Classic LEDCandle ND 2.2-25W BA35 E14 FR	35 mm	123 mm

Approval and Application	
Energy Efficiency Label (EEL)	A++
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
General Information	
Nominal Lifetime (Nom)	15000 h
Rated Lifetime (Hours)	15000 h
Switching Cycle	20000X
Light Technical	
Color Code	827
Correlated Color Temperature (Nom)	2700 K
Color Rendering Index (Nom)	80
LLmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and Housing	
Bulb Finish	Frosted

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	3 kWh
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	5 kWh
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	3 kWh
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	5 kWh
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	3 kWh
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	5 kWh
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	3 kWh

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	25 W	2.2 W
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	40 W	4.3 W
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	25 W	2.2 W
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	40 W	4.3 W

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	25 W	2.2 W
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	40 W	4.3 W
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	25 W	2.2 W

Classic frosted LED candles and lusters

General Information

Order Code	Full Product Name	Cap-Base
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	E14
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	E14
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	E14
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	E14

Order Code	Full Product Name	Cap-Base
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	E27
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	E27
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	E14

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	250 lm	250 lm
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	470 lm	470 lm
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	250 lm	250 lm
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	470 lm	470 lm

Order Code	Full Product Name	Luminous Flux (Nom)	Luminous Flux (Rated) (Nom)
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	250 lm	250 lm
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	470 lm	470 lm
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	250 lm	250 lm

Mechanical and Housing

Order Code	Full Product Name	Bulb Shape
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	B35
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	B35
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	P45
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	P45

Order Code	Full Product Name	Bulb Shape
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	P45
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	P45
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	BA35

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001345202	Classic LEDCandle ND 2.2-25W B35 E14 FR	36 °C
929001345302	Classic LEDCandle ND 4.3-40W E14 827 B35 FR	55 °C
929001345402	Classic LEDLuster ND 2.2-25W P45 E14 FR	36 °C
929001345502	Classic LEDLuster ND 4.3-40W E14 827 P45 FR	55 °C
929001345602	Classic LEDLuster ND 2.2-25W P45 E27 FR	36 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001345702	Classic LEDLuster ND 4.3-40W E27 827 P45 FR	55 °C
929001345802	Classic LEDCandle ND 2.2-25W BA35 E14 FR	36 °C

