



Designed to be seen, looks good on or off

Master Value Decorative LED candles and lusters

The new Deco collection (candles and lusters) transforms your home with a perfect blend of (warm) white light and a lean, minimalistic lighting experience. With very long lifetime, up to 90% energy savings, no flickering and an instant full level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Benefits

- Around 90% energy saving
- Very long lifetime that reduces the need for replacement
- Easy replacement of classic conventional lamps

Features


- Perfect fit and high quality finishing
- High color rendering (CRI above 80) for vivid colors
- Eco-friendly: contains no mercury or other hazardous substances

Application

- Perfect for decorative installations: domestic applications, hospitality (restaurants and hotels)

Master Value Decorative LED candles and lusters

Versions



LEDLustre E27 P45 3.5W




LEDclassic 15W B35 E14 GOLD SP
D RFSRT4




LEDclassic 15W P45 E14 GOLD SP
D SRT4 1

Dimensional drawing




Product	D	C
MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	36 mm	95 mm



Product	D	C
MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	46 mm	80 mm

Master Value Decorative LED candles and lusters

Dimensional drawing



Product	D	C
MAS VLE LEDBulbD 2.6-15W E27 GOLDP45SP G	46 mm	80 mm

General Information	
Switching Cycle	20,000
Nominal lifetime	15,000 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	1800 K
Color rendering index (CRI)	80
Color Code	818
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux	136 lm
Operating and Electrical	
Input Frequency	50 to 60 Hz
Line Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
Wattage Equivalent	15 W
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	38 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Amber
Approval and Application	
Energy Consumption kWh/1000 h	3 kWh

General Information

Order Code	Full Product Name	Cap-Base
929002983402	MAS VLE LEDBulbD 2.6-15W E27 GOLDP45SP G	E27
929002983202	MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	E14
929002983302	MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	E14

Operating and Electrical

Order Code	Full Product Name	Power Consumption	Order Code	Full Product Name	Power Consumption
929002983402	MAS VLE LEDBulbD 2.6-15W E27 GOLDP45SP G	2.6 W	929002983302	MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	2.6 W
929002983202	MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	2.5 W			

Mechanical and Housing

Master Value Decorative LED candles and lusters

Order Code	Full Product Name	Bulb Shape
929002983402	MAS VLE LEDBulbd 2.6-15W E27 GOLDP45SP G	P45
929002983202	MAS VLE LEDCandleD2.5-15WE14 B35GOLDSP G	B35
929002983302	MAS VLE LEDLusterD 2.6-15W E14 P45 SP G	P45

