



# Innovation meets Simplicity: Intelligent lighting revolutionises HighBay illumination

## GreenUp Highbay G2

Height is not an issue any more, maximum 16 m movement detection together with the wireless ZigBee control, GreenUp HighBay G2, light up your space smartly.

### Benefits

- Light as need, provides additional energy savings on the intelligent version (BY560X) (depends on usage behaviour)
- Future-proof system: wireless adjustment of lighting settings and fast re-zoning if use of space changes via the intelligent version (BY560X)
- Precise light distribution to light up your space efficiently
- Provides better protection against dust and insects

### Features

- Different lighting levels and timings can be set per sensor, group and ZigBee network of luminaires (BY560X)
- Advanced sensor technology for effective presence and daylight detection
- High efficacy: Up to 140 lumens per watt
- CRI>80; R9>0; Wide beam, narrow beam and high rack optic choices are available
- Lifetime 65 Khrs @L70B50 with IP40 protection

### Application

- General Industry Application: Warehouse; Distribution centre; Factory
- Indoor sports hall
- Other high ceiling indoor applications

# GreenUp Highbay G2

## Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void


## Versions



## Product details



GreenUp Highbay G2 BY560P  
LED105 B



GreenUp Highbay G2 BY560P  
LED105 F

