



**SmartBright
Suspension is the
most economic LED
linear solution.
Quality light with
good uniformity and
visual comfort is
delivered under
suspension
installation.**

SmartBright Suspension

A linear suspension solution at an affordable price

Benefits

- Stylish product look and feel
- Excellent uniformity for light exit windows
- Visual comfort with enough light output

SmartBright Suspension

Features

- System efficacy up to 90 lm/W
- Lumen output up to 3,000 lm/1.2 m
- Flicker-free for a good on-site experience

Application

- Office
- Retail
- Open Area

Versions



Accessories



Ordercode 911401724662,
911401724682, 911401724722

SmartBright Suspension

Application Conditions

Ambient temperature range	-10 to +35 °C
Maximum dim level	Not applicable
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK03
Ingress protection code	IP20

Controls and Dimming

Dimmable	No
----------	----

Operating and Electrical

Input Voltage	220 to 240 V
---------------	--------------

General Information

Beam angle of light source	- °
CE mark	-
Protection class IEC	Safety class I (I)
Optical cover/lens type	Polystyrene bowl/ cover prismatic
Driver included	Yes
ENEC mark	-
Flammability mark	NO
Glow-wire test	650/30
Light source replaceable	No
Number of gear units	1 unit
Optic type	Symmetrical

Initial Performance (IEC Compliant)

Initial chromaticity	≤5
Init. Colour Rendering Index	>80
Initial LED luminaire efficacy	88 lm/W
Luminous flux tolerance	+/-10%

Mechanical and Housing

Colour	Gray
--------	------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux	Initial input power
32459300	RCO95V LED30S/830 PSU W12L120 Grey GM	6500 K	3000 lm	34 W
32460900	RCO95V LED30S/840 PSU W12L120 Grey GM	3000 K	3000 lm	34 W
32461600	RCO95V LED30S/865 PSU W12L120 Grey GM	4000 K	3000 lm	34 W
32462300	RCO95V LED15S/830 PSU W12L60 Grey GM	6500 K	3000 lm	34 W
32463000	RCO95V LED15S/840 PSU W12L60 Grey GM	3000 K	1500 lm	17 W
32464700	RCO95V LED15S/865 PSU W12L60 Grey GM	4000 K	1500 lm	17 W

