



It delivers super flexibility, a complete product range and seamless system integration for hospitality customers..

Greenspace Flex

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Benefits

- Complete portfolio covering from 400lm to 3000lm, 3CCT and 3 beam angles.
- Super flexibility with modular design, and different trims to suit different application.
- Smart connectivity to seamlessly integration with Interact Hospitality.
- Deep recess for visual comfort
- Easy installation and maintenance

Greenspace Flex

Features

- 6w ~42w (400lm~3200lm)
- CRI 90, SDCM <3
- Beam Angle: NB, MB, WB
- CCT: 2700K, 3000K, 4000K
- High reliability, 50Khrs (L80B50@25°C)

Application

- Guest room
- Bath room
- Corridor
- Lobby

Specifications

Mounting type	Recessed
Operating Temperature range	-20 to +45 °C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Optical Accessories	available through ETO
Dimming	PSU: non-dimmable PSD: dimmable via Dali protocol PSR: trailing dimmable PSR 1-10V: 1-10v dimmable DMX: dimmable via DMX protocol
Control system input	DALI / 1-10V / DMX / trailing edge
Material	Heat sink: die-cast aluminum
Main color of the luminaire	Housing: dark Grey Reflector: color available through ETO
Lumen maintenance at median useful life 50.000h	L80
Luminous flux	468-3990lm
Power consumption	6W-42W





Correlated color temperature - CCT	2700K, 3000K, 4000K
Color Rendering index - CRI	90
Beam angle	NB (Narrow Beam): 15-18° MB (Medium Beam): 20-24° WB (Wide Beam): 30-40° VWB (Very Wide Beam): 50°
Protection Class IEC61140	Class II & Class III for MR16 version
Mechanical impact protection	IK04
Ingress protection	IP20 / IP54(Front side) for selected SKU only
Light source replaceable	No
Driver replaceable	yes
Overall diameter	D55-D150
Installation	recessed Fixation by means of spring fasteners

Versions






Greenspace Flex RS378B P15 M55

Dimensional drawing



Modular Type	D, mm	H, mm
RS378B P6/P11 M55	55	49
RS378B P15 M55	55	49
RS378B P24 M70	70	90
RS378B P33 M87	87	107
RS378B P42 M102	102	116



General Information	
CE mark	-
ENEC mark	-
Flammability mark	-
Light Technical	
Optical cover type	-
Color rendering index (CRI)	>90
Optic type	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Temperature	
Ambient temperature range	-20 to +45 °C
Mechanical and Housing	
Housing Color	Dark gray
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK04
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
01535871	RS378B P11 927 PSD-E NB M55	-	-	-
65337899	RS378B P11 927 PSD-E MB M55	-	-	-
01536071	RS378B P11 927 PSD-E WB M55	-	-	-
01536271	RS378B P11 930 PSD-E MB M55	-	-	-
01536371	RS378B P11 930 PSD-E WB M55	-	-	-
01536471	RS378B P11 940 PSD-E NB M55	-	-	-
01536571	RS378B P11 940 PSD-E MB M55	-	-	-
01536671	RS378B P11 940 PSD-E WB M55	-	-	-
01720892	RS378B P6 927 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01720902	RS378B P6 930 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01720912	RS378B P6 940 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01720922	RS378B P6 927 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01720932	RS378B P6 930 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64994499	RS378B P6 940 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64989099	RS378B P6 927 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64992099	RS378B P6 930 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64995199	RS378B P6 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64996899	RS378B P11 927 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64999999	RS378B P11 930 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721002	RS378B P11 940 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721012	RS378B P11 927 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721022	RS378B P11 930 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65003299	RS378B P11 940 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
64998299	RS378B P11 927 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65001899	RS378B P11 930 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65004999	RS378B P11 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721072	RS378B P6 927 PSR-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721102	RS378B P6 927 PSR-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721112	RS378B P6 930 PSR-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
01721132	RS378B P6 927 PSR-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721172	RS378B P11 930 PSR-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721192	RS378B P11 927 PSR-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65061299	RS378B P11 927 PSR-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65064399	RS378B P11 930 PSR-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721622	RS378B P42 930 PSU-E NB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721632	RS378B P42 940 PSU-E NB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721642	RS378B P42 927 PSU-E MB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721652	RS378B P42 930 PSU-E MB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721662	RS378B P42 940 PSU-E MB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721682	RS378B P42 930 PSU-E WB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01721692	RS378B P42 940 PSU-E WB M102	Yes	Temperature 600 °C, duration 30 s	1 unit
01534971	RS378B P6 927 PSD-E NB M55	-	-	-
01535071	RS378B P6 927 PSD-E MB M55	-	-	-
65329399	RS378B P6 927 PSD-E WB M55	-	-	-
01535371	RS378B P6 930 PSD-E MB M55	-	-	-
01535471	RS378B P6 930 PSD-E WB M55	-	-	-
01535571	RS378B P6 940 PSD-E NB M55	-	-	-
01537771	RS378B P24 927 PSD-E MB M70	-	-	-
65358399	RS378B P24 930 PSD-E MB M70	-	-	-
01538171	RS378B P24 930 PSD-E WB M70	-	-	-
01538271	RS378B P24 940 PSD-E NB M70	-	-	-
01538371	RS378B P24 940 PSD-E MB M70	-	-	-
01538471	RS378B P24 940 PSD-E WB M70	-	-	-
01721432	RS378B P24 927 PSU-E NB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
65017999	RS378B P24 930 PSU-E NB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721452	RS378B P24 940 PSU-E NB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721462	RS378B P24 927 PSU-E MB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721472	RS378B P24 930 PSU-E MB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721482	RS378B P24 940 PSU-E MB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721492	RS378B P24 927 PSU-E WB M70	Yes	Temperature 600 °C, duration 30 s	1 unit

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
65019399	RS378B P24 930 PSU-E WB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01721512	RS378B P24 940 PSU-E WB M70	Yes	Temperature 600 °C, duration 30 s	1 unit
01538571	RS378B P33 927 PSD-E NB M87	-	-	-
01538671	RS378B P33 927 PSD-E MB M87	-	-	-
01538871	RS378B P33 930 PSD-E NB M87	-	-	-
01539171	RS378B P33 940 PSD-E NB M87	-	-	-
65023099	RS378B P33 927 PSU-E NB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65026199	RS378B P33 930 PSU-E NB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65029299	RS378B P33 940 PSU-E NB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65027899	RS378B P33 930 PSU-E MB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65030899	RS378B P33 940 PSU-E MB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65028599	RS378B P33 930 PSU-E WB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
65031599	RS378B P33 940 PSU-E WB M87	Yes	Temperature 600 °C, duration 30 s	1 unit
01539871	RS378B P42 930 PSD-E MB M102	-	-	-
01539971	RS378B P42 930 PSD-E WB M102	-	-	-
01540271	RS378B P42 940 PSD-E WB M102	-	-	-
01545571	RS378B P11 930 PSU-E WW S	-	-	-
01545671	RS378B P11 940 PSU-E WW S	-	-	-
01546471	RS378B P11 930 PSD-E WW S	-	-	-
01546571	RS378B P11 940 PSD-E WW S	-	-	-
01545971	RS378B P15 940 PSU-E WW S	-	-	-
01546771	RS378B P15 930 PSD-E WW S	-	-	-
01536771	RS378B P15 927 PSD-E NB M55	-	-	-
01536871	RS378B P15 927 PSD-E MB M55	-	-	-
01536971	RS378B P15 927 PSD-E WB M55	-	-	-
01537171	RS378B P15 930 PSD-E MB M55	-	-	-
01537271	RS378B P15 930 PSD-E WB M55	-	-	-
01537371	RS378B P15 940 PSD-E NB M55	-	-	-
01537471	RS378B P15 940 PSD-E MB M55	-	-	-
01537571	RS378B P15 940 PSD-E WB M55	-	-	-
01540371	RS378B P15 927 PSR-E 1-10V NB M55	-	-	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-	-	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-	-	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-	-	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-	-	-
01532371	RS378B P6 927 PSU-E MB M43	-	-	-
01532471	RS378B P6 927 PSU-E WB M43	-	-	-
01532571	RS378B P6 930 PSU-E NB M43	-	-	-
01532671	RS378B P6 930 PSU-E MB M43	-	-	-
01532771	RS378B P6 930 PSU-E WB M43	-	-	-
01532871	RS378B P6 940 PSU-E NB M43	-	-	-
01532971	RS378B P6 940 PSU-E MB M43	-	-	-

Order Code	Full Product Name	Driver included	Glow-wire test	Number of gear units
01533071	RS378B P6 940 PSU-E WB M43	-	-	-
01533271	RS378B P6 927 PSR-E MB M43	-	-	-
01533571	RS378B P6 930 PSR-E MB M43	-	-	-
01533671	RS378B P6 930 PSR-E WB M43	-	-	-
01533771	RS378B P6 940 PSR-E NB M43	-	-	-
01534471	RS378B P6 930 PSD-E MB M43	-	-	-
01534571	RS378B P6 930 PSD-E WB M43	-	-	-
01534771	RS378B P6 940 PSD-E MB M43	-	-	-
01721252	RS378B P15 927 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721262	RS378B P15 930 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721272	RS378B P15 940 PSU-E NB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65006399	RS378B P15 927 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721292	RS378B P15 930 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
01721302	RS378B P15 940 PSU-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65007099	RS378B P15 927 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65010099	RS378B P15 930 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65013199	RS378B P15 940 PSU-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65069899	RS378B P15 927 PSR-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65075999	RS378B P15 940 PSR-E MB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65073599	RS378B P15 930 PSR-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit
65076699	RS378B P15 940 PSR-E WB M55	Yes	Temperature 600 °C, duration 30 s	1 unit

Light Technical

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01535871	RS378B P11 927 PSD-E NB M55	-	2700 K	76 lm/W	836 lm
65337899	RS378B P11 927 PSD-E MB M55	-	2700 K	87 lm/W	957 lm
01536071	RS378B P11 927 PSD-E WB M55	-	2700 K	87 lm/W	957 lm
01536271	RS378B P11 930 PSD-E MB M55	-	3000 K	92 lm/W	1,012 lm
01536371	RS378B P11 930 PSD-E WB M55	-	3000 K	92 lm/W	1,012 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01536471	RS378B P11 940 PSD-E NB M55	-	4000 K	87 lm/W	957 lm
01536571	RS378B P11 940 PSD-E MB M55	-	4000 K	100 lm/W	1,100 lm
01536671	RS378B P11 940 PSD-E WB M55	-	4000 K	100 lm/W	1,100 lm
01720892	RS378B P6 927 PSU-E NB M55	- degree(s)	2700 K	75 lm/W	450 lm
01720902	RS378B P6 930 PSU-E NB M55	- degree(s)	3000 K	78 lm/W	468 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01720912	RS378B P6 940 PSU-E NB M55	- degree(s)	4000 K	82 lm/W	492 lm
01720922	RS378B P6 927 PSU-E MB M55	- degree(s)	2700 K	75 lm/W	450 lm
01720932	RS378B P6 930 PSU-E MB M55	- degree(s)	3000 K	78 lm/W	468 lm
64994499	RS378B P6 940 PSU-E MB M55	- degree(s)	4000 K	82 lm/W	492 lm
64989099	RS378B P6 927 PSU-E WB M55	- degree(s)	2700 K	90 lm/W	595 lm
64992099	RS378B P6 930 PSU-E WB M55	- degree(s)	3000 K	78 lm/W	468 lm
64995199	RS378B P6 940 PSU-E WB M55	- degree(s)	4000 K	82 lm/W	492 lm
64996899	RS378B P11 927 PSU-E NB M55	-	2700 K	76 lm/W	836 lm
64999999	RS378B P11 930 PSU-E NB M55	-	3000 K	78 lm/W	858 lm
01721002	RS378B P11 940 PSU-E NB M55	-	4000 K	87 lm/W	957 lm
01721012	RS378B P11 927 PSU-E MB M55	-	2700 K	87 lm/W	957 lm
01721022	RS378B P11 930 PSU-E MB M55	-	3000 K	92 lm/W	1,012 lm
65003299	RS378B P11 940 PSU-E MB M55	-	4000 K	100 lm/W	1,100 lm
64998299	RS378B P11 927 PSU-E WB M55	-	2700 K	87 lm/W	957 lm
65001899	RS378B P11 930 PSU-E WB M55	-	3000 K	92 lm/W	1,012 lm
65004999	RS378B P11 940 PSU-E WB M55	-	4000 K	100 lm/W	1,100 lm
01721072	RS378B P6 927 PSR-E NB M55	-	2700 K	58 lm/W	348 lm
01721102	RS378B P6 927 PSR-E MB M55	-	2700 K	58 lm/W	348 lm
01721112	RS378B P6 930 PSR-E MB M55	-	3000 K	60 lm/W	360 lm
01721132	RS378B P6 927 PSR-E WB M55	-	2700 K	58 lm/W	348 lm
01721172	RS378B P11 930 PSR-E NB M55	-	3000 K	78 lm/W	858 lm
01721192	RS378B P11 927 PSR-E MB M55	-	2700 K	87 lm/W	957 lm
65061299	RS378B P11 927 PSR-E WB M55	-	2700 K	87 lm/W	957 lm
65064399	RS378B P11 930 PSR-E WB M55	-	3000 K	92 lm/W	1,012 lm

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
01721622	RS378B P42 930 PSU-E NB M102	-	3000 K	95 lm/W	3,990 lm
01721632	RS378B P42 940 PSU-E NB M102	-	4000 K	101 lm/W	4,242 lm
01721642	RS378B P42 927 PSU-E MB M102	-	2700 K	90 lm/W	3,780 lm
01721652	RS378B P42 930 PSU-E MB M102	- degree(s)	3000 K	95 lm/W	3,990 lm
01721662	RS378B P42 940 PSU-E MB M102	- degree(s)	4000 K	101 lm/W	4,242 lm
01721682	RS378B P42 930 PSU-E WB M102	- degree(s)	3000 K	95 lm/W	3,990 lm
01721692	RS378B P42 940 PSU-E WB M102	- degree(s)	4000 K	101 lm/W	4,242 lm
01534971	RS378B P6 927 PSD-E NB M55	-	2700 K	75 lm/W	450 lm
01535071	RS378B P6 927 PSD-E MB M55	-	2700 K	70 lm/W	420 lm
65329399	RS378B P6 927 PSD-E WB M55	-	2700 K	70 lm/W	420 lm
01535371	RS378B P6 930 PSD-E MB M55	-	3000 K	73 lm/W	438 lm
01535471	RS378B P6 930 PSD-E WB M55	-	3000 K	73 lm/W	438 lm
01535571	RS378B P6 940 PSD-E NB M55	-	4000 K	82 lm/W	492 lm
01537771	RS378B P24 927 PSD-E MB M70	-	2700 K	80 lm/W	1,920 lm
65358399	RS378B P24 930 PSD-E MB M70	-	3000 K	83 lm/W	1,992 lm
01538171	RS378B P24 930 PSD-E WB M70	-	3000 K	83 lm/W	1,992 lm
01538271	RS378B P24 940 PSD-E NB M70	-	4000 K	90 lm/W	2,160 lm
01538371	RS378B P24 940 PSD-E MB M70	-	4000 K	90 lm/W	2,160 lm
01538471	RS378B P24 940 PSD-E WB M70	-	4000 K	90 lm/W	2,160 lm
01721432	RS378B P24 927 PSU-E NB M70	-	2700 K	80 lm/W	1,920 lm
65017999	RS378B P24 930 PSU-E NB M70	-	3000 K	83 lm/W	1,992 lm
01721452	RS378B P24 940 PSU-E NB M70	-	4000 K	90 lm/W	2,160 lm
01721462	RS378B P24 927 PSU-E MB M70	-	2700 K	80 lm/W	1,920 lm
01721472	RS378B P24 930 PSU-E MB M70	-	3000 K	83 lm/W	1,992 lm

	Full Product	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name				
01721482	RS378B P24 940 - PSU-E MB M70	-	4000 K	90 lm/W	2,160 lm
01721492	RS378B P24 927 - PSU-E WB M70	-	2700 K	80 lm/W	1,920 lm
65019399	RS378B P24 930 - PSU-E WB M70	-	3000 K	83 lm/W	1,992 lm
01721512	RS378B P24 940 - PSU-E WB M70	-	4000 K	90 lm/W	2,160 lm
01538571	RS378B P33 927 - PSD-E NB M87	-	2700 K	80 lm/W	2,640 lm
01538671	RS378B P33 927 - PSD-E MB M87	-	2700 K	80 lm/W	2,640 lm
01538871	RS378B P33 930 - PSD-E NB M87	-	3000 K	83 lm/W	2,739 lm
01539171	RS378B P33 940 - PSD-E NB M87	-	4000 K	90 lm/W	2,970 lm
65023099	RS378B P33 927 - PSU-E NB M87	-	2700 K	80 lm/W	2,640 lm
65026199	RS378B P33 930 - PSU-E NB M87	-	3000 K	83 lm/W	2,739 lm
65029299	RS378B P33 940 - PSU-E NB M87	-	4000 K	90 lm/W	2,970 lm
65027899	RS378B P33 930 - PSU-E MB M87	-	3000 K	83 lm/W	2,739 lm
65030899	RS378B P33 940 - PSU-E MB M87	-	4000 K	90 lm/W	2,970 lm
65028599	RS378B P33 930 - PSU-E WB M87	-	3000 K	83 lm/W	2,739 lm
65031599	RS378B P33 940 - PSU-E WB M87	-	4000 K	90 lm/W	2,970 lm
01539871	RS378B P42 930 - PSD-E MB M102	-	3000 K	95 lm/W	3,990 lm
01539971	RS378B P42 930 - PSD-E WB M102	-	3000 K	95 lm/W	3,990 lm
01540271	RS378B P42 940 - PSD-E WB M102	-	4000 K	101 lm/W	4,242 lm
01545571	RS378B P11 930 - PSU-E WW S	-	3000 K	78 lm/W	858 lm
01545671	RS378B P11 940 - PSU-E WW S	-	4000 K	87 lm/W	957 lm
01546471	RS378B P11 930 - PSD-E WW S	-	3000 K	78 lm/W	858 lm
01546571	RS378B P11 940 - PSD-E WW S	-	4000 K	87 lm/W	957 lm
01545971	RS378B P15 940 - PSU-E WW S	-	4000 K	87 lm/W	1,305 lm
01546771	RS378B P15 930 - PSD-E WW S	-	3000 K	78 lm/W	1,170 lm

	Full Product	Beam angle of light source	Correlated Color Temperature (Nom)	Luminous Efficacy (rated) (Nom)	Luminous Flux
Order Code	Name				
01536771	RS378B P15 927 - PSD-E NB M55	-	2700 K	76 lm/W	1,140 lm
01536871	RS378B P15 927 - PSD-E MB M55	-	2700 K	78 lm/W	1,170 lm
01536971	RS378B P15 927 - PSD-E WB M55	-	2700 K	87 lm/W	1,305 lm
01537171	RS378B P15 930 - PSD-E MB M55	-	3000 K	78 lm/W	1,170 lm
01537271	RS378B P15 930 - PSD-E WB M55	-	3000 K	87 lm/W	1,305 lm
01537371	RS378B P15 940 - PSD-E NB M55	-	4000 K	76 lm/W	1,140 lm
01537471	RS378B P15 940 - PSD-E MB M55	-	4000 K	78 lm/W	1,170 lm
01537571	RS378B P15 940 - PSD-E WB M55	-	4000 K	87 lm/W	1,305 lm
01540371	RS378B P15 927 - PSR-E 1-10V NB M55	-	2700 K	76 lm/W	1,140 lm
01540471	RS378B P15 927 - PSR-E 1-10V MB M55	-	2700 K	78 lm/W	1,170 lm
01540771	RS378B P15 930 - PSR-E 1-10V MB M55	-	3000 K	78 lm/W	1,170 lm
01540871	RS378B P15 930 - PSR-E 1-10V WB M55	-	3000 K	87 lm/W	1,305 lm
01541171	RS378B P15 940 - PSR-E 1-10V WB M55	-	4000 K	87 lm/W	1,305 lm
01532371	RS378B P6 927 - PSU-E MB M43	-	2700 K	75 lm/W	450 lm
01532471	RS378B P6 927 - PSU-E WB M43	-	2700 K	75 lm/W	450 lm
01532571	RS378B P6 930 - PSU-E NB M43	-	3000 K	78 lm/W	468 lm
01532671	RS378B P6 930 - PSU-E MB M43	-	3000 K	78 lm/W	468 lm
01532771	RS378B P6 930 - PSU-E WB M43	-	3000 K	78 lm/W	468 lm
01532871	RS378B P6 940 - PSU-E NB M43	-	4000 K	82 lm/W	492 lm
01532971	RS378B P6 940 - PSU-E MB M43	-	4000 K	82 lm/W	492 lm
01533071	RS378B P6 940 - PSU-E WB M43	-	4000 K	82 lm/W	492 lm
01533271	RS378B P6 927 - PSR-E MB M43	-	2700 K	58 lm/W	348 lm

Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
01533571	RS378B P6 930 PSR-E MB M43	-	3000 K	60 lm/W	360 lm
01533671	RS378B P6 930 PSR-E WB M43	-	3000 K	60 lm/W	360 lm
01533771	RS378B P6 940 PSR-E NB M43	-	4000 K	65 lm/W	390 lm
01534471	RS378B P6 930 PSD-E MB M43	-	3000 K	73 lm/W	438 lm
01534571	RS378B P6 930 PSD-E WB M43	-	3000 K	73 lm/W	438 lm
01534771	RS378B P6 940 PSD-E MB M43	-	4000 K	78 lm/W	468 lm
01721252	RS378B P15 927 PSU-E NB M55	-	2700 K	76 lm/W	1,140 lm
01721262	RS378B P15 930 PSU-E NB M55	-	3000 K	78 lm/W	1,170 lm
01721272	RS378B P15 940 PSU-E NB M55	-	4000 K	87 lm/W	1,305 lm
65006399	RS378B P15 927 PSU-E MB M55	-	2700 K	76 lm/W	1,140 lm

Order Code	Full Product Name	Beam	Correlated	Luminous	Luminous
		angle of light source	Color Temperature (Nom)	Efficacy (rated) (Nom)	
01721292	RS378B P15 930 PSU-E MB M55	-	3000 K	78 lm/W	1,170 lm
01721302	RS378B P15 940 PSU-E MB M55	-	4000 K	87 lm/W	1,305 lm
65007099	RS378B P15 927 PSU-E WB M55	-	2700 K	76 lm/W	1,140 lm
65010099	RS378B P15 930 PSU-E WB M55	-	3000 K	78 lm/W	1,170 lm
65013199	RS378B P15 940 PSU-E WB M55	-	4000 K	87 lm/W	1,305 lm
65069899	RS378B P15 927 PSR-E MB M55	-	2700 K	76 lm/W	1,140 lm
65075999	RS378B P15 940 PSR-E MB M55	-	4000 K	87 lm/W	1,305 lm
65073599	RS378B P15 930 PSR-E WB M55	-	3000 K	78 lm/W	1,170 lm
65076699	RS378B P15 940 PSR-E WB M55	-	4000 K	87 lm/W	1,305 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01535871	RS378B P11 927 PSD-E NB M55	11 W
65337899	RS378B P11 927 PSD-E MB M55	11 W
01536071	RS378B P11 927 PSD-E WB M55	11 W
01536271	RS378B P11 930 PSD-E MB M55	11 W
01536371	RS378B P11 930 PSD-E WB M55	11 W
01536471	RS378B P11 940 PSD-E NB M55	11 W
01536571	RS378B P11 940 PSD-E MB M55	11 W
01536671	RS378B P11 940 PSD-E WB M55	11 W
01720892	RS378B P6 927 PSU-E NB M55	6 W
01720902	RS378B P6 930 PSU-E NB M55	6 W
01720912	RS378B P6 940 PSU-E NB M55	6 W
01720922	RS378B P6 927 PSU-E MB M55	6 W
01720932	RS378B P6 930 PSU-E MB M55	6 W
64994499	RS378B P6 940 PSU-E MB M55	6 W
64989099	RS378B P6 927 PSU-E WB M55	6 W
64992099	RS378B P6 930 PSU-E WB M55	6 W
64995199	RS378B P6 940 PSU-E WB M55	6 W
64996899	RS378B P11 927 PSU-E NB M55	11 W
64999999	RS378B P11 930 PSU-E NB M55	11 W
01721002	RS378B P11 940 PSU-E NB M55	11 W
01721012	RS378B P11 927 PSU-E MB M55	11 W
01721022	RS378B P11 930 PSU-E MB M55	11 W
65003299	RS378B P11 940 PSU-E MB M55	11 W
64998299	RS378B P11 927 PSU-E WB M55	11 W
65001899	RS378B P11 930 PSU-E WB M55	11 W

Order Code	Full Product Name	Power Consumption
65004999	RS378B P11 940 PSU-E WB M55	11 W
01721072	RS378B P6 927 PSR-E NB M55	6 W
01721102	RS378B P6 927 PSR-E MB M55	6 W
01721112	RS378B P6 930 PSR-E MB M55	6 W
01721132	RS378B P6 927 PSR-E WB M55	6 W
01721172	RS378B P11 930 PSR-E NB M55	11 W
01721192	RS378B P11 927 PSR-E MB M55	11 W
65061299	RS378B P11 927 PSR-E WB M55	11 W
65064399	RS378B P11 930 PSR-E WB M55	11 W
01721622	RS378B P42 930 PSU-E NB M102	42 W
01721632	RS378B P42 940 PSU-E NB M102	42 W
01721642	RS378B P42 927 PSU-E MB M102	42 W
01721652	RS378B P42 930 PSU-E MB M102	42 W
01721662	RS378B P42 940 PSU-E MB M102	42 W
01721682	RS378B P42 930 PSU-E WB M102	42 W
01721692	RS378B P42 940 PSU-E WB M102	42 W
01534971	RS378B P6 927 PSD-E NB M55	6 W
01535071	RS378B P6 927 PSD-E MB M55	6 W
65329399	RS378B P6 927 PSD-E WB M55	6 W
01535371	RS378B P6 930 PSD-E MB M55	6 W
01535471	RS378B P6 930 PSD-E WB M55	6 W
01535571	RS378B P6 940 PSD-E NB M55	6 W
01537771	RS378B P24 927 PSD-E MB M70	24 W
65358399	RS378B P24 930 PSD-E MB M70	24 W
01538171	RS378B P24 930 PSD-E WB M70	24 W

Order Code	Full Product Name	Power Consumption
01538271	RS378B P24 940 PSD-E NB M70	24 W
01538371	RS378B P24 940 PSD-E MB M70	24 W
01538471	RS378B P24 940 PSD-E WB M70	24 W
01721432	RS378B P24 927 PSU-E NB M70	24 W
65017999	RS378B P24 930 PSU-E NB M70	24 W
01721452	RS378B P24 940 PSU-E NB M70	24 W
01721462	RS378B P24 927 PSU-E MB M70	24 W
01721472	RS378B P24 930 PSU-E MB M70	24 W
01721482	RS378B P24 940 PSU-E MB M70	24 W
01721492	RS378B P24 927 PSU-E WB M70	24 W
65019399	RS378B P24 930 PSU-E WB M70	24 W
01721512	RS378B P24 940 PSU-E WB M70	24 W
01538571	RS378B P33 927 PSD-E NB M87	33 W
01538671	RS378B P33 927 PSD-E MB M87	33 W
01538871	RS378B P33 930 PSD-E NB M87	33 W
01539171	RS378B P33 940 PSD-E NB M87	33 W
65023099	RS378B P33 927 PSU-E NB M87	33 W
65026199	RS378B P33 930 PSU-E NB M87	33 W
65029299	RS378B P33 940 PSU-E NB M87	33 W
65027899	RS378B P33 930 PSU-E MB M87	33 W
65030899	RS378B P33 940 PSU-E MB M87	33 W
65028599	RS378B P33 930 PSU-E WB M87	33 W
65031599	RS378B P33 940 PSU-E WB M87	33 W
01539871	RS378B P42 930 PSD-E MB M102	42 W
01539971	RS378B P42 930 PSD-E WB M102	42 W
01540271	RS378B P42 940 PSD-E WB M102	42 W
01545571	RS378B P11 930 PSU-E WW S	11 W
01545671	RS378B P11 940 PSU-E WW S	11 W
01546471	RS378B P11 930 PSD-E WW S	11 W
01546571	RS378B P11 940 PSD-E WW S	11 W
01545971	RS378B P15 940 PSU-E WW S	15 W
01546771	RS378B P15 930 PSD-E WW S	15 W
01536771	RS378B P15 927 PSD-E NB M55	15 W
01536871	RS378B P15 927 PSD-E MB M55	15 W
01536971	RS378B P15 927 PSD-E WB M55	15 W
01537171	RS378B P15 930 PSD-E MB M55	15 W
01537271	RS378B P15 930 PSD-E WB M55	15 W

Order Code	Full Product Name	Power Consumption
01537371	RS378B P15 940 PSD-E NB M55	15 W
01537471	RS378B P15 940 PSD-E MB M55	15 W
01537571	RS378B P15 940 PSD-E WB M55	15 W
01540371	RS378B P15 927 PSR-E 1-10V NB M55	15 W
01540471	RS378B P15 927 PSR-E 1-10V MB M55	15 W
01540771	RS378B P15 930 PSR-E 1-10V MB M55	15 W
01540871	RS378B P15 930 PSR-E 1-10V WB M55	15 W
01541171	RS378B P15 940 PSR-E 1-10V WB M55	15 W
01532371	RS378B P6 927 PSU-E MB M43	6 W
01532471	RS378B P6 927 PSU-E WB M43	6 W
01532571	RS378B P6 930 PSU-E NB M43	6 W
01532671	RS378B P6 930 PSU-E MB M43	6 W
01532771	RS378B P6 930 PSU-E WB M43	6 W
01532871	RS378B P6 940 PSU-E NB M43	6 W
01532971	RS378B P6 940 PSU-E MB M43	6 W
01533071	RS378B P6 940 PSU-E WB M43	6 W
01533271	RS378B P6 927 PSR-E MB M43	6 W
01533571	RS378B P6 930 PSR-E MB M43	6 W
01533671	RS378B P6 930 PSR-E WB M43	6 W
01533771	RS378B P6 940 PSR-E NB M43	6 W
01534471	RS378B P6 930 PSD-E MB M43	6 W
01534571	RS378B P6 930 PSD-E WB M43	6 W
01534771	RS378B P6 940 PSD-E MB M43	6 W
01721252	RS378B P15 927 PSU-E NB M55	15 W
01721262	RS378B P15 930 PSU-E NB M55	15 W
01721272	RS378B P15 940 PSU-E NB M55	15 W
65006399	RS378B P15 927 PSU-E MB M55	15 W
01721292	RS378B P15 930 PSU-E MB M55	15 W
01721302	RS378B P15 940 PSU-E MB M55	15 W
65007099	RS378B P15 927 PSU-E WB M55	15 W
65010099	RS378B P15 930 PSU-E WB M55	15 W
65013199	RS378B P15 940 PSU-E WB M55	15 W
65069899	RS378B P15 927 PSR-E MB M55	15 W
65075999	RS378B P15 940 PSR-E MB M55	15 W
65073599	RS378B P15 930 PSR-E WB M55	15 W
65076699	RS378B P15 940 PSR-E WB M55	15 W

Controls and Dimming

Order Code	Full Product Name	Dimmable
01535871	RS378B P11 927 PSD-E NB M55	Yes
65337899	RS378B P11 927 PSD-E MB M55	Yes
01536071	RS378B P11 927 PSD-E WB M55	Yes
01536271	RS378B P11 930 PSD-E MB M55	Yes
01536371	RS378B P11 930 PSD-E WB M55	Yes
01536471	RS378B P11 940 PSD-E NB M55	Yes
01536571	RS378B P11 940 PSD-E MB M55	Yes
01536671	RS378B P11 940 PSD-E WB M55	Yes
01720892	RS378B P6 927 PSU-E NB M55	No
01720902	RS378B P6 930 PSU-E NB M55	No
01720912	RS378B P6 940 PSU-E NB M55	No

Order Code	Full Product Name	Dimmable
01720922	RS378B P6 927 PSU-E MB M55	No
01720932	RS378B P6 930 PSU-E MB M55	No
64994499	RS378B P6 940 PSU-E MB M55	No
64989099	RS378B P6 927 PSU-E WB M55	No
64992099	RS378B P6 930 PSU-E WB M55	No
64995199	RS378B P6 940 PSU-E WB M55	No
64996899	RS378B P11 927 PSU-E NB M55	No
64999999	RS378B P11 930 PSU-E NB M55	No
01721002	RS378B P11 940 PSU-E NB M55	No
01721012	RS378B P11 927 PSU-E MB M55	No
01721022	RS378B P11 930 PSU-E MB M55	No

Order Code	Full Product Name	Dimmable
65003299	RS378B P11 940 PSU-E MB M55	No
64998299	RS378B P11 927 PSU-E WB M55	No
65001899	RS378B P11 930 PSU-E WB M55	No
65004999	RS378B P11 940 PSU-E WB M55	No
01721072	RS378B P6 927 PSR-E NB M55	Yes
01721102	RS378B P6 927 PSR-E MB M55	Yes
01721112	RS378B P6 930 PSR-E MB M55	Yes
01721132	RS378B P6 927 PSR-E WB M55	Yes
01721172	RS378B P11 930 PSR-E NB M55	Yes
01721192	RS378B P11 927 PSR-E MB M55	Yes
65061299	RS378B P11 927 PSR-E WB M55	Yes
65064399	RS378B P11 930 PSR-E WB M55	Yes
01721622	RS378B P42 930 PSU-E NB M102	No
01721632	RS378B P42 940 PSU-E NB M102	No
01721642	RS378B P42 927 PSU-E MB M102	No
01721652	RS378B P42 930 PSU-E MB M102	No
01721662	RS378B P42 940 PSU-E MB M102	No
01721682	RS378B P42 930 PSU-E WB M102	No
01721692	RS378B P42 940 PSU-E WB M102	No
01534971	RS378B P6 927 PSD-E NB M55	Yes
01535071	RS378B P6 927 PSD-E MB M55	Yes
65329399	RS378B P6 927 PSD-E WB M55	Yes
01535371	RS378B P6 930 PSD-E MB M55	Yes
01535471	RS378B P6 930 PSD-E WB M55	Yes
01535571	RS378B P6 940 PSD-E NB M55	Yes
01537771	RS378B P24 927 PSD-E MB M70	Yes
65358399	RS378B P24 930 PSD-E MB M70	Yes
01538171	RS378B P24 930 PSD-E WB M70	Yes
01538271	RS378B P24 940 PSD-E NB M70	Yes
01538371	RS378B P24 940 PSD-E MB M70	Yes
01538471	RS378B P24 940 PSD-E WB M70	Yes
01721432	RS378B P24 927 PSU-E NB M70	No
65017999	RS378B P24 930 PSU-E NB M70	No
01721452	RS378B P24 940 PSU-E NB M70	No
01721462	RS378B P24 927 PSU-E MB M70	No
01721472	RS378B P24 930 PSU-E MB M70	No
01721482	RS378B P24 940 PSU-E MB M70	No
01721492	RS378B P24 927 PSU-E WB M70	No
65019399	RS378B P24 930 PSU-E WB M70	No
01721512	RS378B P24 940 PSU-E WB M70	No
01538571	RS378B P33 927 PSD-E NB M87	Yes
01538671	RS378B P33 927 PSD-E MB M87	Yes
01538871	RS378B P33 930 PSD-E NB M87	Yes
01539171	RS378B P33 940 PSD-E NB M87	Yes
65023099	RS378B P33 927 PSU-E NB M87	No
65026199	RS378B P33 930 PSU-E NB M87	No
65029299	RS378B P33 940 PSU-E NB M87	No
65027899	RS378B P33 930 PSU-E MB M87	No
65030899	RS378B P33 940 PSU-E MB M87	No
65028599	RS378B P33 930 PSU-E WB M87	No
65031599	RS378B P33 940 PSU-E WB M87	No

Order Code	Full Product Name	Dimmable
01539871	RS378B P42 930 PSD-E MB M102	Yes
01539971	RS378B P42 930 PSD-E WB M102	Yes
01540271	RS378B P42 940 PSD-E WB M102	Yes
01545571	RS378B P11 930 PSU-E WW S	No
01545671	RS378B P11 940 PSU-E WW S	No
01546471	RS378B P11 930 PSD-E WW S	Yes
01546571	RS378B P11 940 PSD-E WW S	Yes
01545971	RS378B P15 940 PSU-E WW S	No
01546771	RS378B P15 930 PSD-E WW S	Yes
01536771	RS378B P15 927 PSD-E NB M55	Yes
01536871	RS378B P15 927 PSD-E MB M55	Yes
01536971	RS378B P15 927 PSD-E WB M55	Yes
01537171	RS378B P15 930 PSD-E MB M55	Yes
01537271	RS378B P15 930 PSD-E WB M55	Yes
01537371	RS378B P15 940 PSD-E NB M55	Yes
01537471	RS378B P15 940 PSD-E MB M55	Yes
01537571	RS378B P15 940 PSD-E WB M55	Yes
01540371	RS378B P15 927 PSR-E 1-10V NB M55	Yes
01540471	RS378B P15 927 PSR-E 1-10V MB M55	Yes
01540771	RS378B P15 930 PSR-E 1-10V MB M55	Yes
01540871	RS378B P15 930 PSR-E 1-10V WB M55	Yes
01541171	RS378B P15 940 PSR-E 1-10V WB M55	Yes
01532371	RS378B P6 927 PSU-E MB M43	No
01532471	RS378B P6 927 PSU-E WB M43	No
01532571	RS378B P6 930 PSU-E NB M43	No
01532671	RS378B P6 930 PSU-E MB M43	No
01532771	RS378B P6 930 PSU-E WB M43	No
01532871	RS378B P6 940 PSU-E NB M43	No
01532971	RS378B P6 940 PSU-E MB M43	No
01533071	RS378B P6 940 PSU-E WB M43	No
01533271	RS378B P6 927 PSR-E MB M43	Yes
01533571	RS378B P6 930 PSR-E MB M43	Yes
01533671	RS378B P6 930 PSR-E WB M43	Yes
01533771	RS378B P6 940 PSR-E NB M43	Yes
01534471	RS378B P6 930 PSD-E MB M43	Yes
01534571	RS378B P6 930 PSD-E WB M43	Yes
01534771	RS378B P6 940 PSD-E MB M43	Yes
01721252	RS378B P15 927 PSU-E NB M55	No
01721262	RS378B P15 930 PSU-E NB M55	No
01721272	RS378B P15 940 PSU-E NB M55	No
65006399	RS378B P15 927 PSU-E MB M55	No
01721292	RS378B P15 930 PSU-E MB M55	No
01721302	RS378B P15 940 PSU-E MB M55	No
65007099	RS378B P15 927 PSU-E WB M55	No
65010099	RS378B P15 930 PSU-E WB M55	No
65013199	RS378B P15 940 PSU-E WB M55	No
65069899	RS378B P15 927 PSR-E MB M55	Yes
65075999	RS378B P15 940 PSR-E MB M55	Yes
65073599	RS378B P15 930 PSR-E WB M55	Yes
65076699	RS378B P15 940 PSR-E WB M55	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01535871	RS378B P11 927 PSD-E NB M55	-
65337899	RS378B P11 927 PSD-E MB M55	-
01536071	RS378B P11 927 PSD-E WB M55	-
01536271	RS378B P11 930 PSD-E MB M55	-
01536371	RS378B P11 930 PSD-E WB M55	-
01536471	RS378B P11 940 PSD-E NB M55	-
01536571	RS378B P11 940 PSD-E MB M55	-
01536671	RS378B P11 940 PSD-E WB M55	-
01720892	RS378B P6 927 PSU-E NB M55	SDCM<3
01720902	RS378B P6 930 PSU-E NB M55	SDCM<3
01720912	RS378B P6 940 PSU-E NB M55	SDCM<3
01720922	RS378B P6 927 PSU-E MB M55	SDCM<3
01720932	RS378B P6 930 PSU-E MB M55	SDCM<3
64994499	RS378B P6 940 PSU-E MB M55	SDCM<3
64989099	RS378B P6 927 PSU-E WB M55	SDCM<3
64992099	RS378B P6 930 PSU-E WB M55	SDCM<3
64995199	RS378B P6 940 PSU-E WB M55	SDCM<3
64996899	RS378B P11 927 PSU-E NB M55	SDCM<3
64999999	RS378B P11 930 PSU-E NB M55	SDCM<3
01721002	RS378B P11 940 PSU-E NB M55	SDCM<3
01721012	RS378B P11 927 PSU-E MB M55	SDCM<3
01721022	RS378B P11 930 PSU-E MB M55	SDCM<3
65003299	RS378B P11 940 PSU-E MB M55	SDCM<3
64998299	RS378B P11 927 PSU-E WB M55	SDCM<3
65001899	RS378B P11 930 PSU-E WB M55	SDCM<3
65004999	RS378B P11 940 PSU-E WB M55	SDCM<3
01721072	RS378B P6 927 PSR-E NB M55	SDCM<3
01721102	RS378B P6 927 PSR-E MB M55	SDCM<3
01721112	RS378B P6 930 PSR-E MB M55	SDCM<3
01721132	RS378B P6 927 PSR-E WB M55	SDCM<3
01721172	RS378B P11 930 PSR-E NB M55	SDCM<3
01721192	RS378B P11 927 PSR-E MB M55	SDCM<3
65061299	RS378B P11 927 PSR-E WB M55	SDCM<3
65064399	RS378B P11 930 PSR-E WB M55	SDCM<3
01721622	RS378B P42 930 PSU-E NB M102	SDCM<3
01721632	RS378B P42 940 PSU-E NB M102	SDCM<3
01721642	RS378B P42 927 PSU-E MB M102	SDCM<3
01721652	RS378B P42 930 PSU-E MB M102	SDCM<3
01721662	RS378B P42 940 PSU-E MB M102	SDCM<3
01721682	RS378B P42 930 PSU-E WB M102	SDCM<3
01721692	RS378B P42 940 PSU-E WB M102	SDCM<3
01534971	RS378B P6 927 PSD-E NB M55	-
01535071	RS378B P6 927 PSD-E MB M55	-
65329399	RS378B P6 927 PSD-E WB M55	-
01535371	RS378B P6 930 PSD-E MB M55	-
01535471	RS378B P6 930 PSD-E WB M55	-
01535571	RS378B P6 940 PSD-E NB M55	-
01537771	RS378B P24 927 PSD-E MB M70	-
65358399	RS378B P24 930 PSD-E MB M70	-
01538171	RS378B P24 930 PSD-E WB M70	-
01538271	RS378B P24 940 PSD-E NB M70	-
01538371	RS378B P24 940 PSD-E MB M70	-

Order Code	Full Product Name	Initial chromaticity
01538471	RS378B P24 940 PSD-E WB M70	-
01721432	RS378B P24 927 PSU-E NB M70	SDCM<3
65017999	RS378B P24 930 PSU-E NB M70	SDCM<3
01721452	RS378B P24 940 PSU-E NB M70	SDCM<3
01721462	RS378B P24 927 PSU-E MB M70	SDCM<3
01721472	RS378B P24 930 PSU-E MB M70	SDCM<3
01721482	RS378B P24 940 PSU-E MB M70	SDCM<3
01721492	RS378B P24 927 PSU-E WB M70	SDCM<3
65019399	RS378B P24 930 PSU-E WB M70	SDCM<3
01721512	RS378B P24 940 PSU-E WB M70	SDCM<3
01538571	RS378B P33 927 PSD-E NB M87	-
01538671	RS378B P33 927 PSD-E MB M87	-
01538871	RS378B P33 930 PSD-E NB M87	-
01539171	RS378B P33 940 PSD-E NB M87	-
65023099	RS378B P33 927 PSU-E NB M87	SDCM<3
65026199	RS378B P33 930 PSU-E NB M87	SDCM<3
65029299	RS378B P33 940 PSU-E NB M87	SDCM<3
65027899	RS378B P33 930 PSU-E MB M87	SDCM<3
65030899	RS378B P33 940 PSU-E MB M87	SDCM<3
65028599	RS378B P33 930 PSU-E WB M87	SDCM<3
65031599	RS378B P33 940 PSU-E WB M87	SDCM<3
01539871	RS378B P42 930 PSD-E MB M102	-
01539971	RS378B P42 930 PSD-E WB M102	-
01540271	RS378B P42 940 PSD-E WB M102	-
01545571	RS378B P11 930 PSU-E WW S	-
01545671	RS378B P11 940 PSU-E WW S	-
01546471	RS378B P11 930 PSD-E WW S	-
01546571	RS378B P11 940 PSD-E WW S	-
01545971	RS378B P15 940 PSU-E WW S	-
01546771	RS378B P15 930 PSD-E WW S	-
01536771	RS378B P15 927 PSD-E NB M55	-
01536871	RS378B P15 927 PSD-E MB M55	-
01536971	RS378B P15 927 PSD-E WB M55	-
01537171	RS378B P15 930 PSD-E MB M55	-
01537271	RS378B P15 930 PSD-E WB M55	-
01537371	RS378B P15 940 PSD-E NB M55	-
01537471	RS378B P15 940 PSD-E MB M55	-
01537571	RS378B P15 940 PSD-E WB M55	-
01540371	RS378B P15 927 PSR-E 1-10V NB M55	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-
01532371	RS378B P6 927 PSU-E MB M43	-
01532471	RS378B P6 927 PSU-E WB M43	-
01532571	RS378B P6 930 PSU-E NB M43	-
01532671	RS378B P6 930 PSU-E MB M43	-
01532771	RS378B P6 930 PSU-E WB M43	-
01532871	RS378B P6 940 PSU-E NB M43	-
01532971	RS378B P6 940 PSU-E MB M43	-
01533071	RS378B P6 940 PSU-E WB M43	-
01533271	RS378B P6 927 PSR-E MB M43	-

Order Code	Full Product Name	Initial chromaticity
01533571	RS378B P6 930 PSR-E MB M43	-
01533671	RS378B P6 930 PSR-E WB M43	-
01533771	RS378B P6 940 PSR-E NB M43	-
01534471	RS378B P6 930 PSD-E MB M43	-
01534571	RS378B P6 930 PSD-E WB M43	-
01534771	RS378B P6 940 PSD-E MB M43	-
01721252	RS378B P15 927 PSU-E NB M55	SDCM<3
01721262	RS378B P15 930 PSU-E NB M55	SDCM<3
01721272	RS378B P15 940 PSU-E NB M55	SDCM<3
65006399	RS378B P15 927 PSU-E MB M55	SDCM<3

Order Code	Full Product Name	Initial chromaticity
01721292	RS378B P15 930 PSU-E MB M55	SDCM<3
01721302	RS378B P15 940 PSU-E MB M55	SDCM<3
65007099	RS378B P15 927 PSU-E WB M55	SDCM<3
65010099	RS378B P15 930 PSU-E WB M55	SDCM<3
65013199	RS378B P15 940 PSU-E WB M55	SDCM<3
65069899	RS378B P15 927 PSR-E MB M55	SDCM<3
65075999	RS378B P15 940 PSR-E MB M55	SDCM<3
65073599	RS378B P15 930 PSR-E WB M55	SDCM<3
65076699	RS378B P15 940 PSR-E WB M55	SDCM<3

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50
01535871	RS378B P11 927 PSD-E NB M55	-
65337899	RS378B P11 927 PSD-E MB M55	-
01536071	RS378B P11 927 PSD-E WB M55	-
01536271	RS378B P11 930 PSD-E MB M55	-
01536371	RS378B P11 930 PSD-E WB M55	-
01536471	RS378B P11 940 PSD-E NB M55	-
01536571	RS378B P11 940 PSD-E MB M55	-
01536671	RS378B P11 940 PSD-E WB M55	-
01720892	RS378B P6 927 PSU-E NB M55	50,000 hour(s)
01720902	RS378B P6 930 PSU-E NB M55	50,000 hour(s)
01720912	RS378B P6 940 PSU-E NB M55	50,000 hour(s)
01720922	RS378B P6 927 PSU-E MB M55	50,000 hour(s)
01720932	RS378B P6 930 PSU-E MB M55	50,000 hour(s)
64994499	RS378B P6 940 PSU-E MB M55	50,000 hour(s)
64989099	RS378B P6 927 PSU-E WB M55	50,000 hour(s)
64992099	RS378B P6 930 PSU-E WB M55	50,000 hour(s)
64995199	RS378B P6 940 PSU-E WB M55	50,000 hour(s)
64996899	RS378B P11 927 PSU-E NB M55	50,000 hour(s)
64999999	RS378B P11 930 PSU-E NB M55	50,000 hour(s)
01721002	RS378B P11 940 PSU-E NB M55	50,000 hour(s)
01721012	RS378B P11 927 PSU-E MB M55	50,000 hour(s)
01721022	RS378B P11 930 PSU-E MB M55	50,000 hour(s)
65003299	RS378B P11 940 PSU-E MB M55	50,000 hour(s)
64998299	RS378B P11 927 PSU-E WB M55	50,000 hour(s)
65001899	RS378B P11 930 PSU-E WB M55	50,000 hour(s)
65004999	RS378B P11 940 PSU-E WB M55	50,000 hour(s)
01721072	RS378B P6 927 PSR-E NB M55	50,000 hour(s)
01721102	RS378B P6 927 PSR-E MB M55	50,000 hour(s)
01721112	RS378B P6 930 PSR-E MB M55	50,000 hour(s)
01721132	RS378B P6 927 PSR-E WB M55	50,000 hour(s)
01721172	RS378B P11 930 PSR-E NB M55	50,000 hour(s)
01721192	RS378B P11 927 PSR-E MB M55	50,000 hour(s)
65061299	RS378B P11 927 PSR-E WB M55	50,000 hour(s)
65064399	RS378B P11 930 PSR-E WB M55	50,000 hour(s)
01721622	RS378B P42 930 PSU-E NB M102	50,000 hour(s)
01721632	RS378B P42 940 PSU-E NB M102	50,000 hour(s)
01721642	RS378B P42 927 PSU-E MB M102	50,000 hour(s)
01721652	RS378B P42 930 PSU-E MB M102	50,000 hour(s)

Order Code	Full Product Name	Median useful life L80B50
01721662	RS378B P42 940 PSU-E MB M102	50,000 hour(s)
01721682	RS378B P42 930 PSU-E WB M102	50,000 hour(s)
01721692	RS378B P42 940 PSU-E WB M102	50,000 hour(s)
01534971	RS378B P6 927 PSD-E NB M55	-
01535071	RS378B P6 927 PSD-E MB M55	-
65329399	RS378B P6 927 PSD-E WB M55	-
01535371	RS378B P6 930 PSD-E MB M55	-
01535471	RS378B P6 930 PSD-E WB M55	-
01535571	RS378B P6 940 PSD-E NB M55	-
01537771	RS378B P24 927 PSD-E MB M70	-
65358399	RS378B P24 930 PSD-E MB M70	-
01538171	RS378B P24 930 PSD-E WB M70	-
01538271	RS378B P24 940 PSD-E NB M70	-
01538371	RS378B P24 940 PSD-E MB M70	-
01538471	RS378B P24 940 PSD-E WB M70	-
01721432	RS378B P24 927 PSU-E NB M70	50,000 hour(s)
65017999	RS378B P24 930 PSU-E NB M70	50,000 hour(s)
01721452	RS378B P24 940 PSU-E NB M70	50,000 hour(s)
01721462	RS378B P24 927 PSU-E MB M70	50,000 hour(s)
01721472	RS378B P24 930 PSU-E MB M70	50,000 hour(s)
01721482	RS378B P24 940 PSU-E MB M70	50,000 hour(s)
01721492	RS378B P24 927 PSU-E WB M70	50,000 hour(s)
65019399	RS378B P24 930 PSU-E WB M70	50,000 hour(s)
01721512	RS378B P24 940 PSU-E WB M70	50,000 hour(s)
01538571	RS378B P33 927 PSD-E NB M87	-
01538671	RS378B P33 927 PSD-E MB M87	-
01538871	RS378B P33 930 PSD-E NB M87	-
01539171	RS378B P33 940 PSD-E NB M87	-
65023099	RS378B P33 927 PSU-E NB M87	50,000 hour(s)
65026199	RS378B P33 930 PSU-E NB M87	50,000 hour(s)
65029299	RS378B P33 940 PSU-E NB M87	50,000 hour(s)
65027899	RS378B P33 930 PSU-E MB M87	50,000 hour(s)
65030899	RS378B P33 940 PSU-E MB M87	50,000 hour(s)
65028599	RS378B P33 930 PSU-E WB M87	50,000 hour(s)
65031599	RS378B P33 940 PSU-E WB M87	50,000 hour(s)
01539871	RS378B P42 930 PSD-E MB M102	-
01539971	RS378B P42 930 PSD-E WB M102	-
01540271	RS378B P42 940 PSD-E WB M102	-

Order Code	Full Product Name	Median useful life L80B50
01545571	RS378B P11 930 PSU-E WW S	-
01545671	RS378B P11 940 PSU-E WW S	-
01546471	RS378B P11 930 PSD-E WW S	-
01546571	RS378B P11 940 PSD-E WW S	-
01545971	RS378B P15 940 PSU-E WW S	-
01546771	RS378B P15 930 PSD-E WW S	-
01536771	RS378B P15 927 PSD-E NB M55	-
01536871	RS378B P15 927 PSD-E MB M55	-
01536971	RS378B P15 927 PSD-E WB M55	-
01537171	RS378B P15 930 PSD-E MB M55	-
01537271	RS378B P15 930 PSD-E WB M55	-
01537371	RS378B P15 940 PSD-E NB M55	-
01537471	RS378B P15 940 PSD-E MB M55	-
01537571	RS378B P15 940 PSD-E WB M55	-
01540371	RS378B P15 927 PSR-E 1-10V NB M55	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-
01532371	RS378B P6 927 PSU-E MB M43	-
01532471	RS378B P6 927 PSU-E WB M43	-
01532571	RS378B P6 930 PSU-E NB M43	-
01532671	RS378B P6 930 PSU-E MB M43	-
01532771	RS378B P6 930 PSU-E WB M43	-

Order Code	Full Product Name	Median useful life L80B50
01532871	RS378B P6 940 PSU-E NB M43	-
01532971	RS378B P6 940 PSU-E MB M43	-
01533071	RS378B P6 940 PSU-E WB M43	-
01533271	RS378B P6 927 PSR-E MB M43	-
01533571	RS378B P6 930 PSR-E MB M43	-
01533671	RS378B P6 930 PSR-E WB M43	-
01533771	RS378B P6 940 PSR-E NB M43	-
01534471	RS378B P6 930 PSD-E MB M43	-
01534571	RS378B P6 930 PSD-E WB M43	-
01534771	RS378B P6 940 PSD-E MB M43	-
01721252	RS378B P15 927 PSU-E NB M55	50,000 hour(s)
01721262	RS378B P15 930 PSU-E NB M55	50,000 hour(s)
01721272	RS378B P15 940 PSU-E NB M55	50,000 hour(s)
65006399	RS378B P15 927 PSU-E MB M55	50,000 hour(s)
01721292	RS378B P15 930 PSU-E MB M55	50,000 hour(s)
01721302	RS378B P15 940 PSU-E MB M55	50,000 hour(s)
65007099	RS378B P15 927 PSU-E WB M55	50,000 hour(s)
65010099	RS378B P15 930 PSU-E WB M55	50,000 hour(s)
65013199	RS378B P15 940 PSU-E WB M55	50,000 hour(s)
65069899	RS378B P15 927 PSR-E MB M55	50,000 hour(s)
65075999	RS378B P15 940 PSR-E MB M55	50,000 hour(s)
65073599	RS378B P15 930 PSR-E WB M55	50,000 hour(s)
65076699	RS378B P15 940 PSR-E WB M55	50,000 hour(s)

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
01535871	RS378B P11 927 PSD-E NB M55	-	-
65337899	RS378B P11 927 PSD-E MB M55	-	-
01536071	RS378B P11 927 PSD-E WB M55	-	-
01536271	RS378B P11 930 PSD-E MB M55	-	-
01536371	RS378B P11 930 PSD-E WB M55	-	-
01536471	RS378B P11 940 PSD-E NB M55	-	-
01536571	RS378B P11 940 PSD-E MB M55	-	-
01536671	RS378B P11 940 PSD-E WB M55	-	-
01720892	RS378B P6 927 PSU-E NB M55	Not applicable	No
01720902	RS378B P6 930 PSU-E NB M55	Not applicable	No
01720912	RS378B P6 940 PSU-E NB M55	Not applicable	No
01720922	RS378B P6 927 PSU-E MB M55	Not applicable	No
01720932	RS378B P6 930 PSU-E MB M55	Not applicable	No
64994499	RS378B P6 940 PSU-E MB M55	Not applicable	No
64989099	RS378B P6 927 PSU-E WB M55	Not applicable	No
64992099	RS378B P6 930 PSU-E WB M55	Not applicable	No
64995199	RS378B P6 940 PSU-E WB M55	Not applicable	No
64996899	RS378B P11 927 PSU-E NB M55	Not applicable	No
64999999	RS378B P11 930 PSU-E NB M55	Not applicable	No
01721002	RS378B P11 940 PSU-E NB M55	Not applicable	No
01721012	RS378B P11 927 PSU-E MB M55	Not applicable	No
01721022	RS378B P11 930 PSU-E MB M55	Not applicable	No

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
65003299	RS378B P11 940 PSU-E MB M55	Not applicable	No
64998299	RS378B P11 927 PSU-E WB M55	Not applicable	No
65001899	RS378B P11 930 PSU-E WB M55	Not applicable	No
65004999	RS378B P11 940 PSU-E WB M55	Not applicable	No
01721072	RS378B P6 927 PSR-E NB M55	10%	No
01721102	RS378B P6 927 PSR-E MB M55	10%	No
01721112	RS378B P6 930 PSR-E MB M55	10%	No
01721132	RS378B P6 927 PSR-E WB M55	10%	No
01721172	RS378B P11 930 PSR-E NB M55	10%	No
01721192	RS378B P11 927 PSR-E MB M55	10%	No
65061299	RS378B P11 927 PSR-E WB M55	10%	No
65064399	RS378B P11 930 PSR-E WB M55	10%	No
01721622	RS378B P42 930 PSU-E NB M102	Not applicable	No
01721632	RS378B P42 940 PSU-E NB M102	Not applicable	No
01721642	RS378B P42 927 PSU-E MB M102	Not applicable	No
01721652	RS378B P42 930 PSU-E MB M102	Not applicable	No
01721662	RS378B P42 940 PSU-E MB M102	Not applicable	No
01721682	RS378B P42 930 PSU-E WB M102	Not applicable	No
01721692	RS378B P42 940 PSU-E WB M102	Not applicable	No
01534971	RS378B P6 927 PSD-E NB M55	-	-
01535071	RS378B P6 927 PSD-E MB M55	-	-
65329399	RS378B P6 927 PSD-E WB M55	-	-

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
01535371	RS378B P6 930 PSD-E MB M55	-	-
01535471	RS378B P6 930 PSD-E WB M55	-	-
01535571	RS378B P6 940 PSD-E NB M55	-	-
01537771	RS378B P24 927 PSD-E MB M70	-	-
65358399	RS378B P24 930 PSD-E MB M70	-	-
01538171	RS378B P24 930 PSD-E WB M70	-	-
01538271	RS378B P24 940 PSD-E NB M70	-	-
01538371	RS378B P24 940 PSD-E MB M70	-	-
01538471	RS378B P24 940 PSD-E WB M70	-	-
01721432	RS378B P24 927 PSU-E NB M70	Not applicable	No
65017999	RS378B P24 930 PSU-E NB M70	Not applicable	No
01721452	RS378B P24 940 PSU-E NB M70	Not applicable	No
01721462	RS378B P24 927 PSU-E MB M70	Not applicable	No
01721472	RS378B P24 930 PSU-E MB M70	Not applicable	No
01721482	RS378B P24 940 PSU-E MB M70	Not applicable	No
01721492	RS378B P24 927 PSU-E WB M70	Not applicable	No
65019399	RS378B P24 930 PSU-E WB M70	Not applicable	No
01721512	RS378B P24 940 PSU-E WB M70	Not applicable	No
01538571	RS378B P33 927 PSD-E NB M87	-	-
01538671	RS378B P33 927 PSD-E MB M87	-	-
01538871	RS378B P33 930 PSD-E NB M87	-	-
01539171	RS378B P33 940 PSD-E NB M87	-	-
65023099	RS378B P33 927 PSU-E NB M87	Not applicable	No
65026199	RS378B P33 930 PSU-E NB M87	Not applicable	No
65029299	RS378B P33 940 PSU-E NB M87	Not applicable	No
65027899	RS378B P33 930 PSU-E MB M87	Not applicable	No
65030899	RS378B P33 940 PSU-E MB M87	Not applicable	No
65028599	RS378B P33 930 PSU-E WB M87	Not applicable	No
65031599	RS378B P33 940 PSU-E WB M87	Not applicable	No
01539871	RS378B P42 930 PSD-E MB M102	-	-
01539971	RS378B P42 930 PSD-E WB M102	-	-
01540271	RS378B P42 940 PSD-E WB M102	-	-
01545571	RS378B P11 930 PSU-E WW S	-	-
01545671	RS378B P11 940 PSU-E WW S	-	-
01546471	RS378B P11 930 PSD-E WW S	-	-
01546571	RS378B P11 940 PSD-E WW S	-	-
01545971	RS378B P15 940 PSU-E WW S	-	-
01546771	RS378B P15 930 PSD-E WW S	-	-
01536771	RS378B P15 927 PSD-E NB M55	-	-
01536871	RS378B P15 927 PSD-E MB M55	-	-

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
01536971	RS378B P15 927 PSD-E WB M55	-	-
01537171	RS378B P15 930 PSD-E MB M55	-	-
01537271	RS378B P15 930 PSD-E WB M55	-	-
01537371	RS378B P15 940 PSD-E NB M55	-	-
01537471	RS378B P15 940 PSD-E MB M55	-	-
01537571	RS378B P15 940 PSD-E WB M55	-	-
01540371	RS378B P15 927 PSR-E 1-10V NB M55	-	-
01540471	RS378B P15 927 PSR-E 1-10V MB M55	-	-
01540771	RS378B P15 930 PSR-E 1-10V MB M55	-	-
01540871	RS378B P15 930 PSR-E 1-10V WB M55	-	-
01541171	RS378B P15 940 PSR-E 1-10V WB M55	-	-
01532371	RS378B P6 927 PSU-E MB M43	-	-
01532471	RS378B P6 927 PSU-E WB M43	-	-
01532571	RS378B P6 930 PSU-E NB M43	-	-
01532671	RS378B P6 930 PSU-E MB M43	-	-
01532771	RS378B P6 930 PSU-E WB M43	-	-
01532871	RS378B P6 940 PSU-E NB M43	-	-
01532971	RS378B P6 940 PSU-E MB M43	-	-
01533071	RS378B P6 940 PSU-E WB M43	-	-
01533271	RS378B P6 927 PSR-E MB M43	-	-
01533571	RS378B P6 930 PSR-E MB M43	-	-
01533671	RS378B P6 930 PSR-E WB M43	-	-
01533771	RS378B P6 940 PSR-E NB M43	-	-
01534471	RS378B P6 930 PSD-E MB M43	-	-
01534571	RS378B P6 930 PSD-E WB M43	-	-
01534771	RS378B P6 940 PSD-E MB M43	-	-
01721252	RS378B P15 927 PSU-E NB M55	Not applicable	No
01721262	RS378B P15 930 PSU-E NB M55	Not applicable	No
01721272	RS378B P15 940 PSU-E NB M55	Not applicable	No
65006399	RS378B P15 927 PSU-E MB M55	Not applicable	No
01721292	RS378B P15 930 PSU-E MB M55	Not applicable	No
01721302	RS378B P15 940 PSU-E MB M55	Not applicable	No
65007099	RS378B P15 927 PSU-E WB M55	Not applicable	No
65010099	RS378B P15 930 PSU-E WB M55	Not applicable	No
65013199	RS378B P15 940 PSU-E WB M55	Not applicable	No
65069899	RS378B P15 927 PSR-E MB M55	10%	No
65075999	RS378B P15 940 PSR-E MB M55	10%	No
65073599	RS378B P15 930 PSR-E WB M55	10%	No
65076699	RS378B P15 940 PSR-E WB M55	10%	No

