



Reliable, Energy-saving LED Floodlight

Essential SmartBright G3 LED Floodlight

The Essential SmartBright G3 LED floodlight comes with a compact and sturdy design. Its light weight with robust die-cast aluminium housing and corrosion-proof coating is suitable for general outdoor use. More efficient than the last generation, achieves more energy-savings.

Benefits

- Idea replacement for conventional floodlight
- Safe product and reliable quality

Features

- 1 CCT: 4,000 K
- Power: 10 W, 20 W, 30 W, 50 W and 70 W
- more than 85 lm/w efficacy
- 20-Khr life

Application

- Amenity
- Security
- Landscaping
- Billboard
- Architectural lighting

Essential SmartBright G3 LED Floodlight

Versions




Product details



Essential SmartBright G3 LED
Floodlight 3



Essential SmartBright G3 LED
Floodlight



Essential SmartBright G3 LED
Floodlight 2

Essential SmartBright G3 LED Floodlight

Approval and Application

Mech. impact protection code	IK06
Surge protection (common/differential)	Surge protection level up to 2 kV

Controls and Dimming

Dimmable	No
----------	----

General Information

CE mark	CE mark
Light source colour	840 neutral white
Optical cover/lens type	GB
Driver included	Yes
Flammability mark	F
Light source replaceable	No
Optic type	Symmetrical wide beam

Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature	4000 K
Init. Colour rendering index	>80

Light Technical

Standard tilt angle post-top	-
------------------------------	---

Mechanical and Housing

Colour	Black
--------	-------

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial luminous flux
911401736512	BVP150 LED8/NW 220-240V 10W SWB SAA	850 lm
911401736542	BVP150 LED17/NW 220-240V 20W SWB SAA	1700 lm
911401736572	BVP150 LED25/NW 220-240V 30W SWB SAA	2550 lm

