



Affordability and energy savings - all in one lamp

CorePro LED PL 4pin 2pin

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit CFL-ni is a great LED solution suitable for replacing both 2-pin and 4-pin CFL fluorescent lamps, using an existing ballast. Both vertical and horizontal options are available with the horizontal version having a rotatable end cap to ensure the light is correctly aimed.

Benefits

- Offers lowest cost of installation and easiest upgrade fluorescent CFL's to LED technology
- Dimmable product available for additional savings
- Reliable performance - color and lumen maintenance with excellent lighting uniformity

Features

- Average life rating of 50,000 hours with unmatched ballast compatibility
- Shatter-resistant polycarbonate construction
- Philips proprietary safety features
- DLC, NSF and RoHS listed
- Conventional form factor to fit into existing luminaires

Application


- Office & Industrial
- Residential & Retail
- Hospitality & Healthcare

CorePro LED PL 4pin 2pin

Versions



G24q/GX24q



G24q/GX24q



LEDtube GX23



LEDtube GX23-2



LEDtube GX23-2




LEDtube G24Q



LEDtube G24Q




Dimensional drawing



Product	D1	D2	A1	A2	A3
12PLC/T	24.3	28.4	128.8	148 mm	163.6
LED/32H/840/IF/4P/DIM	mm	mm	mm		mm
1PK 10/1					
12PLC/T	24.3	28.4	128.8	148 mm	163.6
LED/32H/835/IF/4P/DIM	mm	mm	mm		mm
1PK 10/1					
8.5PL-C/T LED/26H-3000	24.3	28.4	128.3	147.5	163.1 mm
IF 4P 10/1	mm	mm	mm	mm	
8.5PL-C/T LED/26H-2700 IF	24.3	28.4	128.3	147.5	163.1 mm
4P 10/1	mm	mm	mm	mm	
8.5PL-C/T LED/26H-3500 IF	24.3	28.4	128.3	147.5	163.1 mm
4P 10/1	mm	mm	mm	mm	
8.5PL-C/T LED/26H-4000	24.3	28.4	128.3	147.5	163.1 mm
IF 4P 10/1	mm	mm	mm	mm	
12PLC/T	24.3	28.4	128.8	148 mm	163.6
LED/32H/830/IF/4P/DIM	mm	mm	mm		mm
1PK 10/1					
12PLC/T	24.3	28.4	128.8	148 mm	163.6
LED/32H/827/IF/4P/DIM	mm	mm	mm		mm
1PK 10/1					

CorePro LED PL 4pin 2pin

Dimensional drawing






Product	D1	D2	A1	A2	A3
12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-3500 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-4000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-2700 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Product	D	D1	A1	A2	A3
5.5PL-C/LED/13H/827/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/840/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/830/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/835/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Product	D	A1	A2	A3
5.5PL-C/LED/13V/830/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/840/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/827/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/835/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

CorePro LED PL 4pin 2pin

Dimensional drawing



Product	D	D1	A1	A2	A3
5PL-C/LED/13H/830/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/840/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/827/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/835/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Product	D	A1	A2	A3
5PL-C/LED/13V/827/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/830/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/840/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/835/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

Product	D	D1	A1	A2	A3
5PL-S/LED/13H/827/IF5/P/2P 20/1	31.1 mm	15.8 mm	108 mm	144 mm	166 mm
5PL-S/LED/13H/840/IF5/P/2P 20/1	31.1 mm	15.8 mm	108 mm	144 mm	166 mm
5PL-S/LED/13H/835/IF5/P/2P 20/1	31.1 mm	15.8 mm	108 mm	144 mm	166 mm
5PL-S/LED/13H/830/IF5/P/2P 20/1	31.1 mm	15.8 mm	108 mm	144 mm	166 mm

CorePro LED PL 4pin 2pin

Operating and Electrical	
Starting Time (Nom)	0.5 s
General Information	
Nominal Lifetime (Nom)	50000 h
Rated Lifetime (Hours)	50000 h
Switching Cycle	50000X
Light Technical	
Color Rendering Index (Nom)	82
Llmf At End Of Nominal Lifetime (Nom)	70 %
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	Yes
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	Yes
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	Yes
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	Yes
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	Yes
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	Yes
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	Yes
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	Yes
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	Yes
458414	10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1	Yes
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	Yes
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	Yes
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	Yes
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	Yes
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	Yes
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	Yes
529511	5PL-S/LED/13H/827/IF5/P/2P 20/1	No
529560	5PL-S/LED/13H/830/IF5/P/2P 20/1	No
529578	5PL-S/LED/13H/835/IF5/P/2P 20/1	No
529586	5PL-S/LED/13H/840/IF5/P/2P 20/1	No
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	No
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	No
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	No
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	No
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	No
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	No
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	No
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	No
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	Yes
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	Yes
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	Yes
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	Yes
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	Yes
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	Yes
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	Yes
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	Yes

Operating and Electrical

Order		Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
Code	Full Product Name			
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	8.5 W

Order		Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
Code	Full Product Name			
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W

CorePro LED PL 4pin 2pin

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
458414	10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	20000-100000 Hz	120 V	10.5 W
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
529511	5PL- S/LED/13H/827/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
529560	5PL- S/LED/13H/830/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
529578	5PL- S/LED/13H/835/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
529586	5PL- S/LED/13H/840/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532309	5PL- C/LED/13H/827/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532317	5PL- C/LED/13H/830/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W

General Information

Order Code	Full Product Name	Cap-Base
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	G24Q/GX24Q
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	G24Q/GX24Q

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
532333	5PL- C/LED/13H/835/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532341	5PL- C/LED/13H/840/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532358	5PL- C/LED/13V/827/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532366	5PL- C/LED/13V/830/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532374	5PL- C/LED/13V/835/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532382	5PL- C/LED/13V/840/IF5/P/2P 20/1	50 to 60 Hz	120-277 V	5 W
532390	5.5PL- C/LED/13H/827/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532408	5.5PL- C/LED/13H/830/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532416	5.5PL- C/LED/13H/835/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532424	5.5PL- C/LED/13H/840/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532432	5.5PL- C/LED/13V/827/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532440	5.5PL- C/LED/13V/830/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532457	5.5PL- C/LED/13V/835/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W
532465	5.5PL- C/LED/13V/840/IF5/P/4P 20/1	25000-100000 Hz	14-60 V	5.5 W

CorePro LED PL 4pin 2pin

Order Code	Full Product Name	Cap-Base
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	G24Q/GX24Q
458414	10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1	G24Q/GX24Q
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	G24Q/GX24Q
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	G24Q/GX24Q
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	G24Q/GX24Q
529511	5PL-S/LED/13H/827/IF5/P/2P 20/1	GX23
529560	5PL-S/LED/13H/830/IF5/P/2P 20/1	GX23
529578	5PL-S/LED/13H/835/IF5/P/2P 20/1	GX23
529586	5PL-S/LED/13H/840/IF5/P/2P 20/1	GX23

Order Code	Full Product Name	Cap-Base
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	GX23-2
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	GX23-2
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	GX23-2
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	GX23-2
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	GX23-2
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	GX23-2
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	GX23-2
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	GX23-2
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	G24Q
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	G24Q
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	G24Q
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	G24Q
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	G24Q
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	G24Q
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	G24Q
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	G24Q

Light Technical (1/2)

			Correlated		
Order		Beam	Color	Color	
Code	Full Product Name	Angle (Nom)	Code	Temperature (Nom)	Luminous Flux (Nom)
458364	8.5PL-C/T LED/ 26H-2700 IF 4P 1PK 10/1	-	827	2700 K	850 lm
458372	8.5PL-C/T LED/ 26H-3000 IF 4P 1PK 10/1	-	830	3000 K	900 lm
458380	8.5PL-C/T LED/ 26H-3500 IF 4P 1PK 10/1	-	835	3500 K	900 lm
458398	8.5PL-C/T LED/ 26H-4000 IF 4P 1PK 10/1	-	841	4000 K	950 lm
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	-	827	2700 K	1300 lm
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	-	830	3000 K	1350 lm
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	-	835	3500 K	1400 lm
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	-	841	4000 K	1450 lm
458406	10.5PL-C/T LED/ 26V-2700 IF 4P 1PK 10/1	-	827	2700 K	1200 lm
458414	10.5PL-C/T LED/ 26V-3000 IF 4P 1PK 10/1	-	830	3000 K	1200 lm
458422	10.5PL-C/T LED/ 26V-3500 IF 4P 1PK 10/1	-	835	3500 K	1200 lm
458430	10.5PL-C/T LED/ 26V-4000 IF 4P 1PK 10/1	-	841	4000 K	1300 lm

Order Code	Full Product Name	Beam	Correlated		
		Angle (Nom)	Color Code	Color Temperature (Nom)	Luminous Flux (Nom)
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	-	827	2700 K	1350 lm
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	-	830	3000 K	1400 lm
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	-	835	3500 K	1450 lm
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	-	841	4000 K	1500 lm
529511	5PL- S/LED/13H/827/IF5/P/2P 20/1	120 °	827	2700 K	520 lm
529560	5PL- S/LED/13H/830/IF5/P/2 P 20/1	120 °	830	3000 K	540 lm
529578	5PL- S/LED/13H/835/IF5/P/2 P 20/1	120 °	835	3500 K	560 lm
529586	5PL- S/LED/13H/840/IF5/P/2 P 20/1	120 °	841	4000 K	580 lm
532309	5PL- C/LED/13H/827/IF5/P/2 P 20/1	150 °	827	2700 K	520 lm

CorePro LED PL 4pin 2pin

Order Code	Full Product Name	Beam Angle	Correlated Color		Luminous Flux (Nom)
		(Nom)	Color Code	Temperature (Nom)	
532317	5PL- C/LED/13H/830/IF5/P/2 P 20/1	150 °	830	3000 K	550 lm
532333	5PL- C/LED/13H/835/IF5/P/2 P 20/1	150 °	835	3500 K	550 lm
532341	5PL- C/LED/13H/840/IF5/P/2 P 20/1	150 °	841	4000 K	580 lm
532358	5PL- C/LED/13V/827/IF5/P/2P 20/1	150 °	827	2700 K	520 lm
532366	5PL- C/LED/13V/830/IF5/P/2 P 20/1	150 °	830	3000 K	550 lm
532374	5PL- C/LED/13V/835/IF5/P/2P 20/1	150 °	835	3500 K	550 lm
532382	5PL- C/LED/13V/840/IF5/P/2 P 20/1	150 °	841	4000 K	580 lm
532390	5.5PL- C/LED/13H/827/IF5/P/4 P 20/1	150 °	827	2700 K	520 lm

Order Code	Full Product Name	Beam Angle	Correlated Color		Luminous Flux (Nom)
		(Nom)	Color Code	Temperature (Nom)	
532408	5.5PL- C/LED/13H/830/IF5/P/4 P 20/1	150 °	830	3000 K	550 lm
532416	5.5PL- C/LED/13H/835/IF5/P/4 P 20/1	150 °	835	3500 K	550 lm
532424	5.5PL- C/LED/13H/840/IF5/P/4 P 20/1	150 °	841	4000 K	580 lm
532432	5.5PL- C/LED/13V/827/IF5/P/4P 20/1	150 °	827	2700 K	520 lm
532440	5.5PL- C/LED/13V/830/IF5/P/4 P 20/1	150 °	830	3000 K	550 lm
532457	5.5PL- C/LED/13V/835/IF5/P/4 P 20/1	150 °	835	3500 K	550 lm
532465	5.5PL- C/LED/13V/840/IF5/P/4 P 20/1	150 °	841	4000 K	580 lm



Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)	Rated Beam
			Angle
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	850 lm	-
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	900 lm	-
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	900 lm	-
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	950 lm	-
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	1300 lm	-
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	1350 lm	-
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	1400 lm	-
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	1450 lm	-
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	1200 lm	-
458414	10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1	1200 lm	-
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	1200 lm	-
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	1300 lm	-
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	1350 lm	-
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	1400 lm	-
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	1450 lm	-
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	1500 lm	-
529511	5PL-S/LED/13H/827/IF5/P/2P 20/1	520 lm	120 °
529560	5PL-S/LED/13H/830/IF5/P/2P 20/1	540 lm	120 °

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)	Rated Beam
			Angle
529578	5PL-S/LED/13H/835/IF5/P/2P 20/1	560 lm	120 °
529586	5PL-S/LED/13H/840/IF5/P/2P 20/1	580 lm	120 °
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	520 lm	150 °
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	550 lm	150 °
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	550 lm	150 °
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	580 lm	150 °
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	520 lm	150 °
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	550 lm	150 °
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	550 lm	150 °
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	580 lm	150 °
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	520 lm	150 °
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	550 lm	150 °
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	550 lm	150 °
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	580 lm	150 °
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	520 lm	150 °
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	550 lm	150 °
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	550 lm	150 °
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	580 lm	150 °

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
458364	8.5PL-C/T LED/26H-2700 IF 4P 1PK 10/1	60 °C
458372	8.5PL-C/T LED/26H-3000 IF 4P 1PK 10/1	60 °C
458380	8.5PL-C/T LED/26H-3500 IF 4P 1PK 10/1	60 °C
458398	8.5PL-C/T LED/26H-4000 IF 4P 1PK 10/1	60 °C
476069	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	-
476077	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	-
476085	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	-
476093	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	-
458406	10.5PL-C/T LED/26V-2700 IF 4P 1PK 10/1	60 °C
458414	10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1	60 °C
458422	10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1	60 °C
458430	10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1	60 °C
476101	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	-
476119	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	-
476127	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	-
476135	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	-
529511	5PL-S/LED/13H/827/IF5/P/2P 20/1	75 °C
529560	5PL-S/LED/13H/830/IF5/P/2P 20/1	75 °C
529578	5PL-S/LED/13H/835/IF5/P/2P 20/1	75 °C
529586	5PL-S/LED/13H/840/IF5/P/2P 20/1	75 °C
532309	5PL-C/LED/13H/827/IF5/P/2P 20/1	70 °C
532317	5PL-C/LED/13H/830/IF5/P/2P 20/1	70 °C
532333	5PL-C/LED/13H/835/IF5/P/2P 20/1	70 °C
532341	5PL-C/LED/13H/840/IF5/P/2P 20/1	70 °C
532358	5PL-C/LED/13V/827/IF5/P/2P 20/1	70 °C
532366	5PL-C/LED/13V/830/IF5/P/2P 20/1	70 °C
532374	5PL-C/LED/13V/835/IF5/P/2P 20/1	70 °C
532382	5PL-C/LED/13V/840/IF5/P/2P 20/1	70 °C
532390	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	75 °C
532408	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	75 °C
532416	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	75 °C
532424	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	75 °C
532432	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	70 °C
532440	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	70 °C
532457	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	70 °C
532465	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	70 °C



CorePro LED PL 4pin 2pin

