



Affordability and energy savings - all in one lamp

CorePro LEDtube InstantFit T8

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit TLED is a great LED solution suitable for replacing T8 fluorescent lamps, using an existing ballast. Specific lamps can also be used on Philips Xitanium driver for Type C applications.

Benefits

- Offers lowest cost of installation and easiest upgrade fluorescent T8's to LED lighting technology
- Dimmable product available for additional savings
- Reliable performance - color and lumen maintenance

Features

- Average life rating of 50,000 hours, with specific lamps up to 70,000 hours
- Compatibility with over 200 ballasts and drivers
- Philips proprietary safety features
- DLC, NSF and RoHS listed
- Available shatter-resistant polycarbonate construction

Application

- Education facilities and Offices
- Industrial and warehouses
- Parking lots and covered car parks


CorePro LEDtube InstantFit T8

Versions



G13

Dimensional drawing



Product	D1	D2	A1	A2	A3
14T8/COR/48-840/IF21/G 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

