



# Bring out the beauty in merchandise with brighter, high performance lighting

## MASTER LEDspot PAR High Lumen

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Benefits

- Lower initial investment for LED CDM replacement PAR30
- Up to 43% energy saving compared to standard CDM lamps
- High efficiency solution >100lm/W

### Features

- Easy retrofit to CDM PAR30L lamps with E27 base
- Emits virtually no heat and will not fade colors
- Lifetime of 25,000 hours
- UV- and IR-free light
- Free of mercury and hazardous materials – RoHS Compliant

### Application

- Shops, hotels, restaurants, museums


# MASTER LEDspot PAR High Lumen

## Versions




LEDspot E27 PAR30L


## Dimensional drawing



Product	D	C
Master LED PAR30L 20W 30D 840	95.5 mm	129 mm




## Accent Diagrams



LEDspot PAR30L E27 20W 4000K 30D

# MASTER LEDspot PAR High Lumen

## Beam Diagrams



LEDspot PAR30L E27 20W 4000K 30D

