



# The easy way to ledify your road lighting – UniStreet gen2

## UniStreet gen2

Designed for large-scale ledification projects, the UniStreet gen2 is the ideal 1:1 luminaire replacement for municipalities. Thanks to its high efficiency and low initial cost, the UniStreet gen2 luminaire enables a fast payback and significant savings in terms of energy consumption within a short period of time. The ease of installation and maintenance is enabled by the Philips Service tag and the Philips SR (System Ready) socket makes it future-ready and you can pair this luminaire with lighting control and software applications such as Interact City. Available with a number of different optics and lumen packages that can even be tuned further to fit exact project requirements, UniStreet gen2 is a true point-to-point replacement solution for conventional light sources. The compact luminaire, using high-quality materials is also easy to dismantle and recycle at the end of its lifetime.

### Benefits

- 1 to 1 replacement for conventional luminaires
- Offers high efficiency and energy savings
- Made of high-quality materials for longer lifetime and minimized maintenance

### Features

- Good application coverage thanks to wide range of optics, tunable flux and tillable spigot
- Easy luminaire identification due to the Philips Service tag
- Future-ready thanks to the SR (System Ready) socket
- Luminaire is also equipped with dedicated light recipes that help with: 1) maintaining an optimal ecosystems for bats or 2) preserving a dark night sky and reduce light pollution

# UniStreet gen2

## Application

- Roads and streets
- Residential streets

## Versions



UniStreet gen2 Micro



UniStreet gen2 Mini



UniStreet gen2 Medium



UniStreet gen2 Large

## Product details



UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2

Bottom view for spigot regulation  
and screw



UniStreet\_LumiStreet\_gen2



# UniStreet gen2

## Product details

UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2

UniStreet\_LumiStreet\_gen2



UniStreet\_LumiStreet\_gen2

UniStreet gen2 spigot regulation



UniStreet\_LumiStreet\_gen2

UniStreet\_LumiStreet\_gen2



## Product details



UniStreet\_LumiStreet\_gen2

### Application Conditions

Maximum dim level	0% (digital)
-------------------	--------------

### Approval and Application

Mech. impact protection code	IK08
------------------------------	------

### General Information

CE mark	CE mark
Optical cover/lens type	Flat glass
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Light source replaceable	Yes
Service tag	Yes

### Light Technical

Standard tilt angle side entry	0°
Standard tilt angle posttop	0°
Upward light output ratio	0

### Mechanical and Housing

Color	Gray
-------	------

## Approval and Application

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866709	BGP281 LED40-4S/740 I DM11 CLO- DDF2 D184	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866784	BGP281 LED60-4S/740 I DM11 CLO- DDF2 D184	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

Order Code	Full Product Name	Surge Protection (Common/Differential)
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode

### Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes	910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Yes
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Yes	910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Yes
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Yes	910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Yes
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	No	910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Yes
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes	910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Yes
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Yes	910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Yes
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Yes	910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Yes
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Yes	910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	No
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Yes	910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	No	910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	No	910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Yes
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Yes	910925866736	BGP281 LED60-4S/740 I DM11 DDF2 D18 48/6	Yes
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Yes	910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Yes	910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Yes

Order Code	Full Product Name	Dimmable
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Yes
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Yes
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Yes
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	No
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Yes
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Yes
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Yes
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	No
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Yes
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Yes
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	No
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Yes
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Yes
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Yes
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Yes
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Yes
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Yes
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Yes
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Yes
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Yes
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Yes
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	No
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Yes
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Yes
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	No
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	No

Order Code	Full Product Name	Dimmable
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Yes
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	No
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Yes
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Yes
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Yes
91092586682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Yes
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	No
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	No
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Yes
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Yes
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Yes
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Yes
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Yes
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Yes
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Yes
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Yes
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Yes
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Yes
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	No
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Yes
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Yes
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Yes
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Yes
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Yes
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Yes
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Yes
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Yes

General Information (1/2)

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED25	1 unit
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED40	1 unit
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED50	1 unit
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	LED25	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED60	1 unit
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED25	1 unit
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	53° x 71°	740 neutral white	LED45	1 unit
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	160° - 42° x 54°	740 neutral white	LED35	1 unit



Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	68° x 158°	740 neutral white	LED40	1 unit
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	160° - 42° x 54°	740 neutral white	LED50	1 unit
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED16	1 unit
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED20	1 unit
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED25	1 unit
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	157° - 33° x 55°	740 neutral white	LED54	1 unit
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED30	1 unit
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED40	1 unit
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED40	1 unit
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	LED40	1 unit
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	68° x 158°	740 neutral white	LED20	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED45	1 unit
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	68° x 158°	830 warm white	LED45	1 unit
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	157° - 33° x 55°	830 warm white	LED30	1 unit
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED54	1 unit
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	157° - 33° x 55°	740 neutral white	LED20	1 unit
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	68° x 158°	740 neutral white	LED35	1 unit
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	68° x 158°	830 warm white	LED50	1 unit
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	160° - 42° x 54°	830 warm white	LED40	1 unit
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	160° - 42° x 54°	740 neutral white	LED20	1 unit
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	68° x 158°	740 neutral white	LED45	1 unit
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	157° - 33° x 55°	740 neutral white	LED45	1 unit
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	160° - 42° x 54°	740 neutral white	LED60	1 unit
910925866785	BGP281 LED40-4S/740 I	68° x 158°	740 neutral white	LED40	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
	DN10 DDF2 D18 SRG1				
910925866815	BGP281	160° - 42° x 54°	740	LED16	1 unit
	LED16-4S/740 I		neutral		
	DM11 DDF2 D18 48/6		white		
910925866916	BGP291	157° - 33° x 55°	740	LED22	1 unit
	LED22-4S/740 II		neutral		
	DM10 MSP CLO SRTH		white		
910925866664	BGP282	157° - 33° x 55°	740	LED100	1 unit
	LED100-4S/740 II		neutral		
	DM10 CLO-DDF2 D1		white		
910925866676	BGP282	157° - 33° x 55°	740	LED120	1 unit
	LED120-4S/740 II		neutral		
	DM10 CLO-DDF2 D1		white		
910925866678	BGP282	157° - 33° x 55°	740	LED70	1 unit
	LED70-4S/740 II		neutral		
	DM10 CLO-DDF2 D18		white		
910925866439	BGP282	160° - 42° x 54°	740	LED120	1 unit
	LED120-4S/740 I		neutral		
	DM11 48/60S		white		
910925866609	BGP282	154° - 31° x 54°	740	LED59	1 unit
	LED59-4S/740 II		neutral		
	DM50 D9 48/60S		white		
910925866677	BGP282	154° - 31° x 54°	740	LED60	1 unit
	LED60-4S/740 I		neutral		
	DM50 D948/60S		white		
910925866678	BGP282	154° - 31° x 54°	740	LED120	1 unit
	LED120-4S/740 I		neutral		
	DM50 D9 48/60S		white		
910925866691	BGP282	160° - 42° x 54°	740	LED70	1 unit
	LED70-4S/740 I		neutral		
	DM11 D948/60S		white		
910925866692	BGP282	160° - 42° x 54°	740	LED80	1 unit
	LED80-4S/740 I		neutral		
	DM11 D948/60S		white		
910925866693	BGP282	160° - 42° x 54°	740	LED90	1 unit
	LED90-4S/740 I		neutral		
	DM11 D948/60S		white		
910925866701	BGP282	157° - 33° x 55°	740	LED80	1 unit
	LED80-4S/740 II		neutral		
	DM10 CLO-DDF2 D18		white		
910925866706	BGP282	157° - 33° x 55°	740	LED60	1 unit
	LED60-4S/740 II		neutral		
	DM10 CLO-DDF2 D18		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866710	BGP282	154° - 31° x 54°	740	LED70	1 unit
	LED70-4S/740 I		neutral		
	DM50 D948/60S		white		
910925866741	BGP282	68° x 158°	740	LED54	1 unit
	LED54-4S/740 I		neutral		
	DN10 DDF2 D18 SRG1		white		
910925866752	BGP282	160° - 42° x 54°	740	LED80	1 unit
	LED80-4S/740 I		neutral		
	DM11 D948/60S		white		
910925866754	BGP282	68° x 158°	740	LED70	1 unit
	LED70-4S/740 I		neutral		
	DN10 48/60S		white		
910925866764	BGP282	68° x 158°	830 warm	LED69	1 unit
	LED69-4S/830 II		white		
	DN10 DDF2 D18 SRG				
910925866770	BGP282	160° - 42° x 54°	740	LED120	1 unit
	LED120-4S/740 I		neutral		
	DM11 D9 48/60S		white		
910925866790	BGP282	61° x 150°	740	LED30	1 unit
	LED30-4S/740 I		neutral		
	DW10 48/60S		white		
910925866794	BGP282	160° - 42° x 54°	830 warm	LED70	1 unit
	LED70-4S/830 II		white		
	DM11 SRG10 48/60S				
910925866803	BGP282	154° - 31° x 54°	740	LED70	1 unit
	LED70-4S/740 I		neutral		
	DM50 D948/60S		white		
910925866806	BGP282	154° - 31° x 54°	740	LED100	1 unit
	LED100-4S/740 I		neutral		
	DM50 48/60S		white		
910925866811	BGP282	61° x 150°	740	LED64	1 unit
	LED64-4S/740 I		neutral		
	DW10 DDF2 D18 SRG1		white		
910925866812	BGP282	160° - 42° x 54°	830 warm	LED74	1 unit
	LED74-4S/830 II		white		
	DM11 DDF2 D18 SRG				
910925866816	BGP282	160° - 42° x 54°	740	LED100	1 unit
	LED100-4S/740 I		neutral		
	DM11 DDF3 D18 48/		white		
91092586682	BGP283	157° - 33° x 55°	740	LED149	1 unit
	LED149-4S/740 II		neutral		
	DM10 CLO-DDF2 D1		white		
910925866440	BGP283	160° - 42° x 54°	740	LED240	2 units
	LED240-4S/740 I		neutral		
	DM11 48/60S		white		
910925866452	BGP283	160° - 42° x 54°	740	LED240	2 units
	LED240-4S/740 I		neutral		
	DM11 SRT SRB SRG1		white		

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED70	1 unit
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED80	1 unit
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED90	1 unit
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED139	1 unit
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	160° - 42° x 54°	740 neutral white	LED160	1 unit
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED149	1 unit
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED139	1 unit

Order Code	Full Product Name	Luminaire light beam spread	Light source color	Lamp family code	Number of gear units
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	53° x 71°	740 neutral white	LED139	1 unit
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	150° - 43° x 67°	740 neutral white	LED200	1 unit
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED100	1 unit
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	68° x 158°	830 warm white	LED100	1 unit
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	154° - 31° x 54°	740 neutral white	LED120	1 unit
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED180	1 unit
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED240	2 units
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED280	2 units
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	160° - 42° x 54°	740 neutral white	LED340	2 units

## General Information (2/2)

Order Code	Full Product Name	Optic type	Product Family Code
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	Distribution narrow 10	BGP281
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281

Order Code	Full Product Name	Optic type	Product Family Code
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	Distribution medium 12	BGP281
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	Distribution medium 11	BGP281
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	Distribution medium 11	BGP281

Order Code	Full Product Name	Optic type	Product Family Code
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	Distribution medium 11	BGP281
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	Distribution medium 10	BGP281
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	Distribution medium 11	BGP281
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	Distribution medium 11	BGP281
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	Distribution narrow 10	BGP281
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP281
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	Distribution medium 10	BGP281
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	Distribution medium 11	BGP281
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP281
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	Distribution narrow 10	BGP281
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	Distribution medium 11	BGP281
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	Distribution medium 11	BGP281
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	Distribution narrow 10	BGP281
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	Distribution medium 10	BGP281
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	Distribution medium 11	BGP281

Order Code	Full Product Name	Optic type	Product Family Code
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP281
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	Distribution medium 11	BGP281
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	Distribution medium 10	BGP291
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP282
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP282
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	Distribution medium 11	BGP282
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP282
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP282
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	Distribution medium 10	BGP282
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	Distribution narrow 10	BGP282
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	Distribution medium 11	BGP282
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	Distribution narrow 10	BGP282
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	Distribution narrow 10	BGP282
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	Distribution medium 11	BGP282
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	Distribution wide 10 10	BGP282
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	Distribution medium 11	BGP282
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	Distribution medium 50	BGP282
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	Distribution medium 50	BGP282

Order Code	Full Product Name	Optic type	Product Family Code
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	Distribution wide 10	BGP282
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	Distribution medium 11	BGP282
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	Distribution medium 11	BGP282
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	Distribution medium 10	BGP283
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	Distribution medium 11	BGP283
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	Distribution medium 11	BGP283
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	Distribution medium 11	BGP283

Order Code	Full Product Name	Optic type	Product Family Code
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	Distribution medium 12	BGP283
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	Distribution extra wide 10	BGP283
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	Distribution narrow 10	BGP283
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	Distribution medium 50	BGP283
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	Distribution medium 50	BGP283
910925866699	BGP284 LED180-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	Distribution medium 11	BGP284

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865663	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	2225 lm
910925865665	BGP281 LED40-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	3344 lm
910925865666	BGP281 LED50-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	4136 lm
910925865667	BGP281 LED25-4S/740 I DN10 SRG10 48/60S	4000 K	70	2225 lm
910925865669	BGP281 LED60-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	4872 lm
910925865674	BGP281 LED25-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	2225 lm
910925865675	BGP281 LED45-4S/740 I DM12 D9SRG10 48/60	4000 K	70	4005 lm
910925865687	BGP281 LED35-4S/740 I DM11 DDF2 D18 48/6	4000 K	70	3115 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925865688	BGP281 LED40-4S/740 II DN10 DDF2 D18 SRG	4000 K	70	3560 lm
910925866438	BGP281 LED50-4S/740 I DM11 48/60S	4000 K	70	4450 lm
910925866450	BGP281 LED50-4S/740 I DM11 SRT SRB SRG10	4000 K	70	4450 lm
910925866673	BGP281 LED16-4S/740 I DM10 DDF27 D18 48/	4000 K	70	1408 lm
910925866674	BGP281 LED20-4S/740 I DM10 DDF27 D18 48/	4000 K	70	1780 lm
910925866675	BGP281 LED25-4S/740 I DM10 DDF27 D18 48/	4000 K	70	2200 lm
910925866676	BGP281 LED54-4S/740 I DM10 DDF27 D18 48/	4000 K	70	4752 lm
910925866687	BGP281 LED20-4S/740 I DM11 D948/60S	4000 K	70	1780 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866688	BGP281 LED30-4S/740 I DM11 D948/60S	4000 K	70	2670 lm
910925866689	BGP281 LED40-4S/740 I DM11 D948/60S	4000 K	70	3560 lm
910925866690	BGP281 LED60-4S/740 I DM11 D948/60S	4000 K	70	5280 lm
910925866708	BGP281 LED40-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3560 lm
910925866709	BGP281 LED40-4S/740 I DM11 CLO-DDF2 D184	4000 K	70	3382 lm
910925866713	BGP281 LED20-4S/740 I DN10 SRG10 48/60S	4000 K	70	1800 lm
910925866714	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3960 lm
910925866719	BGP281 LED45-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	3960 lm
910925866725	BGP281 LED30-4S/830 II DM10 DDF2 D18 SRG	3000 K	80	2670 lm
910925866736	BGP281 LED60-4S/740 I DM11 DDF3 D18 48/6	4000 K	70	5280 lm
910925866737	BGP281 LED54-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	4806 lm
910925866740	BGP281 LED20-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	1691 lm
910925866743	BGP281 LED35-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	3150 lm
910925866744	BGP281 LED50-4S/830 II DN10 D9 SRG10 48/	3000 K	80	4400 lm
910925866750	BGP281 LED40-4S/830 II DM11 D9 SRG10 48/	3000 K	80	3560 lm
910925866763	BGP281 LED20-4S/740 I DM11 CLO D9 48/60S	4000 K	70	1691 lm
910925866768	BGP281 LED45-4S/740 I DN10 48/60S	4000 K	70	4005 lm
910925866782	BGP281 LED45-4S/740 I DM10 DDF2 D18 48/6	4000 K	70	3960 lm
910925866784	BGP281 LED60-4S/740 I DM11 CLO-DDF2 D184	4000 K	70	4928 lm
910925866785	BGP281 LED40-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	3560 lm
910925866815	BGP281 LED16-4S/740 I DM11 DDF2 D18 48/6	4000 K	70	1424 lm
910925866916	BGP291 LED22-4S/740 II DM10 MSP CLO SRTH	4000 K	70	1869 lm
910925865664	BGP282 LED100-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	8004 lm
910925865676	BGP282 LED120-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	9135 lm
910925865678	BGP282 LED70-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	5808 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866439	BGP282 LED120-4S/740 I DM11 48/60S	4000 K	70	10440 lm
910925866609	BGP282 LED59-4S/740 II DM50 D9 48/60S	4000 K	70	5160 lm
910925866677	BGP282 LED60-4S/740 I DM50 D948/60S	4000 K	70	5160 lm
910925866678	BGP282 LED120-4S/740 I DM50 D9 48/60S	4000 K	70	10200 lm
910925866691	BGP282 LED70-4S/740 I DM11 D948/60S	4000 K	70	6230 lm
910925866692	BGP282 LED80-4S/740 I DM11 D948/60S	4000 K	70	7040 lm
910925866693	BGP282 LED90-4S/740 I DM11 D948/60S	4000 K	70	7920 lm
910925866701	BGP282 LED80-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	6336 lm
910925866706	BGP282 LED60-4S/740 II DM10 CLO-DDF2 D18	4000 K	70	4872 lm
910925866710	BGP282 LED70-4S/740 I DM50 D948/60S	4000 K	70	6090 lm
910925866741	BGP282 LED54-4S/740 I DN10 DDF2 D18 SRG1	4000 K	70	4806 lm
910925866752	BGP282 LED80-4S/740 I DM11 D948/60S	4000 K	70	7040 lm
910925866754	BGP282 LED70-4S/740 I DN10 48/60S	4000 K	70	6230 lm
910925866764	BGP282 LED69-4S/830 II DN10 DDF2 D18 SRG	3000 K	80	6160 lm
910925866770	BGP282 LED120-4S/740 I DM11 D9 48/60S	4000 K	70	10440 lm
910925866790	BGP282 LED30-4S/740 I DW10 48/60S	4000 K	70	2670 lm
910925866794	BGP282 LED70-4S/830 II DM11 SRG10 48/60S	3000 K	80	6160 lm
910925866803	BGP282 LED70-4S/740 I DM50 D948/60S	4000 K	70	6090 lm
910925866806	BGP282 LED100-4S/740 I DM50 48/60S	4000 K	70	8600 lm
910925866811	BGP282 LED64-4S/740 I DW10 DDF2 D18 SRG1	4000 K	70	5632 lm
910925866812	BGP282 LED74-4S/830 II DM11 DDF2 D18 SRG	3000 K	80	6438 lm
910925866816	BGP282 LED100-4S/740 I DM11 DDF3 D18 48/	4000 K	70	8800 lm
910925865682	BGP283 LED149-4S/740 II DM10 CLO-DDF2 D1	4000 K	70	11745 lm
910925866440	BGP283 LED240-4S/740 I DM11 48/60S	4000 K	70	20640 lm
910925866452	BGP283 LED240-4S/740 I DM11 SRT SRB SRG1	4000 K	70	20640 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866680	BGP283 LED70-4S/740 II DM50 D9 48/60S	4000 K	70	6160 lm
910925866681	BGP283 LED80-4S/740 II DM50 D9 48/60S	4000 K	70	7040 lm
910925866682	BGP283 LED90-4S/740 II DM50 D9 48/60S	4000 K	70	7830 lm
910925866683	BGP283 LED100-4S/740 II DM50 D9 48/60S	4000 K	70	8700 lm
910925866684	BGP283 LED120-4S/740 II DM50 D9 48/60S	4000 K	70	10440 lm
910925866685	BGP283 LED139-4S/740 II DM50 D9 48/60S	4000 K	70	12040 lm
910925866686	BGP283 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866695	BGP283 LED160-4S/740 I DM11 D9 48/60S	4000 K	70	13920 lm
910925866732	BGP283 LED149-4S/740 II DM50 D9 48/60S	4000 K	70	12900 lm
910925866745	BGP283 LED149-4S/740 I DM50 D9 48/60S	4000 K	70	12900 lm
910925866746	BGP283 LED139-4S/740 I DM50 D9 48/60S	4000 K	70	12040 lm

Order Code	Full Product Name	Init. Corr. Color Temperature	Init. Color Rendering Index	Initial luminous flux
910925866769	BGP283 LED139-4S/740 I DM12 DDF2 D18 SRG	4000 K	70	12320 lm
910925866774	BGP283 LED200-4S/740 I DX10 ALU 48/60S	4000 K	70	16800 lm
910925866775	BGP283 LED100-4S/740 I DM50 D9 48/60S	4000 K	70	8700 lm
910925866776	BGP283 LED100-4S/830 II DN10 DDF2 D18 SR	3000 K	80	8900 lm
910925866788	BGP283 LED120-4S/740 I DM50 D9 48/60S	4000 K	70	10440 lm
910925866807	BGP283 LED120-4S/740 II DM50 D9 48/60S	4000 K	70	10440 lm
910925866669	BGP284 LED180-4S/740 II DM11 D9 48/60S P	4000 K	70	16020 lm
910925866670	BGP284 LED240-4S/740 II DM11 D9 48/60S P	4000 K	70	21120 lm
910925866671	BGP284 LED280-4S/740 II DM11 D9 48/60S P	4000 K	70	24360 lm
910925866672	BGP284 LED340-4S/740 II DM11 D9 48/60S P	4000 K	70	29240 lm

