



Everything you value in a Halogen PAR30 with the benefits of LED. Accent your merchandise or space without distraction.

LED PAR30 S/L

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Benefits

- Up to 80% energy saving compared with halogen lamps
- Lower maintenance costs
- Will not cause fading or damage

Features

- Lifetime of upto 40,000 hours
- Emit virtually no UV/IR light in the beam
- Upto CRI95
- Ranging between 3 to 5-year limited warranty
- Contains no mercury

LED PAR30 S/L

Application

- Hotels, restaurants, bars, cafés, lobbies
- Museums, exhibitions
- Retail shops

Versions



PAR30L



PAR30S



PAR30S



PAR30S



PAR30S



Single Contact Medium Screw PAR
3.75 inch/95mm Long Clear



Single Contact Medium Screw PAR
3.75 inch/95mm Short Clear



Single Contact Medium Screw PAR
3.75 inch/95mm Long Clear

LED PAR30 S/L

Versions



Single Contact Medium Screw PAR
3.75 inch/95mm Short Clear





Single Contact Medium Screw PAR
3.75 inch/95mm Long Clear



Single Contact Medium Screw PAR
3.75 inch/95mm Short Clear

Dimensional drawing







Product	D	C
25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	3-13/16 in	4-11/16 in
25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	3-13/16 in	4-11/16 in
25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	3-13/16 in	4-11/16 in

Product	D	C
23PAR30s/PER/930/F25/ND/120V 6/1FB	3-13/16 in	3-3/4 in

LED PAR30 S/L

Dimensional drawing



Product	D	C
9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	3-13/16 in	4-11/16 in
9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	3-13/16 in	4-11/16 in



Product	D	C
9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	3-13/16 in	3-3/4 in
9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	3-13/16 in	3-3/4 in
9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	3-3/4 in	3-5/8 in

Product	D	C
8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in
8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in
8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in
8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in
8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in
8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	3-3/4 in	3-9/16 in

Product	D	C
8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in
8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in
8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in
8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in
8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in
8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	3-3/4 in	4-9/16 in

LED PAR30 S/L

Dimensional drawing



Operating and electrical

Starting Time (Nom) 0.5 s

General information

Cap-Base E26

Light technical

LLmf At End Of Nominal Lifetime (Nom) 70 %

Mechanical and housing

Bulb Finish Clear

Product	D	C
12PAR30S/EXPERTCOLOR/F25/927/DIM	3-3/4 in	3-11/16 in
12PAR30S/EXPERTCOLOR/F40/940/DIM	4-3/4 in	5-5/16 in
12PAR30S/EXPERTCOLOR/F25/927/DIM B	3-3/4 in	4-5/8 in
12PAR30S/EXPERTCOLOR/S10/927/DIM	3-3/4 in	3-11/16 in
12PAR30S/EXPERTCOLOR/F40/927/DIM	3-3/4 in	4-5/8 in
12PAR30S/EXPERTCOLOR/F25/940/DIM	4-3/4 in	5-5/16 in
12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	3-3/4 in	3-11/16 in
12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	3-3/4 in	3-11/16 in
12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	3-3/4 in	3-11/16 in

Product	D	C
12PAR30L/EXPERTCOLOR/F40/940/DIM	3-3/4 in	4-5/8 in
12PAR30L/EXPERTCOLOR/F25/927/DIM	3-3/4 in	3-11/16 in
12PAR30L/EXPERTCOLOR/F40/927/DIM	3-3/4 in	3-11/16 in
12PAR30L/EXPERTCOLOR/F25/940/DIM	3-3/4 in	4-5/8 in
12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	3-3/4 in	4-5/8 in
12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	3-3/4 in	4-5/8 in
12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	3-3/4 in	4-5/8 in

Approval and application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	- kWh
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	- kWh
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	- kWh
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	- kWh
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	- kWh
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	- kWh
470988	12PAR30L/EXPERTCOLOR/F40/940/DIM	- kWh
471078	12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	- kWh
471086	12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	- kWh
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	- kWh

Order Code	Full Product Name	Energy Consumption kWh/1000 h
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	- kWh
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	- kWh
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	- kWh
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	- kWh
470930	12PAR30S/EXPERTCOLOR/F25/940/DIM	- kWh
470948	12PAR30S/EXPERTCOLOR/F40/940/DIM	- kWh
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	- kWh
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	- kWh
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	- kWh
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	- kWh

LED PAR30 S/L

Order Code	Full Product Name	Energy Consumption kWh/1000 h
546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	- kWh
546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	- kWh
546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	- kWh
546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	- kWh
577759	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	-
567941	8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	-
567957	8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	-
567965	8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	-
567973	8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	-

Controls and dimming

Order Code	Full Product Name	Dimmable
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	Yes
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	Yes
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	Yes
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	Yes
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	Yes
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	Yes
470988	12PAR30L/EXPERTCOLOR/F40/940/DIM	Yes
471078	12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	Yes
471086	12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	Yes
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	Yes
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	Yes
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	Yes
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	Yes
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	Yes
470930	12PAR30S/EXPERTCOLOR/F25/940/DIM	Yes
470948	12PAR30S/EXPERTCOLOR/F40/940/DIM	Yes
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	No
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	No
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	No
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	No
546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	Yes
546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	Yes
546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	Yes
546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	Yes
577759	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	Only with specific dimmers

Operating and electrical

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	60 Hz	120 V	90 W	12 W
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	60 Hz	120 V	90 W	12 W

Order Code	Full Product Name	Energy Consumption kWh/1000 h
567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	-
567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	-
568006	8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	-
568014	8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	-
568022	8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	-
568030	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	-
568048	8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	-
568055	8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	-

Order Code	Full Product Name	Dimmable
567941	8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
567957	8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
567965	8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
567973	8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
568006	8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
568014	8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
568022	8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	Only with specific dimmers
568030	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
568048	8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers
568055	8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	Only with specific dimmers

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	60 Hz	120 V	90 W	12 W
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	60 Hz	120 V	75 W	12 W

LED PAR30 S/L

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)
470914	12PAR30S/ EXPERTCOLOR/ F40/927/DIM	60 Hz	120 V	75 W	12 W
470970	12PAR30L/ EXPERTCOLOR/ F25/940/DIM	60 Hz	120 V	75 W	12 W
470988	12PAR30L/ EXPERTCOLOR/ F40/940/DIM	60 Hz	120 V	75 W	12 W
471078	12PAR30S/ EXPERTCOLOR RETAIL/F25/930/DIM	60 Hz	120 V	75 W	12 W
471086	12PAR30S/ EXPERTCOLOR RETAIL/F40/930/DIM	60 Hz	120 V	75 W	12 W
470898	12PAR30S/ EXPERTCOLOR/ S10/927/DIM	60 Hz	120 V	75 W	12 W
470954	12PAR30L/ EXPERTCOLOR/ F25/927/DIM	60 Hz	120 V	75 W	12 W
470962	12PAR30L/ EXPERTCOLOR/ F40/927/DIM	60 Hz	120 V	75 W	12 W
470906	12PAR30S/ EXPERTCOLOR/ F25/927/DIM	60 Hz	120 V	75 W	12 W
470922	12PAR30S/ EXPERTCOLOR/ F25/927/DIM B	60 Hz	120 V	75 W	12 W
470930	12PAR30S/ EXPERTCOLOR/ F25/940/DIM	60 Hz	120 V	75 W	12 W
470948	12PAR30S/ EXPERTCOLOR/ F40/940/DIM	60 Hz	120 V	75 W	12 W
534644	25.5PAR30L/PER/830/ S15/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534651	25.5PAR30L/PER/830/ F25/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534677	25.5PAR30L/PER/930/ F25/ND/120-277V 6/1FB	50 to 60 Hz	120-277 V	75 W	25.5 W
534693	23PAR30s/PER/930/F2 5/ND/120V 6/1FB	50 to 60 Hz	120 V	75 W	23 W
546969	9.4PAR30L/COR/930/F 25/DIM/120V T20 6/1FB	50 to 60 Hz	120 V	75 W	9.4 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Wattage Equivalent	Power (Nom)
546977	9.4PAR30L/COR/930/F 40/DIM/120V T20 6/1FB	50 to 60 Hz	120 V	75 W	9.4 W
546985	9.4PAR30S/COR/930/F 25/DIM/120V T20 6/1FB	50 to 60 Hz	120 V	75 W	9.4 W
546993	9.4PAR30S/COR/930/F 40/DIM/120V T20 6/1FB	50 to 60 Hz	120 V	75 W	9.4 W
577759	9.4PAR30S/COR/935/F 25/DIM/120V/T20 6/1FB	50 to 60 Hz	120 V	75 W	9.4 W
567941	8.5PAR30L/LED/927/F2 5/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
567957	8.5PAR30L/LED/930/F 25/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
567965	8.5PAR30L/LED/940/F 25/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
567973	8.5PAR30L/LED/927/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
567981	8.5PAR30L/LED/930/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
567999	8.5PAR30L/LED/940/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568006	8.5PAR30S/LED/927/F 25/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568014	8.5PAR30S/LED/930/F 25/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568022	8.5PAR30S/LED/940/F 25/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568030	8.5PAR30S/LED/927/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568048	8.5PAR30S/LED/930/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W
568055	8.5PAR30S/LED/940/F 40/DIM/GULW/T20 6/1FB	50 to 60 Hz	120 V	75 W	8.5 W

General information

LED PAR30 S/L

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
471037	12PAR30L/EXPERTCOLOR RETAIL/ S10/930/DIM	25000 h	50000
471045	12PAR30L/EXPERTCOLOR RETAIL/ F25/930/DIM	25000 h	50000
471052	12PAR30L/EXPERTCOLOR RETAIL/ F40/930/DIM	25000 h	50000
471060	12PAR30S/EXPERTCOLOR RETAIL/ S10/930/DIM	25000 h	50000
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	40000 h	50000
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	40000 h	50000
470988	12PAR30L/EXPERTCOLOR/ F40/940/DIM	40000 h	50000
471078	12PAR30S/EXPERTCOLOR RETAIL/ F25/930/DIM	25000 h	50000
471086	12PAR30S/EXPERTCOLOR RETAIL/ F40/930/DIM	25000 h	50000
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	40000 h	50000
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	40000 h	50000
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	40000 h	50000
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	40000 h	50000
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	40000 h	50000
470930	12PAR30S/EXPERTCOLOR/ F25/940/DIM	40000 h	50000
470948	12PAR30S/EXPERTCOLOR/ F40/940/DIM	40000 h	50000
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	25000 h	50000
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	25000 h	50000
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	25000 h	50000
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	25000 h	50000
546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	25000 h	50000

Order Code	Full Product Name	Nominal Lifetime (Nom)	Switching Cycle
546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	25000 h	50000
546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	25000 h	50000
546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	25000 h	50000
577759	9.4PAR30S/COR/935/F25/DIM/ 120V/T20 6/1FB	25000 h	50000
567941	8.5PAR30L/LED/927/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
567957	8.5PAR30L/LED/930/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
567965	8.5PAR30L/LED/940/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
567973	8.5PAR30L/LED/927/F40/DIM/ GULW/T20 6/1FB	25000 h	50000
567981	8.5PAR30L/LED/930/F40/DIM/ GULW/T20 6/1FB	25000 h	50000
567999	8.5PAR30L/LED/940/F40/DIM/ GULW/T20 6/1FB	25000 h	50000
568006	8.5PAR30S/LED/927/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
568014	8.5PAR30S/LED/930/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
568022	8.5PAR30S/LED/940/F25/DIM/ GULW/T20 6/1FB	25000 h	25000
568030	8.5PAR30S/LED/927/F40/DIM/ GULW/T20 6/1FB	25000 h	50000
568048	8.5PAR30S/LED/930/F40/DIM/ GULW/T20 6/1FB	25000 h	50000
568055	8.5PAR30S/LED/940/F40/DIM/ GULW/T20 6/1FB	25000 h	50000

Light technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	10 °	930	3000 K	90	880 lm	10000 cd
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	25 °	930	3000 K	90	880 lm	4500 cd
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	40 °	930	3000 K	90	880 lm	2000 cd
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	10 °	930	3000 K	90	880 lm	10000 cd
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	40 °	927	2700 K	95	850 lm	1800 cd
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	25 °	940	4000 K	95	950 lm	4800 cd
470988	12PAR30L/EXPERTCOLOR/F40/940/DIM	40 °	940	4000 K	95	950 lm	2100 cd
471078	12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	25 °	930	3000 K	90	880 lm	4500 cd
471086	12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	40 °	930	3000 K	90	880 lm	2000 cd
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	10 °	927	2700 K	95	850 lm	10000 cd

LED PAR30 S/L

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color		
					Rendering Index (Nom)	Luminous Flux (Nom)	Luminous Intensity (Nom)
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	25 °	927	2700 K	95	850 lm	4200 cd
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	40 °	927	2700 K	95	850 lm	1800 cd
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	25 °	927	2700 K	95	850 lm	4200 cd
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	25 °	927	2700 K	95	850 lm	4200 cd
470930	12PAR30S/EXPERTCOLOR/F25/940/DIM	25 °	940	4000 K	95	950 lm	4800 cd
470948	12PAR30S/EXPERTCOLOR/F40/940/DIM	40 °	940	4000 K	95	950 lm	2100 cd
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	15 °	830	3000 K	80	2500 lm	16000 cd
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	25 °	830	3000 K	80	2500 lm	11500 cd
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	25 °	930	3000 K	90	2150 lm	10000 cd
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	25 °	930	3000 K	90	1900 lm	9000 cd
546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	25 °	930	3000 K	90	850 lm	2910 cd
546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	40 °	930	3000 K	90	850 lm	1315 cd
546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	25 °	930	3000 K	90	850 lm	2910 cd
546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	40 °	930	3000 K	90	850 lm	1315 cd
577759	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	25 °	935	3500 K	90	850 lm	2910 cd
567941	8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	25 °	927	2700 K	90	800 lm	3300 cd
567957	8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	25 °	930	3000 K	90	850 lm	3300 cd
567965	8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	25 °	940	4000 K	90	850 lm	3300 cd
567973	8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	40 °	927	2700 K	90	800 lm	1600 cd
567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	40 °	930	3000 K	90	850 lm	1600 cd
567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	40 °	940	4000 K	90	850 lm	1600 cd
568006	8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	25 °	927	2700 K	90	800 lm	3300 cd
568014	8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	25 °	930	3000 K	90	850 lm	3300 cd
568022	8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	25 °	940	4000 K	90	850 lm	3300 cd
568030	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	40 °	927	2700 K	90	800 lm	1600 cd
568048	8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	40 °	930	3000 K	90	850 lm	1600 cd
568055	8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	40 °	940	4000 K	90	850 lm	1600 cd


Mechanical and housing


Order Code	Full Product Name	Bulb Shape	Order Code	Full Product Name	Bulb Shape
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	PAR30L	534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	PAR30S
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	PAR30L	546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	PAR30L
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	PAR30L	546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	PAR30L
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	PAR30S	546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	PAR30S
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	PAR30S	546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	PAR30S
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	PAR30L	577759	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	PAR30S
470988	12PAR30L/EXPERTCOLOR/F40/940/DIM	PAR30L	567941	8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	PAR30L
471078	12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	PAR30S	567957	8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	PAR30L
471086	12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	PAR30S	567965	8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	PAR30L
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	PAR30S	567973	8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	PAR30L
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	PAR30L	567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	PAR30L
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	PAR30L	567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	PAR30L
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	PAR30S	568006	8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	PAR30S
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	PAR30S	568014	8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	PAR30S
470930	12PAR30S/EXPERTCOLOR/F25/940/DIM	PAR30S	568022	8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	PAR30S
470948	12PAR30S/EXPERTCOLOR/F40/940/DIM	PAR30S	568030	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	PAR30S
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	PAR30L	568048	8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	PAR30S
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	PAR30L	568055	8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	PAR30S
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	PAR30L			

LED PAR30 S/L


Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
471037	12PAR30L/EXPERTCOLOR RETAIL/S10/930/DIM	185 °F
471045	12PAR30L/EXPERTCOLOR RETAIL/F25/930/DIM	185 °F
471052	12PAR30L/EXPERTCOLOR RETAIL/F40/930/DIM	185 °F
471060	12PAR30S/EXPERTCOLOR RETAIL/S10/930/DIM	194 °F
470914	12PAR30S/EXPERTCOLOR/F40/927/DIM	194 °F
470970	12PAR30L/EXPERTCOLOR/F25/940/DIM	185 °F
470988	12PAR30L/EXPERTCOLOR/F40/940/DIM	185 °F
471078	12PAR30S/EXPERTCOLOR RETAIL/F25/930/DIM	194 °F
471086	12PAR30S/EXPERTCOLOR RETAIL/F40/930/DIM	194 °F
470898	12PAR30S/EXPERTCOLOR/S10/927/DIM	194 °F
470954	12PAR30L/EXPERTCOLOR/F25/927/DIM	185 °F
470962	12PAR30L/EXPERTCOLOR/F40/927/DIM	185 °F
470906	12PAR30S/EXPERTCOLOR/F25/927/DIM	194 °F
470922	12PAR30S/EXPERTCOLOR/F25/927/DIM B	194 °F
470930	12PAR30S/EXPERTCOLOR/F25/940/DIM	194 °F
470948	12PAR30S/EXPERTCOLOR/F40/940/DIM	194 °F
534644	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	203 °F
534651	25.5PAR30L/PER/830/F25/ND/120-277V 6/1FB	203 °F
534677	25.5PAR30L/PER/930/F25/ND/120-277V 6/1FB	203 °F
534693	23PAR30s/PER/930/F25/ND/120V 6/1FB	201.2 °F
546969	9.4PAR30L/COR/930/F25/DIM/120V T20 6/1FB	176 °F
546977	9.4PAR30L/COR/930/F40/DIM/120V T20 6/1FB	176 °F
546985	9.4PAR30S/COR/930/F25/DIM/120V T20 6/1FB	176 °F
546993	9.4PAR30S/COR/930/F40/DIM/120V T20 6/1FB	176 °F
577759	9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB	167 °F
567941	8.5PAR30L/LED/927/F25/DIM/GULW/T20 6/1FB	158 °F
567957	8.5PAR30L/LED/930/F25/DIM/GULW/T20 6/1FB	158 °F
567965	8.5PAR30L/LED/940/F25/DIM/GULW/T20 6/1FB	158 °F
567973	8.5PAR30L/LED/927/F40/DIM/GULW/T20 6/1FB	158 °F
567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	158 °F
567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	158 °F
568006	8.5PAR30S/LED/927/F25/DIM/GULW/T20 6/1FB	158 °F
568014	8.5PAR30S/LED/930/F25/DIM/GULW/T20 6/1FB	158 °F
568022	8.5PAR30S/LED/940/F25/DIM/GULW/T20 6/1FB	158 °F
568030	8.5PAR30S/LED/927/F40/DIM/GULW/T20 6/1FB	158 °F
568048	8.5PAR30S/LED/930/F40/DIM/GULW/T20 6/1FB	158 °F
568055	8.5PAR30S/LED/940/F40/DIM/GULW/T20 6/1FB	158 °F








LED PAR30 S/L













LED PAR30 S/L





LED PAR30 S/L




LED PAR30 S/L




LED PAR30 S/L




Accent Diagrams




PAR30L 120V 12-75W 900lm 10D 3000K E26 D




PAR30L 120V 12-75W 900lm 25D 3000K E26 D




PAR30L 120V 12-75W 900lm 40D 3000K E26 D




PAR30S 120V 12-75W 900lm 10D 3000K E26 D



PAR30S 120V 12-75W 25D 3000K E26 D WH




PAR30S 12W 850lm 10D 2700K E26




PAR30S 12W 850lm 25D 2700K E26

PAR30S 12W 850lm 40D 2700K E26


Accent Diagrams




PAR30S 12W 950lm 25D 2700K E26




PAR30S 12W 950lm 40D 2700K E26




PAR30L 12W 850lm 25D 2700K E26




PAR30L 12W 850lm 40D 2700K E26




PAR30L 12W 950lm 25D 4000K E26




PAR30L 12W 950lm 40D 4000K E26




LEDspot 25,5 PAR30L 830 S15




LEDspot 25,5 PAR30L 830 F25




LEDspot 25,5 PAR30L 930 F25



LEDspot 23 PAR30L 930 F25




LEDspots 9,4W PAR30L E26 930 25D




LEDspots 9,4W PAR30L E26 930 40D


Accent Diagrams




LEDspots 9,4W PAR30S E26 930 25D




LEDspots 9,4W PAR30S E26 930 40D




LEDspots N DIM 8,5W PAR30L E26 927 25D-LA2




LEDspots N DIM 8,5W PAR30L E26 930 25D-LA2




LEDspots N DIM 8,5W PAR30L E26 940 25D-LA2




LEDspots N DIM 8,5W PAR30L E26 927 40D-LA2



LEDspots N DIM 8,5W PAR30L E26 930 40D-LA2




LEDspots N DIM 8,5W PAR30L E26 940 40D-LA2




LEDspots N DIM 8,5W PAR30S E26 927 25D-LA2

LED PAR30 S/L


Accent Diagrams




LEDspots N DIM 8,5W PAR30S E26 930 25D-LA2




LEDspots N DIM 8,5W PAR30S E26 940 25D-LA2




LEDspots N DIM 8,5W PAR30S E26 927 40D-LA2



LEDspots N DIM 8,5W PAR30S E26 930 40D-LA2




LEDspots N DIM 8,5W PAR30S E26 940 40D-LA2



Accent Diagram


Beam Diagrams



PAR30L 120V 12-75W 900lm 10D 3000K E26 D




PAR30L 120V 12-75W 900lm 25D 3000K E26 D




PAR30L 120V 12-75W 900lm 40D 3000K E26 D

LED PAR30 S/L


Beam Diagrams




PAR30S 120V 12-75W 900lm 10D 3000K E26 D




PAR30S 120V 12-75W 25D 3000K E26 D WH




PAR30S 120V 12-75W 900lm 40D 3000K E26 D




PAR30S 12W 850lm 10D 2700K E26




PAR30S 12W 850lm 25D 2700K E26




PAR30S 12W 850lm 40D 2700K E26




PAR30S 12W 950lm 25D 2700K E26




PAR30S 12W 950lm 40D 2700K E26




PAR30L 12W 850lm 25D 2700K E26



PAR30L 12W 850lm 40D 2700K E26




PAR30L 12W 950lm 25D 4000K E26




PAR30L 12W 950lm 40D 4000K E26

LED PAR30 S/L


Beam Diagrams




LEDspot 25,5 PAR30L 830 S15




LEDspot 25,5 PAR30L 830 F25




LEDspot 25,5 PAR30L 930 F25




LEDspot 23 PAR30L 930 F25




LEDspots 9,4W PAR30L E26 930 25D




LEDspots 9,4W PAR30L E26 930 40D




LEDspots 9,4W PAR30S E26 930 25D




LEDspots 9,4W PAR30S E26 930 40D




LEDspots N DIM 8,5W PAR30L E26 927 25D-LBP



LEDspots N DIM 8,5W PAR30L E26 930 25D-LBP




LEDspots N DIM 8,5W PAR30L E26 940 25D-LBP




LEDspots N DIM 8,5W PAR30L E26 927 40D-LBP


Beam Diagrams




LEDspots N DIM 8,5W PAR30L E26 930 40D-LBP




LEDspots N DIM 8,5W PAR30L E26 940 40D-LBP




LEDspots N DIM 8,5W PAR30S E26 927 25D-LBP




LEDspots N DIM 8,5W PAR30S E26 930 25D-LBP




LEDspots N DIM 8,5W PAR30S E26 940 25D-LBP




LEDspots N DIM 8,5W PAR30S E26 927 40D-LBP



LEDspots N DIM 8,5W PAR30S E26 930 40D-LBP



LEDspots N DIM 8,5W PAR30S E26 940 40D-LBP



Beam Diagram

LED PAR30 S/L

