



The perfect festive touch for holidays and special occasions

LED Party Bulbs

Philips A shape party lamps provided a bright light and color to a wide variety of applications. Ideal for special occasions, parties, and holidays.

Benefits

- Long life -- lowers maintenance costs by reducing re-lamp frequency
- Creates a festive feel
- Adds a pop of color to any room

Features

- Available in Red, Blue, Green, Purple, Yellow and Orange
- 15,000 hour rated average life
- Instant on
- Emits virtually no UV/IR light
- No mercury for a safe environment

Application

- Hospitality
- Restaurants
- Ideal for parties, festivals and holidays in patios, decks and gazebos

LED Party Bulbs

Versions



LEDbulb Color A19 E26 Red



LEDbulb Color P A19 E27 Purple



LEDbulb Color P A19 E27 Red





LEDbulb Color P A19 E27 Yellow



LEDbulb Color P A19 E27 Orange

Dimensional drawing



Product	D	C
8A19/LED/ORANGE/ND 120V E27 6/1FB	60 mm	107 mm
8A19/LED/PURPLE/ND 120V E27 6/1FB	60 mm	107 mm
8A19/LED/RED/ND 120V E27 6/1FB	60 mm	107 mm
8A19/LED/YELLOW/ND 120V E27 6/1FB	60 mm	107 mm

Product	D	C
4A19/LED/RED/G/E26/ND 6/1BC	60 mm	106 mm

LED Party Bulbs

General Information	
Switching Cycle	20,000
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Starting Time (Nom)	0.5 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	A19

General Information

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001937003	4A19/LED/RED/G/E26/ND 6/1BC	E26	15,000 hour(s)
929001998971	8A19/LED/PURPLE/ND 120V E27 6/1FB	E27	10,000 hour(s)
929001998471	8A19/LED/RED/ND 120V E27 6/1FB	E27	10,000 hour(s)

Order Code	Full Product Name	Cap-Base	Nominal lifetime
929001998771	8A19/LED/YELLOW/ND 120V E27 6/1FB	E27	10,000 hour(s)
929001998871	8A19/LED/ORANGE/ND 120V E27 6/1FB	E27	10,000 hour(s)

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Color rendering index (CRI)	Color Code
929001937003	4A19/LED/RED/G/E26/ND 6/1BC	-	60	Red
929001998971	8A19/LED/PURPLE/ND 120V E27 6/1FB	120 degree(s)	54	-
929001998471	8A19/LED/RED/ND 120V E27 6/1FB	120 degree(s)	54	-

Order Code	Full Product Name	Beam Angle (Nom)	Color rendering index (CRI)	Color Code
929001998771	8A19/LED/YELLOW/ND 120V E27 6/1FB	160 degree(s)	62	-
929001998871	8A19/LED/ORANGE/ND 120V E27 6/1FB	160 degree(s)	38	-

Operating and Electrical

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001937003	4A19/LED/RE D/G/E26/ND 6/1BC	60 Hz	60 Hz	4 W	40 W
929001998971	8A19/LED/ PURPLE/ND 120V E27 6/1FB	50 to 60 Hz	50 to 60 Hz	8 W	-
929001998471	8A19/LED/RE D/ND 120V E27 6/1FB	50 to 60 Hz	50 to 60 Hz	8 W	-

Order Code	Full Product Name	Input Frequency	Line Frequency	Power Consumption	Wattage Equivalent
929001998771	8A19/LED/ YELLOW/ND 120V E27 6/1FB	50 to 60 Hz	50 to 60 Hz	8 W	-
929001998871	8A19/LED/ ORANGE/ND 120V E27 6/1FB	50 to 60 Hz	50 to 60 Hz	8 W	-

Temperature

LED Party Bulbs

Order Code	Full Product Name	T-Case Maximum (Nom)
929001937003	4A19/LED/RED/G/E26/ND 6/1BC	50 °C
929001998971	8A19/LED/PURPLE/ND 120V E27 6/1FB	80 °C
929001998471	8A19/LED/RED/ND 120V E27 6/1FB	80 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001998771	8A19/LED/YELLOW/ND 120V E27 6/1FB	80 °C
929001998871	8A19/LED/ORANGE/ND 120V E27 6/1FB	80 °C


Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929001937003	4A19/LED/RED/G/E26/ND 6/1BC	Red
929001998971	8A19/LED/PURPLE/ND 120V E27 6/1FB	-
929001998471	8A19/LED/RED/ND 120V E27 6/1FB	-


Order Code	Full Product Name	Bulb Finish
929001998771	8A19/LED/YELLOW/ND 120V E27 6/1FB	-
929001998871	8A19/LED/ORANGE/ND 120V E27 6/1FB	-

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/
		1000 h
929001937003	4A19/LED/RED/G/E26/ND 6/1BC	- kWh
929001998971	8A19/LED/PURPLE/ND 120V E27 6/1FB	-
929001998471	8A19/LED/RED/ND 120V E27 6/1FB	-
929001998771	8A19/LED/YELLOW/ND 120V E27 6/1FB	-
929001998871	8A19/LED/ORANGE/ND 120V E27 6/1FB	-



LED Party Bulbs



LED Party Bulbs

