



Elegant industrial design with fantastic light quality, superior efficiency and long-term reliability.

Green Perform Highbay Elite

Following the success of GreenPerform Highbay families, GreenPerform Highbay Elite is coming as a big surprising gift for industry solution, with big innovative insights embedded. Elite comes with a completely new finless aesthetics design which own iF design award 2019 & Reddot design award 2019. Next to unique look & feel, it also offers higher system efficiency, better light quality, longer lifetime and interact system offering with affordable price.

Benefits

- Elegant industrial design
- Strong energy saving story
- Superior light quality
- Robust & Reliable with a long service lifetime
- Various application requirements satisfied with complete product family

Features

- System efficacy 145lm/W \pm 10%
- Improved COA performance for light quality
- Long service lifetime 75Khrs L70B50 @Ta 35°C
- Complete lumen package offering, 10Klm/15Klm/20Klm/25Klm/30Klm available
- Multiple optics available: WB & NB
- Suitable for hook, pipe, bracket mounting

Green Perform Highbay Elite

Application

- General manufacturing
- Warehouses and logistical centers
- Exhibition halls and high ceiling lounges

Versions



BY718P LED150



BY718P LED250



BY718P



BY718P



BY718P



BY718P LED100



BY718P LED200

Green Perform Highbay Elite

Application Conditions

Ambient temperature range	-30 to +50 °C
Suitable for random switching	No

Approval and Application

Mech. impact protection code	IK08
Ingress protection code	IP65

General Information

CE mark	CE mark
Protection class IEC	Safety class I
Driver included	Yes
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Optic type	Symmetrical

Initial Performance (IEC Compliant)

Init. Color Rendering Index	>80
Luminous flux tolerance	+/-10%

Application Conditions

Order Code	Full Product Name	Maximum dim level
911401504761	BY718P LED150/CW PSU WB 120-277 JP	Not applicable
911401505261	BY718P LED150/CW PSD WB 120-277 JP	1%
911401513061	BY718P LED150/CW PSD NB NCH	1%
911401513161	BY718P LED150/CW PSD WB NCH	1%
911401513261	BY718P LED150/NW PSD NB NCH	1%
911401513361	BY718P LED150/NW PSD WB NCH	1%
911401580551	BY718P LED150/CW PSD NB	1%
911401580651	BY718P LED150/CW PSD WB	1%
911401580751	BY718P LED150/NW PSD NB	1%
911401580851	BY718P LED150/NW PSD WB	1%
911401581751	BY718P LED150/NW PSD WB CAU	1%
911401504861	BY718P LED250/CW PSU NB 120-277 JP	Not applicable
911401504961	BY718P LED250/CW PSU WB 120-277 JP	Not applicable
911401505061	BY718P LED300/CW PSU NB 120-277 JP	Not applicable
911401505161	BY718P LED300/CW PSU WB 120-277 JP	Not applicable
911401505361	BY718P LED250/CW PSD NB 120-277 JP	1%
911401505461	BY718P LED250/CW PSD WB 120-277 JP	1%
911401505561	BY718P LED300/CW PSD NB 120-277 JP	1%
911401505661	BY718P LED300/CW PSD WB 120-277 JP	1%
911401513861	BY718P LED250/CW PSD NB NCH	1%
911401513961	BY718P LED250/CW PSD WB NCH	1%
911401514061	BY718P LED250/NW PSD NB NCH	1%
911401514161	BY718P LED250/NW PSD WB NCH	1%
911401514261	BY718P LED300/CW PSD NB NCH	1%
911401514361	BY718P LED300/CW PSD WB NCH	1%
911401514461	BY718P LED300/NW PSD NB NCH	1%
911401514561	BY718P LED300/NW PSD WB NCH	1%
911401580951	BY718P LED250/CW PSD NB	1%
911401581051	BY718P LED250/CW PSD WB	1%
911401581151	BY718P LED250/NW PSD NB	1%
911401581251	BY718P LED250/NW PSD WB	1%
911401581351	BY718P LED300/CW PSD NB	1%
911401581451	BY718P LED300/CW PSD WB	1%
911401581551	BY718P LED300/NW PSD NB	1%
911401581651	BY718P LED300/NW PSD WB	1%
911401581851	BY718P LED250/NW PSD WB CAU	1%
911401581951	BY718P LED300/NW PSD WB CAU	1%
911401507761	BY718P LED100/NW PSU NB NCH	Not applicable
911401507861	BY718P LED100/CW PSU NB NCH	Not applicable
911401568851	BY718P LED100/CW PSU NB	Not applicable
911401568951	BY718P LED100/CW PSU WB	Not applicable
911401569051	BY718P LED100/NW PSU NB	Not applicable
911401569151	BY718P LED100/NW PSU WB	Not applicable
911401569651	BY718P LED100/NW PSU WB CAU	Not applicable
911401573451	BY718P LED100/NW PSU WB NCH	Not applicable
911401573551	BY718P LED100/CW PSU WB NCH	Not applicable
911401507961	BY718P LED150/CW PSU NB NCH	Not applicable
911401508061	BY718P LED150/NW PSU NB NCH	Not applicable
911401508161	BY718P LED200/NW PSU NB NCH	Not applicable
911401508261	BY718P LED200/CW PSU NB NCH	Not applicable
911401569251	BY718P LED200/CW PSU NB	Not applicable

Green Perform Highbay Elite

Order Code	Full Product Name	Maximum dim level
911401569351	BY718P LED200/CW PSU WB	Not applicable
911401569451	BY718P LED200/NW PSU NB	Not applicable
911401569551	BY718P LED200/NW PSU WB	Not applicable
911401569751	BY718P LED200/NW PSU WB CAU	Not applicable
911401573651	BY718P LED200/NW PSU WB NCH	Not applicable
911401573751	BY718P LED200/CW PSU WB NCH	Not applicable
911401576451	BY718P LED150/CW PSU NB	Not applicable
911401576551	BY718P LED150/CW PSU WB	Not applicable
911401576651	BY718P LED150/NW PSU NB	Not applicable
911401576751	BY718P LED150/NW PSU WB	Not applicable
911401577651	BY718P LED150/CW PSU WB NCH	Not applicable
911401577751	BY718P LED150/NW PSU WB NCH	Not applicable
911401578051	BY718P LED150/NW PSU WB CAU	Not applicable
911401508361	BY718P LED250/CW PSU NB NCH	Not applicable
911401508461	BY718P LED250/NW PSU NB NCH	Not applicable
911401508561	BY718P LED300/CW PSU NB NCH	Not applicable
911401508661	BY718P LED300/NW PSU NB NCH	Not applicable
911401508761	BY718P LED300/CW PSU WB NCH	Not applicable
911401508861	BY718P LED300/NW PSU WB NCH	Not applicable
911401576851	BY718P LED250/CW PSU NB	Not applicable
911401576951	BY718P LED250/CW PSU WB	Not applicable
911401577051	BY718P LED250/NW PSU NB	Not applicable
911401577151	BY718P LED250/NW PSU WB	Not applicable
911401577251	BY718P LED300/CW PSU NB	Not applicable
911401577351	BY718P LED300/CW PSU WB	Not applicable
911401577451	BY718P LED300/NW PSU NB	Not applicable
911401577551	BY718P LED300/NW PSU WB	Not applicable
911401577851	BY718P LED250/CW PSU WB NCH	Not applicable
911401577951	BY718P LED250/NW PSU WB NCH	Not applicable
911401578151	BY718P LED250/NW PSU WB CAU	Not applicable
911401578251	BY718P LED300/NW PSU WB CAU	Not applicable
911401512661	BY718P LED100/CW PSD NB NCH	1%
911401512761	BY718P LED100/CW PSD WB NCH	1%
911401512861	BY718P LED100/NW PSD NB NCH	1%
911401512961	BY718P LED100/NW PSD WB NCH	1%
911401571851	BY718P LED100/CW PSD NB	1%
911401571951	BY718P LED100/CW PSD WB	1%
911401572051	BY718P LED100/NW PSD NB	1%
911401572151	BY718P LED100/NW PSD WB	1%
911401573851	BY718P LED100/NW PSD WB CAU	1%
911401599151	BY718P LED100/CW PSU WB 120-277 JP	Not applicable
911401599451	BY718P LED100/CW PSD WB 120-277 JP	1%
911401513461	BY718P LED200/CW PSD NB NCH	1%
911401513561	BY718P LED200/CW PSD WB NCH	1%
911401513661	BY718P LED200/NW PSD NB NCH	1%
911401513761	BY718P LED200/NW PSD WB NCH	1%
911401572251	BY718P LED200/CW PSD NB	1%
911401572351	BY718P LED200/CW PSD WB	1%
911401572451	BY718P LED200/NW PSD NB	1%
911401572551	BY718P LED200/NW PSD WB	1%
911401573951	BY718P LED200/NW PSD WB CAU	1%
911401599251	BY718P LED200/CW PSU NB 120-277 JP	Not applicable

Green Perform Highbay Elite

Order Code	Full Product Name	Maximum dim level
911401599351	BY718P LED200/CW PSU WB 120-277 JP	Not applicable
911401599551	BY718P LED200/CW PSD WB 120-277 JP	1%

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
911401504761	BY718P LED150/CW PSU WB 120-277 JP	No	911401507961	BY718P LED150/CW PSU NB NCH	No
911401505261	BY718P LED150/CW PSD WB 120-277 JP	Yes	911401508061	BY718P LED150/NW PSU NB NCH	No
911401513061	BY718P LED150/CW PSD NB NCH	Yes	911401508161	BY718P LED200/NW PSU NB NCH	No
911401513161	BY718P LED150/CW PSD WB NCH	Yes	911401508261	BY718P LED200/CW PSU NB NCH	No
911401513261	BY718P LED150/NW PSD NB NCH	Yes	911401569251	BY718P LED200/CW PSU NB	No
911401513361	BY718P LED150/NW PSD WB NCH	Yes	911401569351	BY718P LED200/CW PSU WB	No
911401580551	BY718P LED150/CW PSD NB	Yes	911401569451	BY718P LED200/NW PSU NB	No
911401580651	BY718P LED150/CW PSD WB	Yes	911401569551	BY718P LED200/NW PSU WB	No
911401580751	BY718P LED150/NW PSD NB	Yes	911401569751	BY718P LED200/NW PSU WB CAU	No
911401580851	BY718P LED150/NW PSD WB	Yes	911401573651	BY718P LED200/NW PSU WB NCH	No
911401581751	BY718P LED150/NW PSD WB CAU	Yes	911401573751	BY718P LED200/CW PSU WB NCH	No
911401504861	BY718P LED250/CW PSU NB 120-277 JP	No	911401576451	BY718P LED150/CW PSU NB	No
911401504961	BY718P LED250/CW PSU WB 120-277 JP	No	911401576551	BY718P LED150/CW PSU WB	No
911401505061	BY718P LED300/CW PSU NB 120-277 JP	No	911401576651	BY718P LED150/NW PSU NB	No
911401505161	BY718P LED300/CW PSU WB 120-277 JP	No	911401576751	BY718P LED150/NW PSU WB	No
911401505361	BY718P LED250/CW PSD NB 120-277 JP	Yes	911401577651	BY718P LED150/CW PSU WB NCH	No
911401505461	BY718P LED250/CW PSD WB 120-277 JP	Yes	911401577751	BY718P LED150/NW PSU WB NCH	No
911401505561	BY718P LED300/CW PSD NB 120-277 JP	Yes	911401578051	BY718P LED150/NW PSU WB CAU	No
911401505661	BY718P LED300/CW PSD WB 120-277 JP	Yes	911401508361	BY718P LED250/CW PSU NB NCH	No
911401513861	BY718P LED250/CW PSD NB NCH	Yes	911401508461	BY718P LED250/NW PSU NB NCH	No
911401513961	BY718P LED250/CW PSD WB NCH	Yes	911401508561	BY718P LED300/CW PSU NB NCH	No
911401514061	BY718P LED250/NW PSD NB NCH	Yes	911401508661	BY718P LED300/NW PSU NB NCH	No
911401514161	BY718P LED250/NW PSD WB NCH	Yes	911401508761	BY718P LED300/CW PSU WB NCH	No
911401514261	BY718P LED300/CW PSD NB NCH	Yes	911401508861	BY718P LED300/NW PSU WB NCH	No
911401514361	BY718P LED300/CW PSD WB NCH	Yes	911401576851	BY718P LED250/CW PSU NB	No
911401514461	BY718P LED300/NW PSD NB NCH	Yes	911401576951	BY718P LED250/CW PSU WB	No
911401514561	BY718P LED300/NW PSD WB NCH	Yes	911401577051	BY718P LED250/NW PSU NB	No
911401580951	BY718P LED250/CW PSD NB	Yes	911401577151	BY718P LED250/NW PSU WB	No
911401581051	BY718P LED250/CW PSD WB	Yes	911401577251	BY718P LED300/CW PSU NB	No
911401581151	BY718P LED250/NW PSD NB	Yes	911401577351	BY718P LED300/CW PSU WB	No
911401581251	BY718P LED250/NW PSD WB	Yes	911401577451	BY718P LED300/NW PSU NB	No
911401581351	BY718P LED300/CW PSD NB	Yes	911401577551	BY718P LED300/NW PSU WB	No
911401581451	BY718P LED300/CW PSD WB	Yes	911401577851	BY718P LED250/CW PSU WB NCH	No
911401581551	BY718P LED300/NW PSD NB	Yes	911401577951	BY718P LED250/NW PSU WB NCH	No
911401581651	BY718P LED300/NW PSD WB	Yes	911401578151	BY718P LED250/NW PSU WB CAU	No
911401581851	BY718P LED250/NW PSD WB CAU	Yes	911401578251	BY718P LED300/NW PSU WB CAU	No
911401581951	BY718P LED300/NW PSD WB CAU	Yes	911401512661	BY718P LED100/CW PSD NB NCH	Yes
911401507761	BY718P LED100/NW PSU NB NCH	No	911401512761	BY718P LED100/CW PSD WB NCH	Yes
911401507861	BY718P LED100/CW PSU NB NCH	No	911401512861	BY718P LED100/NW PSD NB NCH	Yes
911401568851	BY718P LED100/CW PSU NB	No	911401512961	BY718P LED100/NW PSD WB NCH	Yes
911401568951	BY718P LED100/CW PSU WB	No	911401571851	BY718P LED100/CW PSD NB	Yes
911401569051	BY718P LED100/NW PSU NB	No	911401571951	BY718P LED100/CW PSD WB	Yes
911401569151	BY718P LED100/NW PSU WB	No	911401572051	BY718P LED100/NW PSD NB	Yes
911401569651	BY718P LED100/NW PSU WB CAU	No	911401572151	BY718P LED100/NW PSD WB	Yes
911401573451	BY718P LED100/NW PSU WB NCH	No	911401573851	BY718P LED100/NW PSD WB CAU	Yes
911401573551	BY718P LED100/CW PSU WB NCH	No	911401599151	BY718P LED100/CW PSU WB 120-277 JP	No

Green Perform Highbay Elite

Order Code	Full Product Name	Dimmable
911401599451	BY718P LED100/CW PSD WB 120-277 JP	Yes
911401513461	BY718P LED200/CW PSD NB NCH	Yes
911401513561	BY718P LED200/CW PSD WB NCH	Yes
911401513661	BY718P LED200/NW PSD NB NCH	Yes
911401513761	BY718P LED200/NW PSD WB NCH	Yes
911401572251	BY718P LED200/CW PSD NB	Yes
911401572351	BY718P LED200/CW PSD WB	Yes

Order Code	Full Product Name	Dimmable
911401572451	BY718P LED200/NW PSD NB	Yes
911401572551	BY718P LED200/NW PSD WB	Yes
911401573951	BY718P LED200/NW PSD WB CAU	Yes
911401599251	BY718P LED200/CW PSU NB 120-277 JP	No
911401599351	BY718P LED200/CW PSU WB 120-277 JP	No
911401599551	BY718P LED200/CW PSD WB 120-277 JP	Yes

Operating and Electrical

Order Code	Full Product Name	Input Voltage
911401504761	BY718P LED150/CW PSU WB 120-277 JP	120 to 277 V
911401505261	BY718P LED150/CW PSD WB 120-277 JP	120 to 277 V
911401513061	BY718P LED150/CW PSD NB NCH	220 to 240 V
911401513161	BY718P LED150/CW PSD WB NCH	220 to 240 V
911401513261	BY718P LED150/NW PSD NB NCH	220 to 240 V
911401513361	BY718P LED150/NW PSD WB NCH	220 to 240 V
911401580551	BY718P LED150/CW PSD NB	220 to 240 V
911401580651	BY718P LED150/CW PSD WB	220 to 240 V
911401580751	BY718P LED150/NW PSD NB	220 to 240 V
911401580851	BY718P LED150/NW PSD WB	220 to 240 V
911401581751	BY718P LED150/NW PSD WB CAU	220 to 240 V
911401504861	BY718P LED250/CW PSU NB 120-277 JP	120 to 277 V
911401504961	BY718P LED250/CW PSU WB 120-277 JP	120 to 277 V
911401505061	BY718P LED300/CW PSU NB 120-277 JP	120 to 277 V
911401505161	BY718P LED300/CW PSU WB 120-277 JP	120 to 277 V
911401505361	BY718P LED250/CW PSD NB 120-277 JP	120 to 277 V
911401505461	BY718P LED250/CW PSD WB 120-277 JP	120 to 277 V
911401505561	BY718P LED300/CW PSD NB 120-277 JP	120 to 277 V
911401505661	BY718P LED300/CW PSD WB 120-277 JP	120 to 277 V
911401513861	BY718P LED250/CW PSD NB NCH	220 to 240 V
911401513961	BY718P LED250/CW PSD WB NCH	220 to 240 V
911401514061	BY718P LED250/NW PSD NB NCH	220 to 240 V
911401514161	BY718P LED250/NW PSD WB NCH	220 to 240 V
911401514261	BY718P LED300/CW PSD NB NCH	220 to 240 V
911401514361	BY718P LED300/CW PSD WB NCH	220 to 240 V
911401514461	BY718P LED300/NW PSD NB NCH	220 to 240 V
911401514561	BY718P LED300/NW PSD WB NCH	220 to 240 V
911401580951	BY718P LED250/CW PSD NB	220 to 240 V
911401581051	BY718P LED250/CW PSD WB	220 to 240 V
911401581151	BY718P LED250/NW PSD NB	220 to 240 V
911401581251	BY718P LED250/NW PSD WB	220 to 240 V
911401581351	BY718P LED300/CW PSD NB	220 to 240 V
911401581451	BY718P LED300/CW PSD WB	220 to 240 V
911401581551	BY718P LED300/NW PSD NB	220 to 240 V
911401581651	BY718P LED300/NW PSD WB	220 to 240 V
911401581851	BY718P LED250/NW PSD WB CAU	220 to 240 V
911401581951	BY718P LED300/NW PSD WB CAU	220 to 240 V
911401507761	BY718P LED100/NW PSU NB NCH	220 to 240 V
911401507861	BY718P LED100/CW PSU NB NCH	220 to 240 V
911401568851	BY718P LED100/CW PSU NB	220 to 240 V
911401568951	BY718P LED100/CW PSU WB	220 to 240 V

Order Code	Full Product Name	Input Voltage
911401569051	BY718P LED100/NW PSU NB	220 to 240 V
911401569151	BY718P LED100/NW PSU WB	220 to 240 V
911401569651	BY718P LED100/NW PSU WB CAU	220 to 240 V
911401573451	BY718P LED100/NW PSU WB NCH	220 to 240 V
911401573551	BY718P LED100/CW PSU WB NCH	220 to 240 V
911401507961	BY718P LED150/CW PSU NB NCH	220 to 240 V
911401508061	BY718P LED150/NW PSU NB NCH	220 to 240 V
911401508161	BY718P LED200/NW PSU NB NCH	220 to 240 V
911401508261	BY718P LED200/CW PSU NB NCH	220 to 240 V
911401569251	BY718P LED200/CW PSU NB	220 to 240 V
911401569351	BY718P LED200/CW PSU WB	220 to 240 V
911401569451	BY718P LED200/NW PSU NB	220 to 240 V
911401569551	BY718P LED200/NW PSU WB	220 to 240 V
911401569751	BY718P LED200/NW PSU WB CAU	220 to 240 V
911401573651	BY718P LED200/NW PSU WB NCH	220 to 240 V
911401573751	BY718P LED200/CW PSU WB NCH	220 to 240 V
911401576451	BY718P LED150/CW PSU NB	220 to 240 V
911401576551	BY718P LED150/CW PSU WB	220 to 240 V
911401576651	BY718P LED150/NW PSU NB	220 to 240 V
911401576751	BY718P LED150/NW PSU WB	220 to 240 V
911401577651	BY718P LED150/CW PSU WB NCH	220 to 240 V
911401577751	BY718P LED150/NW PSU WB NCH	220 to 240 V
911401578051	BY718P LED150/NW PSU WB CAU	220 to 240 V
911401508361	BY718P LED250/CW PSU NB NCH	220 to 240 V
911401508461	BY718P LED250/NW PSU NB NCH	220 to 240 V
911401508561	BY718P LED300/CW PSU NB NCH	220 to 240 V
911401508661	BY718P LED300/NW PSU NB NCH	220 to 240 V
911401508761	BY718P LED300/CW PSU WB NCH	220 to 240 V
911401508861	BY718P LED300/NW PSU WB NCH	220 to 240 V
911401576851	BY718P LED250/CW PSU NB	220 to 240 V
911401576951	BY718P LED250/CW PSU WB	220 to 240 V
911401577051	BY718P LED250/NW PSU NB	220 to 240 V
911401577151	BY718P LED250/NW PSU WB	220 to 240 V
911401577251	BY718P LED300/CW PSU NB	220 to 240 V
911401577351	BY718P LED300/CW PSU WB	220 to 240 V
911401577451	BY718P LED300/NW PSU NB	220 to 240 V
911401577551	BY718P LED300/NW PSU WB	220 to 240 V
911401577851	BY718P LED250/CW PSU WB NCH	220 to 240 V
911401577951	BY718P LED250/NW PSU WB NCH	220 to 240 V
911401578151	BY718P LED250/NW PSU WB CAU	220 to 240 V
911401578251	BY718P LED300/NW PSU WB CAU	220 to 240 V

Green Perform Highbay Elite

Order Code	Full Product Name	Input Voltage
911401512661	BY718P LED100/CW PSD NB NCH	220 to 240 V
911401512761	BY718P LED100/CW PSD WB NCH	220 to 240 V
911401512861	BY718P LED100/NW PSD NB NCH	220 to 240 V
911401512961	BY718P LED100/NW PSD WB NCH	220 to 240 V
911401571851	BY718P LED100/CW PSD NB	220 to 240 V
911401571951	BY718P LED100/CW PSD WB	220 to 240 V
911401572051	BY718P LED100/NW PSD NB	220 to 240 V
911401572151	BY718P LED100/NW PSD WB	220 to 240 V
911401573851	BY718P LED100/NW PSD WB CAU	220 to 240 V
911401599151	BY718P LED100/CW PSU WB 120-277 JP	120 to 277 V
911401599451	BY718P LED100/CW PSD WB 120-277 JP	120 to 277 V
911401513461	BY718P LED200/CW PSD NB NCH	220 to 240 V

Order Code	Full Product Name	Input Voltage
911401513561	BY718P LED200/CW PSD WB NCH	220 to 240 V
911401513661	BY718P LED200/NW PSD NB NCH	220 to 240 V
911401513761	BY718P LED200/NW PSD WB NCH	220 to 240 V
911401572251	BY718P LED200/CW PSD NB	220 to 240 V
911401572351	BY718P LED200/CW PSD WB	220 to 240 V
911401572451	BY718P LED200/NW PSD NB	220 to 240 V
911401572551	BY718P LED200/NW PSD WB	220 to 240 V
911401573951	BY718P LED200/NW PSD WB CAU	220 to 240 V
911401599251	BY718P LED200/CW PSU NB 120-277 JP	120 to 277 V
911401599351	BY718P LED200/CW PSU WB 120-277 JP	120 to 277 V
911401599551	BY718P LED200/CW PSD WB 120-277 JP	120 to 277 V

General Information

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401504761	BY718P LED150/CW PSU WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401505261	BY718P LED150/CW PSD WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401513061	BY718P LED150/CW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513161	BY718P LED150/CW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513261	BY718P LED150/NW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513361	BY718P LED150/NW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401580551	BY718P LED150/CW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes
911401580651	BY718P LED150/CW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes
911401580751	BY718P LED150/NW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes
911401580851	BY718P LED150/NW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes
911401581751	BY718P LED150/NW PSD WB CAU	Polycarbonate bowl/cover	-	1 unit	Yes

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401504861	BY718P LED250/CW PSU NB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401504961	BY718P LED250/CW PSU WB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505061	BY718P LED300/CW PSU NB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505161	BY718P LED300/CW PSU WB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505361	BY718P LED250/CW PSD NB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505461	BY718P LED250/CW PSD WB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505561	BY718P LED300/CW PSD NB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401505661	BY718P LED300/CW PSD WB 120-277 JP	Polycarbonate bowl/cover	-	2 units	Yes
911401513861	BY718P LED250/CW PSD NB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401513961	BY718P LED250/CW PSD WB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401514061	BY718P LED250/NW PSD NB NCH	Polycarbonate bowl/cover	-	2 units	Yes

Green Perform Highbay Elite

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401514161	BY718P LED250/NW PSD WB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401514261	BY718P LED300/CW PSD NB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401514361	BY718P LED300/CW PSD WB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401514461	BY718P LED300/NW PSD NB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401514561	BY718P LED300/NW PSD WB NCH	Polycarbonate bowl/cover	-	2 units	Yes
911401580951	BY718P LED250/CW PSD NB	Polycarbonate bowl/cover	-	2 units	Yes
911401581051	BY718P LED250/CW PSD WB	Polycarbonate bowl/cover	-	2 units	Yes
911401581151	BY718P LED250/NW PSD NB	Polycarbonate bowl/cover	-	2 units	Yes
911401581251	BY718P LED250/NW PSD WB	Polycarbonate bowl/cover	-	2 units	Yes
911401581351	BY718P LED300/CW PSD NB	Polycarbonate bowl/cover	-	2 units	Yes
911401581451	BY718P LED300/CW PSD WB	Polycarbonate bowl/cover	-	2 units	Yes
911401581551	BY718P LED300/NW PSD NB	Polycarbonate bowl/cover	-	2 units	Yes
911401581651	BY718P LED300/NW PSD WB	Polycarbonate bowl/cover	-	2 units	Yes
911401581851	BY718P LED250/NW PSD WB CAU	Polycarbonate bowl/cover	-	2 units	Yes
911401581951	BY718P LED300/NW PSD WB CAU	Polycarbonate bowl/cover	-	2 units	Yes
911401507761	BY718P LED100/NW PSU NB NCH	Lens	-	1 unit	-
911401507861	BY718P LED100/CW PSU NB NCH	Lens	-	1 unit	-

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401568851	BY718P LED100/CW PSU NB	Lens	-	1 unit	-
911401568951	BY718P LED100/CW PSU WB	Lens	-	1 unit	-
911401569051	BY718P LED100/NW PSU NB	Lens	-	1 unit	-
911401569151	BY718P LED100/NW PSU WB	Lens	-	1 unit	-
911401569651	BY718P LED100/NW PSU WB CAU	Lens	-	1 unit	-
911401573451	BY718P LED100/NW PSU WB NCH	Lens	-	1 unit	-
911401573551	BY718P LED100/CW PSU WB NCH	Lens	-	1 unit	-
911401507961	BY718P LED150/CW PSU NB NCH	Lens	-	1 unit	-
911401508061	BY718P LED150/NW PSU NB NCH	Lens	-	1 unit	-
911401508161	BY718P LED200/NW PSU NB NCH	Lens	-	1 unit	-
911401508261	BY718P LED200/CW PSU NB NCH	Lens	-	1 unit	-
911401569251	BY718P LED200/CW PSU NB	Lens	-	1 unit	-
911401569351	BY718P LED200/CW PSU WB	Lens	-	1 unit	-
911401569451	BY718P LED200/NW PSU NB	Lens	-	1 unit	-
911401569551	BY718P LED200/NW PSU WB	Lens	-	1 unit	-
911401569751	BY718P LED200/NW PSU WB CAU	Lens	-	1 unit	-
911401573651	BY718P LED200/NW PSU WB NCH	Lens	-	1 unit	-

Green Perform Highbay Elite

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401573751	BY718P LED200/CW PSU WB NCH	Lens	-	1 unit	-
911401576451	BY718P LED150/CW PSU NB	Lens	-	1 unit	-
911401576551	BY718P LED150/CW PSU WB	Lens	-	1 unit	-
911401576651	BY718P LED150/NW PSU NB	Lens	-	1 unit	-
911401576751	BY718P LED150/NW PSU WB	Lens	-	1 unit	-
911401577651	BY718P LED150/CW PSU WB NCH	Lens	-	1 unit	-
911401577751	BY718P LED150/NW PSU WB NCH	Lens	-	1 unit	-
911401578051	BY718P LED150/NW PSU WB CAU	Lens	-	1 unit	-
911401508361	BY718P LED250/CW PSU NB NCH	Lens	-	1 unit	-
911401508461	BY718P LED250/NW PSU NB NCH	Lens	-	1 unit	-
911401508561	BY718P LED300/CW PSU NB NCH	Lens	-	1 unit	-
911401508661	BY718P LED300/NW PSU NB NCH	Lens	-	1 unit	-
911401508761	BY718P LED300/CW PSU WB NCH	Lens	-	1 unit	-
911401508861	BY718P LED300/NW PSU WB NCH	Lens	-	1 unit	-
911401576851	BY718P LED250/CW PSU NB	Lens	-	1 unit	-
911401576951	BY718P LED250/CW PSU WB	Lens	-	1 unit	-
911401577051	BY718P LED250/NW PSU NB	Lens	-	1 unit	-

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401577151	BY718P LED250/NW PSU WB	Lens	-	1 unit	-
911401577251	BY718P LED300/CW PSU NB	Lens	-	1 unit	-
911401577351	BY718P LED300/CW PSU WB	Lens	-	1 unit	-
911401577451	BY718P LED300/NW PSU NB	Lens	-	1 unit	-
911401577551	BY718P LED300/NW PSU WB	Lens	-	1 unit	-
911401577851	BY718P LED250/CW PSU WB NCH	Lens	-	1 unit	-
911401577951	BY718P LED250/NW PSU WB NCH	Lens	-	1 unit	-
911401578151	BY718P LED250/NW PSU WB CAU	Lens	-	1 unit	-
911401578251	BY718P LED300/NW PSU WB CAU	Lens	-	1 unit	-
911401512661	BY718P LED100/CW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401512761	BY718P LED100/CW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401512861	BY718P LED100/NW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401512961	BY718P LED100/NW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401571851	BY718P LED100/CW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes
911401571951	BY718P LED100/CW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes
911401572051	BY718P LED100/NW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes
911401572151	BY718P LED100/NW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes

Green Perform Highbay Elite

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401573851	BY718P LED100/NW PSD WB CAU	Polycarbonate bowl/cover	-	1 unit	Yes
911401599151	BY718P LED100/CW PSU WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401599451	BY718P LED100/CW PSD WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401513461	BY718P LED200/CW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513561	BY718P LED200/CW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513661	BY718P LED200/NW PSD NB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401513761	BY718P LED200/NW PSD WB NCH	Polycarbonate bowl/cover	-	1 unit	Yes
911401572251	BY718P LED200/CW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes

Order Code	Full Product Name	Optical cover/ lens type	ENEC mark	Number of gear units	Service tag
911401572351	BY718P LED200/CW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes
911401572451	BY718P LED200/NW PSD NB	Polycarbonate bowl/cover	-	1 unit	Yes
911401572551	BY718P LED200/NW PSD WB	Polycarbonate bowl/cover	-	1 unit	Yes
911401573951	BY718P LED200/NW PSD WB CAU	Polycarbonate bowl/cover	-	1 unit	Yes
911401599251	BY718P LED200/CW PSU NB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401599351	BY718P LED200/CW PSU WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes
911401599551	BY718P LED200/CW PSD WB 120-277 JP	Polycarbonate bowl/cover	-	1 unit	Yes

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401504761	BY718P LED150/CW PSU WB 120-277 JP	6500 K	137 lm/W	15000 lm	109 W
911401505261	BY718P LED150/CW PSD WB 120-277 JP	6500 K	137 lm/W	15000 lm	109 W
911401513061	BY718P LED150/CW PSD NB NCH	6500 K	137 lm/W	15000 lm	109 W
911401513161	BY718P LED150/CW PSD WB NCH	6500 K	137 lm/W	15000 lm	109 W
911401513261	BY718P LED150/NW PSD NB NCH	4000 K	137 lm/W	15000 lm	109 W
911401513361	BY718P LED150/NW PSD WB NCH	4000 K	137 lm/W	15000 lm	109 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401580551	BY718P LED150/CW PSD NB	6500 K	137 lm/W	15000 lm	109 W
911401580651	BY718P LED150/CW PSD WB	6500 K	137 lm/W	15000 lm	109 W
911401580751	BY718P LED150/NW PSD NB	4000 K	137 lm/W	15000 lm	109 W
911401580851	BY718P LED150/NW PSD WB	4000 K	137 lm/W	15000 lm	109 W
911401581751	BY718P LED150/NW PSD WB CAU	4000 K	137 lm/W	15000 lm	109 W
911401504861	BY718P LED250/CW PSU NB 120-277 JP	6500 K	137 lm/W	25000 lm	183 W
911401504961	BY718P LED250/CW	6500 K	137 lm/W	25000 lm	183 W

Green Perform Highbay Elite

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
	PSU WB 120-277 JP				
911401505061	BY718P LED300/CW PSU NB 120-277 JP	6500 K	137 lm/W	30000 lm	217 W
911401505161	BY718P LED300/CW PSU WB 120-277 JP	6500 K	137 lm/W	30000 lm	217 W
911401505361	BY718P LED250/CW PSD NB 120-277 JP	6500 K	137 lm/W	25000 lm	183 W
911401505461	BY718P LED250/CW PSD WB 120-277 JP	6500 K	137 lm/W	25000 lm	183 W
911401505561	BY718P LED300/CW PSD NB 120-277 JP	6500 K	137 lm/W	30000 lm	217 W
911401505661	BY718P LED300/CW PSD WB 120-277 JP	6500 K	137 lm/W	30000 lm	217 W
911401513861	BY718P LED250/CW PSD NB NCH	6500 K	137 lm/W	25000 lm	183 W
911401513961	BY718P LED250/CW PSD WB NCH	6500 K	137 lm/W	25000 lm	183 W
911401514061	BY718P LED250/NW PSD NB NCH	4000 K	137 lm/W	25000 lm	183 W
911401514161	BY718P LED250/NW PSD WB NCH	4000 K	137 lm/W	25000 lm	183 W
911401514261	BY718P LED300/CW PSD NB NCH	6500 K	137 lm/W	30000 lm	217 W
911401514361	BY718P LED300/CW PSD WB NCH	6500 K	137 lm/W	30000 lm	217 W
911401514461	BY718P LED300/NW PSD NB NCH	4000 K	137 lm/W	30000 lm	217 W
911401514561	BY718P LED300/NW PSD WB NCH	4000 K	137 lm/W	30000 lm	217 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401580951	BY718P LED250/CW PSD NB	6500 K	137 lm/W	25000 lm	183 W
911401581051	BY718P LED250/CW PSD WB	6500 K	137 lm/W	25000 lm	183 W
911401581151	BY718P LED250/NW PSD NB	4000 K	137 lm/W	25000 lm	183 W
911401581251	BY718P LED250/NW PSD WB	4000 K	137 lm/W	25000 lm	183 W
911401581351	BY718P LED300/CW PSD NB	6500 K	137 lm/W	30000 lm	217 W
911401581451	BY718P LED300/CW PSD WB	6500 K	137 lm/W	30000 lm	217 W
911401581551	BY718P LED300/NW PSD NB	4000 K	137 lm/W	30000 lm	217 W
911401581651	BY718P LED300/NW PSD WB	4000 K	137 lm/W	30000 lm	217 W
911401581851	BY718P LED250/NW PSD WB CAU	4000 K	137 lm/W	25000 lm	183 W
911401581951	BY718P LED300/NW PSD WB CAU	4000 K	137 lm/W	30000 lm	217 W
911401507761	BY718P LED100/NW PSU NB NCH	4000 K	145 lm/W	10000 lm	68 W
911401507861	BY718P LED100/CW PSU NB NCH	6500 K	145 lm/W	10000 lm	68 W
911401568851	BY718P LED100/CW PSU NB	6500 K	145 lm/W	10000 lm	68 W
911401568951	BY718P LED100/CW PSU WB	6500 K	145 lm/W	10000 lm	68 W
911401569051	BY718P LED100/NW PSU NB	4000 K	145 lm/W	10000 lm	68 W
911401569151	BY718P LED100/NW PSU WB	4000 K	145 lm/W	10000 lm	68 W

Green Perform Highbay Elite

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401569651	BY718P LED100/NW PSU WB CAU	4000 K	145 lm/W	10000 lm	68 W
911401573451	BY718P LED100/NW PSU WB NCH	4000 K	145 lm/W	10000 lm	68 W
911401573551	BY718P LED100/CW PSU WB NCH	6500 K	145 lm/W	10000 lm	68 W
911401507961	BY718P LED150/CW PSU NB NCH	6500 K	145 lm/W	15000 lm	102 W
911401508061	BY718P LED150/NW PSU NB NCH	4000 K	145 lm/W	15000 lm	102 W
911401508161	BY718P LED200/NW PSU NB NCH	4000 K	145 lm/W	20000 lm	135 W
911401508261	BY718P LED200/CW PSU NB NCH	6500 K	145 lm/W	20000 lm	135 W
911401569251	BY718P LED200/CW PSU NB	6500 K	145 lm/W	20000 lm	135 W
911401569351	BY718P LED200/CW PSU WB	6500 K	145 lm/W	20000 lm	135 W
911401569451	BY718P LED200/NW PSU NB	4000 K	145 lm/W	20000 lm	135 W
911401569551	BY718P LED200/NW PSU WB	4000 K	145 lm/W	20000 lm	135 W
911401569751	BY718P LED200/NW PSU WB CAU	4000 K	145 lm/W	20000 lm	135 W
911401573651	BY718P LED200/NW PSU WB NCH	4000 K	145 lm/W	20000 lm	135 W
911401573751	BY718P LED200/CW PSU WB NCH	6500 K	145 lm/W	20000 lm	135 W
911401576451	BY718P LED150/CW PSU NB	6500 K	145 lm/W	15000 lm	102 W
911401576551	BY718P LED150/CW PSU WB	6500 K	145 lm/W	15000 lm	102 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401576651	BY718P LED150/NW PSU NB	4000 K	145 lm/W	15000 lm	102 W
911401576751	BY718P LED150/NW PSU WB	4000 K	145 lm/W	15000 lm	102 W
911401577651	BY718P LED150/CW PSU WB NCH	6500 K	145 lm/W	15000 lm	102 W
911401577751	BY718P LED150/NW PSU WB NCH	4000 K	145 lm/W	15000 lm	102 W
911401578051	BY718P LED150/NW PSU WB CAU	4000 K	145 lm/W	15000 lm	102 W
911401508361	BY718P LED250/CW PSU NB NCH	6500 K	145 lm/W	25000 lm	169 W
911401508461	BY718P LED250/NW PSU NB NCH	4000 K	145 lm/W	25000 lm	169 W
911401508561	BY718P LED300/CW PSU NB NCH	6500 K	145 lm/W	30000 lm	203 W
911401508661	BY718P LED300/NW PSU NB NCH	4000 K	145 lm/W	30000 lm	203 W
911401508761	BY718P LED300/CW PSU WB NCH	6500 K	145 lm/W	30000 lm	203 W
911401508861	BY718P LED300/NW PSU WB NCH	4000 K	145 lm/W	30000 lm	203 W
911401576851	BY718P LED250/CW PSU NB	6500 K	145 lm/W	25000 lm	169 W
911401576951	BY718P LED250/CW PSU WB	6500 K	145 lm/W	25000 lm	169 W
911401577051	BY718P LED250/NW PSU NB	4000 K	145 lm/W	25000 lm	169 W
911401577151	BY718P LED250/NW PSU WB	4000 K	145 lm/W	25000 lm	169 W
911401577251	BY718P LED300/CW PSU NB	6500 K	145 lm/W	30000 lm	203 W

Green Perform Highbay Elite

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401577351	BY718P LED300/CW PSU WB	6500 K	145 lm/W	30000 lm	203 W
911401577451	BY718P LED300/NW PSU NB	4000 K	145 lm/W	30000 lm	203 W
911401577551	BY718P LED300/NW PSU WB	4000 K	145 lm/W	30000 lm	203 W
911401577851	BY718P LED250/CW PSU WB NCH	6500 K	145 lm/W	25000 lm	169 W
911401577951	BY718P LED250/NW PSU WB NCH	4000 K	145 lm/W	25000 lm	169 W
911401578151	BY718P LED250/NW PSU WB CAU	4000 K	145 lm/W	25000 lm	169 W
911401578251	BY718P LED300/NW PSU WB CAU	4000 K	145 lm/W	30000 lm	203 W
911401512661	BY718P LED100/CW PSD NB NCH	6500 K	137 lm/W	10000 lm	73 W
911401512761	BY718P LED100/CW PSD WB NCH	6500 K	137 lm/W	10000 lm	73 W
911401512861	BY718P LED100/NW PSD NB NCH	4000 K	137 lm/W	10000 lm	73 W
911401512961	BY718P LED100/NW PSD WB NCH	4000 K	137 lm/W	10000 lm	73 W
911401571851	BY718P LED100/CW PSD NB	6500 K	137 lm/W	10000 lm	73 W
911401571951	BY718P LED100/CW PSD WB	6500 K	137 lm/W	10000 lm	73 W
911401572051	BY718P LED100/NW PSD NB	4000 K	137 lm/W	10000 lm	73 W
911401572151	BY718P LED100/NW PSD WB	4000 K	137 lm/W	10000 lm	73 W
911401573851	BY718P LED100/NW PSD WB CAU	4000 K	137 lm/W	10000 lm	73 W

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial LED luminaire efficacy	Initial luminous flux	Initial input power
911401599151	BY718P LED100/CW PSU WB 120-277 JP	6500 K	137 lm/W	10000 lm	73 W
911401599451	BY718P LED100/CW PSD WB 120-277 JP	6500 K	137 lm/W	10000 lm	73 W
911401513461	BY718P LED200/CW PSD NB NCH	6500 K	137 lm/W	20000 lm	145 W
911401513561	BY718P LED200/CW PSD WB NCH	6500 K	137 lm/W	20000 lm	145 W
911401513661	BY718P LED200/NW PSD NB NCH	4000 K	137 lm/W	20000 lm	145 W
911401513761	BY718P LED200/NW PSD WB NCH	4000 K	137 lm/W	20000 lm	145 W
911401572251	BY718P LED200/CW PSD NB	6500 K	137 lm/W	20000 lm	145 W
911401572351	BY718P LED200/CW PSD WB	6500 K	137 lm/W	20000 lm	145 W
911401572451	BY718P LED200/NW PSD NB	4000 K	137 lm/W	20000 lm	145 W
911401572551	BY718P LED200/NW PSD WB	4000 K	137 lm/W	20000 lm	145 W
911401573951	BY718P LED200/NW PSD WB CAU	4000 K	137 lm/W	20000 lm	145 W
911401599251	BY718P LED200/CW PSU NB 120-277 JP	6500 K	137 lm/W	20000 lm	145 W
911401599351	BY718P LED200/CW PSU WB 120-277 JP	6500 K	137 lm/W	20000 lm	145 W
911401599551	BY718P LED200/CW PSD WB 120-277 JP	6500 K	137 lm/W	20000 lm	145 W

Mechanical and Housing

Green Perform Highbay Elite

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401504761	BY718P LED150/CW PSU WB 120-277 JP	Black and gray	911401569551	BY718P LED200/NW PSU WB	Gray
911401505261	BY718P LED150/CW PSD WB 120-277 JP	Black and gray	911401569751	BY718P LED200/NW PSU WB CAU	Gray
911401513061	BY718P LED150/CW PSD NB NCH	Black and gray	911401573651	BY718P LED200/NW PSU WB NCH	Gray
911401513161	BY718P LED150/CW PSD WB NCH	Black and gray	911401573751	BY718P LED200/CW PSU WB NCH	Gray
911401513261	BY718P LED150/NW PSD NB NCH	Black and gray	911401576451	BY718P LED150/CW PSU NB	Gray
911401513361	BY718P LED150/NW PSD WB NCH	Black and gray	911401576551	BY718P LED150/CW PSU WB	Gray
911401580551	BY718P LED150/CW PSD NB	Black and gray	911401576651	BY718P LED150/NW PSU NB	Gray
911401580651	BY718P LED150/CW PSD WB	Black and gray	911401576751	BY718P LED150/NW PSU WB	Gray
911401580751	BY718P LED150/NW PSD NB	Black and gray	911401577651	BY718P LED150/CW PSU WB NCH	Gray
911401580851	BY718P LED150/NW PSD WB	Black and gray	911401577751	BY718P LED150/NW PSU WB NCH	Gray
911401581751	BY718P LED150/NW PSD WB CAU	Black and gray	911401578051	BY718P LED150/NW PSU WB CAU	Gray
911401504861	BY718P LED250/CW PSU NB 120-277 JP	Black and gray	911401508361	BY718P LED250/CW PSU NB NCH	Gray
911401504961	BY718P LED250/CW PSU WB 120-277 JP	Black and gray	911401508461	BY718P LED250/NW PSU NB NCH	Gray
911401505061	BY718P LED300/CW PSU NB 120-277 JP	Black and gray	911401508561	BY718P LED300/CW PSU NB NCH	Gray
911401505161	BY718P LED300/CW PSU WB 120-277 JP	Black and gray	911401508661	BY718P LED300/NW PSU NB NCH	Gray
911401505361	BY718P LED250/CW PSD NB 120-277 JP	Black and gray	911401508761	BY718P LED300/CW PSU WB NCH	Gray
911401505461	BY718P LED250/CW PSD WB 120-277 JP	Black and gray	911401508861	BY718P LED300/NW PSU WB NCH	Gray
911401505561	BY718P LED300/CW PSD NB 120-277 JP	Black and gray	911401576851	BY718P LED250/CW PSU NB	Gray
911401505661	BY718P LED300/CW PSD WB 120-277 JP	Black and gray	911401576951	BY718P LED250/CW PSU WB	Gray
911401513861	BY718P LED250/CW PSD NB NCH	Black and gray	911401577051	BY718P LED250/NW PSU NB	Gray
911401513961	BY718P LED250/CW PSD WB NCH	Black and gray	911401577151	BY718P LED250/NW PSU WB	Gray
911401514061	BY718P LED250/NW PSD NB NCH	Black and gray	911401577251	BY718P LED300/CW PSU NB	Gray
911401514161	BY718P LED250/NW PSD WB NCH	Black and gray	911401577351	BY718P LED300/CW PSU WB	Gray
911401514261	BY718P LED300/CW PSD NB NCH	Black and gray	911401577451	BY718P LED300/NW PSU NB	Gray
911401514361	BY718P LED300/CW PSD WB NCH	Black and gray	911401577551	BY718P LED300/NW PSU WB	Gray
911401514461	BY718P LED300/NW PSD NB NCH	Black and gray	911401577851	BY718P LED250/CW PSU WB NCH	Gray
911401514561	BY718P LED300/NW PSD WB NCH	Black and gray	911401577951	BY718P LED250/NW PSU WB NCH	Gray
911401580951	BY718P LED250/CW PSD NB	Black and gray	911401578151	BY718P LED250/NW PSU WB CAU	Gray
911401581051	BY718P LED250/CW PSD WB	Black and gray	911401578251	BY718P LED300/NW PSU WB CAU	Gray
911401581151	BY718P LED250/NW PSD NB	Black and gray	911401512661	BY718P LED100/CW PSD NB NCH	Black and gray
911401581251	BY718P LED250/NW PSD WB	Black and gray	911401512761	BY718P LED100/CW PSD WB NCH	Black and gray
911401581351	BY718P LED300/CW PSD NB	Black and gray	911401512861	BY718P LED100/NW PSD NB NCH	Black and gray
911401581451	BY718P LED300/CW PSD WB	Black and gray	911401512961	BY718P LED100/NW PSD WB NCH	Black and gray
911401581551	BY718P LED300/NW PSD NB	Black and gray	911401571851	BY718P LED100/CW PSD NB	Black and gray
911401581651	BY718P LED300/NW PSD WB	Black and gray	911401571951	BY718P LED100/CW PSD WB	Black and gray
911401581851	BY718P LED250/NW PSD WB CAU	Black and gray	911401572051	BY718P LED100/NW PSD NB	Black and gray
911401581951	BY718P LED300/NW PSD WB CAU	Black and gray	911401572151	BY718P LED100/NW PSD WB	Black and gray
911401507761	BY718P LED100/NW PSU NB NCH	Gray	911401573851	BY718P LED100/NW PSD WB CAU	Black and gray
911401507861	BY718P LED100/CW PSU NB NCH	Gray	911401599151	BY718P LED100/CW PSU WB 120-277 JP	Black and gray
911401568851	BY718P LED100/CW PSU NB	Gray	911401599451	BY718P LED100/CW PSD WB 120-277 JP	Black and gray
911401568951	BY718P LED100/CW PSU WB	Gray	911401513461	BY718P LED200/CW PSD NB NCH	Black and gray
911401569051	BY718P LED100/NW PSU NB	Gray	911401513561	BY718P LED200/CW PSD WB NCH	Black and gray
911401569151	BY718P LED100/NW PSU WB	Gray	911401513661	BY718P LED200/NW PSD NB NCH	Black and gray
911401569651	BY718P LED100/NW PSU WB CAU	Gray	911401513761	BY718P LED200/NW PSD WB NCH	Black and gray
911401573451	BY718P LED100/NW PSU WB NCH	Gray	911401572251	BY718P LED200/CW PSD NB	Black and gray
911401573551	BY718P LED100/CW PSU WB NCH	Gray	911401572351	BY718P LED200/CW PSD WB	Black and gray
911401507961	BY718P LED150/CW PSU NB NCH	Gray	911401572451	BY718P LED200/NW PSD NB	Black and gray
911401508061	BY718P LED150/NW PSU NB NCH	Gray	911401572551	BY718P LED200/NW PSD WB	Black and gray
911401508161	BY718P LED200/NW PSU NB NCH	Gray	911401573951	BY718P LED200/NW PSD WB CAU	Black and gray
911401508261	BY718P LED200/CW PSU NB NCH	Gray	911401599251	BY718P LED200/CW PSU NB 120-277 JP	Black and gray
911401569251	BY718P LED200/CW PSU NB	Gray	911401599351	BY718P LED200/CW PSU WB 120-277 JP	Black and gray
911401569351	BY718P LED200/CW PSU WB	Gray	911401599551	BY718P LED200/CW PSD WB 120-277 JP	Black and gray
911401569451	BY718P LED200/NW PSU NB	Gray			

Green Perform Highbay Elite

