



# Affordable LED replacements for compact fluorescent 4-pin & 2-pin lamps

## PL-C/T

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

### Benefits

- Reduced lighting costs
- Excellent lighting uniformity and lumen maintenance
- Unmatched compatibility with existing ballasts

### Features

- Excellent energy efficiency
- Horizontal lamps rotate to ensure the best possible lighting effect
- Easy installation. Plug-and-play replacement of existing CFL-ni lamps
- Conventional form factor fits into existing luminaires

### Application


- Retail & hospitality
- Residential
- Healthcare

# PL-C/T

## Versions



G24q/GX24q



G24q/GX24q



LEDtube GX23-2



LEDtube GX23-2






LEDtube G24Q



LEDtube G24Q

Dimensional drawing






Product	D	A1	A2	A3
5PL-C/LED/13V/835/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/827/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/830/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5PL-C/LED/13V/840/IF5/P/2P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-2700 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-3000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-3500 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm
10.5PL-C/T LED/26V-4000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Product	D1	D2	A1	A2	A3
12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	mm	mm	mm	mm	mm
12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	mm	mm	mm	mm	mm
12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	mm	mm	mm	mm	mm
8.5PL-C/T LED/26H-3000 IF 4P 10/1	mm	mm	mm	mm	mm
8.5PL-C/T LED/26H-2700 IF 4P 10/1	mm	mm	mm	mm	mm
8.5PL-C/T LED/26H-3500 IF 4P 10/1	mm	mm	mm	mm	mm

Dimensional drawing

Product	D1	D2	A1	A2	A3
8.5PL-C/T LED/26H-4000	24.3	28.4	128.3	147.5	163.1 mm
IF 4P 10/1	mm	mm	mm	mm	
12PLC/T	24.3	28.4	128.8	148 mm	163.6
LED/32H/840/IF/4P/DIM	mm	mm	mm		mm
1PK 10/1					



Product	D	D1	A1	A2	A3
5PL-C/LED/13H/835/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/827/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/830/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5PL-C/LED/13H/840/IF5/P/2P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Product	D	D1	A1	A2	A3
5.5PL-C/LED/13H/835/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/827/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/840/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm
5.5PL-C/LED/13H/830/IF5/P/4P 20/1	27 mm	27 mm	91.5 mm	122.4 mm	137.4 mm

Product	D	A1	A2	A3
5.5PL-C/LED/13V/830/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/840/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/827/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm
5.5PL-C/LED/13V/835/IF5/P/4P 20/1	45.7 mm	24.6 mm	101.6 mm	117.6 mm

**Approval and Application**

Energy Consumption kWh/1000 h	- kWh
Energy Efficiency Label (EEL)	Not applicable

**Operating and Electrical**

Starting Time (Nom)	0.5 s
---------------------	-------

**General Information**

Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X

**Light Technical**

Color Rendering Index (Nom)	82
Llmf At End Of Nominal Lifetime (Nom)	70 %

**Mechanical and Housing**

Bulb Shape	Tube, single-ended
------------	--------------------

**Temperature**

T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C

**Controls and Dimming**

Order Code	Full Product Name	Dimmable
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	Yes
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	Yes
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	Yes
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	Yes
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	Yes
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	Yes
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	Yes
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	Yes
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	Yes
929001388504	10.5PL-C/T LED/26V-3000 IF 4P 10/1	Yes
929001388604	10.5PL-C/T LED/26V-3500 IF 4P 10/1	Yes
929001388704	10.5PL-C/T LED/26V-4000 IF 4P 10/1	Yes
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	Yes
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	Yes
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	Yes
929001820404	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	Yes
929001884504	5PL-C/LED/13H/827/IF5/P/2P 20/1	No
929001884604	5PL-C/LED/13H/830/IF5/P/2P 20/1	No
929001884704	5PL-C/LED/13H/835/IF5/P/2P 20/1	No
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	No
929001884904	5PL-C/LED/13V/827/IF5/P/2P 20/1	No
929001885004	5PL-C/LED/13V/830/IF5/P/2P 20/1	No
929001885104	5PL-C/LED/13V/835/IF5/P/2P 20/1	No
929001885204	5PL-C/LED/13V/840/IF5/P/2P 20/1	No
929001885304	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	Yes
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	Yes
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	Yes
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	Yes
929001885704	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	Yes
929001885804	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	Yes
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	Yes
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	Yes

**Operating and Electrical**

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated)
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	20000-100000 Hz	120 V	8.5 W
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	20000-100000 Hz	120 V	8.5 W
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	20000-100000 Hz	120 V	8.5 W
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	20000-100000 Hz	120 V	8.5 W
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated)
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	20000-100000 Hz	120 V	10.5 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
929001388504	10.5PL-C/T LED/ 26V-3000 IF 4P 10/1	20000-100000 Hz	120 V	10.5 W
929001388604	10.5PL-C/T LED/ 26V-3500 IF 4P 10/1	20000-100000 Hz	120 V	10.5 W
929001388704	10.5PL-C/T LED/ 26V-4000 IF 4P 10/1	20000-100000 Hz	120 V	10.5 W
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001820404	12PLC/T LED/32V/840/IF/4P/DI M 1PK 10/1	20000-100000 Hz	25-55 V	12 W
929001884504	5PL- C/LED/13H/827/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001884604	5PL- C/LED/13H/830/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001884704	5PL- C/LED/13H/835/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001884804	5PL- C/LED/13H/840/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001884904	5PL- C/LED/13V/827/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W

Order Code	Full Product Name	Input Frequency	Voltage (Nom)	Power (Rated) (Nom)
929001885004	5PL- C/LED/13V/830/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001885104	5PL- C/LED/13V/835/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001885204	5PL- C/LED/13V/840/IF5/P/2 P 20/1	50 to 60 Hz	120-277 V	5 W
929001885304	5.5PL- C/LED/13H/827/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885404	5.5PL- C/LED/13H/830/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885504	5.5PL- C/LED/13H/835/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885604	5.5PL- C/LED/13H/840/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885704	5.5PL- C/LED/13V/827/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885804	5.5PL- C/LED/13V/830/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001885904	5.5PL- C/LED/13V/835/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W
929001886004	5.5PL- C/LED/13V/840/IF5/P/4 P 20/1	25000-100000 Hz	14-60 V	5.5 W

General Information

Order Code	Full Product Name	Cap-Base
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	G24Q
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	G24Q
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	G24Q
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	G24Q
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	G24Q
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	G24Q
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	G24Q
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	G24Q
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	GX24q
929001388504	10.5PL-C/T LED/26V-3000 IF 4P 10/1	GX24q
929001388604	10.5PL-C/T LED/26V-3500 IF 4P 10/1	GX24q
929001388704	10.5PL-C/T LED/26V-4000 IF 4P 10/1	GX24q
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	GX24q

Order Code	Full Product Name	Cap-Base
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	GX24q
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	GX24q
929001820404	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	GX24q
929001884504	5PL-C/LED/13H/827/IF5/P/2P 20/1	GX23-2
929001884604	5PL-C/LED/13H/830/IF5/P/2P 20/1	GX23-2
929001884704	5PL-C/LED/13H/835/IF5/P/2P 20/1	GX23-2
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	GX23-2
929001884904	5PL-C/LED/13V/827/IF5/P/2P 20/1	GX23-2
929001885004	5PL-C/LED/13V/830/IF5/P/2P 20/1	GX23-2
929001885104	5PL-C/LED/13V/835/IF5/P/2P 20/1	GX23-2
929001885204	5PL-C/LED/13V/840/IF5/P/2P 20/1	GX23-2
929001885304	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	G24Q
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	G24Q

# PL-C/T

Order Code	Full Product Name	Cap-Base
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	G24Q
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	G24Q
929001885704	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	G24Q

Order Code	Full Product Name	Cap-Base
929001885804	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	G24Q
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	G24Q
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	G24Q

## Light Technical (1/2)

Order Code	Full Product Name	Beam	Correlated		Luminous Flux (Nom)
		Angle (Nom)	Color Code	Temperature (Nom)	
929001388004	8.5PL-C/T LED/ 26H-2700 IF 4P 10/1	120 °	827	2700 K	850 lm
929001388104	8.5PL-C/T LED/ 26H-3000 IF 4P 10/1	120 °	830	3000 K	900 lm
929001388204	8.5PL-C/T LED/ 26H-3500 IF 4P 10/1	120 °	835	3500 K	900 lm
929001388304	8.5PL-C/T LED/ 26H-4000 IF 4P 10/1	120 °	840	4000 K	950 lm
929001819704	12PLC/T LED/32H/827/IF/4P/ DIM 1PK 10/1	120 °	827	2700 K	1300 lm
929001819804	12PLC/T LED/32H/830/IF/4P/ DIM 1PK 10/1	120 °	830	3000 K	1350 lm
929001819904	12PLC/T LED/32H/835/IF/4P/ DIM 1PK 10/1	120 °	835	3500 K	1400 lm
929001820004	12PLC/T LED/32H/840/IF/4P/ DIM 1PK 10/1	120 °	840	4000 K	1450 lm
929001388404	10.5PL-C/T LED/ 26V-2700 IF 4P 10/1	120 °	827	2700 K	1200 lm
929001388504	10.5PL-C/T LED/ 26V-3000 IF 4P 10/1	120 °	830	3000 K	1200 lm
929001388604	10.5PL-C/T LED/ 26V-3500 IF 4P 10/1	120 °	835	3500 K	1200 lm
929001388704	10.5PL-C/T LED/ 26V-4000 IF 4P 10/1	120 °	840	4000 K	1300 lm
929001820104	12PLC/T LED/32V/827/IF/4P/ DIM 1PK 10/1	120 °	827	2700 K	1350 lm
929001820204	12PLC/T LED/32V/830/IF/4P/ DIM 1PK 10/1	120 °	830	3000 K	1400 lm
929001820304	12PLC/T LED/32V/835/IF/4P/ DIM 1PK 10/1	120 °	835	3500 K	1450 lm
929001820404	12PLC/T LED/32V/840/IF/4P/ DIM 1PK 10/1	120 °	840	4000 K	1500 lm

Order Code	Full Product Name	Beam	Correlated		Luminous Flux (Nom)
		Angle (Nom)	Color Code	Temperature (Nom)	
929001884504	5PL- C/LED/13H/827/IF5/ P/2P 20/1	150 °	827	2700 K	520 lm
929001884604	5PL- C/LED/13H/830/IF5/ P/2P 20/1	150 °	830	3000 K	550 lm
929001884704	5PL- C/LED/13H/835/IF5/ P/2P 20/1	150 °	835	3500 K	550 lm
929001884804	5PL- C/LED/13H/840/IF5/ P/2P 20/1	150 °	840	4000 K	580 lm
929001884904	5PL- C/LED/13V/827/IF5/ P/2P 20/1	150 °	827	2700 K	520 lm
929001885004	5PL- C/LED/13V/830/IF5/ P/2P 20/1	150 °	830	3000 K	550 lm
929001885104	5PL- C/LED/13V/835/IF5/ P/2P 20/1	150 °	835	3500 K	550 lm
929001885204	5PL- C/LED/13V/840/IF5/ P/2P 20/1	150 °	840	4000 K	580 lm
929001885304	5.5PL- C/LED/13H/827/IF5/ P/4P 20/1	150 °	827	2700 K	520 lm
929001885404	5.5PL- C/LED/13H/830/IF5/ P/4P 20/1	150 °	830	3000 K	550 lm
929001885504	5.5PL- C/LED/13H/835/IF5/ P/4P 20/1	150 °	835	3500 K	550 lm
929001885604	5.5PL- C/LED/13H/840/IF5/ P/4P 20/1	150 °	840	4000 K	580 lm
929001885704	5.5PL- C/LED/13V/827/IF5/ P/4P 20/1	150 °	827	2700 K	520 lm
929001885804	5.5PL- C/LED/13V/830/IF5/ P/4P 20/1	150 °	830	3000 K	550 lm

## PL-C/T

Order Code	Full Product Name	Correlated			
		Beam Angle (Nom)	Color Code	Temperature (Nom)	Luminous Flux (Nom)
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	150 °	835	3500 K	550 lm

Order Code	Full Product Name	Correlated			
		Beam Angle (Nom)	Color Code	Temperature (Nom)	Luminous Flux (Nom)
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	150 °	840	4000 K	580 lm

### Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	850 lm
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	900 lm
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	900 lm
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	950 lm
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	1300 lm
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	1350 lm
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	1400 lm
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	1450 lm
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	1200 lm
929001388504	10.5PL-C/T LED/26V-3000 IF 4P 10/1	1200 lm
929001388604	10.5PL-C/T LED/26V-3500 IF 4P 10/1	1200 lm
929001388704	10.5PL-C/T LED/26V-4000 IF 4P 10/1	1300 lm
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	1350 lm
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	1400 lm
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	1450 lm
929001820404	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	1500 lm

Order Code	Full Product Name	Luminous Flux (Rated) (Nom)
929001884504	5PL-C/LED/13H/827/IF5/P/2P 20/1	-
929001884604	5PL-C/LED/13H/830/IF5/P/2P 20/1	-
929001884704	5PL-C/LED/13H/835/IF5/P/2P 20/1	-
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	-
929001884904	5PL-C/LED/13V/827/IF5/P/2P 20/1	-
929001885004	5PL-C/LED/13V/830/IF5/P/2P 20/1	-
929001885104	5PL-C/LED/13V/835/IF5/P/2P 20/1	-
929001885204	5PL-C/LED/13V/840/IF5/P/2P 20/1	-
929001885304	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	-
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	-
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	-
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	-
929001885704	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	-
929001885804	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	-
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	-
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	-

### Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	Frosted
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	Frosted
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	Frosted
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	Frosted
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	Frosted
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	Frosted
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	Frosted
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	Frosted
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	Frosted
929001388504	10.5PL-C/T LED/26V-3000 IF 4P 10/1	Frosted
929001388604	10.5PL-C/T LED/26V-3500 IF 4P 10/1	Frosted
929001388704	10.5PL-C/T LED/26V-4000 IF 4P 10/1	Frosted
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	Frosted
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	Frosted
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	Frosted
929001820404	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	Frosted

Order Code	Full Product Name	Bulb Finish
929001884504	5PL-C/LED/13H/827/IF5/P/2P 20/1	-
929001884604	5PL-C/LED/13H/830/IF5/P/2P 20/1	-
929001884704	5PL-C/LED/13H/835/IF5/P/2P 20/1	-
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	-
929001884904	5PL-C/LED/13V/827/IF5/P/2P 20/1	-
929001885004	5PL-C/LED/13V/830/IF5/P/2P 20/1	-
929001885104	5PL-C/LED/13V/835/IF5/P/2P 20/1	-
929001885204	5PL-C/LED/13V/840/IF5/P/2P 20/1	-
929001885304	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	-
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	-
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	-
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	-
929001885704	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	-
929001885804	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	-
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	-
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	-

### Temperature



# PL-C/T

Order Code	Full Product Name	T-Case Maximum (Nom)
929001388004	8.5PL-C/T LED/26H-2700 IF 4P 10/1	60 °C
929001388104	8.5PL-C/T LED/26H-3000 IF 4P 10/1	60 °C
929001388204	8.5PL-C/T LED/26H-3500 IF 4P 10/1	60 °C
929001388304	8.5PL-C/T LED/26H-4000 IF 4P 10/1	60 °C
929001819704	12PLC/T LED/32H/827/IF/4P/DIM 1PK 10/1	25 °C
929001819804	12PLC/T LED/32H/830/IF/4P/DIM 1PK 10/1	25 °C
929001819904	12PLC/T LED/32H/835/IF/4P/DIM 1PK 10/1	25 °C
929001820004	12PLC/T LED/32H/840/IF/4P/DIM 1PK 10/1	25 °C
929001388404	10.5PL-C/T LED/26V-2700 IF 4P 10/1	60 °C
929001388504	10.5PL-C/T LED/26V-3000 IF 4P 10/1	60 °C
929001388604	10.5PL-C/T LED/26V-3500 IF 4P 10/1	60 °C
929001388704	10.5PL-C/T LED/26V-4000 IF 4P 10/1	60 °C
929001820104	12PLC/T LED/32V/827/IF/4P/DIM 1PK 10/1	25 °C
929001820204	12PLC/T LED/32V/830/IF/4P/DIM 1PK 10/1	25 °C
929001820304	12PLC/T LED/32V/835/IF/4P/DIM 1PK 10/1	25 °C
929001820404	12PLC/T LED/32V/840/IF/4P/DIM 1PK 10/1	25 °C
929001884504	5PL-C/LED/13H/827/IF5/P/2P 20/1	70 °C
929001884604	5PL-C/LED/13H/830/IF5/P/2P 20/1	70 °C
929001884704	5PL-C/LED/13H/835/IF5/P/2P 20/1	70 °C
929001884804	5PL-C/LED/13H/840/IF5/P/2P 20/1	70 °C
929001884904	5PL-C/LED/13V/827/IF5/P/2P 20/1	70 °C
929001885004	5PL-C/LED/13V/830/IF5/P/2P 20/1	70 °C
929001885104	5PL-C/LED/13V/835/IF5/P/2P 20/1	70 °C
929001885204	5PL-C/LED/13V/840/IF5/P/2P 20/1	70 °C
929001885304	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	75 °C
929001885404	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	75 °C
929001885504	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	75 °C
929001885604	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	75 °C
929001885704	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	70 °C
929001885804	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	70 °C
929001885904	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	70 °C
929001886004	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	70 °C

