



Instant retrofit, instant savings

LED Highbay

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Benefits

- Energy savings of >50%
- Direct lamp replacement without a ballast or fixture change (UL Type A)
- Operates on 400W, 320W and 250W ballasts

Features

- Standard EX39 base to replace metal halide lamps
- Works on probe and pulse start ballasts (Type A only)
- Available with 1000 lumens of "up-light" to fully illuminate fixtures (Type A only)
- Upto 5-year limited warranty
- Two beam options, wide or narrow available

Application

- Warehouses, Industrial & Retail
- Gymnasiums

LED Highbay

Versions



EX39 Others



Single Contact Medium Screw T-shape Frosted



Single Contact Medium Screw T-shape Frosted




Single Contact Medium Screw T-shape Frosted



Exclusionary Mogul Screw T-shape Frosted


Dimensional drawing



Product	D	C
75HB/LED/840/ND FB 4/1	141 mm	267 mm
65HB/LED/840/ND FB 4/1	141 mm	267 mm
75HB/LED/850/ND FB 4/1	141 mm	267 mm
65HB/LED/850/ND FB 4/1	141 mm	267 mm

LED Highbay



Dimensional drawing



Product	D	C
150HB/LED/750/ND WB DL BB 2/1	211 mm	252 mm
150HB/LED/740/ND NB DL BB 2/1	211 mm	252 mm
150HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm
150HB/LED/750/ND NB DL BB 2/1	211 mm	252 mm
125HB/LED/740/ND NB DL BB 2/1	211 mm	252 mm
100HB/LED/750/ND NB DL BB 2/1	211 mm	252 mm
125HB/LED/750/ND WB DL BB 2/1	211 mm	252 mm
100HB/LED/750/ND WB DL BB 2/1	211 mm	252 mm
100HB/LED/740/ND NB DL BB 2/1	211 mm	252 mm
125HB/LED/750/ND NB DL BB 2/1	211 mm	252 mm
125HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm
100HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm
165HB/LED/840/ND NB UDL 2/1	209.7 mm	245.7 mm
165HB/LED/840/ND WB UDL 2/1	209.7 mm	245.7 mm
165HB/LED/740/ND NB DL 2/1	209.7 mm	245.7 mm
165HB/LED/740/ND WB DL 2/1	209.7 mm	245.7 mm


Product	D	C
45HB/LED/840/ND FB 6/1	160 mm	264 mm
45HB/LED/850/ND FB 6/1	160 mm	264 mm
45HB/LED/830/ND FB 6/1	160 mm	264 mm

Product	D	C
38HB/LED/840/ND FB 6/1	138 mm	238 mm
38HB/LED/850/ND FB 6/1	138 mm	238 mm
38HB/LED/830/ND FB 6/1	138 mm	238 mm



LED Highbay

Dimensional drawing



Product	D	C
25HB/LED/850/ND FB 6/1	118 mm	209 mm
25HB/LED/840/ND FB 6/1	118 mm	209 mm
25HB/LED/830/ND FB 6/1	118 mm	209 mm

Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Frequency	50 to 60 Hz
Starting Time (Nom)	0.5 s
General Information	
Switching Cycle	50000X
Light Technical	
LLmf At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001264804	165HB/LED/740/ND NB DL 2/1	/ V	400 W	165 W
929001265004	165HB/LED/740/ND WB DL 2/1	/ V	400 W	165 W
929001265304	165HB/LED/840/ND NB UDL 2/1	/ V	400 W	165 W
929001265504	165HB/LED/840/ND WB UDL 2/1	/ V	400 W	165 W
929001851304	100HB/LED/740/ND NB DL BB 2/1	120-277 V	250 W	100 W
929001851404	100HB/LED/740/ND WB DL BB 2/1	120-277 V	250 W	100 W
929001851704	100HB/LED/750/ND NB DL BB 2/1	120-277 V	250 W	100 W
929001851804	100HB/LED/750/ND WB DL BB 2/1	120-277 V	250 W	100 W
929001852104	125HB/LED/740/ND NB DL BB 2/1	120-277 V	320 W	125 W

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001852204	125HB/LED/740/ND WB DL BB 2/1	120-277 V	320 W	125 W
929001852504	125HB/LED/750/ND NB DL BB 2/1	120-277 V	320 W	125 W
929001852604	125HB/LED/750/ND WB DL BB 2/1	120-277 V	320 W	125 W
929001852904	150HB/LED/740/ND NB DL BB 2/1	120-277 V	400 W	150 W
929001853004	150HB/LED/740/ND WB DL BB 2/1	120-277 V	400 W	150 W
929001853304	150HB/LED/750/ND NB DL BB 2/1	120-277 V	400 W	150 W
929001853404	150HB/LED/750/ND WB DL BB 2/1	120-277 V	400 W	150 W
929001989604	25HB/LED/830/ND FB 6/1	120 V	70 W	25 W
929001990004	25HB/LED/850/ND FB 6/1	120 V	70 W	25 W

LED Highbay

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001999104	25HB/LED/840/ND FB 6/1	120 V	70 W	25 W
929001989704	38HB/LED/830/ND FB 6/1	120 V	85 W	38 W
929001990104	38HB/LED/850/ND FB 6/1	120 V	85 W	38 W
929001999204	38HB/LED/840/ND FB 6/1	120 V	85 W	38 W
929001989804	45HB/LED/830/ND FB 6/1	120 V	100 W	45 W
929001990204	45HB/LED/850/ND FB 6/1	120 V	100 W	45 W

Order Code	Full Product Name	Voltage (Nom)	Wattage Equivalent	Power (Rated) (Nom)
929001999304	45HB/LED/840/ND FB 6/1	120 V	100 W	45 W
929001990304	65HB/LED/850/ND FB 4/1	120-277 V	150 W	65 W
929001990504	75HB/LED/850/ND FB 4/1	120-277 V	175 W	75 W
929001993004	65HB/LED/840/ND FB 4/1	120-277 V	150 W	65 W
929001993104	75HB/LED/840/ND FB 4/1	120-277 V	175 W	75 W

General Information

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001264804	165HB/LED/740/ND NB DL 2/1	EX39	50000 h
929001265004	165HB/LED/740/ND WB DL 2/1	EX39	50000 h
929001265304	165HB/LED/840/ND NB UDL 2/1	EX39	50000 h
929001265504	165HB/LED/840/ND WB UDL 2/1	EX39	50000 h
929001851304	100HB/LED/740/ND NB DL BB 2/1	EX39	50000 h
929001851404	100HB/LED/740/ND WB DL BB 2/1	EX39	50000 h
929001851704	100HB/LED/750/ND NB DL BB 2/1	EX39	50000 h
929001851804	100HB/LED/750/ND WB DL BB 2/1	EX39	50000 h
929001852104	125HB/LED/740/ND NB DL BB 2/1	EX39	50000 h
929001852204	125HB/LED/740/ND WB DL BB 2/1	EX39	50000 h
929001852504	125HB/LED/750/ND NB DL BB 2/1	EX39	50000 h
929001852604	125HB/LED/750/ND WB DL BB 2/1	EX39	50000 h
929001852904	150HB/LED/740/ND NB DL BB 2/1	EX39	50000 h
929001853004	150HB/LED/740/ND WB DL BB 2/1	EX39	50000 h
929001853304	150HB/LED/750/ND NB DL BB 2/1	EX39	50000 h

Order Code	Full Product Name	Cap-Base	Nominal Lifetime (Nom)
929001853404	150HB/LED/750/ND WB DL BB 2/1	EX39	50000 h
929001989604	25HB/LED/830/ND FB 6/1	E26	25000 h
929001990004	25HB/LED/850/ND FB 6/1	E26	25000 h
929001999104	25HB/LED/840/ND FB 6/1	E26	25000 h
929001989704	38HB/LED/830/ND FB 6/1	E26	25000 h
929001990104	38HB/LED/850/ND FB 6/1	E26	25000 h
929001999204	38HB/LED/840/ND FB 6/1	E26	25000 h
929001989804	45HB/LED/830/ND FB 6/1	E26	25000 h
929001990204	45HB/LED/850/ND FB 6/1	E26	25000 h
929001999304	45HB/LED/840/ND FB 6/1	E26	25000 h
929001990304	65HB/LED/850/ND FB 4/1	EX39	25000 h
929001990504	75HB/LED/850/ND FB 4/1	EX39	25000 h
929001993004	65HB/LED/840/ND FB 4/1	EX39	25000 h
929001993104	75HB/LED/840/ND FB 4/1	EX39	25000 h

Light Technical

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
929001264804	165HB/LED/740/ND NB DL 2/1	60 °	740	4000 K	70	20000 lm
929001265004	165HB/LED/740/ND WB DL 2/1	120 °	740	4000 K	70	20000 lm
929001265304	165HB/LED/840/ND NB UDL 2/1	60 °	840	4000 K	80	19000 lm
929001265504	165HB/LED/840/ND WB UDL 2/1	120 °	840	4000 K	80	19000 lm
929001851304	100HB/LED/740/ND NB DL BB 2/1	70 °	740	4000 K	70	12000 lm
929001851404	100HB/LED/740/ND WB DL BB 2/1	130 °	740	4000 K	70	12000 lm
929001851704	100HB/LED/750/ND NB DL BB 2/1	70 °	750	5000 K	70	12000 lm
929001851804	100HB/LED/750/ND WB DL BB 2/1	130 °	750	5000 K	70	12000 lm
929001852104	125HB/LED/740/ND NB DL BB 2/1	70 °	740	4000 K	70	16000 lm
929001852204	125HB/LED/740/ND WB DL BB 2/1	130 °	740	4000 K	70	16000 lm
929001852504	125HB/LED/750/ND NB DL BB 2/1	70 °	750	5000 K	70	16000 lm
929001852604	125HB/LED/750/ND WB DL BB 2/1	130 °	750	5000 K	70	16000 lm
929001852904	150HB/LED/740/ND NB DL BB 2/1	70 °	740	4000 K	70	20000 lm

LED Highbay

Order Code	Full Product Name	Beam Angle (Nom)	Color Code	Correlated Color Temperature (Nom)	Color Rendering Index (Nom)	Luminous Flux (Nom)
929001853004	150HB/LED/740/ND WB DL BB 2/1	130 °	740	4000 K	70	20000 lm
929001853304	150HB/LED/750/ND NB DL BB 2/1	70 °	750	5000 K	70	20000 lm
929001853404	150HB/LED/750/ND WB DL BB 2/1	130 °	750	5000 K	70	20000 lm
929001989604	25HB/LED/830/ND FB 6/1	200 °	830	3000 K	80	2650 lm
929001990004	25HB/LED/850/ND FB 6/1	200 °	850	5000 K	80	2800 lm
929001999104	25HB/LED/840/ND FB 6/1	200 °	840	4000 K	80	2800 lm
929001989704	38HB/LED/830/ND FB 6/1	200 °	830	3000 K	80	3500 lm
929001990104	38HB/LED/850/ND FB 6/1	200 °	850	5000 K	80	3800 lm
929001999204	38HB/LED/840/ND FB 6/1	200 °	840	4000 K	80	3800 lm
929001989804	45HB/LED/830/ND FB 6/1	200 °	830	3000 K	80	4500 lm
929001990204	45HB/LED/850/ND FB 6/1	200 °	850	5000 K	80	4800 lm
929001999304	45HB/LED/840/ND FB 6/1	200 °	840	4000 K	80	4800 lm
929001990304	65HB/LED/850/ND FB 4/1	240 °	850	5000 K	80	7000 lm
929001990504	75HB/LED/850/ND FB 4/1	240 °	850	5000 K	80	8500 lm
929001993004	65HB/LED/840/ND FB 4/1	240 °	840	4000 K	80	7000 lm
929001993104	75HB/LED/840/ND FB 4/1	240 °	840	4000 K	80	8500 lm

Mechanical and Housing










Order Code	Full Product Name	Bulb Finish	Bulb Shape	Order Code	Full Product Name	Bulb Finish	Bulb Shape
929001264804	165HB/LED/740/ND NB DL 2/1	-	Others	929001853404	150HB/LED/750/ND WB DL BB 2/1	-	Others
929001265004	165HB/LED/740/ND WB DL 2/1	-	Others	929001989604	25HB/LED/830/ND FB 6/1	Frosted	T-shape
929001265304	165HB/LED/840/ND NB UDL 2/1	-	Others	929001990004	25HB/LED/850/ND FB 6/1	Frosted	T-shape
929001265504	165HB/LED/840/ND WB UDL 2/1	-	Others	929001999104	25HB/LED/840/ND FB 6/1	Frosted	T-shape
929001851304	100HB/LED/740/ND NB DL BB 2/1	-	Others	929001989704	38HB/LED/830/ND FB 6/1	Frosted	T-shape
929001851404	100HB/LED/740/ND WB DL BB 2/1	-	Others	929001990104	38HB/LED/850/ND FB 6/1	Frosted	T-shape
929001851704	100HB/LED/750/ND NB DL BB 2/1	-	Others	929001999204	38HB/LED/840/ND FB 6/1	Frosted	T-shape
929001851804	100HB/LED/750/ND WB DL BB 2/1	-	Others	929001989804	45HB/LED/830/ND FB 6/1	Frosted	T-shape
929001852104	125HB/LED/740/ND NB DL BB 2/1	-	Others	929001990204	45HB/LED/850/ND FB 6/1	Frosted	T-shape
929001852204	125HB/LED/740/ND WB DL BB 2/1	-	Others	929001999304	45HB/LED/840/ND FB 6/1	Frosted	T-shape
929001852504	125HB/LED/750/ND NB DL BB 2/1	-	Others	929001990304	65HB/LED/850/ND FB 4/1	Frosted	T-shape
929001852604	125HB/LED/750/ND WB DL BB 2/1	-	Others	929001990504	75HB/LED/850/ND FB 4/1	Frosted	T-shape
929001852904	150HB/LED/740/ND NB DL BB 2/1	-	Others	929001993004	65HB/LED/840/ND FB 4/1	Frosted	T-shape
929001853004	150HB/LED/740/ND WB DL BB 2/1	-	Others	929001993104	75HB/LED/840/ND FB 4/1	Frosted	T-shape
929001853304	150HB/LED/750/ND NB DL BB 2/1	-	Others				

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)	Order Code	Full Product Name	T-Case Maximum (Nom)
929001264804	165HB/LED/740/ND NB DL 2/1	85 °C	929001852904	150HB/LED/740/ND NB DL BB 2/1	80 °C
929001265004	165HB/LED/740/ND WB DL 2/1	85 °C	929001853004	150HB/LED/740/ND WB DL BB 2/1	80 °C
929001265304	165HB/LED/840/ND NB UDL 2/1	85 °C	929001853304	150HB/LED/750/ND NB DL BB 2/1	80 °C
929001265504	165HB/LED/840/ND WB UDL 2/1	85 °C	929001853404	150HB/LED/750/ND WB DL BB 2/1	80 °C
929001851304	100HB/LED/740/ND NB DL BB 2/1	70 °C	929001989604	25HB/LED/830/ND FB 6/1	90 °C
929001851404	100HB/LED/740/ND WB DL BB 2/1	70 °C	929001990004	25HB/LED/850/ND FB 6/1	90 °C
929001851704	100HB/LED/750/ND NB DL BB 2/1	70 °C	929001999104	25HB/LED/840/ND FB 6/1	90 °C
929001851804	100HB/LED/750/ND WB DL BB 2/1	70 °C	929001989704	38HB/LED/830/ND FB 6/1	90 °C
929001852104	125HB/LED/740/ND NB DL BB 2/1	75 °C	929001990104	38HB/LED/850/ND FB 6/1	90 °C
929001852204	125HB/LED/740/ND WB DL BB 2/1	75 °C	929001999204	38HB/LED/840/ND FB 6/1	90 °C
929001852504	125HB/LED/750/ND NB DL BB 2/1	75 °C	929001989804	45HB/LED/830/ND FB 6/1	90 °C
929001852604	125HB/LED/750/ND WB DL BB 2/1	75 °C	929001990204	45HB/LED/850/ND FB 6/1	90 °C

LED Highbay

Order Code	Full Product Name	T-Case Maximum (Nom)
929001999304	45HB/LED/840/ND FB 6/1	90 °C
929001990304	65HB/LED/850/ND FB 4/1	98 °C
929001990504	75HB/LED/850/ND FB 4/1	98 °C
929001993004	65HB/LED/840/ND FB 4/1	98 °C
929001993104	75HB/LED/840/ND FB 4/1	98 °C



LED Highbay

