



Instant retrofit, instant savings

LED Corn Cobs

Philips Corn Cob LED replacement lamps are perfect LED replacement for a variety of outdoor applications. High intensity illumination, which means you get added visibility for applications like streets, public areas, and much more for a fraction of the energy used by conventional HID.

Benefits

- Energy savings of >50%
- omni-directional lighting enabling use in a variety of applications

Features

- Standard EX39 base to replace metal halide lamps and E39 options
- Available in 3000K, 4000K and 5000K CCTs
- Available in ranges between 70W and 400W replacements options and upto 16,800 lumens
- 3-year limited warranty
- Surge 4&6 KV

Application

- Wall packs, Shoeboxes, Post-Top fixtures
- Parking lots, public areas and office outdoor fixtures

LED Corn Cobs

Versions



LEDTForce LS NAM1 Corncob EX39 1



LEDTForce LS DLC Corncob 2



LEDTForce Corncob EX39 3



LEDTForce LS DLC Corncob 3



LEDTForce LS NAM1 Corncob EX39 3



LEDTForce Corncob E26 1



LEDTForce LS NAM1 Corncob EX39 2



LEDTForce LS DLC Corncob 1




LEDTForce LS Corncob



LEDTForce Corncob EX39 4





Dimensional drawing



Product	D	C
115CC/LED/3CCT/LS EX39 BB 3/1	102 mm	211 mm
145CC/LED/3CCT/LS EX39 BB 3/1	102 mm	211 mm

LED Corn Cobs

Dimensional drawing



Product	D	C
45CC/LED/3CCT/LS EX39 G3 BB 3/1	85 mm	245 mm
45CC/LED/830/LS EX39 G3 BB 3/1	85 mm	245 mm
45CC/LED/840/LS EX39 G3 BB 3/1	85 mm	245 mm
45CC/LED/850/LS EX39 G3 BB 3/1	85 mm	245 mm
54CC/LED/3CCT/LS EX39 G3 BB 3/1	85 mm	245 mm
54CC/LED/830/LS EX39 G3 BB 3/1	85 mm	245 mm
54CC/LED/840/LS EX39 G3 BB 3/1	85 mm	245 mm
54CC/LED/850/LS EX39 G3 BB 3/1	85 mm	245 mm





Product	D	C
18CC/LED/830/ND E26 G2 BB 6/1	60 mm	145 mm
18CC/LED/840/ND E26 G2 BB 6/1	60 mm	145 mm
18CC/LED/850/ND E26 G2 BB 6/1	60 mm	145 mm

Product	D	C
115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	102 mm	211 mm
115CC/LED/840/LS EX39 G2 BB 3/1	102 mm	211 mm
115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	102 mm	211 mm
115CC/LED/850/LS EX39 G2 BB 3/1	102 mm	211 mm
150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	102 mm	211 mm
150CC/LED/840/LS EX39 G2 BB 3/1	102 mm	211 mm
150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	102 mm	211 mm
150CC/LED/850/LS EX39 G2 BB 3/1	102 mm	211 mm

Product	D	C
80CC/LED/3CCT/LS EX39 BB 3/1	91 mm	196 mm

LED Corn Cobs

Dimensional drawing



Product	D	C
36CC/LED/830/ND E26 G2 BB 6/1	85 mm	201 mm
36CC/LED/840/ND E26 G2 BB 6/1	85 mm	201 mm
36CC/LED/850/ND E26 G2 BB 6/1	85 mm	201 mm



Product	D	C
80CC/LED/840/LS EX39 G2 BB 3/1	91 mm	196 mm
80CC/LED/850/LS EX39 G2 BB 3/1	91 mm	196 mm

Product	D	C
36CC/LED/3CCT/LS EX39 G3 BB 3/1	85 mm	215 mm
36CC/LED/830/LS EX39 G3 BB 3/1	85 mm	215 mm
36CC/LED/840/LS EX39 G3 BB 3/1	85 mm	215 mm
36CC/LED/850/LS EX39 G3 BB 3/1	85 mm	215 mm

Product	D	C
63CC/LED/3CCT/LS EX39 G3 BB 3/1	85 mm	260 mm
63CC/LED/830/LS EX39 G3 BB 3/1	85 mm	260 mm
63CC/LED/840/LS EX39 G3 BB 3/1	85 mm	260 mm
63CC/LED/850/LS EX39 G3 BB 3/1	85 mm	260 mm

LED Corn Cobs

Dimensional drawing



Product	D	C
450CC/LED/840/LS EX39 BB 3/1	142 mm	308 mm
450CC/LED/850/LS EX39 BB 3/1	142 mm	308 mm

Product	D	C
27CC/LED/830/ND E26 G2 BB 6/1	60 mm	170 mm
27CC/LED/840/ND E26 G2 BB 6/1	60 mm	170 mm
27CC/LED/850/ND E26 G2 BB 6/1	60 mm	170 mm

General Information	
Switching Cycle	50,000
Nominal lifetime	50,000 hour(s)
Light Technical	
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	Corncob

General Information

Order Code	Full Product Name	Cap-Base
929002999204	45CC/LED/830/LS EX39 G3 BB 3/1	EX39
929002999304	45CC/LED/840/LS EX39 G3 BB 3/1	EX39
929002999404	45CC/LED/850/LS EX39 G3 BB 3/1	EX39
929002999504	54CC/LED/830/LS EX39 G3 BB 3/1	EX39
929002999604	54CC/LED/840/LS EX39 G3 BB 3/1	EX39
929002999704	54CC/LED/850/LS EX39 G3 BB 3/1	EX39
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	EX39
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	EX39
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	EX39

Order Code	Full Product Name	Cap-Base
9290029996704	150CC/LED/840/LS EX39 G2 BB 3/1	EX39
9290029996804	150CC/LED/850/LS EX39 G2 BB 3/1	EX39
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	EX39
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	EX39
929002999804	63CC/LED/830/LS EX39 G3 BB 3/1	EX39
929002999904	63CC/LED/840/LS EX39 G3 BB 3/1	EX39
929003000004	63CC/LED/850/LS EX39 G3 BB 3/1	EX39
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	EX39
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	EX39

LED Corn Cobs

Order Code	Full Product Name	Cap-Base
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	E26
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	E26
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	E26
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	EX39
929002996204	80CC/LED/850/LS EX39 G2 BB 3/1	EX39
929002395204	18CC/LED/830/ND E26 G2 BB 6/1	E26
929002395304	18CC/LED/840/ND E26 G2 BB 6/1	E26
929002395404	18CC/LED/850/ND E26 G2 BB 6/1	E26
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	EX39
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	EX39
929002395504	27CC/LED/830/ND E26 G2 BB 6/1	E26

Order Code	Full Product Name	Cap-Base
929002395604	27CC/LED/840/ND E26 G2 BB 6/1	E26
929002395704	27CC/LED/850/ND E26 G2 BB 6/1	E26
929003019704	450CC/LED/840/LS EX39 BB 3/1	EX39
929003019804	450CC/LED/850/LS EX39 BB 3/1	EX39
929002998904	36CC/LED/830/LS EX39 G3 BB 3/1	EX39
929002999004	36CC/LED/840/LS EX39 G3 BB 3/1	EX39
929002999104	36CC/LED/850/LS EX39 G3 BB 3/1	EX39
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	EX39
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	EX39
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	EX39
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	EX39

Light Technical

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929002999204	45CC/LED/830/L S EX39 G3 BB 3/1	3000 K	80	830	6,200 lm
929002999304	45CC/LED/840/L S EX39 G3 BB 3/1	4000 K	80	840	6,500 lm
929002999404	45CC/LED/850/L S EX39 G3 BB 3/1	5000 K	80	850	6,700 lm
929002999504	54CC/LED/830/L S EX39 G3 BB 3/1	3000 K	80	830	7,500 lm
929002999604	54CC/LED/840/L S EX39 G3 BB 3/1	4000 K	80	840	7,800 lm
929002999704	54CC/LED/850/L S EX39 G3 BB 3/1	5000 K	80	850	8,000 lm
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	3000 K	80	3000K/4000K/5000K	11,500 lm
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	Selectable	80	850	-
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	Selectable	80	850	-
929002996704	150CC/LED/840/LS EX39 G2 BB 3/1	-	-	-	-
929002996804	150CC/LED/850/LS EX39 G2 BB 3/1	-	-	-	-
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	4000 K	80	840	23,500 lm
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	5000 K	80	850	23,500 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929002999804	63CC/LED/830/L S EX39 G3 BB 3/1	3000 K	80	830	8,600 lm
929002999904	63CC/LED/840/L S EX39 G3 BB 3/1	4000 K	80	840	9,000 lm
929003000004	63CC/LED/850/L S EX39 G3 BB 3/1	5000 K	80	850	9,200 lm
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	Selectable	80	850	-
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	3000 K	80	3000K/4000K/5000K	20,500 lm
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	3000 K	80	830	5,000 lm
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	4000 K	80	840	5,200 lm
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	5000 K	80	850	5,400 lm
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	-	-	-	-
929002996204	80CC/LED/850/L S EX39 G2 BB 3/1	-	-	-	-
929002395204	18CC/LED/830/N D E26 G2 BB 6/1	3000 K	80	830	2,300 lm
929002395304	18CC/LED/840/N D E26 G2 BB 6/1	4000 K	80	840	2,400 lm
929002395404	18CC/LED/850/N D E26 G2 BB 6/1	5000 K	80	850	2,500 lm

LED Corn Cobs

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	3000 K	80	3000K/4000K/5000K	15,800 lm
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	Selectable	80	850	-
929002395504	27CC/LED/830/N D E26 G2 BB 6/1	3000 K	80	830	3,500 lm
929002395604	27CC/LED/840/N D E26 G2 BB 6/1	4000 K	80	840	3,700 lm
929002395704	27CC/LED/850/N D E26 G2 BB 6/1	5000 K	80	850	3,800 lm
929003019704	450CC/LED/840/LS EX39 BB 3/1	4000 K	80	840	65,000 lm
929003019804	450CC/LED/850/LS EX39 BB 3/1	5000 K	80	850	65,000 lm
929002998904	36CC/LED/830/L S EX39 G3 BB 3/1	3000 K	80	830	5,000 lm

Order Code	Full Product Name	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Color Code	Luminous Flux
929002999004	36CC/LED/840/L S EX39 G3 BB 3/1	4000 K	80	840	5,200 lm
929002999104	36CC/LED/850/L S EX39 G3 BB 3/1	5000 K	80	850	5,400 lm
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	-	-	-	-
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	-	-	-	-
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	4000 K	80	840	18,000 lm
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	5000 K	80	850	18,000 lm

Operating and Electrical

Order Code	Full Product Name	Line Frequency	Power Consumption	Starting Time (Nom)
929002999204	45CC/LED/830/LS EX39 G3 BB 3/1	50 to 60 Hz	45 W	1 s
929002999304	45CC/LED/840/LS EX39 G3 BB 3/1	50 to 60 Hz	45 W	1 s
929002999404	45CC/LED/850/LS EX39 G3 BB 3/1	50 to 60 Hz	45 W	1 s
929002999504	54CC/LED/830/LS EX39 G3 BB 3/1	50 to 60 Hz	54 W	1 s
929002999604	54CC/LED/840/LS EX39 G3 BB 3/1	50 to 60 Hz	54 W	1 s
929002999704	54CC/LED/850/LS EX39 G3 BB 3/1	50 to 60 Hz	54 W	1 s
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	-	80 W	2 s
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	50 to 60 Hz	45 W	1 s
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	50 to 60 Hz	54 W	1 s
929002996704	150CC/LED/840/LS EX39 G2 BB 3/1	50 to 60 Hz	150 W	-
929002996804	150CC/LED/850/LS EX39 G2 BB 3/1	50 to 60 Hz	150 W	-
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	50 to 60 Hz	150 W	1.5 s

Order Code	Full Product Name	Line Frequency	Power Consumption	Starting Time (Nom)
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	50 to 60 Hz	150 W	1.5 s
929002999804	63CC/LED/830/LS EX39 G3 BB 3/1	50 to 60 Hz	63 W	1 s
929002999904	63CC/LED/840/LS EX39 G3 BB 3/1	50 to 60 Hz	63 W	1 s
929003000004	63CC/LED/850/LS EX39 G3 BB 3/1	50 to 60 Hz	63 W	1 s
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	50 to 60 Hz	63 W	1 s
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	-	145 W	2 s
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	50 to 60 Hz	36 W	1 s
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	50 to 60 Hz	36 W	1 s
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	50 to 60 Hz	36 W	1 s
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	50 to 60 Hz	80 W	-
929002996204	80CC/LED/850/LS EX39 G2 BB 3/1	50 to 60 Hz	80 W	-
929002395204	18CC/LED/830/ND E26 G2 BB 6/1	50 to 60 Hz	18 W	1 s

LED Corn Cobs

Order Code	Full Product Name	Line Frequency	Power	Starting Time
			Consumption	(Nom)
929002395304	18CC/LED/840/ND E26 G2 BB 6/1	50 to 60 Hz	18 W	1 s
929002395404	18CC/LED/850/ND E26 G2 BB 6/1	50 to 60 Hz	18 W	1 s
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	-	115 W	2 s
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	50 to 60 Hz	36 W	1 s
929002395504	27CC/LED/830/ND E26 G2 BB 6/1	50 to 60 Hz	27 W	1 s
929002395604	27CC/LED/840/ND E26 G2 BB 6/1	50 to 60 Hz	27 W	1 s
929002395704	27CC/LED/850/ND E26 G2 BB 6/1	50 to 60 Hz	27 W	1 s
929003019704	450CC/LED/840/LS EX39 BB 3/1	50 to 60 Hz	450 W	2 s
929003019804	450CC/LED/850/LS EX39 BB 3/1	50 to 60 Hz	450 W	2 s

Order Code	Full Product Name	Line Frequency	Power	Starting Time
			Consumption	(Nom)
929002998904	36CC/LED/830/LS EX39 G3 BB 3/1	50 to 60 Hz	36 W	1 s
929002999004	36CC/LED/840/LS EX39 G3 BB 3/1	50 to 60 Hz	36 W	1 s
929002999104	36CC/LED/850/LS EX39 G3 BB 3/1	50 to 60 Hz	36 W	1 s
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	50 to 60 Hz	115 W	-
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	50 to 60 Hz	115 W	-
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	50 to 60 Hz	115 W	1.5 s
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	50 to 60 Hz	115 W	1.5 s

Temperature

Order Code	Full Product Name	Ambient temperature	T-Case
		range	Maximum (Nom)
929002999204	45CC/LED/830/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002999304	45CC/LED/840/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002999404	45CC/LED/850/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002999504	54CC/LED/830/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929002999604	54CC/LED/840/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929002999704	54CC/LED/850/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	-20 to +55 °C	41.75 °C
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	-	60 °C
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	-	65 °C
929002996704	150CC/LED/840/LS EX39 G2 BB 3/1	-20 °C to 45 °C	34 °C
929002996804	150CC/LED/850/LS EX39 G2 BB 3/1	-20 °C to 45 °C	34 °C
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	-20 °C to 55 °C	38.4 °C
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	-20 °C to 55 °C	38.4 °C

Order Code	Full Product Name	Ambient temperature	T-Case
		range	Maximum (Nom)
929002999804	63CC/LED/830/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929002999904	63CC/LED/840/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929003000004	63CC/LED/850/LS EX39 G3 BB 3/1	-20 °C to 45 °C	65 °C
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	-	65 °C
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	-20 to +55 °C	40 °C
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	-20 °C to 45 °C	37.1 °C
929002996204	80CC/LED/850/LS EX39 G2 BB 3/1	-20 °C to 45 °C	37.1 °C
929002395204	18CC/LED/830/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002395304	18CC/LED/840/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002395404	18CC/LED/850/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C

LED Corn Cobs

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	-20 to +55 °C	35.5 °C
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002395504	27CC/LED/830/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002395604	27CC/LED/840/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929002395704	27CC/LED/850/ND E26 G2 BB 6/1	-20 °C to 45 °C	60 °C
929003019704	450CC/LED/840/LS EX39 BB 3/1	-20 °C to 45 °C	42.5 °C
929003019804	450CC/LED/850/LS EX39 BB 3/1	-20 °C to 45 °C	42.5 °C

Order Code	Full Product Name	Ambient temperature range	T-Case Maximum (Nom)
929002998904	36CC/LED/830/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002999004	36CC/LED/840/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002999104	36CC/LED/850/LS EX39 G3 BB 3/1	-20 °C to 45 °C	60 °C
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	-20 °C to 45 °C	41 °C
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	-20 °C to 45 °C	41 °C
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	-20 °C to 55 °C	32.5 °C
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	-20 °C to 55 °C	32.5 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
929002999204	45CC/LED/830/LS EX39 G3 BB 3/1	Preset Dimming
929002999304	45CC/LED/840/LS EX39 G3 BB 3/1	Preset Dimming
929002999404	45CC/LED/850/LS EX39 G3 BB 3/1	Preset Dimming
929002999504	54CC/LED/830/LS EX39 G3 BB 3/1	Preset Dimming
929002999604	54CC/LED/840/LS EX39 G3 BB 3/1	Preset Dimming
929002999704	54CC/LED/850/LS EX39 G3 BB 3/1	Preset Dimming
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	Variac Dimming
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	Preset Dimming
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	Preset Dimming
929002996704	150CC/LED/840/LS EX39 G2 BB 3/1	Preset Dimming
929002996804	150CC/LED/850/LS EX39 G2 BB 3/1	Preset Dimming
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	Only with specific dimmers
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	Only with specific dimmers
929002999804	63CC/LED/830/LS EX39 G3 BB 3/1	Preset Dimming
929002999904	63CC/LED/840/LS EX39 G3 BB 3/1	Preset Dimming
929003000004	63CC/LED/850/LS EX39 G3 BB 3/1	Preset Dimming
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	Preset Dimming
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	Variac Dimming
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	No
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	No

Order Code	Full Product Name	Dimmable
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	No
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	Preset Dimming
929002996204	80CC/LED/850/LS EX39 G2 BB 3/1	Preset Dimming
929002395204	18CC/LED/830/ND E26 G2 BB 6/1	No
929002395304	18CC/LED/840/ND E26 G2 BB 6/1	No
929002395404	18CC/LED/850/ND E26 G2 BB 6/1	No
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	Variac Dimming
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	Preset Dimming
929002395504	27CC/LED/830/ND E26 G2 BB 6/1	No
929002395604	27CC/LED/840/ND E26 G2 BB 6/1	No
929002395704	27CC/LED/850/ND E26 G2 BB 6/1	No
929003019704	450CC/LED/840/LS EX39 BB 3/1	Preset Dimming
929003019804	450CC/LED/850/LS EX39 BB 3/1	Preset Dimming
929002998904	36CC/LED/830/LS EX39 G3 BB 3/1	Preset Dimming
929002999004	36CC/LED/840/LS EX39 G3 BB 3/1	Preset Dimming
929002999104	36CC/LED/850/LS EX39 G3 BB 3/1	Preset Dimming
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	Preset Dimming
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	Preset Dimming
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	Only with specific dimmers
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	Only with specific dimmers







Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002999204	45CC/LED/830/LS EX39 G3 BB 3/1	-
929002999304	45CC/LED/840/LS EX39 G3 BB 3/1	-
929002999404	45CC/LED/850/LS EX39 G3 BB 3/1	-
929002999504	54CC/LED/830/LS EX39 G3 BB 3/1	-











Order Code	Full Product Name	Energy Consumption kWh/1000 h
929002999604	54CC/LED/840/LS EX39 G3 BB 3/1	-
929002999704	54CC/LED/850/LS EX39 G3 BB 3/1	-
929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	-
929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	-

LED Corn Cobs

Order Code	Full Product Name	Energy Consumption kWh/1000 h
929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	-
929002996704	150CC/LED/840/LS EX39 G2 BB 3/1	-
929002996804	150CC/LED/850/LS EX39 G2 BB 3/1	-
929003507204	150CC/LED/840/LS EX39 G2 BB 277-480V 3/1	-
929003507304	150CC/LED/850/LS EX39 G2 BB 277-480V 3/1	-
929002999804	63CC/LED/830/LS EX39 G3 BB 3/1	-
929002999904	63CC/LED/840/LS EX39 G3 BB 3/1	-
929003000004	63CC/LED/850/LS EX39 G3 BB 3/1	-
929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	-
929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	-
929002395804	36CC/LED/830/ND E26 G2 BB 6/1	36 kWh
929002395904	36CC/LED/840/ND E26 G2 BB 6/1	36 kWh
929002396004	36CC/LED/850/ND E26 G2 BB 6/1	36 kWh
929002996104	80CC/LED/840/LS EX39 G2 BB 3/1	-
929002996204	80CC/LED/850/LS EX39 G2 BB 3/1	-
929002395204	18CC/LED/830/ND E26 G2 BB 6/1	18 kWh
929002395304	18CC/LED/840/ND E26 G2 BB 6/1	18 kWh
929002395404	18CC/LED/850/ND E26 G2 BB 6/1	18 kWh
929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	-
929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	-
929002395504	27CC/LED/830/ND E26 G2 BB 6/1	27 kWh
929002395604	27CC/LED/840/ND E26 G2 BB 6/1	27 kWh
929002395704	27CC/LED/850/ND E26 G2 BB 6/1	27 kWh
929003019704	450CC/LED/840/LS EX39 BB 3/1	-
929003019804	450CC/LED/850/LS EX39 BB 3/1	-
929002998904	36CC/LED/830/LS EX39 G3 BB 3/1	-
929002999004	36CC/LED/840/LS EX39 G3 BB 3/1	-
929002999104	36CC/LED/850/LS EX39 G3 BB 3/1	-
929002996404	115CC/LED/840/LS EX39 G2 BB 3/1	-
929002996504	115CC/LED/850/LS EX39 G2 BB 3/1	-
929003507004	115CC/LED/840/LS EX39 G2 BB 277-480V 3/1	-
929003507104	115CC/LED/850/LS EX39 G2 BB 277-480V 3/1	-



LED Corn Cobs



LED Corn Cobs

