



Reliable and vivid, easy to light

Essential SmartBright Spotlight

The Essential SmartBright Spotlight is an ideal solution for outdoor landscapes, parks, houses, parterres, wooded areas and heritage building lighting. It not only provides amazing and vivid light with compact and robust diecast aluminium housing and spiker but is also easy to install with one-step quick spike installation. Tempered glass enhances the durability of the fixture and accurate lens design ensures the light effects.

Benefits

- Easier installation
- Robust housing
- Vivid lighting

Features

- IP65 / IK06
- CRI80
- 15,000 hrs lifetime
- 168 hrs salt spray test
- CB and EMC compliant
- Beam angle options
- Mono green light option

Application

- Landscape, architectural lighting
- Plazas, squares
- Parking, parterres, trees, boscage
- Amenity
- Security

Essential SmartBright Spotlight

Versions



Product details



BGP150/151

Approval and Application

Mech. impact protection code IK06

Controls and Dimming

Dimmable No

General Information

Optical cover/lens type G

Driver included Yes

Flammability mark NO

Light source replaceable No

Initial Performance (IEC Compliant)

Init. Colour Rendering Index >80

Light Technical

Standard tilt angle posttop -

Mechanical and Housing

Colour Black

General Information

Order Code	Full Product Name	CE mark	Light source colour
911401755492	BGP150 LED520/WW 8W 20D	-	830 warm white
911401755652	BGP150 LED400/WW 6W 20D GM	CE mark	830 warm white
911401755692	BGP150 LED520/WW 8W 45D GM	CE mark	830 warm white
911401755702	BGP150 LED580/NW 8W 45D GM	CE mark	840 neutral white
911401755712	BGP150 LED400/WW 6W 45D GM	CE mark	830 warm white
911401755732	BGP150 LED250/WW 3W 45D GM	CE mark	830 warm white
911401755742	BGP150 LED300/NW 3W 45D GM	CE mark	840 neutral white

Initial Performance (IEC Compliant)

Essential SmartBright Spotlight

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401755492	BGP150 LED520/WW 8W 20D	3000 K	520 lm
911401755652	BGP150 LED400/WW 6W 20D	3000 K	400 lm
	GM		
911401755692	BGP150 LED520/WW 8W 45D	3000 K	520 lm
	GM		
911401755702	BGP150 LED580/NW 8W 45D	4000 K	520 lm
	GM		

Order Code	Full Product Name	Init. Corr. Colour Temperature	Initial luminous flux
911401755712	BGP150 LED400/WW 6W 45D	3000 K	400 lm
	GM		
911401755732	BGP150 LED250/WW 3W 45D	3000 K	250 lm
	GM		
911401755742	BGP150 LED300/NW 3W 45D	4000 K	250 lm
	GM		

