



Reliable and vivid, easy to light

Essential SmartBright Spotlight

The Essential SmartBright Spotlight is an ideal solution for outdoor landscapes, parks, houses, parterres, wooded areas and heritage building lighting. It not only provides amazing and vivid light with compact and robust diecast aluminium housing and spiker but is also easy to install with one-step quick spike installation. Tempered glass enhances the durability of the fixture and accurate lens design ensures the light effects.

Benefits

- Easier installation
- Robust housing
- Vivid lighting

Features

- IP65 / IK06
- CRI80
- 15,000 hrs lifetime
- 168 hrs salt spray test
- CB and EMC compliant
- Beam angle options
- Mono green light option

Application

- Landscape, architectural lighting
- Plazas, squares
- Parking, parterres, trees, boscage
- Amenity
- Security

Essential SmartBright Spotlight

Versions



Product details



BGP150/151

Accessories



Ordercode 911401755582

Essential SmartBright Spotlight

Approval and Application	
Mech. impact protection code	IK06
Controls and Dimming	
Dimmable	No
General Information	
Optical cover/lens type	Glass
Driver included	Yes
Flammability mark	-
Light source replaceable	No
Light Technical	
Standard tilt angle posttop	-
Mechanical and Housing	
Colour	Black

General Information

Order Code	Full Product Name	CE mark	Light source colour
911401755592	BGP151 LED520/WW 8W 20D	-	830 warm white
911401755602	BGP151 LED580/NW 8W 20D	-	840 neutral white
911401755612	BGP151 LED250/WW 3W 20D	-	830 warm white
911401755622	BGP151 LED300/NW 3W 20D	-	840 neutral white
911401755632	BGP150 LED520/WW 8W 20D GM	CE mark	830 warm white
911401755642	BGP150 LED580/NW 8W 20D GM	CE mark	840 neutral white
911401755652	BGP150 LED400/WW 6W 20D GM	CE mark	830 warm white
911401755662	BGP150 LED480/NW 6W 20D GM	CE mark	840 neutral white
911401755672	BGP150 LED250/WW 3W 20D GM	CE mark	830 warm white
911401755682	BGP150 LED300/NW 3W 20D GM	CE mark	840 neutral white
911401755692	BGP150 LED520/WW 8W 45D GM	CE mark	830 warm white
911401755702	BGP150 LED580/NW 8W 45D GM	CE mark	840 neutral white
911401755712	BGP150 LED400/WW 6W 45D GM	CE mark	830 warm white
911401755722	BGP150 LED480/NW 6W 45D GM	CE mark	840 neutral white
911401755732	BGP150 LED250/WW 3W 45D GM	CE mark	830 warm white
911401755742	BGP150 LED300/NW 3W 45D GM	CE mark	840 neutral white
911401755752	BGP150 LED G 8W 35D GM	CE mark	Green

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401755592	BGP151 LED520/WW 8W 20D	3000 K	>80	520 lm
911401755602	BGP151 LED580/NW 8W 20D	4000 K	>80	520 lm
911401755612	BGP151 LED250/WW 3W 20D	3000 K	>80	250 lm
911401755622	BGP151 LED300/NW 3W 20D	4000 K	>80	250 lm
911401755632	BGP150 LED520/WW 8W 20D GM	3000 K	>80	520 lm
911401755642	BGP150 LED580/NW 8W 20D GM	4000 K	>80	520 lm
911401755652	BGP150 LED400/WW 6W 20D GM	3000 K	>80	400 lm
911401755662	BGP150 LED480/NW 6W 20D GM	4000 K	>80	400 lm
911401755672	BGP150 LED250/WW 3W 20D GM	3000 K	>80	250 lm

Order Code	Full Product Name	Init. Colour		
		Init. Corr. Colour Temperature	Rendering Index	Initial luminous flux
911401755682	BGP150 LED300/NW 3W 20D GM	4000 K	>80	250 lm
911401755692	BGP150 LED520/WW 8W 45D GM	3000 K	>80	520 lm
911401755702	BGP150 LED580/NW 8W 45D GM	4000 K	>80	520 lm
911401755712	BGP150 LED400/WW 6W 45D GM	3000 K	>80	400 lm
911401755722	BGP150 LED480/NW 6W 45D GM	4000 K	>80	400 lm
911401755732	BGP150 LED250/WW 3W 45D GM	3000 K	>80	250 lm
911401755742	BGP150 LED300/NW 3W 45D GM	4000 K	>80	250 lm
911401755752	BGP150 LED G 8W 35D GM	- K	N.A.	400 lm

