



Elegant and Brighter

UNIBollard

UNIBollard is dedicated to light up public environments of park, buildings outside area, compound areas to bring you a more bright light in evening with the safety and convenience. Its graceful appearance is also a part of public scenery to beautify area you live.

Benefits

- Long-lasting working period
- IP68 connector for easy connection and reliability
- Anti-UV cover without concerns of yellowing

Features

- 0.3M (0.45M) / 0.6M / 1.2M height for option
- Up to 1100 lm
- CRI80
- Look and feel: cylinder and cubic housing for alternatives
- 50K hours L70B50 @ ta 35°C


Application

- Public spaces
- Residential gardens, paths

Warnings and Safety

- Use additional surge protection device in electrical circuit for lighting wiring.

Versions



Dimensional drawing



General Information	
CE mark	-
Driver included	Yes
Flammability mark	-
Light source replaceable	No
Light Technical	
Light source color	830 warm white
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	>80
Standard tilt angle posttop	-
Controls and Dimming	
Dimmable	No
Approval and Application	
Mech. impact protection code	IK06
Ingress protection code	IP65

Order Code	Full Product Name	Optical cover type	Luminous Flux
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	Polycarbonate bowl/cover opal	1,000 lm
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Polycarbonate bowl/cover frosted	760 lm
911401755252	BCP212 LED1000/WW 13W 100-240V Rec	Polycarbonate bowl/cover opal	1,000 lm
AL			

Operating and Electrical

Order Code	Full Product Name	Power Consumption
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	15 W

Order Code	Full Product Name	Power Consumption
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	13 W

Order Code	Full Product Name	Power Consumption
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	15 W

Order Code	Full Product Name	Power Consumption
911401755252	BCP212 LED1000/WW 13W 100-240V Rec AL	13 W

Mechanical and Housing

Order Code	Full Product Name	Housing Color
911401755262	BCP310 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
911401755242	BCP211 LED1000/WW 13W 100-240V Rec AL	Aluminum and white

Order Code	Full Product Name	Housing Color
911401755272	BCP311 LED760/WW 15W 100-240V Cyl BK	Black and aluminum
911401755252	BCP212 LED1000/WW 13W 100-240V Rec AL	Aluminum and white

