



Full Range Recessed Up-light to Make Your Space Distinctive

UNIlIn-ground

UNIlIn-ground family provide a completed range of up-lights in terms of wattage, beam angle, colour temperature, etc. It is to make your space distinctive, safer and more convenient as well. Compact and robust design with aluminium housing, waterproof connectors ensure long-lasting operation without the need for more care after installation. Waterproof connectors allow easier installation and reduce your installation cost. Apart from high-quality white light, RGB (and mono RGB) are available with DMX512 decoder built-in side.

Benefits

- Easy to opt
- Quick installation
- Long lifespan
- Robust design for severe conditions

Features

- wide range of wattage from 1 W to 36 W
- more options on light beam angle
- warm white is standard and neutral white, RGB and mono RGB is customised
- compact design and lower height of fittings
- IK67, IP67 rated, pass 20 KN static load and 500 hrs salty-spray test passed
- working temperature -40 °C to +50 °C

Application

- Public spaces
- Vertical architectural surfaces
- Playgrounds