



UrbanSpark all in onesolar post top lantern

UrbanSpark

Integrated solar post top lantern with Lithium Ferro Phosphate battery, vertically mounted mono-crystalline solar panel and MPPT charger. Extruded aluminium construction for sturdiness and long life. Choice of street light and post top optics and pole height of 4 & 6 metres. Charger and battery accommodated inside the pole and accessible through service hatch for ease of maintenance. Vertically mounted panels on all four sides to catch sunlight throughout the day. IP-68 battery to prevent damage in case of water logging.

Benefits

- Brings light to areas without access to electric grid
- Elegant design
- Preserves landscape as no trenching for cabling required
- Saves energy
- Environment friendly

Features

- Replaceable IP-68 Lithium Ferro Phosphate battery for long life and hassle free operations
- MPPT charge controller for maximum efficiency
- Sturdy aluminium alloy construction for sturdiness and long life
- Factory set dimming profile for run time maximisation

Application

- Cities
- Office campuses
- Parks
- Residential Societies
- Heritage Roads

Versions



Accessories



Ordercode 911401800602,
911401800702

Controls and Dimming

Order Code	Full Product Name	Dimmable
10111051	BGP161 LED2500/NW 12V SD 4.0M 7043 CC	Yes
10111071	BGP161 LED2500/NW 12V SD 4.0M 9006 CC	Yes
01800502	BDP301 LED 6M 7043	-

Order Code	Full Product Name	Dimmable
01800802	BDP301 LED 4M 7043	-
01897201	BDP301 LED 4M 9006	-
01897301	BDP301 LED 6M 9006	-

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour Rendering Index
10111051	BGP161 LED2500/NW 12V SD 4.0M 7043 CC	4000 K	>70
10111071	BGP161 LED2500/NW 12V SD 4.0M 9006 CC	4000 K	>70

Order Code	Full Product Name	Init. Corr. Colour Temperature	Init. Colour Rendering Index
01800502	BDP301 LED 6M 7043	-	-
01800802	BDP301 LED 4M 7043	-	-
01897201	BDP301 LED 4M 9006	-	-
01897301	BDP301 LED 6M 9006	-	-

Mechanical and Housing

Order Code	Full Product Name	Colour
10111051	BGP161 LED2500/NW 12V SD 4.0M 7043 CC	RAL 7043
10111071	BGP161 LED2500/NW 12V SD 4.0M 9006 CC	RAL 9006
01800502	BDP301 LED 6M 7043	RAL 7043

Order Code	Full Product Name	Colour
01800802	BDP301 LED 4M 7043	RAL 7043
01897201	BDP301 LED 4M 9006	RAL 9006
01897301	BDP301 LED 6M 9006	RAL 9006

