



# Sturdy and Reliable versatile lighting solution

## EnduraLED Bulkhead

EnduraLED Bulkhead luminaire is a sustainable and reliable offering for indoor or semi-outdoor public area with IP66 ingress protection. The product offers two lumen packs with two different CCT's and suitable for versatile applications such as staircases, industrial areas, circulation areas, lift wells etc. Pressure die cast housing and high impact resistance polycarbonate cover make this bulkhead maintenance free solution for heavy duty industries.

### Benefits

### Features

### Application

### Warnings and Safety

# EnduraLED Bulkhead

## Versions



### WT202W

#### Application Conditions

Ambient temperature range 0 to +45 °C

#### Approval and Application

Mech. impact protection code IK09

Ingress protection code IP66

#### Controls and Dimming

Dimmable No

#### Operating and Electrical

Input Voltage 140–270 V

#### General Information

Beam angle of light source 120 °

Protection class IEC Safety class I

Optical cover/lens type Polycarbonate

Driver included Yes

Flammability mark For mounting on normally flammable surfaces

Optic type Beam angle 120°

#### Initial Performance (IEC Compliant)

Initial chromaticity <5

Init. Color Rendering Index >80

Initial LED luminaire efficacy 110 lm/W

#### Mechanical and Housing

Color Gray

#### Initial Performance (IEC Compliant)

Order Code	Full Product Name	Init. Corr. Color Temperature	Initial luminous flux	Initial input power
919515813250	WT202W LED10S CW PSU S3 PC	6500 K	1100 lm	10 W
919515813251	WT202W LED10S NW PSU S3 PC	4000 K	1100 lm	10 W
919515813252	WT202W LED6S CW PSU S3 PC	6500 K	700 lm	6 W
919515813253	WT202W LED6S NW PSU S3 PC	4000 K	700 lm	6 W

## EnduraLED Bulkhead

