



Elegant outlook design projector for the retail segment

Truefashion Projector GCGM

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Benefits

- Slim and compact outlook design with inside track driver.
- Excellent light quality of punch effect.
- Dedicated light recipe for fashion and food.
- System connectivity with Dali-VLC.

Features

- Lumen packages (1000/2000/3000/4000lm).
- 3 beams options (NB/MB/WB).
- Dali-VLC Control.
- Track version available in 1C, 3C.
- CB, EMC, CCC, ACC.
- Lifetime 50K Hours.

Application

- Retail fashion store
- Shopping mall
- Food & large retail

Warnings and Safety

- 3 years

Truefashion Projector GCGM

Specifications

Type	ST700T: Tracklight
	RS700B: recessed round
	GD700B: recessed square
Mounting type	Track installation
	Recessed
Operating Temperature range	-15 to +35°C
Light Source	COB
Mains Voltage	220-240V AC/ 50-60Hz
Dimming	PSD: Dimmable via Dali protocol
Control system input	DALI
Material	Housing: die-cast aluminum
Main color of the luminaire	White RAL9003 / Black RAL9011
Lumen maintenance at median useful life	L70 50.000h

Luminous flux	1000lm - 4000lm
Power consumption	8.2W - 40.3W
Correlated color temperature - CCT	3000K,4000K,Premium White, Premium Color
Color Rendering index -	80/90
CRI	
Beam angle	VNB(Very Narrow Beam): 11°
	NB (Narrow Beam): 13-19°
	MB (Medium Beam): 23-24°
	WB (Wide Beam): 30-34°
Protection Class	Class II
IEC61140	
Ingress protection	IP20
Installation	Track
	Recessed

Versions



RS700B LED10 LED20 BK



GD700B 1 head BK



RS700B LED30 40 WH




GD700B 2 heads WH



GD700B 2 heads BK

Dimensional drawing



General Information	
CE mark	CE mark
ENEC mark	-
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Controls and Dimming	
Dimmable	No
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	-
Ingress protection code	IP20
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

General Information

Order Code	Full Product Name	Driver included	Light source replaceable	Number of gear units
01520171	RS700B LED20 930PW PSU NB BK	-	-	-
52115500	GD700B LED10 830 PSU MB WH	-	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-	-
01518471	GD700B LED10 830 PSU MB BK	-	-	-
73101100	GD700B LED20 930PW PSU MB BK	-	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-	-
01522171	RS700B LED40 930PC PSU MB WH	-	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	Yes	No	1 unit
01546761	ST700T LED20 930PC PSU MB 1C WH	Yes	No	1 unit
01546861	ST700T LED20 930PC PSU WB 1C WH	Yes	No	1 unit
01547061	ST700T LED20 930PC PSU MB 1C BK	Yes	No	1 unit
01547261	ST700T LED30 930PC PSU MB 1C WH	Yes	No	1 unit
01547361	ST700T LED30 930PC PSU WB 1C WH	Yes	No	1 unit
01547461	ST700T LED30 930PC PSU MB 1C BK	Yes	No	1 unit
01547661	ST700T LED40 930PC PSU MB 1C WH	Yes	No	1 unit
01547761	ST700T LED40 930PC PSU WB 1C WH	Yes	No	1 unit
01547861	ST700T LED40 930PC PSU MB 1C BK	Yes	No	1 unit
01548161	ST700T LED20 930PC PSU MB 1C BK HB	Yes	No	1 unit
01561761	ST700T LED10 830 PSU WB 1C WH	Yes	No	1 unit
01561961	ST700T LED10 830 PSU WB 1C BK	Yes	No	1 unit
01562161	ST700T LED20 830 PSU WB 1C WH	Yes	No	1 unit
52111700	GD700B 2XLED10 830 PSU MB WH	-	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-	-
51947300	GD700B 2XLED10 830 PSU MB BK	-	-	-

Light Technical (1/2)

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
01520171	RS700B LED20 930PW PSU NB BK	-	3000 K	Lens	>90
52115500	GD700B LED10 830 PSU MB WH	-	3000 K	Lens	>80

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
01518571	GD700B LED20 930PW PSU MB WH	-	3000 K	Lens	>90

Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
01530571	GD700B LED20 940PW PSU MB WH HB	-	4000 K	Lens	>90
01575561	ST700T LED30 930PW PSU MB 3C BK	-	3000 K	Fashion proof optic beam angle 24°	>90
01576061	ST700T LED30 930PW PSD VLC WB BK	-	3000 K	Fashion proof optic beam angle 36°	>90
01576261	ST700T LED30 930PW PSD VLC WB WH	-	3000 K	Fashion proof optic beam angle 36°	>90
01518471	GD700B LED10 830 PSU MB BK	-	3000 K	Lens	>80
73101100	GD700B LED20 930PW PSU MB BK	-	3000 K	Lens	>90
01520771	RS700B LED30 930PW PSU MB WH	-	3000 K	Lens	>90
01520871	RS700B LED30 930PW PSU WB WH	-	3000 K	Lens	>90
01520971	RS700B LED30 940PW PSU MB WH	-	4000 K	Lens	>90
01521471	RS700B LED30 930PC PSU MB WH	-	3000 K	Lens	>90
01521771	RS700B LED40 940PW PSU MB WH	-	4000 K	Lens	>90
01522171	RS700B LED40 930PC PSU MB WH	-	3000 K	Lens	>90
01519471	RS700B LED10 830 PSU MB WH	-	3000 K	Lens	>80
01519571	RS700B LED10 830 PSU WB WH	-	3000 K	Lens	>80
01519871	RS700B LED20 930PW PSU MB WH	-	3000 K	Lens	>90
01519971	RS700B LED20 930PW PSU WB WH	-	3000 K	Lens	>90

Order Code	Full Product Name	Beam angle of light source	Correlated Color Temperature (Nom)	Optical cover type	Color rendering index (CRI)
01520071	RS700B LED20 940PW PSU MB WH	-	4000 K	Lens	>90
01546661	ST700T LED20 930PC PSU NB 1C WH	120 degree(s)	3000 K	Lens	>90
01546761	ST700T LED20 930PC PSU MB 1C WH	120 degree(s)	3000 K	Lens	>90
01546861	ST700T LED20 930PC PSU WB 1C WH	120 degree(s)	3000 K	Lens	>90
01547061	ST700T LED20 930PC PSU MB 1C BK	120 degree(s)	3000 K	Lens	>90
01547261	ST700T LED30 930PC PSU MB 1C WH	120 degree(s)	3000 K	Lens	>90
01547361	ST700T LED30 930PC PSU WB 1C WH	120 degree(s)	3000 K	Lens	>90
01547461	ST700T LED30 930PC PSU MB 1C BK	120 degree(s)	3000 K	Lens	>90
01547661	ST700T LED40 930PC PSU MB 1C WH	120 degree(s)	3000 K	Lens	>90
01547761	ST700T LED40 930PC PSU WB 1C WH	120 degree(s)	3000 K	Lens	>90
01547861	ST700T LED40 930PC PSU MB 1C BK	120 degree(s)	3000 K	Lens	>90
01548161	ST700T LED20 930PC PSU MB 1C BK HB	120 degree(s)	3000 K	Lens	>90
01561761	ST700T LED10 830 PSU WB 1C WH	120 degree(s)	3000 K	Lens	>80
01561961	ST700T LED10 830 PSU WB 1C BK	120 degree(s)	3000 K	Lens	>80
01562161	ST700T LED20 830 PSU WB 1C WH	120 degree(s)	3000 K	Lens	>80
52111700	GD700B 2XLED10 830 PSU MB WH	-	3000 K	Lens	>80
01518971	GD700B 2XLED20 930PW PSU MB WH	-	3000 K	Lens	>90
51947300	GD700B 2XLED10 830 PSU MB BK	-	3000 K	Lens	>80

Light Technical (2/2)

Order Code	Full Product Name	Luminous Efficacy (rated)	Luminous Flux	Optic type
		(Nom)		
01520171	RS700B LED20 930PW PSU NB BK	79 lm/W	1,685 lm	-
52115500	GD700B LED10 830 PSU MB WH	114 lm/W	942 lm	-
01518571	GD700B LED20 930PW PSU MB WH	79 lm/W	1,685 lm	-
01530571	GD700B LED20 940PW PSU MB WH HB	56 lm/W	1,184 lm	-
01575561	ST700T LED30 930PW PSU MB 3C BK	85 lm/W	3,168.44 lm	-
01576061	ST700T LED30 930PW PSD VLC WB BK	85 lm/W	3,001.68 lm	-
01576261	ST700T LED30 930PW PSD VLC WB WH	85 lm/W	3,001.68 lm	-
01518471	GD700B LED10 830 PSU MB BK	114 lm/W	942 lm	-
73101100	GD700B LED20 930PW PSU MB BK	79 lm/W	1,685 lm	-
01520771	RS700B LED30 930PW PSU MB WH	92 lm/W	2,844 lm	-
01520871	RS700B LED30 930PW PSU WB WH	91 lm/W	2,809 lm	-
01520971	RS700B LED30 940PW PSU MB WH	100 lm/W	3,076 lm	-
01521471	RS700B LED30 930PC PSU MB WH	87 lm/W	2,669 lm	-
01521771	RS700B LED40 940PW PSU MB WH	100 lm/W	4,025 lm	-
01522171	RS700B LED40 930PC PSU MB WH	85 lm/W	3,429 lm	-
01519471	RS700B LED10 830 PSU MB WH	114 lm/W	942 lm	-
01519571	RS700B LED10 830 PSU WB WH	108 lm/W	886 lm	-
01519871	RS700B LED20 930PW PSU MB WH	79 lm/W	1,685 lm	-
01519971	RS700B LED20 930PW PSU WB WH	75 lm/W	1,586 lm	-

Order Code	Full Product Name	Luminous Efficacy (rated)	Luminous Flux	Optic type
		(Nom)		
01520071	RS700B LED20 940PW PSU MB WH	86 lm/W	1,829 lm	-
01546661	ST700T LED20 930PC PSU NB 1C WH	72.1 lm/W	1,604.8 lm	Beam angle 15°
01546761	ST700T LED20 930PC PSU MB 1C WH	72.1 lm/W	1,604.8 lm	Beam angle 24°
01546861	ST700T LED20 930PC PSU WB 1C WH	67.9 lm/W	1,510.4 lm	Beam angle 30°
01547061	ST700T LED20 930PC PSU MB 1C BK	72.1 lm/W	1,604.8 lm	Beam angle 24°
01547261	ST700T LED30 930PC PSU MB 1C WH	70.5 lm/W	2,684.72 lm	Beam angle 23°
01547361	ST700T LED30 930PC PSU WB 1C WH	67.6 lm/W	2,575.9 lm	Beam angle 33°
01547461	ST700T LED30 930PC PSU MB 1C BK	70.5 lm/W	2,684.72 lm	Beam angle 23°
01547661	ST700T LED40 930PC PSU MB 1C WH	75.3 lm/W	3,299.16 lm	Beam angle 24°
01547761	ST700T LED40 930PC PSU WB 1C WH	71.4 lm/W	3,125.52 lm	Beam angle 34°
01547861	ST700T LED40 930PC PSU MB 1C BK	75.3 lm/W	3,299.16 lm	Beam angle 24°
01548161	ST700T LED20 930PC PSU MB 1C BK HB	46.7 lm/W	1,038.4 lm	Beam angle 21°
01561761	ST700T LED10 830 PSU WB 1C WH	101 lm/W	1,079.2 lm	Beam angle 30°
01561961	ST700T LED10 830 PSU WB 1C BK	101 lm/W	1,079.2 lm	Beam angle 30°
01562161	ST700T LED20 830 PSU WB 1C WH	86.7 lm/W	1,930.4 lm	Beam angle 30°
52111700	GD700B 2XLED10 830 PSU MB WH	114 lm/W	1,884 lm	-
01518971	GD700B 2XLED20 930PW PSU MB WH	79 lm/W	3,369 lm	-
51947300	GD700B 2XLED10 830 PSU MB BK	114 lm/W	1,884 lm	-

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01520171	RS700B LED20 930PW PSU NB BK	21 W
52115500	GD700B LED10 830 PSU MB WH	8 W
01518571	GD700B LED20 930PW PSU MB WH	21 W
01530571	GD700B LED20 940PW PSU MB WH HB	21 W
01575561	ST700T LED30 930PW PSU MB 3C BK	37.1 W
01576061	ST700T LED30 930PW PSD VLC WB BK	35 W

Order Code	Full Product Name	Power Consumption
01576261	ST700T LED30 930PW PSD VLC WB WH	35 W
01518471	GD700B LED10 830 PSU MB BK	8 W
73101100	GD700B LED20 930PW PSU MB BK	21 W
01520771	RS700B LED30 930PW PSU MB WH	31 W
01520871	RS700B LED30 930PW PSU WB WH	31 W
01520971	RS700B LED30 940PW PSU MB WH	31 W

Truefashion Projector GCGM

Order Code	Full Product Name	Power Consumption
01521471	RS700B LED30 930PC PSU MB WH	31 W
01521771	RS700B LED40 940PW PSU MB WH	40 W
01522171	RS700B LED40 930PC PSU MB WH	40 W
01519471	RS700B LED10 830 PSU MB WH	8 W
01519571	RS700B LED10 830 PSU WB WH	8 W
01519871	RS700B LED20 930PW PSU MB WH	21 W
01519971	RS700B LED20 930PW PSU WB WH	21 W
01520071	RS700B LED20 940PW PSU MB WH	21 W
01546661	ST700T LED20 930PC PSU NB 1C WH	22.3 W
01546761	ST700T LED20 930PC PSU MB 1C WH	22.3 W
01546861	ST700T LED20 930PC PSU WB 1C WH	22.3 W
01547061	ST700T LED20 930PC PSU MB 1C BK	22.3 W
01547261	ST700T LED30 930PC PSU MB 1C WH	38.1 W

Order Code	Full Product Name	Power Consumption
01547361	ST700T LED30 930PC PSU WB 1C WH	38.1 W
01547461	ST700T LED30 930PC PSU MB 1C BK	38.1 W
01547661	ST700T LED40 930PC PSU MB 1C WH	43.8 W
01547761	ST700T LED40 930PC PSU WB 1C WH	43.8 W
01547861	ST700T LED40 930PC PSU MB 1C BK	43.8 W
01548161	ST700T LED20 930PC PSU MB 1C BK HB	22.3 W
01561761	ST700T LED10 830 PSU WB 1C WH	10.7 W
01561961	ST700T LED10 830 PSU WB 1C BK	10.7 W
01562161	ST700T LED20 830 PSU WB 1C WH	22.3 W
52111700	GD700B 2XLED10 830 PSU MB WH	16 W
01518971	GD700B 2XLED20 930PW PSU MB WH	42 W
51947300	GD700B 2XLED10 830 PSU MB BK	16 W

Temperature

Order Code	Full Product Name	Ambient temperature range
01520171	RS700B LED20 930PW PSU NB BK	-15 to +35 °C
52115500	GD700B LED10 830 PSU MB WH	-15 to +35 °C
01518571	GD700B LED20 930PW PSU MB WH	-15 to +35 °C
01530571	GD700B LED20 940PW PSU MB WH HB	-15 to +35 °C
01575561	ST700T LED30 930PW PSU MB 3C BK	-20 to +35 °C
01576061	ST700T LED30 930PW PSD VLC WB BK	-20 to +35 °C
01576261	ST700T LED30 930PW PSD VLC WB WH	-20 to +35 °C
01518471	GD700B LED10 830 PSU MB BK	-15 to +35 °C
73101100	GD700B LED20 930PW PSU MB BK	-15 to +35 °C
01520771	RS700B LED30 930PW PSU MB WH	-15 to +35 °C
01520871	RS700B LED30 930PW PSU WB WH	-15 to +35 °C
01520971	RS700B LED30 940PW PSU MB WH	-15 to +35 °C
01521471	RS700B LED30 930PC PSU MB WH	-15 to +35 °C
01521771	RS700B LED40 940PW PSU MB WH	-15 to +35 °C
01522171	RS700B LED40 930PC PSU MB WH	-15 to +35 °C
01519471	RS700B LED10 830 PSU MB WH	-15 to +35 °C
01519571	RS700B LED10 830 PSU WB WH	-15 to +35 °C
01519871	RS700B LED20 930PW PSU MB WH	-15 to +35 °C
01519971	RS700B LED20 930PW PSU WB WH	-15 to +35 °C

Order Code	Full Product Name	Ambient temperature range
01520071	RS700B LED20 940PW PSU MB WH	-15 to +35 °C
01546661	ST700T LED20 930PC PSU NB 1C WH	-20 to +35 °C
01546761	ST700T LED20 930PC PSU MB 1C WH	-20 to +35 °C
01546861	ST700T LED20 930PC PSU WB 1C WH	-20 to +35 °C
01547061	ST700T LED20 930PC PSU MB 1C BK	-20 to +35 °C
01547261	ST700T LED30 930PC PSU MB 1C WH	-20 to +35 °C
01547361	ST700T LED30 930PC PSU WB 1C WH	-20 to +35 °C
01547461	ST700T LED30 930PC PSU MB 1C BK	-20 to +35 °C
01547661	ST700T LED40 930PC PSU MB 1C WH	-20 to +35 °C
01547761	ST700T LED40 930PC PSU WB 1C WH	-20 to +35 °C
01547861	ST700T LED40 930PC PSU MB 1C BK	-20 to +35 °C
01548161	ST700T LED20 930PC PSU MB 1C BK HB	-20 to +35 °C
01561761	ST700T LED10 830 PSU WB 1C WH	-20 to +35 °C
01561961	ST700T LED10 830 PSU WB 1C BK	-20 to +35 °C
01562161	ST700T LED20 830 PSU WB 1C WH	-20 to +35 °C
52111700	GD700B 2XLED10 830 PSU MB WH	-15 to +35 °C
01518971	GD700B 2XLED20 930PW PSU MB WH	-15 to +35 °C
51947300	GD700B 2XLED10 830 PSU MB BK	-15 to +35 °C

Mechanical and Housing

Order Code	Full Product Name	Housing Color
01520171	RS700B LED20 930PW PSU NB BK	Black
52115500	GD700B LED10 830 PSU MB WH	White RAL 9003
01518571	GD700B LED20 930PW PSU MB WH	White RAL 9003
01530571	GD700B LED20 940PW PSU MB WH HB	White RAL 9003
01575561	ST700T LED30 930PW PSU MB 3C BK	White and black
01576061	ST700T LED30 930PW PSD VLC WB BK	White and black
01576261	ST700T LED30 930PW PSD VLC WB WH	White and black
01518471	GD700B LED10 830 PSU MB BK	Black
73101100	GD700B LED20 930PW PSU MB BK	Black
01520771	RS700B LED30 930PW PSU MB WH	White RAL 9003
01520871	RS700B LED30 930PW PSU WB WH	White RAL 9003

Order Code	Full Product Name	Housing Color
01520971	RS700B LED30 940PW PSU MB WH	White RAL 9003
01521471	RS700B LED30 930PC PSU MB WH	White RAL 9003
01521771	RS700B LED40 940PW PSU MB WH	White RAL 9003
01522171	RS700B LED40 930PC PSU MB WH	White RAL 9003
01519471	RS700B LED10 830 PSU MB WH	White RAL 9003
01519571	RS700B LED10 830 PSU WB WH	White RAL 9003
01519871	RS700B LED20 930PW PSU MB WH	White RAL 9003
01519971	RS700B LED20 930PW PSU WB WH	White RAL 9003
01520071	RS700B LED20 940PW PSU MB WH	White RAL 9003
01546661	ST700T LED20 930PC PSU NB 1C WH	White
01546761	ST700T LED20 930PC PSU MB 1C WH	White

Order Code	Full Product Name	Housing Color
01546861	ST700T LED20 930PC PSU WB 1C WH	White
01547061	ST700T LED20 930PC PSU MB 1C BK	Black
01547261	ST700T LED30 930PC PSU MB 1C WH	White
01547361	ST700T LED30 930PC PSU WB 1C WH	White
01547461	ST700T LED30 930PC PSU MB 1C BK	Black
01547661	ST700T LED40 930PC PSU MB 1C WH	White
01547761	ST700T LED40 930PC PSU WB 1C WH	White
01547861	ST700T LED40 930PC PSU MB 1C BK	Black

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01520171	RS700B LED20 930PW PSU NB BK	-
52115500	GD700B LED10 830 PSU MB WH	-
01518571	GD700B LED20 930PW PSU MB WH	-
01530571	GD700B LED20 940PW PSU MB WH HB	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-
01518471	GD700B LED10 830 PSU MB BK	-
73101100	GD700B LED20 930PW PSU MB BK	-
01520771	RS700B LED30 930PW PSU MB WH	-
01520871	RS700B LED30 930PW PSU WB WH	-
01520971	RS700B LED30 940PW PSU MB WH	-
01521471	RS700B LED30 930PC PSU MB WH	-
01521771	RS700B LED40 940PW PSU MB WH	-
01522171	RS700B LED40 930PC PSU MB WH	-
01519471	RS700B LED10 830 PSU MB WH	-
01519571	RS700B LED10 830 PSU WB WH	-
01519871	RS700B LED20 930PW PSU MB WH	-
01519971	RS700B LED20 930PW PSU WB WH	-

Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
01520171	RS700B LED20 930PW PSU NB BK	-	-	-
52115500	GD700B LED10 830 PSU MB WH	-	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-	-

Order Code	Full Product Name	Housing Color
01548161	ST700T LED20 930PC PSU MB 1C BK HB	Black
01561761	ST700T LED10 830 PSU WB 1C WH	White
01561961	ST700T LED10 830 PSU WB 1C BK	Black
01562161	ST700T LED20 830 PSU WB 1C WH	White
52111700	GD700B 2XLED10 830 PSU MB WH	White RAL 9003
01518971	GD700B 2XLED20 930PW PSU MB WH	White RAL 9003
51947300	GD700B 2XLED10 830 PSU MB BK	Black

Order Code	Full Product Name	Initial chromaticity
01520071	RS700B LED20 940PW PSU MB WH	-
01546661	ST700T LED20 930PC PSU NB 1C WH	(0.422, 0.386) SDCM<3
01546761	ST700T LED20 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01546861	ST700T LED20 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547061	ST700T LED20 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01547261	ST700T LED30 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01547361	ST700T LED30 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547461	ST700T LED30 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01547661	ST700T LED40 930PC PSU MB 1C WH	(0.422, 0.386) SDCM<3
01547761	ST700T LED40 930PC PSU WB 1C WH	(0.422, 0.386) SDCM<3
01547861	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386) SDCM<3
01548161	ST700T LED20 930PC PSU MB 1C BK HB	(0.422, 0.386) SDCM<3
01561761	ST700T LED10 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3
01561961	ST700T LED10 830 PSU WB 1C BK	(0.434, 0.403) SDCM<3
01562161	ST700T LED20 830 PSU WB 1C WH	(0.434, 0.403) SDCM<3
52111700	GD700B 2XLED10 830 PSU MB WH	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-
51947300	GD700B 2XLED10 830 PSU MB BK	-

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
01518471	GD700B LED10 830 PSU MB BK	-	-	-
73101100	GD700B LED20 930PW PSU MB BK	-	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-	-

Truefashion Projector GCGM

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
01522171	RS700B LED40 930PC PSU MB WH	-	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-	-
01519971	RS700B LED20 930PW PSU WB WH	-	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01546761	ST700T LED20 930PC PSU MB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01546861	ST700T LED20 930PC PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01547061	ST700T LED20 930PC PSU MB 1C BK	0.14 %	50,000 hour(s)	32,600 hour(s)
01547261	ST700T LED30 930PC PSU MB 1C WH	0.14 %	45,000 hour(s)	21,200 hour(s)
01547361	ST700T LED30 930PC PSU WB 1C WH	0.14 %	45,000 hour(s)	21,200 hour(s)

Order Code	Full Product Name	Driver failure rate at 5000 h	Median useful life L80B50	Median useful life L90B50
01547461	ST700T LED30 930PC PSU MB 1C BK	0.14 %	45,000 hour(s)	21,200 hour(s)
01547661	ST700T LED40 930PC PSU MB 1C WH	0.23 %	38,700 hour(s)	18,200 hour(s)
01547761	ST700T LED40 930PC PSU WB 1C WH	0.23 %	38,700 hour(s)	18,200 hour(s)
01547861	ST700T LED40 930PC PSU MB 1C BK	0.23 %	38,700 hour(s)	18,200 hour(s)
01548161	ST700T LED20 930PC PSU MB 1C BK HB	0.14 %	50,000 hour(s)	32,600 hour(s)
01561761	ST700T LED10 830 PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
01561961	ST700T LED10 830 PSU WB 1C BK	0.14 %	50,000 hour(s)	32,600 hour(s)
01562161	ST700T LED20 830 PSU WB 1C WH	0.14 %	50,000 hour(s)	32,600 hour(s)
52111700	GD700B 2XLED10 830 PSU MB WH	-	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-	-
51947300	GD700B 2XLED10 830 PSU MB BK	-	-	-

Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
01520171	RS700B LED20 930PW PSU NB BK	-	-
52115500	GD700B LED10 830 PSU MB WH	-	-
01518571	GD700B LED20 930PW PSU MB WH	-	-
01530571	GD700B LED20 940PW PSU MB WH HB	-	-
01575561	ST700T LED30 930PW PSU MB 3C BK	-	-
01576061	ST700T LED30 930PW PSD VLC WB BK	-	-
01576261	ST700T LED30 930PW PSD VLC WB WH	-	-
01518471	GD700B LED10 830 PSU MB BK	-	-
73101100	GD700B LED20 930PW PSU MB BK	-	-
01520771	RS700B LED30 930PW PSU MB WH	-	-
01520871	RS700B LED30 930PW PSU WB WH	-	-
01520971	RS700B LED30 940PW PSU MB WH	-	-
01521471	RS700B LED30 930PC PSU MB WH	-	-
01521771	RS700B LED40 940PW PSU MB WH	-	-
01522171	RS700B LED40 930PC PSU MB WH	-	-
01519471	RS700B LED10 830 PSU MB WH	-	-
01519571	RS700B LED10 830 PSU WB WH	-	-
01519871	RS700B LED20 930PW PSU MB WH	-	-

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
01519971	RS700B LED20 930PW PSU WB WH	-	-
01520071	RS700B LED20 940PW PSU MB WH	-	-
01546661	ST700T LED20 930PC PSU NB 1C WH	Not applicable	No
01546761	ST700T LED20 930PC PSU MB 1C WH	Not applicable	No
01546861	ST700T LED20 930PC PSU WB 1C WH	Not applicable	No
01547061	ST700T LED20 930PC PSU MB 1C BK	Not applicable	No
01547261	ST700T LED30 930PC PSU MB 1C WH	Not applicable	No
01547361	ST700T LED30 930PC PSU WB 1C WH	Not applicable	No
01547461	ST700T LED30 930PC PSU MB 1C BK	Not applicable	No
01547661	ST700T LED40 930PC PSU MB 1C WH	Not applicable	No
01547761	ST700T LED40 930PC PSU WB 1C WH	Not applicable	No
01547861	ST700T LED40 930PC PSU MB 1C BK	Not applicable	No
01548161	ST700T LED20 930PC PSU MB 1C BK HB	Not applicable	No
01561761	ST700T LED10 830 PSU WB 1C WH	Not applicable	No
01561961	ST700T LED10 830 PSU WB 1C BK	Not applicable	No
01562161	ST700T LED20 830 PSU WB 1C WH	Not applicable	No
52111700	GD700B 2XLED10 830 PSU MB WH	-	-
01518971	GD700B 2XLED20 930PW PSU MB WH	-	-
51947300	GD700B 2XLED10 830 PSU MB BK	-	-

