



# Truefashion GCGM, ST700T, Elegant outlook design, quality of light with dedicated light recipe, system connectivity with Dali-VLC.

## Truefashion Projector GCGM

Truefashion Projector is targeting to approach mid-high end retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, in order to create comfortable ambience and impressive shopping experience to stimulate the store sales for retail customers.

### Benefits

- Slim and compact outlook design with inside track driver
- Excellent light quality of punch effect
- Dedicated light recipe for fashion and food
- System connectivity with Dali-VLC

# Truefashion Projector GCGM

## Features

- Lumen packages (1000/2000/3000/4000lm)
- 3 beams options (NB/MB/WB)
- Dali-VLC Control
- Track version available in 1C, 3C
- CB, EMC, CCC, ACC
- Lifetime 50K Hrs

## Application

- Retail fashion store
- Shopping mall
- Food & large retail

## Warnings and Safety

- 3 years

## Versions



Truefashion projector GCGM



ST700T

Application Conditions	
Ambient temperature range	-20 to +35 °C
Approval and Application	
Ingress protection code	IP20
Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Voltage	220 to 240 V
General Information	
CE mark	CE mark
Protection class IEC	Safety class II
Initial Performance (IEC Compliant)	
Init. Corr. Color Temperature	3000 K
Luminous flux tolerance	+/-10%

## Application Conditions

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401546661	ST700T LED20 930PC PSU NB 1C WH	Not applicable	No
911401546761	ST700T LED20 930PC PSU MB 1C WH	Not applicable	No
911401546861	ST700T LED20 930PC PSU WB 1C WH	Not applicable	No
911401546961	ST700T LED20 930PC PSU NB 1C BK	Not applicable	No
911401547061	ST700T LED20 930PC PSU MB 1C BK	Not applicable	No
911401547161	ST700T LED20 930PC PSU WB 1C BK	Not applicable	No
911401547261	ST700T LED30 930PC PSU MB 1C WH	Not applicable	No
911401547361	ST700T LED30 930PC PSU WB 1C WH	Not applicable	No
911401547461	ST700T LED30 930PC PSU MB 1C BK	Not applicable	No
911401547561	ST700T LED30 930PC PSU WB 1C BK	Not applicable	No
911401547661	ST700T LED40 930PC PSU MB 1C WH	Not applicable	No
911401547761	ST700T LED40 930PC PSU WB 1C WH	Not applicable	No
911401547861	ST700T LED40 930PC PSU MB 1C BK	Not applicable	No
911401547961	ST700T LED40 930PC PSU WB 1C BK	Not applicable	No
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	Not applicable	No
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	Not applicable	No
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	Not applicable	No
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	Not applicable	No

Order Code	Full Product Name	Maximum dim level	Suitable for random switching
911401561661	ST700T LED10 830 PSU MB 1C WH	Not applicable	No
911401561761	ST700T LED10 830 PSU WB 1C WH	Not applicable	No
911401561861	ST700T LED10 830 PSU MB 1C BK	Not applicable	No
911401561961	ST700T LED10 830 PSU WB 1C BK	Not applicable	No
911401562061	ST700T LED20 830 PSU NB 1C WH	Not applicable	No
911401562161	ST700T LED20 830 PSU WB 1C WH	Not applicable	No
911401562261	ST700T LED20 830 PSU NB 1C BK	Not applicable	No
911401562361	ST700T LED20 830 PSU WB 1C BK	Not applicable	No
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	-

## Approval and Application

Order Code	Full Product Name	Mech. impact protection code
911401546661	ST700T LED20 930PC PSU NB 1C WH	-
911401546761	ST700T LED20 930PC PSU MB 1C WH	-
911401546861	ST700T LED20 930PC PSU WB 1C WH	-
911401546961	ST700T LED20 930PC PSU NB 1C BK	-
911401547061	ST700T LED20 930PC PSU MB 1C BK	-
911401547161	ST700T LED20 930PC PSU WB 1C BK	-
911401547261	ST700T LED30 930PC PSU MB 1C WH	-
911401547361	ST700T LED30 930PC PSU WB 1C WH	-
911401547461	ST700T LED30 930PC PSU MB 1C BK	-
911401547561	ST700T LED30 930PC PSU WB 1C BK	-
911401547661	ST700T LED40 930PC PSU MB 1C WH	-
911401547761	ST700T LED40 930PC PSU WB 1C WH	-
911401547861	ST700T LED40 930PC PSU MB 1C BK	-
911401547961	ST700T LED40 930PC PSU WB 1C BK	-
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	-
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	-
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	-

Order Code	Full Product Name	Mech. impact protection code
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	-
911401561661	ST700T LED10 830 PSU MB 1C WH	-
911401561761	ST700T LED10 830 PSU WB 1C WH	-
911401561861	ST700T LED10 830 PSU MB 1C BK	-
911401561961	ST700T LED10 830 PSU WB 1C BK	-
911401562061	ST700T LED20 830 PSU NB 1C WH	-
911401562161	ST700T LED20 830 PSU WB 1C WH	-
911401562261	ST700T LED20 830 PSU NB 1C BK	-
911401562361	ST700T LED20 830 PSU WB 1C BK	-
911401575561	ST700T LED30 930PW PSU MB 3C BK	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-

## General Information (1/2)

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Driver included	ENEC mark
911401546661	ST700T LED20 930PC PSU NB 1C WH	120 °	-	Yes	-
911401546761	ST700T LED20 930PC PSU MB 1C WH	120 °	-	Yes	-
911401546861	ST700T LED20 930PC PSU WB 1C WH	120 °	-	Yes	-

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Driver included	ENEC mark
911401546961	ST700T LED20 930PC PSU NB 1C BK	120 °	-	Yes	-
911401547061	ST700T LED20 930PC PSU MB 1C BK	120 °	-	Yes	-
911401547161	ST700T LED20 930PC PSU WB 1C BK	120 °	-	Yes	-

## Truefashion Projector GCGM

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Driver included	ENEC mark
911401547261	ST700T LED30 930PC PSU MB 1C WH	120 °	-	Yes	-
911401547361	ST700T LED30 930PC PSU WB 1C WH	120 °	-	Yes	-
911401547461	ST700T LED30 930PC PSU MB 1C BK	120 °	-	Yes	-
911401547561	ST700T LED30 930PC PSU WB 1C BK	120 °	-	Yes	-
911401547661	ST700T LED40 930PC PSU MB 1C WH	120 °	-	Yes	-
911401547761	ST700T LED40 930PC PSU WB 1C WH	120 °	-	Yes	-
911401547861	ST700T LED40 930PC PSU MB 1C BK	120 °	-	Yes	-
911401547961	ST700T LED40 930PC PSU WB 1C BK	120 °	-	Yes	-
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	120 °	-	Yes	-
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	120 °	-	Yes	-
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	120 °	-	Yes	-
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	120 °	-	Yes	-
911401561661	ST700T LED10 830 PSU MB 1C WH	120 °	-	Yes	-
911401561761	ST700T LED10 830 PSU WB 1C WH	120 °	-	Yes	-
911401561861	ST700T LED10 830 PSU MB 1C BK	120 °	-	Yes	-
911401561961	ST700T LED10 830 PSU WB 1C BK	120 °	-	Yes	-
911401562061	ST700T LED20 830 PSU NB 1C WH	120 °	-	Yes	-
911401562161	ST700T LED20 830 PSU WB 1C WH	120 °	-	Yes	-

Order Code	Full Product Name	Beam angle of light source	Optical cover/lens type	Driver included	ENEC mark
911401562261	ST700T LED20 830 PSU NB 1C BK	120 °	-	Yes	-
911401562361	ST700T LED20 830 PSU WB 1C BK	120 °	-	Yes	-
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	Fashion proof optic beam angle 24°	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	Fashion proof optic beam angle 36°	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	Fashion proof optic beam angle 24°	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	Fashion proof optic beam angle 36°	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	Fashion proof optic beam angle 24°	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	Fashion proof optic beam angle 36°	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	Fashion proof optic beam angle 24°	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	Fashion proof optic beam angle 36°	-	-

### General Information (2/2)

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401546661	ST700T LED20 930PC PSU NB 1C WH	No	1 unit	Beam angle 15°
911401546761	ST700T LED20 930PC PSU MB 1C WH	No	1 unit	Beam angle 24°
911401546861	ST700T LED20 930PC PSU WB 1C WH	No	1 unit	Beam angle 30°
911401546961	ST700T LED20 930PC PSU NB 1C BK	No	1 unit	Beam angle 15°

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401547061	ST700T LED20 930PC PSU MB 1C BK	No	1 unit	Beam angle 24°
911401547161	ST700T LED20 930PC PSU WB 1C BK	No	1 unit	Beam angle 30°
911401547261	ST700T LED30 930PC PSU MB 1C WH	No	1 unit	Beam angle 23°
911401547361	ST700T LED30 930PC PSU WB 1C WH	No	1 unit	Beam angle 33°

# Truefashion Projector GCGM

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401547461	ST700T LED30 930PC PSU MB 1C BK	No	1 unit	Beam angle 23°
911401547561	ST700T LED30 930PC PSU WB 1C BK	No	1 unit	Beam angle 33°
911401547661	ST700T LED40 930PC PSU MB 1C WH	No	1 unit	Beam angle 24°
911401547761	ST700T LED40 930PC PSU WB 1C WH	No	1 unit	Beam angle 34°
911401547861	ST700T LED40 930PC PSU MB 1C BK	No	1 unit	Beam angle 24°
911401547961	ST700T LED40 930PC PSU WB 1C BK	No	1 unit	Beam angle 34°
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	No	1 unit	Beam angle 21°
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	No	1 unit	Beam angle 21°
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	No	1 unit	Beam angle 24°
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	No	1 unit	Beam angle 24°
911401561661	ST700T LED10 830 PSU MB 1C WH	No	1 unit	Beam angle 24°
911401561761	ST700T LED10 830 PSU WB 1C WH	No	1 unit	Beam angle 30°
911401561861	ST700T LED10 830 PSU MB 1C BK	No	1 unit	Beam angle 24°

Order Code	Full Product Name	Light source replaceable	Number of gear units	Optic type
911401561961	ST700T LED10 830 PSU WB 1C BK	No	1 unit	Beam angle 30°
911401562061	ST700T LED20 830 PSU NB 1C WH	No	1 unit	Beam angle 15°
911401562161	ST700T LED20 830 PSU WB 1C WH	No	1 unit	Beam angle 30°
911401562261	ST700T LED20 830 PSU NB 1C BK	No	1 unit	Beam angle 15°
911401562361	ST700T LED20 830 PSU WB 1C BK	No	1 unit	Beam angle 30°
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	-	-

## Initial Performance (IEC Compliant) (1/2)

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering		Initial LED luminaire efficacy	Initial luminous flux
			Index	Initial LED luminaire efficacy		
911401546661	ST700T LED20 930PC PSU NB 1C WH	(0.422, 0.386)	>90	72.1 lm/W	1604.8 lm	
911401546761	ST700T LED20 930PC PSU MB 1C WH	(0.422, 0.386)	>90	72.1 lm/W	1604.8 lm	
911401546861	ST700T LED20 930PC PSU WB 1C WH	(0.422, 0.386)	>90	67.9 lm/W	1510.4 lm	
911401546961	ST700T LED20 930PC	(0.422, 0.386)	>90	72.1 lm/W	1604.8 lm	

Order Code	Full Product Name	Initial chromaticity	Init. Color Rendering		Initial LED luminaire efficacy	Initial luminous flux
			Index	Initial LED luminaire efficacy		
911401547061	ST700T LED20 930PC PSU MB 1C BK	(0.422, 0.386)	>90	72.1 lm/W	1604.8 lm	
911401547161	ST700T LED20 930PC PSU WB 1C BK	(0.422, 0.386)	>90	67.9 lm/W	1510.4 lm	
911401547261	ST700T LED30 930PC PSU MB 1C WH	(0.422, 0.386)	>90	70.5 lm/W	2684.72 lm	

## Truefashion Projector GCGM

Order Code	Full Product		Init. Color		Initial luminous flux
	Name	Initial chromaticity	Rendering Index	Initial LED luminaire efficacy	
911401547361	ST700T LED30 930PC PSU WB 1C WH	(0.422, 0.386)	>90	67.6 lm/W	2575.9 lm
911401547461	ST700T LED30 930PC PSU MB 1C BK	(0.422, 0.386)	>90	70.5 lm/W	2684.72 lm
911401547561	ST700T LED30 930PC PSU WB 1C BK	(0.422, 0.386)	>90	67.6 lm/W	2575.88 lm
911401547661	ST700T LED40 930PC PSU MB 1C WH	(0.422, 0.386)	>90	75.3 lm/W	3299.16 lm
911401547761	ST700T LED40 930PC PSU WB 1C WH	(0.422, 0.386)	>90	71.4 lm/W	3125.52 lm
911401547861	ST700T LED40 930PC PSU MB 1C BK	(0.422, 0.386)	>90	75.3 lm/W	3299.16 lm
911401547961	ST700T LED40 930PC PSU WB 1C BK	(0.422, 0.386)	>90	71.4 lm/W	3125.52 lm
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	(0.422, 0.386)	>90	46.7 lm/W	1038.4 lm
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	(0.422, 0.386)	>90	46.7 lm/W	1038.4 lm
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	(0.422, 0.386)	>80	44.6 lm/W	1953.45 lm

Order Code	Full Product		Init. Color		Initial luminous flux
	Name	Initial chromaticity	Rendering Index	Initial LED luminaire efficacy	
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	(0.422, 0.386)	>80	44.6 lm/W	1953.45 lm
911401561661	ST700T LED10 830 PSU MB 1C WH	(0.434, 0.403)	>80	107.3 lm/W	1146.65 lm
911401561761	ST700T LED10 830 PSU WB 1C WH	(0.434, 0.403)	>80	101 lm/W	1079.2 lm
911401561861	ST700T LED10 830 PSU MB 1C BK	(0.434, 0.403)	>80	107.3 lm/W	1146.65 lm
911401561961	ST700T LED10 830 PSU WB 1C BK	(0.434, 0.403)	>80	101 lm/W	1079.2 lm
911401562061	ST700T LED20 830 PSU NB 1C WH	(0.434, 0.403)	>80	92.2 lm/W	2051.05 lm
911401562161	ST700T LED20 830 PSU WB 1C WH	(0.434, 0.403)	>80	86.7 lm/W	1930.4 lm
911401562261	ST700T LED20 830 PSU NB 1C BK	(0.434, 0.403)	>80	92.2 lm/W	2051.05 lm
911401562361	ST700T LED20 830 PSU WB 1C BK	(0.434, 0.403)	>80	86.7 lm/W	1930.4 lm
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	>90	85.40831032215648 lm/W	3168.44 lm
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	>90	80.91313609467456 lm/W	3001.68 lm
911401575761	ST700T LED30 930PW	-	>90	85.40831032215648 lm/W	3168.44 lm

# Truefashion Projector GCGM

Order Code	Full Product		Init. Color		Initial luminous flux
	Name	Initial chromaticity	Rendering Index	Initial LED luminaire efficacy	
911401575861	PSU MB 3C WH				
	ST700T	-	>90	80.91313609467456	3001.68
	LED30			lm/W	lm
	930PW				
911401575961	PSU WB 3C WH				
	ST700T	-	>90	90.61613412228797	3168.44
	LED30			lm/W	lm
	930PW				
911401576061	PSD VLC MB BK				
	ST700T	-	>90	85.84686390532543	3001.68
	LED30			lm/W	lm
	930PW				
	PSD VLC WB BK				
	ST700T	-	>90		
	LED30				
	930PW				

Order Code	Full Product		Init. Color		Initial luminous flux
	Name	Initial chromaticity	Rendering Index	Initial LED luminaire efficacy	
911401576161	ST700T	-	>90	90.61613412228797	3168.44
	LED30			lm/W	lm
	930PW				
	PSD VLC MB WH				
911401576261	ST700T	-	>90	85.84686390532543	3001.68
	LED30			lm/W	lm
	930PW				
	PSD VLC WB WH				

## Initial Performance (IEC Compliant) (2/2)

Order Code	Full Product Name	Initial input power
911401546661	ST700T LED20 930PC PSU NB 1C WH	22.3 W
911401546761	ST700T LED20 930PC PSU MB 1C WH	22.3 W
911401546861	ST700T LED20 930PC PSU WB 1C WH	22.3 W
911401546961	ST700T LED20 930PC PSU NB 1C BK	22.3 W
911401547061	ST700T LED20 930PC PSU MB 1C BK	22.3 W
911401547161	ST700T LED20 930PC PSU WB 1C BK	22.3 W
911401547261	ST700T LED30 930PC PSU MB 1C WH	38.1 W
911401547361	ST700T LED30 930PC PSU WB 1C WH	38.1 W
911401547461	ST700T LED30 930PC PSU MB 1C BK	38.1 W
911401547561	ST700T LED30 930PC PSU WB 1C BK	38.1 W
911401547661	ST700T LED40 930PC PSU MB 1C WH	43.8 W
911401547761	ST700T LED40 930PC PSU WB 1C WH	43.8 W
911401547861	ST700T LED40 930PC PSU MB 1C BK	43.8 W
911401547961	ST700T LED40 930PC PSU WB 1C BK	43.8 W
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	22.3 W
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	22.3 W
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	43.8 W

Order Code	Full Product Name	Initial input power
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	43.8 W
911401561661	ST700T LED10 830 PSU MB 1C WH	10.7 W
911401561761	ST700T LED10 830 PSU WB 1C WH	10.7 W
911401561861	ST700T LED10 830 PSU MB 1C BK	10.7 W
911401561961	ST700T LED10 830 PSU WB 1C BK	10.7 W
911401562061	ST700T LED20 830 PSU NB 1C WH	22.3 W
911401562161	ST700T LED20 830 PSU WB 1C WH	22.3 W
911401562261	ST700T LED20 830 PSU NB 1C BK	22.3 W
911401562361	ST700T LED20 830 PSU WB 1C BK	22.3 W
911401575561	ST700T LED30 930PW PSU MB 3C BK	37.1 W
911401575661	ST700T LED30 930PW PSU WB 3C BK	37.1 W
911401575761	ST700T LED30 930PW PSU MB 3C WH	37.1 W
911401575861	ST700T LED30 930PW PSU WB 3C WH	37.1 W
911401575961	ST700T LED30 930PW PSD VLC MB BK	35 W
911401576061	ST700T LED30 930PW PSD VLC WB BK	35 W
911401576161	ST700T LED30 930PW PSD VLC MB WH	35 W
911401576261	ST700T LED30 930PW PSD VLC WB WH	35 W

## Mechanical and Housing

Order Code	Full Product Name	Color
911401546661	ST700T LED20 930PC PSU NB 1C WH	-
911401546761	ST700T LED20 930PC PSU MB 1C WH	-
911401546861	ST700T LED20 930PC PSU WB 1C WH	-
911401546961	ST700T LED20 930PC PSU NB 1C BK	-
911401547061	ST700T LED20 930PC PSU MB 1C BK	-
911401547161	ST700T LED20 930PC PSU WB 1C BK	-
911401547261	ST700T LED30 930PC PSU MB 1C WH	-

Order Code	Full Product Name	Color
911401547361	ST700T LED30 930PC PSU WB 1C WH	-
911401547461	ST700T LED30 930PC PSU MB 1C BK	-
911401547561	ST700T LED30 930PC PSU WB 1C BK	-
911401547661	ST700T LED40 930PC PSU MB 1C WH	-
911401547761	ST700T LED40 930PC PSU WB 1C WH	-
911401547861	ST700T LED40 930PC PSU MB 1C BK	-
911401547961	ST700T LED40 930PC PSU WB 1C BK	-

## Truefashion Projector GCGM

Order Code	Full Product Name	Color
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	-
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	-
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	-
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	-
911401561661	ST700T LED10 830 PSU MB 1C WH	-
911401561761	ST700T LED10 830 PSU WB 1C WH	-
911401561861	ST700T LED10 830 PSU MB 1C BK	-
911401561961	ST700T LED10 830 PSU WB 1C BK	-
911401562061	ST700T LED20 830 PSU NB 1C WH	-
911401562161	ST700T LED20 830 PSU WB 1C WH	-

Order Code	Full Product Name	Color
911401562261	ST700T LED20 830 PSU NB 1C BK	-
911401562361	ST700T LED20 830 PSU WB 1C BK	-
911401575561	ST700T LED30 930PW PSU MB 3C BK	White and black
911401575661	ST700T LED30 930PW PSU WB 3C BK	White and black
911401575761	ST700T LED30 930PW PSU MB 3C WH	White and black
911401575861	ST700T LED30 930PW PSU WB 3C WH	White and black
911401575961	ST700T LED30 930PW PSD VLC MB BK	White and black
911401576061	ST700T LED30 930PW PSD VLC WB BK	White and black
911401576161	ST700T LED30 930PW PSD VLC MB WH	White and black
911401576261	ST700T LED30 930PW PSD VLC WB WH	White and black

### Over Time Performance (IEC Compliant)

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401546661	ST700T LED20 930PC PSU NB 1C WH	50000 h	32600 h
911401546761	ST700T LED20 930PC PSU MB 1C WH	50000 h	32600 h
911401546861	ST700T LED20 930PC PSU WB 1C WH	50000 h	32600 h
911401546961	ST700T LED20 930PC PSU NB 1C BK	50000 h	32600 h
911401547061	ST700T LED20 930PC PSU MB 1C BK	50000 h	32600 h
911401547161	ST700T LED20 930PC PSU WB 1C BK	50000 h	32600 h
911401547261	ST700T LED30 930PC PSU MB 1C WH	45000 h	21200 h
911401547361	ST700T LED30 930PC PSU WB 1C WH	45000 h	21200 h
911401547461	ST700T LED30 930PC PSU MB 1C BK	45000 h	21200 h
911401547561	ST700T LED30 930PC PSU WB 1C BK	45000 h	21200 h
911401547661	ST700T LED40 930PC PSU MB 1C WH	38700 h	18200 h
911401547761	ST700T LED40 930PC PSU WB 1C WH	38700 h	18200 h
911401547861	ST700T LED40 930PC PSU MB 1C BK	38700 h	18200 h
911401547961	ST700T LED40 930PC PSU WB 1C BK	38700 h	18200 h
911401548061	ST700T LED20 930PC PSU MB 1C WH HB	50000 h	32600 h
911401548161	ST700T LED20 930PC PSU MB 1C BK HB	50000 h	32600 h
911401548261	ST700T LED40 930PC PSU MB 1C WH HB	38700 h	18200 h

Order Code	Full Product Name	Median useful life L80B50	Median useful life L90B50
911401548361	ST700T LED40 930PC PSU MB 1C BK HB	38700 h	18200 h
911401561661	ST700T LED10 830 PSU MB 1C WH	50000 h	32600 h
911401561761	ST700T LED10 830 PSU WB 1C WH	50000 h	32600 h
911401561861	ST700T LED10 830 PSU MB 1C BK	50000 h	32600 h
911401561961	ST700T LED10 830 PSU WB 1C BK	50000 h	32600 h
911401562061	ST700T LED20 830 PSU NB 1C WH	50000 h	32600 h
911401562161	ST700T LED20 830 PSU WB 1C WH	50000 h	32600 h
911401562261	ST700T LED20 830 PSU NB 1C BK	50000 h	32600 h
911401562361	ST700T LED20 830 PSU WB 1C BK	50000 h	32600 h
911401575561	ST700T LED30 930PW PSU MB 3C BK	-	-
911401575661	ST700T LED30 930PW PSU WB 3C BK	-	-
911401575761	ST700T LED30 930PW PSU MB 3C WH	-	-
911401575861	ST700T LED30 930PW PSU WB 3C WH	-	-
911401575961	ST700T LED30 930PW PSD VLC MB BK	-	-
911401576061	ST700T LED30 930PW PSD VLC WB BK	-	-
911401576161	ST700T LED30 930PW PSD VLC MB WH	-	-
911401576261	ST700T LED30 930PW PSD VLC WB WH	-	-



# Truefashion Projector GCGM

