



A simple LED for everyday use

Ecohome

EcoHome LEDbulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize initial investment

Benefits

- Up to 90% energy saving compared with traditional incandescent lamps
- Lower maintenance costs
- Low initial investment

Features

- Easy retrofit with existing E27
- Long lifetime
- Non-Dimmable
- UV- and IR-free light

Application

- Domestic applications

Versions





E27 A60 FR



E27 A60 FR

Dimensional drawing



Product	D	C
EcoHome LEDBulb 7W E27 6500KHV 1CT/48AR	60 mm	108 mm
EcoHome LEDBulb 10W E27 6500KHV 1CT/48AR	60 mm	108 mm
EcoHome LEDBulb 7W E27 3000KHV 1CT/48AR	60 mm	108 mm
EcoHome LEDBulb 10W E27 3000KHV 1CT/48AR	60 mm	108 mm

Product	D	C
EcoHome LEDBulb 12W E27 3000KHV 1CT/48AR	60 mm	108 mm
EcoHome LEDBulb 12W E27 6500KHV 1CT/48AR	60 mm	108 mm

Controls and Dimming	
Dimmable	No
Operating and Electrical	
Input Frequency	50 to 60 Hz
Voltage (Nom)	220-240 V
Starting Time (Nom)	0.5 s
General Information	
Cap-Base	E27
Nominal Lifetime (Nom)	10000 h
Switching Cycle	50000X
Light Technical	
Beam Angle (Nom)	130 °
Color Rendering Index (Nom)	70
Llmf At End Of Nominal Lifetime (Nom)	70 %
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	A60

Operating and Electrical

Order Code	Full Product Name	Wattage Equivalent	Power (Rated) (Nom)
929001954811	EcoHome LEDBulb 10W E27 6500KHV 1CT/48AR	65 W	10 W
929001955111	EcoHome LEDBulb 7W E27 3000KHV 1CT/48AR	50 W	7 W
929001955211	EcoHome LEDBulb 7W E27 6500KHV 1CT/48AR	50 W	7 W
929001955311	EcoHome LEDBulb 10W E27 3000KHV 1CT/48AR	65 W	10 W
929001954911	EcoHome LEDBulb 12W E27 3000KHV 1CT/48AR	80 W	12 W
929001955011	EcoHome LEDBulb 12W E27 6500KHV 1CT/48AR	80 W	12 W

Light Technical

Order Code	Full Product Name	Color Code	Correlated Color	
			Temperature (Nom)	Luminous Flux (Nom)
929001954811	EcoHome LEDBulb 10W E27 6500KHV 1CT/48AR	765	6500 K	750 lm
929001955111	EcoHome LEDBulb 7W E27 3000KHV 1CT/48AR	730	3000 K	480 lm
929001955211	EcoHome LEDBulb 7W E27 6500KHV 1CT/48AR	765	6500 K	500 lm

Order Code	Full Product Name	Color Code	Correlated Color	
			Temperature (Nom)	Luminous Flux (Nom)
929001955311	EcoHome LEDBulb 10W E27 3000KHV 1CT/48AR	730	3000 K	710 lm
929001954911	EcoHome LEDBulb 12W E27 3000KHV 1CT/48AR	730	3000 K	900 lm
929001955011	EcoHome LEDBulb 12W E27 6500KHV 1CT/48AR	765	6500 K	950 lm

Temperature

Order Code	Full Product Name	T-Case Maximum (Nom)
929001954811	EcoHome LEDBulb 10W E27 6500KHV 1CT/48AR	78 °C
929001955111	EcoHome LEDBulb 7W E27 3000KHV 1CT/48AR	75 °C
929001955211	EcoHome LEDBulb 7W E27 6500KHV 1CT/48AR	75 °C
929001955311	EcoHome LEDBulb 10W E27 3000KHV 1CT/48AR	78 °C
929001954911	EcoHome LEDBulb 12W E27 3000KHV 1CT/48AR	75 °C

Order Code	Full Product Name	T-Case Maximum (Nom)
929001955011	EcoHome LEDBulb 12W E27 6500KHV 1CT/48AR	75 °C

