



Smartbright Waterproof Batten G3 provide flexibility to customer to choose from 3 sizes, standard and through wiring version and 2 CCTs to cater to different customer needs

Smartbright Waterproof G3 WT068C

Philips Smartbright Waterproof G3 batten offers exceptional value. It is Perfect for everyday lighting installations. Available in 3 standard sizes, it has option of Standard and through wiring version.

Benefits

- Lifetime: 30,000 hrs @ L70B50, 3 Years warranty
- IP66, IK06
- Quick connector for easy installation

Smartbright Waterproof G3 WT068C

Features


- 2 colour temperatures, 3 sizes and Standard and through wiring version
- IP66/IK06 – Water and dustproof. For all weather
- Reliable with a long service life of 30 000 hours L70
- 3 years warranty
- Quick connector for easy installation

Application


- Parking Garages
- Offices

Dimensional drawing

WT068C TW-4ft



WT068C-4ft



Smartbright Waterproof G3 WT068C

General Information	
CE mark	CE mark
Light Technical	
Optical cover/lens type	-
Color rendering index (CRI)	>80
Luminous Efficacy (rated) (Nom)	110 lm/W
Luminous Flux	3,600 lumen
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	33 W
Temperature	
Ambient temperature range	-20 to +45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing Color	White and gray
Approval and Application	
Protection class IEC	Safety class II
Mech. impact protection code	IK06
Ingress protection code	IP66
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%

Order Code	Full Product Name	Correlated Color Temperature (Nom)
911401881480	WT068C CW LED36 L1200 PSU	6500 K
911401881780	WT068C NW LED36 L1200 PSU	4000 K
911401882080	WT068C CW LED36 L1200 PSU TW1	6500 K

